

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584132

Luminaire Tested: **HCC8W25D010MB-HM82555830-81WWWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584132
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W25D010MB-HM82555830-81WWWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2283.3 lumens
Efficiency: N/A
Efficacy: 85.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584132
CATALOG NUMBER: HCC8W25D010MB-HM82555830-81WWWB

Luminous Intensity Polar Plot





TEST NUMBER: P584132

CATALOG NUMBER: HCC8W25D010MB-HM82555830-81WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75								
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65								
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57								
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50								
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45								
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40								
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37								
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33								
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	35008	35008	35008
5°	36291	34891	33694
10°	37318	34590	32317
15°	38149	33977	30890
20°	38207	32651	29636
25°	37478	30836	28587
30°	35543	28592	27332
35°	32295	26046	26106
40°	28238	23371	24603
45°	24473	20815	22925
50°	21429	18489	20887
55°	19075	16381	18903
60°	17200	14721	16608
65°	15527	12944	14476
70°	13957	10900	10756
75°	12307	8638	8066
80°	10317	7156	7725
85°	7996	6298	6864



TEST NUMBER: P584132
 CATALOG NUMBER: HCC8W25D010MB-HM82555830-81WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.1	4.7
10°-20°	301.7	13.2
20°-30°	431.1	18.9
30°-40°	458.1	20.1
40°-50°	394.4	17.3
50°-60°	294.9	12.9
60°-70°	188.1	8.2
70°-80°	85.6	3.7
80°-90°	22.4	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	839.9	36.8
0°-40°	1297.9	56.8
0°-60°	1987.2	87.0
0°-90°	2283.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2283.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1135	1135	1135	1135	1135	
5°	1172	1156	1127	1098	1088	112
15°	1195	1155	1064	992	968	337
25°	1102	1032	906	852	840	504
35°	858	798	692	674	694	534
45°	561	530	477	490	526	436
55°	355	326	305	331	352	319
65°	213	189	177	185	198	212
75°	103	89	72	66	68	110
85°	23	19	18	19	19	27
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584132

CATALOG NUMBER: HCC8W25D010MB-HM82555830-81WWWB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1135.3	1135.3	1135.3	1135.3	1135.3	1135.3	1135.3	1135.3	1135.3	1135.3	1135.3
2.5°	1156.2	1153.0	1154.6	1153.0	1154.6	1154.6	1151.4	1151.4	1151.4	1151.4	1146.6
5°	1172.4	1170.8	1170.8	1169.2	1167.5	1169.2	1167.5	1165.9	1162.7	1161.1	1156.2
7.5°	1182.0	1182.0	1182.0	1182.0	1180.4	1178.8	1177.2	1174.0	1170.8	1167.5	1164.3
10°	1191.8	1193.4	1191.8	1190.1	1188.4	1185.2	1183.6	1180.4	1175.6	1170.8	1167.5
12.5°	1196.6	1196.6	1195.0	1195.0	1191.8	1190.1	1185.2	1180.4	1175.6	1170.8	1162.7
15°	1195.0	1195.0	1193.4	1191.8	1186.8	1185.2	1182.0	1177.2	1169.2	1162.7	1154.6
17.5°	1185.2	1183.6	1180.4	1180.4	1174.0	1172.4	1169.2	1162.7	1154.6	1144.9	1135.3
20°	1164.3	1164.3	1162.7	1161.1	1154.6	1149.8	1146.6	1138.5	1132.1	1120.7	1111.1
22.5°	1135.3	1138.5	1135.3	1132.1	1124.0	1122.3	1117.5	1107.9	1098.1	1085.3	1074.0
25°	1101.5	1099.9	1098.1	1094.9	1088.5	1085.3	1078.9	1069.1	1059.5	1045.0	1032.1
27.5°	1057.9	1051.4	1051.4	1045.0	1040.1	1035.3	1032.1	1022.4	1009.5	998.2	982.0
30°	998.2	999.8	991.8	990.2	982.0	978.8	972.4	962.7	951.4	938.5	925.7
32.5°	933.7	928.9	928.9	922.4	915.9	911.1	909.5	898.3	888.5	875.7	862.7
35°	857.9	857.9	853.1	851.5	845.0	841.8	837.0	830.5	819.2	808.0	798.2
37.5°	783.8	780.5	778.9	775.6	770.8	766.0	766.0	754.7	753.1	740.2	727.3
40°	701.5	704.7	701.5	696.7	695.1	691.9	690.2	683.7	678.9	667.6	659.5
42.5°	632.2	628.9	628.9	627.3	620.8	620.8	617.6	614.4	606.4	603.2	593.4
45°	561.2	564.4	559.6	561.2	554.7	554.7	554.7	548.3	541.8	537.0	530.5
47.5°	499.9	501.5	501.5	496.7	495.1	495.1	491.9	488.7	483.7	477.3	472.5
50°	446.7	448.3	445.1	443.5	440.2	438.6	438.6	432.2	429.0	422.5	419.2
52.5°	398.4	398.4	396.6	396.6	391.8	391.8	388.6	383.8	380.6	377.4	369.3
55°	354.8	354.8	353.2	351.6	351.6	346.7	345.1	340.3	337.0	330.6	325.7
57.5°	312.9	314.5	312.9	311.3	309.7	308.1	304.7	299.9	296.7	291.9	288.7
60°	278.9	278.9	277.3	275.7	272.5	270.9	269.3	266.1	261.3	258.0	253.2
62.5°	246.7	245.1	243.5	241.9	238.7	238.7	235.4	232.2	227.4	224.2	221.0
65°	212.8	212.8	211.2	211.2	209.6	206.4	204.8	203.2	196.8	195.2	188.6
67.5°	182.2	183.8	180.6	180.6	177.4	177.4	175.8	171.0	169.3	166.1	162.9
70°	154.8	154.8	154.8	153.2	150.0	148.4	146.7	143.5	141.9	138.7	135.5
72.5°	127.4	127.4	125.8	125.8	124.1	122.5	120.9	117.7	117.7	114.5	111.3
75°	103.3	103.3	101.5	99.9	98.3	98.3	96.7	95.1	91.9	90.3	88.7
77.5°	79.0	79.0	79.0	77.4	75.8	75.8	75.8	72.5	69.3	69.3	67.7
80°	58.1	58.1	56.4	56.4	54.8	54.8	54.8	53.2	51.6	50.0	48.4
82.5°	38.7	38.7	38.7	38.7	37.1	37.1	37.1	35.5	33.8	33.8	33.8
85°	22.6	22.6	22.6	22.6	21.0	21.0	21.0	21.0	21.0	19.4	19.4
87.5°	9.6	8.0	9.6	8.0	9.6	8.0	9.6	8.0	8.0	8.0	8.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584132

CATALOG NUMBER: HCC8W25D010MB-HM82555830-81WWWB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1135.3	1135.3	1135.3	1135.3	1135.3	1135.3	1135.3	1135.3	1135.3	1135.3	1135.3
2.5°	1148.2	1146.6	1144.9	1143.3	1143.3	1141.7	1138.5	1136.9	1135.3	1133.7	1133.7
5°	1154.6	1153.0	1149.8	1146.6	1144.9	1141.7	1138.5	1135.3	1132.1	1127.2	1125.6
7.5°	1159.5	1154.6	1151.4	1144.9	1143.3	1140.1	1135.3	1130.5	1124.0	1117.5	1112.7
10°	1159.5	1153.0	1148.2	1140.1	1136.9	1133.7	1127.2	1119.1	1111.1	1104.7	1096.5
12.5°	1156.2	1148.2	1140.1	1132.1	1127.2	1122.3	1112.7	1104.7	1094.9	1085.3	1078.9
15°	1144.9	1135.3	1125.6	1115.9	1111.1	1104.7	1094.9	1083.7	1074.0	1064.3	1053.0
17.5°	1124.0	1114.3	1103.1	1091.7	1085.3	1080.5	1065.9	1057.9	1043.4	1033.7	1024.0
20°	1096.5	1085.3	1070.7	1059.5	1051.4	1046.6	1035.3	1020.8	1009.5	995.0	985.3
22.5°	1061.1	1046.6	1032.1	1020.8	1012.8	1006.2	991.8	977.2	967.6	954.7	943.4
25°	1019.2	1004.6	990.2	974.0	966.0	959.5	946.6	933.7	920.8	906.3	896.7
27.5°	969.2	953.0	940.1	925.7	917.5	907.9	893.3	880.5	867.6	857.9	845.0
30°	914.3	896.7	883.7	869.2	861.1	853.1	838.6	825.6	814.4	803.0	796.6
32.5°	848.2	835.3	822.4	808.0	801.4	796.6	782.1	769.2	756.3	746.6	741.8
35°	785.4	770.8	759.5	746.6	738.6	733.7	720.9	709.5	703.1	691.9	685.3
37.5°	719.3	707.9	695.1	682.1	677.3	672.5	662.8	651.5	641.8	633.8	630.6
40°	649.9	640.2	628.9	620.8	616.0	611.2	603.2	595.0	588.6	580.6	577.3
42.5°	583.8	577.3	567.6	558.0	553.1	551.5	541.8	535.4	532.1	528.9	525.7
45°	524.1	514.5	507.9	501.5	496.7	493.5	488.7	483.7	480.5	477.3	474.1
47.5°	466.1	458.0	451.5	446.7	441.8	440.2	437.0	432.2	429.0	429.0	429.0
50°	412.8	406.4	400.0	396.6	395.0	391.8	388.6	387.0	385.4	385.4	385.4
52.5°	366.0	359.6	354.8	351.6	351.6	348.3	345.1	343.5	343.5	343.5	343.5
55°	322.5	317.7	314.5	311.3	308.1	306.4	306.4	306.4	304.7	304.7	306.4
57.5°	283.9	280.6	275.7	272.5	270.9	270.9	269.3	267.7	269.3	270.9	272.5
60°	248.3	245.1	243.5	238.7	238.7	238.7	237.0	237.0	237.0	238.7	240.3
62.5°	216.1	214.4	211.2	209.6	208.0	208.0	206.4	206.4	206.4	206.4	208.0
65°	187.0	183.8	180.6	180.6	180.6	179.0	179.0	175.8	177.4	177.4	175.8
67.5°	159.6	156.4	154.8	153.2	151.6	151.6	150.0	148.4	146.7	146.7	146.7
70°	133.9	130.6	130.6	127.4	127.4	125.8	124.1	124.1	122.5	120.9	119.3
72.5°	108.1	106.5	104.9	103.3	103.3	103.3	101.5	99.9	98.3	96.7	93.5
75°	85.5	85.5	82.3	80.7	80.7	79.0	77.4	75.8	74.2	72.5	70.9
77.5°	66.1	64.5	61.3	59.7	59.7	59.7	58.1	56.4	54.8	53.2	51.6
80°	48.4	46.8	45.2	43.5	43.5	43.5	41.9	41.9	40.3	40.3	40.3
82.5°	32.2	32.2	30.6	30.6	30.6	30.6	29.0	29.0	29.0	29.0	29.0
85°	19.4	19.4	17.8	17.8	17.8	17.8	17.8	17.8	17.8	17.8	17.8
87.5°	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584132

CATALOG NUMBER: HCC8W25D010MB-HM82555830-81WWWB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1135.3	1135.3	1135.3	1135.3	1135.3	1135.3	1135.3	1135.3	1135.3	1135.3	1135.3
2.5°	1130.5	1130.5	1127.2	1125.6	1124.0	1125.6	1122.3	1120.7	1119.1	1119.1	1117.5
5°	1120.7	1119.1	1112.7	1111.1	1109.5	1107.9	1104.7	1101.5	1098.1	1096.5	1094.9
7.5°	1107.9	1103.1	1096.5	1094.9	1093.3	1088.5	1083.7	1080.5	1075.6	1074.0	1070.7
10°	1090.1	1083.7	1078.9	1074.0	1070.7	1065.9	1061.1	1056.3	1049.8	1048.2	1043.4
12.5°	1069.1	1061.1	1051.4	1049.8	1045.0	1038.5	1032.1	1027.2	1022.4	1019.2	1014.4
15°	1043.4	1035.3	1025.6	1020.8	1016.0	1011.2	1003.0	996.6	991.8	987.0	982.0
17.5°	1012.8	1003.0	995.0	990.2	987.0	978.8	972.4	964.4	959.5	954.7	949.8
20°	975.6	967.6	956.3	951.4	949.8	943.4	935.3	932.1	925.7	920.8	917.5
22.5°	933.7	925.7	915.9	912.7	906.3	903.1	894.9	891.7	888.5	883.7	882.1
25°	886.9	878.9	870.8	869.2	864.3	861.1	856.3	851.5	851.5	846.6	846.6
27.5°	838.6	830.5	824.0	820.8	819.2	816.0	811.2	809.6	808.0	806.4	806.4
30°	787.0	777.2	774.0	772.4	770.8	767.6	766.0	762.8	764.4	766.0	764.4
32.5°	732.1	728.9	722.5	719.3	720.9	719.3	716.0	719.3	717.6	720.9	722.5
35°	678.9	675.7	672.5	672.5	669.3	669.3	669.3	670.9	674.1	675.7	678.9
37.5°	627.3	622.4	620.8	619.2	620.8	620.8	620.8	624.1	627.3	630.6	635.4
40°	572.4	569.2	569.2	569.2	569.2	574.1	572.4	575.7	579.0	583.8	588.6
42.5°	520.9	520.9	522.5	522.5	522.5	522.5	525.7	530.5	535.4	540.2	545.1
45°	472.5	472.5	472.5	475.7	475.7	477.3	483.7	487.0	490.3	495.1	499.9
47.5°	427.4	427.4	429.0	430.6	432.2	435.4	438.6	443.5	448.3	451.5	456.4
50°	385.4	387.0	390.2	393.4	393.4	395.0	400.0	403.2	406.4	411.2	412.8
52.5°	345.1	348.3	351.6	353.2	354.8	358.0	359.6	364.4	366.0	370.9	372.5
55°	308.1	309.7	314.5	316.1	316.1	319.3	322.5	325.7	330.6	330.6	333.8
57.5°	274.1	275.7	278.9	280.6	278.9	283.9	285.5	288.7	290.3	293.5	295.1
60°	240.3	243.5	245.1	245.1	246.7	248.3	251.6	251.6	254.8	258.0	258.0
62.5°	208.0	209.6	211.2	212.8	214.4	212.8	217.7	217.7	221.0	222.6	225.8
65°	177.4	179.0	179.0	180.6	180.6	182.2	182.2	183.8	185.4	188.6	190.2
67.5°	146.7	146.7	146.7	148.4	146.7	148.4	148.4	150.0	150.0	153.2	154.8
70°	119.3	117.7	116.1	116.1	116.1	116.1	114.5	116.1	116.1	117.7	117.7
72.5°	91.9	90.3	88.7	87.1	87.1	85.5	83.9	85.5	85.5	87.1	87.1
75°	69.3	66.1	66.1	66.1	64.5	64.5	64.5	66.1	66.1	66.1	67.7
77.5°	51.6	51.6	50.0	50.0	50.0	51.6	51.6	53.2	53.2	53.2	53.2
80°	38.7	40.3	40.3	40.3	40.3	41.9	41.9	41.9	41.9	43.5	43.5
82.5°	29.0	29.0	29.0	29.0	30.6	30.6	30.6	30.6	30.6	30.6	30.6
85°	17.8	19.4	19.4	17.8	19.4	19.4	19.4	19.4	19.4	19.4	19.4
87.5°	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584132

CATALOG NUMBER: HCC8W25D010MB-HM82555830-81WWWB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1135.3	1135.3	1135.3	1135.3	1135.3	1135.3	1135.3	1135.3
2.5°	1115.9	1115.9	1115.9	1115.9	1114.3	1114.3	1114.3	1112.7
5°	1091.7	1091.7	1091.7	1088.5	1090.1	1090.1	1086.9	1088.5
7.5°	1067.5	1065.9	1064.3	1064.3	1062.7	1061.1	1059.5	1061.1
10°	1040.1	1035.3	1035.3	1033.7	1033.7	1030.4	1030.4	1032.1
12.5°	1009.5	1006.2	1006.2	1004.6	1003.0	1001.4	999.8	999.8
15°	978.8	975.6	974.0	972.4	970.8	967.6	969.2	967.6
17.5°	948.2	943.4	943.4	941.8	940.1	936.9	936.9	935.3
20°	912.7	911.1	907.9	909.5	907.9	904.7	903.1	903.1
22.5°	877.3	877.3	875.7	875.7	874.1	872.4	870.8	870.8
25°	843.4	841.8	843.4	843.4	838.6	838.6	838.6	840.2
27.5°	804.6	806.4	804.6	804.6	804.6	804.6	806.4	804.6
30°	766.0	766.0	766.0	767.6	770.8	769.2	769.2	767.6
32.5°	724.1	725.7	725.7	727.3	728.9	732.1	732.1	733.7
35°	682.1	685.3	686.9	685.3	690.2	690.2	693.5	693.5
37.5°	638.6	640.2	643.4	645.0	648.3	649.9	651.5	651.5
40°	591.8	598.2	599.8	601.6	606.4	606.4	608.0	611.2
42.5°	548.3	554.7	556.4	558.0	561.2	566.0	564.4	567.6
45°	506.3	511.2	512.9	514.5	519.3	520.9	520.9	525.7
47.5°	461.2	464.4	466.1	469.3	472.5	475.7	478.9	477.3
50°	416.0	420.9	424.1	425.8	430.6	432.2	433.8	435.4
52.5°	375.8	379.0	380.6	382.2	387.0	388.6	390.2	393.4
55°	337.0	338.7	341.9	340.3	345.1	346.7	348.3	351.6
57.5°	298.3	299.9	301.5	301.5	304.7	308.1	309.7	311.3
60°	261.3	264.5	266.1	266.1	266.1	269.3	269.3	269.3
62.5°	227.4	227.4	229.0	229.0	232.2	232.2	232.2	232.2
65°	191.9	193.6	195.2	195.2	198.4	196.8	200.0	198.4
67.5°	154.8	154.8	158.0	158.0	156.4	158.0	158.0	158.0
70°	117.7	117.7	119.3	119.3	119.3	119.3	119.3	119.3
72.5°	87.1	87.1	87.1	88.7	87.1	87.1	88.7	87.1
75°	67.7	67.7	67.7	67.7	67.7	67.7	67.7	67.7
77.5°	53.2	53.2	54.8	54.8	54.8	54.8	54.8	54.8
80°	43.5	43.5	43.5	43.5	45.2	43.5	43.5	43.5
82.5°	32.2	30.6	32.2	30.6	32.2	32.2	32.2	32.2
85°	19.4	19.4	19.4	19.4	19.4	19.4	19.4	19.4
87.5°	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)