

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584140

Luminaire Tested: **HCC8S25D010SL-HM82555835-81RWWC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584140
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S25D010SL-HM82555835-81RWWC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2434.0 lumens
Efficiency: N/A
Efficacy: 90.8 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.08 / 1.17
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584140
CATALOG NUMBER: HCC8S25D010SL-HM82555835-81RWWC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584140

CATALOG NUMBER: HCC8S25D010SL-HM82555835-81RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	84	82	79	77								
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67								
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	69	65	61	59								
5	81	70	62	56	80	69	62	56	67	61	56	65	59	55	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	39492	39492	39492
5°	40014	39324	38953
10°	40424	38924	38335
15°	40831	38101	37335
20°	40625	36697	35854
25°	39676	34497	34031
30°	37686	32025	31904
35°	34305	29223	29479
40°	30078	26153	27119
45°	25947	23265	24905
50°	22720	20427	22562
55°	20134	17558	19859
60°	18138	14764	16454
65°	16344	11850	12601
70°	14335	8637	6933
75°	12224	4492	1835
80°	9412	1208	302
85°	6050	0	0



TEST NUMBER: P584140
 CATALOG NUMBER: HCC8S25D010SL-HM82555835-81RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.8	5.0
10°-20°	339.7	14.0
20°-30°	482.1	19.8
30°-40°	507.5	20.9
40°-50°	431.7	17.7
50°-60°	312.0	12.8
60°-70°	177.5	7.3
70°-80°	55.9	2.3
80°-90°	6.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	942.6	38.7
0°-40°	1450.1	59.6
0°-60°	2193.9	90.1
0°-90°	2434.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2434.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1281	1281	1281	1281	1281	
5°	1293	1286	1270	1262	1258	123
15°	1279	1246	1194	1171	1170	360
25°	1166	1108	1014	997	1000	534
35°	911	858	776	771	783	567
45°	595	573	534	547	571	463
55°	374	347	327	345	369	338
65°	224	193	162	161	173	222
75°	103	79	38	17	15	110
85°	17	10	0	0	0	22
90°	0	0	0	0	0	



TEST NUMBER: P584140

CATALOG NUMBER: HCC8S25D010SL-HM82555835-81RWWC

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1280.7	1280.7	1280.7	1280.7	1280.7	1280.7	1280.7	1280.7	1280.7	1280.7	1280.7
2.5°	1287.5	1289.2	1285.8	1285.8	1289.2	1285.8	1287.5	1287.5	1285.8	1285.8	1284.1
5°	1292.7	1291.0	1291.0	1291.0	1292.7	1289.2	1287.5	1289.2	1285.8	1285.8	1285.8
7.5°	1294.4	1294.4	1292.7	1291.0	1291.0	1291.0	1289.2	1287.5	1285.8	1282.4	1280.7
10°	1291.0	1291.0	1292.7	1289.2	1289.2	1285.8	1285.8	1282.4	1282.4	1279.0	1273.8
12.5°	1287.5	1285.8	1285.8	1282.4	1282.4	1279.0	1279.0	1273.8	1272.1	1267.0	1261.9
15°	1279.0	1277.3	1273.8	1272.1	1270.4	1268.7	1265.3	1263.6	1258.4	1251.6	1246.4
17.5°	1261.9	1260.1	1258.4	1255.0	1251.6	1249.9	1248.2	1243.1	1236.3	1231.1	1222.6
20°	1238.0	1236.3	1236.3	1231.1	1229.4	1224.3	1222.6	1215.7	1210.6	1200.3	1193.5
22.5°	1205.5	1207.2	1203.8	1200.3	1196.9	1191.8	1188.3	1181.5	1172.9	1162.7	1154.2
25°	1166.1	1167.8	1164.4	1161.0	1155.9	1152.5	1149.1	1138.8	1130.2	1118.3	1108.0
27.5°	1116.5	1116.5	1116.5	1113.1	1104.6	1102.8	1099.4	1089.2	1077.2	1067.0	1056.7
30°	1058.4	1056.7	1056.7	1051.6	1048.2	1041.3	1036.2	1027.6	1019.1	1007.1	995.1
32.5°	988.3	990.0	984.9	981.5	976.4	976.4	969.5	962.7	952.4	940.4	928.4
35°	911.3	913.0	909.6	907.9	899.4	897.7	896.0	887.5	880.6	872.0	858.4
37.5°	832.7	831.0	829.2	829.2	824.1	820.7	817.3	812.2	802.0	795.1	788.3
40°	747.2	747.2	747.2	745.5	743.8	740.3	738.6	735.2	728.5	721.6	716.5
42.5°	670.2	670.2	668.5	666.8	663.4	665.1	661.7	658.3	651.4	646.3	643.0
45°	595.0	595.0	595.0	596.7	593.3	588.2	588.2	584.8	581.3	577.9	572.8
47.5°	528.4	533.5	530.1	528.4	530.1	523.2	523.2	519.8	516.4	513.0	506.1
50°	473.6	473.6	473.6	470.3	468.6	468.6	463.4	460.0	458.3	454.9	448.0
52.5°	424.0	420.6	420.6	418.9	417.2	413.8	413.8	410.3	403.5	400.1	394.9
55°	374.5	374.5	372.8	371.1	369.4	367.7	365.9	360.8	357.4	352.2	347.1
57.5°	330.0	333.4	331.7	328.3	324.9	324.9	321.4	318.0	312.9	307.7	302.6
60°	294.1	292.4	292.4	290.7	287.3	285.6	283.9	278.7	273.6	268.5	263.3
62.5°	256.5	256.5	256.5	253.1	249.6	247.9	246.2	242.8	235.9	230.8	227.4
65°	224.0	222.2	220.5	218.8	217.1	213.8	212.1	208.6	203.5	198.4	193.2
67.5°	191.5	189.8	189.8	188.1	183.0	181.3	181.3	176.1	171.0	165.9	160.7
70°	159.0	159.0	159.0	155.6	153.9	152.2	150.4	147.0	141.9	136.7	131.6
72.5°	131.6	129.9	129.9	128.3	123.2	121.4	119.7	116.3	111.2	107.7	104.3
75°	102.6	102.6	100.9	99.2	97.5	95.8	94.1	90.6	85.5	80.4	78.6
77.5°	78.6	76.9	76.9	75.2	71.8	70.1	70.1	66.7	61.5	58.1	54.7
80°	53.0	54.7	53.0	51.3	49.5	47.8	46.1	44.4	41.1	37.7	34.2
82.5°	32.5	34.2	32.5	32.5	30.8	29.1	29.1	25.7	24.0	22.3	20.5
85°	17.1	17.1	17.1	17.1	15.4	15.4	15.4	13.7	12.0	10.3	10.3
87.5°	5.1	6.8	5.1	5.1	5.1	5.1	5.1	5.1	3.4	3.4	3.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584140

CATALOG NUMBER: HCC8S25D010SL-HM82555835-81RWWC

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1280.7	1280.7	1280.7	1280.7	1280.7	1280.7	1280.7	1280.7	1280.7	1280.7	1280.7
2.5°	1285.8	1284.1	1282.4	1282.4	1282.4	1282.4	1282.4	1280.7	1279.0	1279.0	1279.0
5°	1282.4	1282.4	1282.4	1280.7	1279.0	1279.0	1275.5	1273.8	1272.1	1270.4	1268.7
7.5°	1279.0	1275.5	1273.8	1272.1	1270.4	1270.4	1267.0	1263.6	1263.6	1260.1	1256.7
10°	1268.7	1267.0	1263.6	1260.1	1258.4	1256.7	1253.3	1248.2	1246.4	1243.1	1239.7
12.5°	1256.7	1253.3	1249.9	1243.1	1241.4	1239.7	1232.9	1227.7	1224.3	1222.6	1214.0
15°	1241.4	1234.6	1229.4	1220.9	1219.2	1215.7	1210.6	1205.5	1198.6	1193.5	1190.1
17.5°	1214.0	1207.2	1198.6	1190.1	1186.6	1186.6	1178.1	1171.2	1162.7	1159.2	1152.5
20°	1181.5	1172.9	1166.1	1155.9	1150.8	1145.6	1140.5	1130.2	1123.4	1118.3	1109.7
22.5°	1143.9	1132.0	1123.4	1113.1	1104.6	1099.4	1090.9	1082.3	1073.7	1068.7	1061.9
25°	1096.0	1085.7	1072.1	1061.9	1056.7	1049.9	1039.6	1031.1	1022.5	1013.9	1010.5
27.5°	1043.0	1029.3	1017.4	1005.4	1000.2	995.1	983.2	973.0	966.1	957.5	954.1
30°	984.9	971.2	957.5	947.3	942.1	933.6	926.7	914.7	906.2	899.4	890.9
32.5°	918.2	907.9	896.0	880.6	877.2	870.3	860.1	854.9	844.7	839.5	832.7
35°	846.4	839.5	827.5	815.6	810.5	807.1	798.5	788.3	781.4	776.3	772.9
37.5°	778.0	769.4	757.5	748.9	745.5	740.3	730.1	725.0	718.2	714.8	707.9
40°	704.5	695.9	687.4	682.2	677.1	673.7	666.8	661.7	654.8	649.7	648.0
42.5°	632.7	627.6	620.7	613.9	612.1	607.0	603.6	598.5	593.3	591.6	586.5
45°	567.6	562.5	555.8	548.9	547.2	543.8	542.1	536.9	533.5	533.5	533.5
47.5°	502.7	497.6	490.7	487.3	489.0	482.1	482.1	480.4	477.0	477.0	478.7
50°	444.6	437.7	436.0	432.6	429.2	425.8	427.5	422.3	422.3	425.8	424.0
52.5°	389.8	383.1	381.3	377.9	376.2	376.2	374.5	374.5	372.8	374.5	374.5
55°	340.3	335.1	331.7	328.3	326.6	326.6	326.6	324.9	323.1	326.6	328.3
57.5°	295.9	294.1	290.7	285.6	283.9	282.2	280.4	280.4	280.4	280.4	282.2
60°	256.5	253.1	249.6	244.5	244.5	242.8	241.1	239.4	239.4	239.4	239.4
62.5°	222.2	217.1	212.1	208.6	206.9	205.2	203.5	200.1	200.1	200.1	200.1
65°	188.1	183.0	179.5	176.1	172.7	172.7	169.3	167.6	164.1	162.4	159.0
67.5°	155.6	152.2	148.7	143.6	141.9	140.2	136.7	135.0	129.9	128.3	126.6
70°	126.6	121.4	118.0	114.6	112.9	109.5	106.0	102.6	99.2	95.8	92.3
72.5°	99.2	94.1	90.6	87.2	83.8	83.8	78.6	75.2	70.1	66.7	61.5
75°	73.5	68.4	64.9	59.8	58.1	56.4	51.3	47.8	42.8	37.7	34.2
77.5°	49.5	46.1	42.8	37.7	34.2	34.2	29.1	25.7	22.3	17.1	15.4
80°	30.8	27.4	24.0	20.5	20.5	17.1	15.4	12.0	8.6	6.8	5.1
82.5°	17.1	15.4	13.7	10.3	10.3	8.6	6.8	5.1	3.4	1.7	1.7
85°	8.6	6.8	5.1	5.1	3.4	3.4	3.4	1.7	1.7	0.0	0.0
87.5°	3.4	1.7	1.7	1.7	1.7	1.7	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584140

CATALOG NUMBER: HCC8S25D010SL-HM82555835-81RWWC

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1280.7	1280.7	1280.7	1280.7	1280.7	1280.7	1280.7	1280.7	1280.7	1280.7	1280.7
2.5°	1277.3	1277.3	1275.5	1275.5	1275.5	1273.8	1275.5	1273.8	1273.8	1273.8	1275.5
5°	1270.4	1267.0	1267.0	1265.3	1265.3	1263.6	1265.3	1263.6	1261.9	1260.1	1261.9
7.5°	1256.7	1253.3	1251.6	1249.9	1249.9	1249.9	1248.2	1246.4	1248.2	1243.1	1246.4
10°	1238.0	1236.3	1232.9	1231.1	1229.4	1231.1	1229.4	1226.0	1226.0	1226.0	1224.3
12.5°	1214.0	1210.6	1208.9	1207.2	1203.8	1203.8	1205.5	1202.0	1202.0	1198.6	1198.6
15°	1184.9	1181.5	1178.1	1178.1	1174.6	1174.6	1172.9	1172.9	1171.2	1169.5	1169.5
17.5°	1149.1	1143.9	1140.5	1142.2	1140.5	1138.8	1138.8	1135.4	1133.7	1135.4	1135.4
20°	1106.3	1102.8	1099.4	1101.1	1097.7	1096.0	1097.7	1092.6	1094.3	1094.3	1094.3
22.5°	1058.4	1056.7	1051.6	1051.6	1048.2	1046.5	1048.2	1048.2	1049.9	1048.2	1048.2
25°	1005.4	1001.9	998.5	998.5	996.8	995.1	996.8	998.5	996.8	998.5	998.5
27.5°	949.0	943.8	943.8	940.4	940.4	942.1	940.4	942.1	943.8	943.8	947.3
30°	887.5	885.7	884.0	882.3	882.3	884.0	884.0	884.0	885.7	889.2	889.2
32.5°	829.2	825.8	822.4	822.4	825.8	824.1	825.8	825.8	829.2	829.2	832.7
35°	766.0	766.0	762.6	764.3	764.3	764.3	764.3	767.7	771.1	772.9	776.3
37.5°	707.9	702.8	704.5	704.5	706.2	704.5	709.6	709.6	713.0	713.0	716.5
40°	644.6	644.6	646.3	644.6	646.3	646.3	649.7	653.1	654.8	658.3	660.0
42.5°	584.8	588.2	584.8	586.5	588.2	589.9	591.6	593.3	600.2	603.6	608.7
45°	530.1	531.8	533.5	535.2	533.5	536.9	538.6	542.1	547.2	548.9	550.6
47.5°	477.0	478.7	480.4	482.1	482.1	485.6	487.3	490.7	494.1	495.8	497.6
50°	425.8	429.2	430.9	430.9	432.6	436.0	439.4	439.4	442.9	448.0	449.7
52.5°	379.6	379.6	383.1	384.8	386.4	386.4	391.5	393.2	394.9	398.4	401.8
55°	328.3	333.4	335.1	335.1	338.5	342.0	343.7	345.4	345.4	352.2	352.2
57.5°	283.9	285.6	289.0	289.0	289.0	294.1	294.1	297.6	299.3	300.9	304.3
60°	239.4	242.8	242.8	244.5	242.8	246.2	247.9	251.3	253.1	254.8	256.5
62.5°	198.4	198.4	200.1	200.1	200.1	200.1	203.5	203.5	206.9	208.6	210.4
65°	159.0	159.0	159.0	159.0	159.0	159.0	159.0	159.0	160.7	160.7	164.1
67.5°	123.2	121.4	118.0	119.7	118.0	118.0	116.3	116.3	118.0	118.0	121.4
70°	88.9	87.2	83.8	83.8	82.1	80.4	78.6	76.9	75.2	75.2	75.2
72.5°	58.1	54.7	49.5	47.8	47.8	44.4	41.1	39.4	39.4	39.4	39.4
75°	29.1	25.7	22.3	20.5	20.5	17.1	18.8	17.1	17.1	17.1	17.1
77.5°	12.0	8.6	6.8	6.8	6.8	5.1	5.1	5.1	5.1	5.1	5.1
80°	3.4	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
82.5°	1.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584140

CATALOG NUMBER: HCC8S25D010SL-HM82555835-81RWWC

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1280.7	1280.7	1280.7	1280.7	1280.7	1280.7	1280.7	1280.7
2.5°	1273.8	1273.8	1270.4	1272.1	1272.1	1272.1	1272.1	1272.1
5°	1258.4	1260.1	1258.4	1260.1	1260.1	1258.4	1258.4	1258.4
7.5°	1243.1	1244.7	1243.1	1244.7	1244.7	1244.7	1243.1	1243.1
10°	1224.3	1224.3	1224.3	1224.3	1224.3	1222.6	1224.3	1224.3
12.5°	1198.6	1198.6	1198.6	1200.3	1200.3	1198.6	1198.6	1196.9
15°	1171.2	1167.8	1169.5	1171.2	1169.5	1169.5	1169.5	1169.5
17.5°	1133.7	1135.4	1133.7	1133.7	1133.7	1133.7	1135.4	1133.7
20°	1094.3	1094.3	1096.0	1094.3	1094.3	1094.3	1094.3	1092.6
22.5°	1049.9	1048.2	1048.2	1049.9	1049.9	1048.2	1049.9	1049.9
25°	1000.2	1001.9	1000.2	1000.2	1001.9	1001.9	1001.9	1000.2
27.5°	947.3	949.0	950.7	949.0	949.0	949.0	950.7	952.4
30°	892.6	896.0	892.6	892.6	896.0	894.3	896.0	896.0
32.5°	834.4	839.5	836.1	839.5	839.5	841.2	839.5	841.2
35°	776.3	781.4	781.4	781.4	783.1	784.8	784.8	783.1
37.5°	721.6	723.3	723.3	726.7	728.5	730.1	730.1	728.5
40°	665.1	668.5	670.2	670.2	670.2	673.7	677.1	673.7
42.5°	610.4	612.1	613.9	613.9	617.3	619.0	620.7	620.7
45°	557.5	560.8	562.5	564.2	565.9	569.3	567.6	571.1
47.5°	502.7	507.8	509.5	511.2	514.7	516.4	518.1	519.8
50°	453.1	456.6	456.6	460.0	465.1	465.1	468.6	470.3
52.5°	403.5	405.2	406.9	408.6	412.1	415.5	415.5	418.9
55°	355.7	357.4	357.4	359.1	360.8	367.7	369.4	369.4
57.5°	306.0	306.0	309.4	311.2	312.9	316.3	316.3	316.3
60°	258.2	259.9	259.9	261.6	263.3	266.8	268.5	266.8
62.5°	210.4	212.1	212.1	213.8	217.1	218.8	217.1	217.1
65°	165.9	167.6	167.6	169.3	172.7	172.7	171.0	172.7
67.5°	121.4	121.4	121.4	121.4	121.4	121.4	121.4	121.4
70°	76.9	75.2	73.5	75.2	75.2	75.2	73.5	76.9
72.5°	37.7	39.4	39.4	39.4	39.4	39.4	39.4	37.7
75°	17.1	17.1	15.4	15.4	15.4	17.1	17.1	15.4
77.5°	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1
80°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)