

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584148

Luminaire Tested: **HCC8W25D010BZ-HM82555835-81WWW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584148
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W25D010BZ-HM82555835-81WWW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2324.7 lumens
Efficiency: N/A
Efficacy: 86.7 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584148
CATALOG NUMBER: HCC8W25D010BZ-HM82555835-81WWW

Luminous Intensity Polar Plot





TEST NUMBER: P584148

CATALOG NUMBER: HCC8W25D010BZ-HM82555835-81WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76								
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66								
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58								
5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51								
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	38841	38841	38841
5°	40206	38618	37086
10°	41100	37944	34997
15°	41683	36665	32684
20°	41561	34883	30341
25°	40530	32622	27856
30°	38402	30002	25562
35°	34934	27153	23226
40°	30686	24144	20984
45°	26754	21242	18708
50°	23286	18613	16483
55°	20768	16354	14333
60°	18866	14333	12230
65°	16957	12470	11105
70°	15102	10630	10017
75°	13237	8960	8554
80°	11223	7281	7583
85°	8491	5449	6050



TEST NUMBER: P584148

CATALOG NUMBER: HCC8W25D010BZ-HM82555835-81WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.0	5.1
10°-20°	325.1	14.0
20°-30°	451.2	19.4
30°-40°	466.5	20.1
40°-50°	390.6	16.8
50°-60°	283.6	12.2
60°-70°	179.0	7.7
70°-80°	88.6	3.8
80°-90°	22.0	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	894.3	38.5
0°-40°	1360.8	58.5
0°-60°	2035.0	87.5
0°-90°	2324.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2324.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1260	1260	1260	1260	1260	
5°	1299	1284	1248	1214	1198	124
15°	1306	1256	1148	1056	1024	367
25°	1191	1114	959	854	819	546
35°	928	860	721	639	617	578
45°	614	569	487	439	429	475
55°	386	352	304	279	267	349
65°	232	203	171	150	152	232
75°	111	92	75	72	72	119
85°	24	19	15	17	17	29
90°	0	0	0	0	0	



TEST NUMBER: P584148

CATALOG NUMBER: HCC8W25D010BZ-HM82555835-81WWW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1259.6	1259.6	1259.6	1259.6	1259.6	1259.6	1259.6	1259.6	1259.6	1259.6	1259.6
2.5°	1280.1	1280.1	1281.9	1280.1	1280.1	1280.1	1278.4	1278.4	1276.7	1276.7	1273.3
5°	1298.9	1295.4	1298.9	1295.4	1295.4	1295.4	1293.7	1290.3	1288.6	1285.3	1283.6
7.5°	1307.4	1305.7	1305.7	1304.0	1304.0	1302.3	1300.6	1298.9	1292.0	1290.3	1285.3
10°	1312.6	1310.9	1310.9	1309.1	1305.7	1305.7	1302.3	1300.6	1292.0	1288.6	1281.9
12.5°	1310.9	1310.9	1310.9	1309.1	1304.0	1302.3	1298.9	1293.7	1287.0	1280.1	1273.3
15°	1305.7	1305.7	1302.3	1300.6	1295.4	1292.0	1290.3	1281.9	1275.0	1266.5	1256.2
17.5°	1288.6	1288.6	1287.0	1283.6	1278.4	1275.0	1271.6	1263.0	1256.2	1242.5	1232.2
20°	1266.5	1264.7	1263.0	1257.9	1252.8	1251.0	1245.9	1233.9	1225.5	1215.2	1201.5
22.5°	1233.9	1232.2	1230.5	1227.1	1218.6	1215.2	1211.8	1203.2	1187.8	1177.5	1160.5
25°	1191.2	1191.2	1187.8	1182.7	1174.1	1170.7	1165.6	1157.1	1143.4	1128.0	1114.3
27.5°	1141.7	1140.0	1134.8	1131.4	1124.6	1119.4	1110.9	1100.6	1087.0	1075.0	1057.9
30°	1078.5	1078.5	1075.0	1069.9	1061.3	1057.9	1051.1	1039.1	1025.5	1010.1	998.1
32.5°	1006.7	1006.7	1001.5	998.1	993.0	984.4	982.7	969.1	957.1	945.1	931.4
35°	928.0	929.7	926.3	919.5	911.0	911.0	907.6	895.6	881.9	869.9	859.6
37.5°	849.4	844.3	842.6	839.2	834.1	827.2	823.8	818.7	806.7	798.1	782.8
40°	762.3	764.0	760.6	757.1	755.4	750.3	748.6	740.0	731.5	721.3	714.4
42.5°	683.6	683.6	683.6	680.2	676.8	671.6	669.9	664.8	654.6	647.8	637.5
45°	613.5	608.4	608.4	606.7	605.0	601.6	596.5	593.1	586.3	581.1	569.1
47.5°	545.2	546.9	545.2	543.5	538.3	536.6	534.9	528.2	521.3	516.2	507.6
50°	485.4	488.8	485.4	485.4	481.9	480.2	476.8	471.7	466.6	458.1	449.5
52.5°	435.8	435.8	434.1	432.4	427.3	423.8	422.1	420.4	411.8	405.1	398.3
55°	386.3	388.0	388.0	382.8	381.1	377.7	376.0	370.9	367.4	357.2	352.0
57.5°	343.6	341.9	343.6	340.2	336.7	333.3	331.6	328.2	323.0	316.2	309.3
60°	305.9	302.5	302.5	300.8	297.4	295.6	292.2	287.1	282.1	275.2	270.1
62.5°	268.4	266.6	264.9	263.2	259.8	258.1	256.4	251.2	246.1	241.0	235.8
65°	232.4	232.4	230.7	227.3	225.6	223.8	222.1	218.8	212.0	208.5	203.4
67.5°	200.0	198.3	198.3	194.8	191.4	189.7	189.7	186.3	181.2	176.0	172.6
70°	167.5	169.2	167.5	165.7	162.3	162.3	158.9	157.2	150.4	148.7	143.6
72.5°	138.5	138.5	136.7	136.7	133.3	131.6	131.6	128.2	124.8	121.3	117.9
75°	111.1	111.1	111.1	109.4	107.6	104.2	104.2	102.5	99.1	95.7	92.3
77.5°	87.2	85.5	85.5	83.8	82.1	80.4	80.4	78.6	75.2	73.5	70.1
80°	63.2	61.5	61.5	61.5	58.1	59.8	58.1	56.4	54.7	53.0	51.3
82.5°	41.0	42.7	42.7	41.0	39.3	39.3	39.3	37.6	37.6	35.8	34.1
85°	24.0	24.0	24.0	24.0	22.3	22.3	22.3	20.5	20.5	20.5	18.8
87.5°	10.3	10.3	10.3	10.3	10.3	10.3	8.6	8.6	8.6	8.6	8.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584148

CATALOG NUMBER: HCC8W25D010BZ-HM82555835-81WWW

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1259.6	1259.6	1259.6	1259.6	1259.6	1259.6	1259.6	1259.6	1259.6	1259.6	1259.6
2.5°	1273.3	1269.9	1268.2	1266.5	1266.5	1264.7	1263.0	1259.6	1259.6	1256.2	1254.5
5°	1280.1	1275.0	1271.6	1268.2	1266.5	1263.0	1259.6	1254.5	1252.8	1247.6	1242.5
7.5°	1281.9	1273.3	1269.9	1263.0	1259.6	1256.2	1249.3	1244.2	1237.3	1232.2	1225.5
10°	1275.0	1268.2	1259.6	1251.0	1249.3	1244.2	1233.9	1227.1	1218.6	1211.8	1201.5
12.5°	1264.7	1254.5	1245.9	1235.6	1230.5	1225.5	1215.2	1204.9	1192.9	1181.0	1170.7
15°	1247.6	1235.6	1223.8	1211.8	1204.9	1199.8	1187.8	1175.8	1163.8	1148.5	1138.3
17.5°	1222.0	1208.4	1196.4	1181.0	1174.1	1169.0	1153.7	1140.0	1124.6	1109.2	1099.0
20°	1189.5	1172.4	1158.8	1141.7	1136.6	1128.0	1112.6	1097.3	1080.2	1063.0	1051.1
22.5°	1146.8	1129.7	1114.3	1097.3	1088.7	1080.2	1064.8	1045.9	1028.9	1015.2	1003.2
25°	1097.3	1081.9	1063.0	1047.6	1037.4	1027.2	1010.1	994.7	979.3	958.8	946.8
27.5°	1042.5	1023.8	1010.1	989.5	979.3	972.5	953.7	933.1	919.5	900.7	887.0
30°	981.0	964.0	948.6	928.0	917.7	911.0	893.9	875.0	861.4	842.6	828.9
32.5°	916.0	897.3	878.5	864.8	852.8	846.0	827.2	815.2	798.1	782.8	767.4
35°	846.0	827.2	813.5	794.7	787.8	781.1	765.7	750.3	734.9	721.3	709.3
37.5°	770.8	757.1	741.7	728.0	722.9	716.2	697.3	683.6	671.6	658.1	647.8
40°	697.3	685.3	675.1	661.4	652.9	647.8	634.1	622.1	608.4	599.8	589.7
42.5°	630.7	617.0	606.7	596.5	588.0	582.8	570.8	562.3	552.0	543.5	531.6
45°	560.6	553.7	541.7	533.3	528.2	521.3	512.7	502.5	493.9	487.1	478.5
47.5°	499.0	492.2	483.6	473.4	470.1	464.9	456.4	449.5	442.7	435.8	427.3
50°	442.7	434.1	427.3	420.4	417.0	411.8	403.4	400.0	394.8	388.0	382.8
52.5°	391.4	384.6	377.7	369.2	367.4	364.0	358.9	352.0	346.9	343.6	340.2
55°	345.3	338.4	333.3	326.5	324.7	321.3	314.5	311.0	307.6	304.2	300.8
57.5°	304.2	297.4	290.5	287.1	283.7	280.3	278.6	273.5	270.1	268.4	264.9
60°	266.6	259.8	254.7	249.5	247.8	246.1	242.7	239.3	235.8	232.4	230.7
62.5°	230.7	223.8	220.4	217.1	213.7	213.7	210.3	206.8	203.4	201.7	198.3
65°	198.3	194.8	189.7	184.6	182.9	182.9	177.7	176.0	174.3	170.9	167.5
67.5°	167.5	164.0	158.9	157.2	155.6	153.9	152.2	148.7	145.3	143.6	140.2
70°	140.2	136.7	133.3	131.6	129.9	128.2	124.8	123.0	119.6	117.9	116.2
72.5°	112.8	111.1	107.6	105.9	104.2	102.5	100.8	99.1	95.7	94.1	92.3
75°	90.6	88.9	85.5	83.8	82.1	82.1	80.4	76.9	75.2	75.2	73.5
77.5°	68.4	66.7	64.9	63.2	61.5	61.5	59.8	58.1	56.4	56.4	54.7
80°	49.5	47.8	46.1	46.1	46.1	44.4	42.7	42.7	41.0	41.0	39.3
82.5°	32.4	32.4	30.8	30.8	30.8	29.1	29.1	27.4	27.4	27.4	27.4
85°	18.8	18.8	18.8	17.1	17.1	17.1	17.1	17.1	17.1	15.4	17.1
87.5°	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6	6.8	6.8	6.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584148

CATALOG NUMBER: HCC8W25D010BZ-HM82555835-81WWW

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1259.6	1259.6	1259.6	1259.6	1259.6	1259.6	1259.6	1259.6	1259.6	1259.6	1259.6
2.5°	1252.8	1251.0	1247.6	1247.6	1244.2	1244.2	1242.5	1240.8	1239.1	1237.3	1235.6
5°	1240.8	1233.9	1230.5	1228.8	1225.5	1223.8	1218.6	1215.2	1213.5	1210.1	1206.6
7.5°	1218.6	1211.8	1204.9	1203.2	1201.5	1194.7	1189.5	1184.4	1181.0	1177.5	1174.1
10°	1192.9	1186.1	1177.5	1174.1	1170.7	1162.2	1155.4	1150.2	1143.4	1136.6	1134.8
12.5°	1162.2	1152.0	1141.7	1138.3	1133.1	1124.6	1117.7	1109.2	1104.0	1095.6	1093.9
15°	1126.3	1114.3	1105.7	1097.3	1093.9	1085.3	1073.3	1066.5	1056.2	1052.8	1044.2
17.5°	1083.6	1071.6	1059.6	1056.2	1051.1	1039.1	1027.2	1018.6	1008.4	1003.2	998.1
20°	1039.1	1023.8	1011.8	1008.4	1001.5	991.2	979.3	970.8	962.3	952.0	946.8
22.5°	987.8	970.8	960.5	952.0	950.3	938.3	924.6	917.7	911.0	902.4	895.6
25°	931.4	916.0	904.2	897.3	893.9	883.6	873.3	864.8	854.5	849.4	840.9
27.5°	873.3	863.1	847.8	840.9	835.8	827.2	815.2	810.1	799.8	793.0	787.8
30°	816.9	801.5	793.0	784.5	779.4	770.8	760.6	755.4	746.9	740.0	734.9
32.5°	755.4	745.1	733.2	729.7	722.9	714.4	707.6	699.0	692.2	685.3	683.6
35°	699.0	685.3	673.4	669.9	664.8	656.3	652.9	647.8	639.2	637.5	630.7
37.5°	637.5	630.7	617.0	611.8	610.1	603.3	596.5	593.1	588.0	582.8	581.1
40°	579.4	570.8	564.0	558.9	555.4	550.3	543.5	541.7	538.3	531.6	529.9
42.5°	524.7	516.2	509.3	507.6	502.5	497.3	493.9	488.8	487.1	485.4	481.9
45°	471.7	466.6	459.8	458.1	456.4	449.5	446.1	442.7	439.2	437.5	434.1
47.5°	423.8	418.7	413.6	411.8	408.5	406.8	401.7	400.0	394.8	393.1	391.4
50°	377.7	374.3	370.9	369.2	365.7	364.0	360.6	357.2	353.7	352.0	350.3
52.5°	336.7	333.3	329.9	328.2	326.5	323.0	319.6	316.2	314.5	312.8	311.0
55°	297.4	293.9	292.2	290.5	288.8	287.1	282.1	280.3	278.6	276.9	273.5
57.5°	261.5	258.1	254.7	254.7	252.9	251.2	247.8	244.4	244.4	241.0	237.5
60°	229.0	225.6	222.1	220.4	218.8	215.4	213.7	212.0	210.3	208.5	205.1
62.5°	194.8	193.1	189.7	189.7	186.3	184.6	182.9	181.2	179.4	176.0	174.3
65°	165.7	164.0	160.6	158.9	158.9	157.2	153.9	152.2	150.4	150.4	148.7
67.5°	138.5	136.7	133.3	131.6	131.6	129.9	128.2	128.2	126.5	124.8	126.5
70°	114.5	111.1	111.1	109.4	109.4	107.6	105.9	105.9	105.9	107.6	107.6
72.5°	90.6	88.9	87.2	87.2	87.2	87.2	85.5	85.5	87.2	88.9	88.9
75°	71.8	70.1	70.1	70.1	68.4	68.4	70.1	70.1	71.8	71.8	71.8
77.5°	53.0	53.0	53.0	53.0	53.0	53.0	54.7	54.7	56.4	56.4	56.4
80°	39.3	39.3	39.3	39.3	39.3	41.0	41.0	41.0	41.0	41.0	42.7
82.5°	27.4	27.4	27.4	27.4	27.4	27.4	27.4	29.1	29.1	29.1	29.1
85°	15.4	17.1	17.1	17.1	17.1	17.1	17.1	17.1	17.1	17.1	17.1
87.5°	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584148

CATALOG NUMBER: HCC8W25D010BZ-HM82555835-81WWW

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1259.6	1259.6	1259.6	1259.6	1259.6	1259.6	1259.6	1259.6
2.5°	1233.9	1233.9	1233.9	1235.6	1232.2	1232.2	1232.2	1232.2
5°	1204.9	1203.2	1201.5	1203.2	1199.8	1199.8	1198.1	1198.1
7.5°	1169.0	1167.3	1165.6	1165.6	1162.2	1162.2	1160.5	1158.8
10°	1129.7	1126.3	1128.0	1124.6	1122.9	1121.1	1119.4	1117.7
12.5°	1087.0	1083.6	1081.9	1078.5	1075.0	1073.3	1075.0	1071.6
15°	1040.8	1035.8	1034.0	1030.6	1027.2	1025.5	1025.5	1023.8
17.5°	989.5	986.1	984.4	981.0	979.3	975.8	974.2	972.5
20°	941.7	933.1	934.9	931.4	929.7	922.9	922.9	924.6
22.5°	888.7	883.6	880.2	876.8	875.0	871.6	871.6	869.9
25°	835.8	830.6	828.9	825.5	823.8	820.4	818.7	818.7
27.5°	784.5	777.7	777.7	774.3	770.8	769.1	767.4	765.7
30°	729.7	724.6	722.9	722.9	721.3	721.3	716.2	717.9
32.5°	678.5	675.1	673.4	669.9	669.9	668.2	668.2	663.1
35°	627.2	622.1	623.8	620.4	618.7	617.0	618.7	617.0
37.5°	577.7	574.3	574.3	570.8	570.8	569.1	567.4	570.8
40°	528.2	526.4	524.7	523.0	524.7	523.0	519.6	521.3
42.5°	478.5	478.5	476.8	476.8	475.1	475.1	475.1	475.1
45°	434.1	432.4	432.4	430.7	430.7	430.7	430.7	429.0
47.5°	389.7	388.0	388.0	388.0	386.3	386.3	384.6	386.3
50°	346.9	346.9	345.3	345.3	346.9	345.3	343.6	343.6
52.5°	307.6	307.6	305.9	305.9	304.2	302.5	304.2	304.2
55°	271.8	270.1	268.4	268.4	266.6	264.9	264.9	266.6
57.5°	237.5	235.8	234.1	234.1	230.7	229.0	229.0	229.0
60°	205.1	201.7	201.7	200.0	200.0	198.3	198.3	198.3
62.5°	174.3	172.6	172.6	172.6	172.6	170.9	170.9	170.9
65°	148.7	148.7	148.7	150.4	150.4	152.2	152.2	152.2
67.5°	128.2	129.9	129.9	129.9	131.6	131.6	131.6	129.9
70°	109.4	109.4	109.4	111.1	111.1	111.1	111.1	111.1
72.5°	90.6	90.6	90.6	90.6	90.6	90.6	90.6	90.6
75°	71.8	73.5	73.5	73.5	71.8	73.5	73.5	71.8
77.5°	56.4	56.4	56.4	56.4	56.4	56.4	56.4	56.4
80°	42.7	42.7	42.7	42.7	42.7	42.7	42.7	42.7
82.5°	29.1	29.1	29.1	29.1	29.1	29.1	29.1	29.1
85°	17.1	17.1	17.1	17.1	17.1	17.1	17.1	17.1
87.5°	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)