

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584148

Luminaire Tested: **HCC8W25D010SL-HM82555835-81WWW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584148  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W25D010SL-HM82555835-81WWW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2324.7 lumens  
Efficiency: N/A  
Efficacy: 86.7 lumens/watt  
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584148  
CATALOG NUMBER: HCC8W25D010SL-HM82555835-81WWW

### Luminous Intensity Polar Plot





TEST NUMBER: P584148

CATALOG NUMBER: HCC8W25D010SL-HM82555835-81WWW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76								
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66								
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58								
5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51								
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	38841	38841	38841
5°	40206	38618	37086
10°	41100	37944	34997
15°	41683	36665	32684
20°	41561	34883	30341
25°	40530	32622	27856
30°	38402	30002	25562
35°	34934	27153	23226
40°	30686	24144	20984
45°	26754	21242	18708
50°	23286	18613	16483
55°	20768	16354	14333
60°	18866	14333	12230
65°	16957	12470	11105
70°	15102	10630	10017
75°	13237	8960	8554
80°	11223	7281	7583
85°	8491	5449	6050



TEST NUMBER: P584148  
 CATALOG NUMBER: HCC8W25D010SL-HM82555835-81WWW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	118.0	5.1
10°-20°	325.1	14.0
20°-30°	451.2	19.4
30°-40°	466.5	20.1
40°-50°	390.6	16.8
50°-60°	283.6	12.2
60°-70°	179.0	7.7
70°-80°	88.6	3.8
80°-90°	22.0	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	894.3	38.5
0°-40°	1360.8	58.5
0°-60°	2035.0	87.5
0°-90°	2324.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2324.7	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1260	1260	1260	1260	1260	
5°	1299	1284	1248	1214	1198	124
15°	1306	1256	1148	1056	1024	367
25°	1191	1114	959	854	819	546
35°	928	860	721	639	617	578
45°	614	569	487	439	429	475
55°	386	352	304	279	267	349
65°	232	203	171	150	152	232
75°	111	92	75	72	72	119
85°	24	19	15	17	17	29
90°	0	0	0	0	0	



TEST NUMBER: P584148

CATALOG NUMBER: HCC8W25D010SL-HM82555835-81WWW

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1259.6	1259.6	1259.6	1259.6	1259.6	1259.6	1259.6	1259.6	1259.6	1259.6	1259.6
2.5°	1280.1	1280.1	1281.9	1280.1	1280.1	1280.1	1278.4	1278.4	1276.7	1276.7	1273.3
5°	1298.9	1295.4	1298.9	1295.4	1295.4	1295.4	1293.7	1290.3	1288.6	1285.3	1283.6
7.5°	1307.4	1305.7	1305.7	1304.0	1304.0	1302.3	1300.6	1298.9	1292.0	1290.3	1285.3
10°	1312.6	1310.9	1310.9	1309.1	1305.7	1305.7	1302.3	1300.6	1292.0	1288.6	1281.9
12.5°	1310.9	1310.9	1310.9	1309.1	1304.0	1302.3	1298.9	1293.7	1287.0	1280.1	1273.3
15°	1305.7	1305.7	1302.3	1300.6	1295.4	1292.0	1290.3	1281.9	1275.0	1266.5	1256.2
17.5°	1288.6	1288.6	1287.0	1283.6	1278.4	1275.0	1271.6	1263.0	1256.2	1242.5	1232.2
20°	1266.5	1264.7	1263.0	1257.9	1252.8	1251.0	1245.9	1233.9	1225.5	1215.2	1201.5
22.5°	1233.9	1232.2	1230.5	1227.1	1218.6	1215.2	1211.8	1203.2	1187.8	1177.5	1160.5
25°	1191.2	1191.2	1187.8	1182.7	1174.1	1170.7	1165.6	1157.1	1143.4	1128.0	1114.3
27.5°	1141.7	1140.0	1134.8	1131.4	1124.6	1119.4	1110.9	1100.6	1087.0	1075.0	1057.9
30°	1078.5	1078.5	1075.0	1069.9	1061.3	1057.9	1051.1	1039.1	1025.5	1010.1	998.1
32.5°	1006.7	1006.7	1001.5	998.1	993.0	984.4	982.7	969.1	957.1	945.1	931.4
35°	928.0	929.7	926.3	919.5	911.0	911.0	907.6	895.6	881.9	869.9	859.6
37.5°	849.4	844.3	842.6	839.2	834.1	827.2	823.8	818.7	806.7	798.1	782.8
40°	762.3	764.0	760.6	757.1	755.4	750.3	748.6	740.0	731.5	721.3	714.4
42.5°	683.6	683.6	683.6	680.2	676.8	671.6	669.9	664.8	654.6	647.8	637.5
45°	613.5	608.4	608.4	606.7	605.0	601.6	596.5	593.1	586.3	581.1	569.1
47.5°	545.2	546.9	545.2	543.5	538.3	536.6	534.9	528.2	521.3	516.2	507.6
50°	485.4	488.8	485.4	485.4	481.9	480.2	476.8	471.7	466.6	458.1	449.5
52.5°	435.8	435.8	434.1	432.4	427.3	423.8	422.1	420.4	411.8	405.1	398.3
55°	386.3	388.0	388.0	382.8	381.1	377.7	376.0	370.9	367.4	357.2	352.0
57.5°	343.6	341.9	343.6	340.2	336.7	333.3	331.6	328.2	323.0	316.2	309.3
60°	305.9	302.5	302.5	300.8	297.4	295.6	292.2	287.1	282.1	275.2	270.1
62.5°	268.4	266.6	264.9	263.2	259.8	258.1	256.4	251.2	246.1	241.0	235.8
65°	232.4	232.4	230.7	227.3	225.6	223.8	222.1	218.8	212.0	208.5	203.4
67.5°	200.0	198.3	198.3	194.8	191.4	189.7	189.7	186.3	181.2	176.0	172.6
70°	167.5	169.2	167.5	165.7	162.3	162.3	158.9	157.2	150.4	148.7	143.6
72.5°	138.5	138.5	136.7	136.7	133.3	131.6	131.6	128.2	124.8	121.3	117.9
75°	111.1	111.1	111.1	109.4	107.6	104.2	104.2	102.5	99.1	95.7	92.3
77.5°	87.2	85.5	85.5	83.8	82.1	80.4	80.4	78.6	75.2	73.5	70.1
80°	63.2	61.5	61.5	61.5	58.1	59.8	58.1	56.4	54.7	53.0	51.3
82.5°	41.0	42.7	42.7	41.0	39.3	39.3	39.3	37.6	37.6	35.8	34.1
85°	24.0	24.0	24.0	24.0	22.3	22.3	22.3	20.5	20.5	20.5	18.8
87.5°	10.3	10.3	10.3	10.3	10.3	10.3	8.6	8.6	8.6	8.6	8.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584148

CATALOG NUMBER: HCC8W25D010SL-HM82555835-81WWW

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1259.6	1259.6	1259.6	1259.6	1259.6	1259.6	1259.6	1259.6	1259.6	1259.6	1259.6
2.5°	1273.3	1269.9	1268.2	1266.5	1266.5	1264.7	1263.0	1259.6	1259.6	1256.2	1254.5
5°	1280.1	1275.0	1271.6	1268.2	1266.5	1263.0	1259.6	1254.5	1252.8	1247.6	1242.5
7.5°	1281.9	1273.3	1269.9	1263.0	1259.6	1256.2	1249.3	1244.2	1237.3	1232.2	1225.5
10°	1275.0	1268.2	1259.6	1251.0	1249.3	1244.2	1233.9	1227.1	1218.6	1211.8	1201.5
12.5°	1264.7	1254.5	1245.9	1235.6	1230.5	1225.5	1215.2	1204.9	1192.9	1181.0	1170.7
15°	1247.6	1235.6	1223.8	1211.8	1204.9	1199.8	1187.8	1175.8	1163.8	1148.5	1138.3
17.5°	1222.0	1208.4	1196.4	1181.0	1174.1	1169.0	1153.7	1140.0	1124.6	1109.2	1099.0
20°	1189.5	1172.4	1158.8	1141.7	1136.6	1128.0	1112.6	1097.3	1080.2	1063.0	1051.1
22.5°	1146.8	1129.7	1114.3	1097.3	1088.7	1080.2	1064.8	1045.9	1028.9	1015.2	1003.2
25°	1097.3	1081.9	1063.0	1047.6	1037.4	1027.2	1010.1	994.7	979.3	958.8	946.8
27.5°	1042.5	1023.8	1010.1	989.5	979.3	972.5	953.7	933.1	919.5	900.7	887.0
30°	981.0	964.0	948.6	928.0	917.7	911.0	893.9	875.0	861.4	842.6	828.9
32.5°	916.0	897.3	878.5	864.8	852.8	846.0	827.2	815.2	798.1	782.8	767.4
35°	846.0	827.2	813.5	794.7	787.8	781.1	765.7	750.3	734.9	721.3	709.3
37.5°	770.8	757.1	741.7	728.0	722.9	716.2	697.3	683.6	671.6	658.1	647.8
40°	697.3	685.3	675.1	661.4	652.9	647.8	634.1	622.1	608.4	599.8	589.7
42.5°	630.7	617.0	606.7	596.5	588.0	582.8	570.8	562.3	552.0	543.5	531.6
45°	560.6	553.7	541.7	533.3	528.2	521.3	512.7	502.5	493.9	487.1	478.5
47.5°	499.0	492.2	483.6	473.4	470.1	464.9	456.4	449.5	442.7	435.8	427.3
50°	442.7	434.1	427.3	420.4	417.0	411.8	403.4	400.0	394.8	388.0	382.8
52.5°	391.4	384.6	377.7	369.2	367.4	364.0	358.9	352.0	346.9	343.6	340.2
55°	345.3	338.4	333.3	326.5	324.7	321.3	314.5	311.0	307.6	304.2	300.8
57.5°	304.2	297.4	290.5	287.1	283.7	280.3	278.6	273.5	270.1	268.4	264.9
60°	266.6	259.8	254.7	249.5	247.8	246.1	242.7	239.3	235.8	232.4	230.7
62.5°	230.7	223.8	220.4	217.1	213.7	213.7	210.3	206.8	203.4	201.7	198.3
65°	198.3	194.8	189.7	184.6	182.9	182.9	177.7	176.0	174.3	170.9	167.5
67.5°	167.5	164.0	158.9	157.2	155.6	153.9	152.2	148.7	145.3	143.6	140.2
70°	140.2	136.7	133.3	131.6	129.9	128.2	124.8	123.0	119.6	117.9	116.2
72.5°	112.8	111.1	107.6	105.9	104.2	102.5	100.8	99.1	95.7	94.1	92.3
75°	90.6	88.9	85.5	83.8	82.1	82.1	80.4	76.9	75.2	75.2	73.5
77.5°	68.4	66.7	64.9	63.2	61.5	61.5	59.8	58.1	56.4	56.4	54.7
80°	49.5	47.8	46.1	46.1	46.1	44.4	42.7	42.7	41.0	41.0	39.3
82.5°	32.4	32.4	30.8	30.8	30.8	29.1	29.1	27.4	27.4	27.4	27.4
85°	18.8	18.8	18.8	17.1	17.1	17.1	17.1	17.1	17.1	15.4	17.1
87.5°	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6	6.8	6.8	6.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584148

CATALOG NUMBER: HCC8W25D010SL-HM82555835-81WWW

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1259.6	1259.6	1259.6	1259.6	1259.6	1259.6	1259.6	1259.6	1259.6	1259.6	1259.6
2.5°	1252.8	1251.0	1247.6	1247.6	1244.2	1244.2	1242.5	1240.8	1239.1	1237.3	1235.6
5°	1240.8	1233.9	1230.5	1228.8	1225.5	1223.8	1218.6	1215.2	1213.5	1210.1	1206.6
7.5°	1218.6	1211.8	1204.9	1203.2	1201.5	1194.7	1189.5	1184.4	1181.0	1177.5	1174.1
10°	1192.9	1186.1	1177.5	1174.1	1170.7	1162.2	1155.4	1150.2	1143.4	1136.6	1134.8
12.5°	1162.2	1152.0	1141.7	1138.3	1133.1	1124.6	1117.7	1109.2	1104.0	1095.6	1093.9
15°	1126.3	1114.3	1105.7	1097.3	1093.9	1085.3	1073.3	1066.5	1056.2	1052.8	1044.2
17.5°	1083.6	1071.6	1059.6	1056.2	1051.1	1039.1	1027.2	1018.6	1008.4	1003.2	998.1
20°	1039.1	1023.8	1011.8	1008.4	1001.5	991.2	979.3	970.8	962.3	952.0	946.8
22.5°	987.8	970.8	960.5	952.0	950.3	938.3	924.6	917.7	911.0	902.4	895.6
25°	931.4	916.0	904.2	897.3	893.9	883.6	873.3	864.8	854.5	849.4	840.9
27.5°	873.3	863.1	847.8	840.9	835.8	827.2	815.2	810.1	799.8	793.0	787.8
30°	816.9	801.5	793.0	784.5	779.4	770.8	760.6	755.4	746.9	740.0	734.9
32.5°	755.4	745.1	733.2	729.7	722.9	714.4	707.6	699.0	692.2	685.3	683.6
35°	699.0	685.3	673.4	669.9	664.8	656.3	652.9	647.8	639.2	637.5	630.7
37.5°	637.5	630.7	617.0	611.8	610.1	603.3	596.5	593.1	588.0	582.8	581.1
40°	579.4	570.8	564.0	558.9	555.4	550.3	543.5	541.7	538.3	531.6	529.9
42.5°	524.7	516.2	509.3	507.6	502.5	497.3	493.9	488.8	487.1	485.4	481.9
45°	471.7	466.6	459.8	458.1	456.4	449.5	446.1	442.7	439.2	437.5	434.1
47.5°	423.8	418.7	413.6	411.8	408.5	406.8	401.7	400.0	394.8	393.1	391.4
50°	377.7	374.3	370.9	369.2	365.7	364.0	360.6	357.2	353.7	352.0	350.3
52.5°	336.7	333.3	329.9	328.2	326.5	323.0	319.6	316.2	314.5	312.8	311.0
55°	297.4	293.9	292.2	290.5	288.8	287.1	282.1	280.3	278.6	276.9	273.5
57.5°	261.5	258.1	254.7	254.7	252.9	251.2	247.8	244.4	244.4	241.0	237.5
60°	229.0	225.6	222.1	220.4	218.8	215.4	213.7	212.0	210.3	208.5	205.1
62.5°	194.8	193.1	189.7	189.7	186.3	184.6	182.9	181.2	179.4	176.0	174.3
65°	165.7	164.0	160.6	158.9	158.9	157.2	153.9	152.2	150.4	150.4	148.7
67.5°	138.5	136.7	133.3	131.6	131.6	129.9	128.2	128.2	126.5	124.8	126.5
70°	114.5	111.1	111.1	109.4	109.4	107.6	105.9	105.9	105.9	107.6	107.6
72.5°	90.6	88.9	87.2	87.2	87.2	87.2	85.5	85.5	87.2	88.9	88.9
75°	71.8	70.1	70.1	70.1	68.4	68.4	70.1	70.1	71.8	71.8	71.8
77.5°	53.0	53.0	53.0	53.0	53.0	53.0	54.7	54.7	56.4	56.4	56.4
80°	39.3	39.3	39.3	39.3	39.3	41.0	41.0	41.0	41.0	41.0	42.7
82.5°	27.4	27.4	27.4	27.4	27.4	27.4	27.4	29.1	29.1	29.1	29.1
85°	15.4	17.1	17.1	17.1	17.1	17.1	17.1	17.1	17.1	17.1	17.1
87.5°	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584148

CATALOG NUMBER: HCC8W25D010SL-HM82555835-81WWW

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1259.6	1259.6	1259.6	1259.6	1259.6	1259.6	1259.6	1259.6
2.5°	1233.9	1233.9	1233.9	1235.6	1232.2	1232.2	1232.2	1232.2
5°	1204.9	1203.2	1201.5	1203.2	1199.8	1199.8	1198.1	1198.1
7.5°	1169.0	1167.3	1165.6	1165.6	1162.2	1162.2	1160.5	1158.8
10°	1129.7	1126.3	1128.0	1124.6	1122.9	1121.1	1119.4	1117.7
12.5°	1087.0	1083.6	1081.9	1078.5	1075.0	1073.3	1075.0	1071.6
15°	1040.8	1035.8	1034.0	1030.6	1027.2	1025.5	1025.5	1023.8
17.5°	989.5	986.1	984.4	981.0	979.3	975.8	974.2	972.5
20°	941.7	933.1	934.9	931.4	929.7	922.9	922.9	924.6
22.5°	888.7	883.6	880.2	876.8	875.0	871.6	871.6	869.9
25°	835.8	830.6	828.9	825.5	823.8	820.4	818.7	818.7
27.5°	784.5	777.7	777.7	774.3	770.8	769.1	767.4	765.7
30°	729.7	724.6	722.9	722.9	721.3	721.3	716.2	717.9
32.5°	678.5	675.1	673.4	669.9	669.9	668.2	668.2	663.1
35°	627.2	622.1	623.8	620.4	618.7	617.0	618.7	617.0
37.5°	577.7	574.3	574.3	570.8	570.8	569.1	567.4	570.8
40°	528.2	526.4	524.7	523.0	524.7	523.0	519.6	521.3
42.5°	478.5	478.5	476.8	476.8	475.1	475.1	475.1	475.1
45°	434.1	432.4	432.4	430.7	430.7	430.7	430.7	429.0
47.5°	389.7	388.0	388.0	388.0	386.3	386.3	384.6	386.3
50°	346.9	346.9	345.3	345.3	346.9	345.3	343.6	343.6
52.5°	307.6	307.6	305.9	305.9	304.2	302.5	304.2	304.2
55°	271.8	270.1	268.4	268.4	266.6	264.9	264.9	266.6
57.5°	237.5	235.8	234.1	234.1	230.7	229.0	229.0	229.0
60°	205.1	201.7	201.7	200.0	200.0	198.3	198.3	198.3
62.5°	174.3	172.6	172.6	172.6	172.6	170.9	170.9	170.9
65°	148.7	148.7	148.7	150.4	150.4	152.2	152.2	152.2
67.5°	128.2	129.9	129.9	129.9	131.6	131.6	131.6	129.9
70°	109.4	109.4	109.4	111.1	111.1	111.1	111.1	111.1
72.5°	90.6	90.6	90.6	90.6	90.6	90.6	90.6	90.6
75°	71.8	73.5	73.5	73.5	71.8	73.5	73.5	71.8
77.5°	56.4	56.4	56.4	56.4	56.4	56.4	56.4	56.4
80°	42.7	42.7	42.7	42.7	42.7	42.7	42.7	42.7
82.5°	29.1	29.1	29.1	29.1	29.1	29.1	29.1	29.1
85°	17.1	17.1	17.1	17.1	17.1	17.1	17.1	17.1
87.5°	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)