

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584145

Luminaire Tested: **HCC8S25D010MW-HM82555835-81WDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584145
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S25D010MW-HM82555835-81WDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2625.5 lumens
Efficiency: N/A
Efficacy: 98.0 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584145
CATALOG NUMBER: HCC8S25D010MW-HM82555835-81WDW

Luminous Intensity Polar Plot





TEST NUMBER: P584145

CATALOG NUMBER: HCC8S25D010MW-HM82555835-81WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89																			
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79																			
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70																			
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63																			
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57																			
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52																			
7	74	63	56	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48																			
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44																			
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40																			
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	52490
5°	52424
10°	51909
15°	51286
20°	50811
25°	50240
30°	47403
35°	38600
40°	21327
45°	14238
50°	12626
55°	11849
60°	11699
65°	11594
70°	10477
75°	9365
80°	8186
85°	7253



TEST NUMBER: P584145
 CATALOG NUMBER: HCC8S25D010MW-HM82555835-81WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.5	6.1
10°-20°	453.6	17.3
20°-30°	674.0	25.7
30°-40°	607.0	23.1
40°-50°	269.1	10.2
50°-60°	199.3	7.6
60°-70°	155.0	5.9
70°-80°	84.0	3.2
80°-90°	23.0	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1288.1	49.1
0°-40°	1895.1	72.2
0°-60°	2363.5	90.0
0°-90°	2625.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2625.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1702	
5°	1694	161
15°	1606	454
25°	1477	674
35°	1025	607
45°	326	269
55°	220	199
65°	159	155
75°	79	84
85°	20	23
90°	0	



TEST NUMBER: P584145
CATALOG NUMBER: HCC8S25D010MW-HM82555835-81WDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1702.2
2.5°	1698.7
5°	1693.6
7.5°	1680.0
10°	1657.8
12.5°	1632.1
15°	1606.5
17.5°	1580.8
20°	1548.4
22.5°	1515.9
25°	1476.6
27.5°	1416.8
30°	1331.3
32.5°	1208.2
35°	1025.4
37.5°	765.7
40°	529.8
42.5°	391.4
45°	326.5
47.5°	288.8
50°	263.2
52.5°	239.3
55°	220.4
57.5°	205.1
60°	189.7
62.5°	176.0
65°	158.9
67.5°	138.5
70°	116.2
72.5°	97.4
75°	78.6
77.5°	61.5
80°	46.1
82.5°	32.4
85°	20.5
87.5°	8.6
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)