

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584153

Luminaire Tested: **HCC8W25D010BZ-HM82555840-81NDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584153
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W25D010BZ-HM82555840-81NDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2749.1 lumens
Efficiency: N/A
Efficacy: 102.6 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.27
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584153
CATALOG NUMBER: HCC8W25D010BZ-HM82555840-81NDC

Luminous Intensity Polar Plot





TEST NUMBER: P584153

CATALOG NUMBER: HCC8W25D010BZ-HM82555840-81NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	115	112	110	108	112	110	108	107	106	105	103	102	101	100	99	98	97	96	96	94	93	91	91	96		
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91	91	89	87	87	91	96		
3	106	101	97	93	104	99	96	93	97	94	91	95	92	90	92	90	89	87	87	85	83	83	87	91		
4	102	96	91	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83	83	81	80	80	84	88		
5	98	92	87	83	97	91	86	83	89	85	82	87	84	82	86	83	81	80	80	77	75	73	77	91		
6	95	88	83	79	93	87	82	79	86	82	79	84	81	78	83	80	78	76	76	74	72	71	75	89		
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73	73	71	69	68	73	87		
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	70	70	68	66	65	69	85		
9	85	78	73	70	84	77	73	70	76	72	70	76	72	69	75	72	69	67	67	65	63	62	66	81		
10	83	75	70	67	82	75	70	67	74	70	67	73	69	67	73	69	67	65	63	61	59	57	61	77		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	517440
5°	331899
10°	149928
15°	90463
20°	68935
25°	55670
30°	40798
35°	14772
40°	5515
45°	2503
50°	801
55°	199
60°	111
65°	131
70°	0
75°	0
80°	320
85°	637



TEST NUMBER: P584153
 CATALOG NUMBER: HCC8W25D010BZ-HM82555840-81NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	817.8	29.7
10°-20°	830.6	30.2
20°-30°	743.6	27.0
30°-40°	299.5	10.9
40°-50°	49.1	1.8
50°-60°	4.5	0.2
60°-70°	1.6	0.1
70°-80°	1.2	0.0
80°-90°	1.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2391.9	87.0
0°-40°	2691.5	97.9
0°-60°	2745.1	99.9
0°-90°	2749.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2749.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16780	
5°	10722	818
15°	2834	831
25°	1636	744
35°	392	300
45°	57	49
55°	4	4
65°	2	2
75°	0	1
85°	2	2
90°	0	



TEST NUMBER: P584153
CATALOG NUMBER: HCC8W25D010BZ-HM82555840-81NDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	16780.2
0.5°	16728.4
1°	16511.8
1.5°	16163.8
2°	15636.3
2.5°	15012.6
3°	14231.5
3.5°	13374.6
4°	12526.8
4.5°	11577.4
5°	10722.3
5.5°	9791.2
6°	9036.0
6.5°	8249.5
7°	7631.2
7.5°	6977.9
8°	6452.2
8.5°	5924.7
9°	5528.6
9.5°	5091.8
10°	4788.2
12.5°	3531.5
15°	2833.7
17.5°	2421.0
20°	2100.7
22.5°	1845.3
25°	1636.2
27.5°	1427.1
30°	1145.8
32.5°	736.7
35°	392.4
37.5°	216.6
40°	137.0
42.5°	90.7
45°	57.4
47.5°	35.2
50°	16.7
52.5°	5.6
55°	3.7
57.5°	1.8
60°	1.8
62.5°	1.8
65°	1.8



TEST NUMBER: P584153
CATALOG NUMBER: HCC8W25D010BZ-HM82555840-81NDC

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	1.8
80°	1.8
82.5°	1.8
85°	1.8
87.5°	1.8
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



67.5°		1.8
70°		0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)