

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584166

Luminaire Tested: **HCC8S25D010BZ-HM82555840-81WWWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584166
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S25D010BZ-HM82555840-81WWWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2621.4 lumens
Efficiency: N/A
Efficacy: 97.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584166
CATALOG NUMBER: HCC8S25D010BZ-HM82555840-81WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584166

CATALOG NUMBER: HCC8S25D010BZ-HM82555840-81WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87					87			
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75					75			
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65					65			
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57					57			
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50					50			
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45					45			
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40					40			
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37					37			
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33					33			
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30					30			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	40192	40192	40192
5°	41664	40058	38683
10°	42841	39710	37102
15°	43793	39008	35464
20°	43861	37485	34020
25°	43023	35402	32820
30°	40805	32829	31380
35°	37076	29901	29969
40°	32421	26829	28246
45°	28093	23902	26322
50°	24605	21223	23982
55°	21897	18811	21698
60°	19754	16898	19069
65°	17833	14856	16614
70°	16021	12523	12352
75°	14106	9936	9269
80°	11845	8222	8879
85°	9164	7182	7890



TEST NUMBER: P584166

CATALOG NUMBER: HCC8S25D010BZ-HM82555840-81WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.0	4.7
10°-20°	346.3	13.2
20°-30°	494.9	18.9
30°-40°	525.9	20.1
40°-50°	452.8	17.3
50°-60°	338.5	12.9
60°-70°	215.9	8.2
70°-80°	98.3	3.7
80°-90°	25.8	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	964.2	36.8
0°-40°	1490.1	56.8
0°-60°	2281.4	87.0
0°-90°	2621.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2621.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1303	1303	1303	1303	1303	
5°	1346	1327	1294	1261	1250	129
15°	1372	1326	1222	1139	1111	386
25°	1264	1185	1040	978	965	579
35°	985	916	794	774	796	613
45°	644	609	548	563	604	501
55°	407	374	350	380	404	366
65°	244	217	204	213	228	244
75°	118	102	83	76	78	126
85°	26	22	20	22	22	31
90°	0	0	0	0	0	



TEST NUMBER: P584166

CATALOG NUMBER: HCC8S25D010BZ-HM82555840-81WWWB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1303.4	1303.4	1303.4	1303.4	1303.4	1303.4	1303.4	1303.4	1303.4	1303.4	1303.4
2.5°	1327.4	1323.7	1325.6	1323.7	1325.6	1325.6	1321.9	1321.9	1321.9	1321.9	1316.3
5°	1346.0	1344.1	1344.1	1342.2	1340.4	1342.2	1340.4	1338.6	1334.8	1333.0	1327.4
7.5°	1357.1	1357.1	1357.1	1357.1	1355.2	1353.3	1351.5	1347.8	1344.1	1340.4	1336.6
10°	1368.2	1370.0	1368.2	1366.3	1364.5	1360.7	1358.9	1355.2	1349.7	1344.1	1340.4
12.5°	1373.7	1373.7	1371.8	1371.8	1368.2	1366.3	1360.7	1355.2	1349.7	1344.1	1334.8
15°	1371.8	1371.8	1370.0	1368.2	1362.6	1360.7	1357.1	1351.5	1342.2	1334.8	1325.6
17.5°	1360.7	1358.9	1355.2	1355.2	1347.8	1346.0	1342.2	1334.8	1325.6	1314.5	1303.4
20°	1336.6	1336.6	1334.8	1333.0	1325.6	1320.1	1316.3	1307.1	1299.6	1286.7	1275.5
22.5°	1303.4	1307.1	1303.4	1299.6	1290.4	1288.6	1283.0	1271.9	1260.8	1246.0	1233.0
25°	1264.5	1262.6	1260.8	1257.0	1249.7	1246.0	1238.5	1227.5	1216.4	1199.7	1184.9
27.5°	1214.4	1207.1	1207.1	1199.7	1194.1	1188.6	1184.9	1173.8	1158.9	1146.0	1127.5
30°	1146.0	1147.9	1138.6	1136.8	1127.5	1123.8	1116.3	1105.3	1092.3	1077.5	1062.7
32.5°	1071.9	1066.4	1066.4	1059.0	1051.6	1046.0	1044.2	1031.3	1020.1	1005.3	990.5
35°	984.9	984.9	979.4	977.6	970.2	966.4	960.9	953.5	940.5	927.6	916.5
37.5°	899.8	896.0	894.2	890.6	885.0	879.4	879.4	866.5	864.6	849.8	834.9
40°	805.4	809.0	805.4	799.8	797.9	794.3	792.3	785.0	779.4	766.4	757.2
42.5°	725.8	722.0	722.0	720.2	712.7	712.7	709.1	705.3	696.1	692.4	681.3
45°	644.2	648.0	642.4	644.2	636.9	636.9	636.9	629.5	622.1	616.5	609.2
47.5°	573.9	575.8	575.8	570.2	568.4	568.4	564.6	561.0	555.4	548.1	542.5
50°	512.9	514.7	510.9	509.1	505.5	503.5	503.5	496.2	492.4	485.0	481.4
52.5°	457.3	457.3	455.4	455.4	449.9	449.9	446.2	440.6	436.9	433.2	423.9
55°	407.3	407.3	405.4	403.6	403.6	398.0	396.2	390.7	386.9	379.5	374.0
57.5°	359.2	361.0	359.2	357.3	355.5	353.6	349.9	344.3	340.7	335.1	331.4
60°	320.3	320.3	318.4	316.6	312.9	311.0	309.2	305.5	299.9	296.2	290.6
62.5°	283.2	281.4	279.6	277.7	274.0	274.0	270.3	266.6	261.1	257.3	253.6
65°	244.4	244.4	242.6	242.6	240.6	237.0	235.1	233.3	225.9	224.1	216.6
67.5°	209.2	211.0	207.4	207.4	203.6	203.6	201.8	196.2	194.4	190.7	187.0
70°	177.7	177.7	177.7	175.9	172.2	170.3	168.5	164.8	163.0	159.2	155.5
72.5°	146.3	146.3	144.5	144.5	142.5	140.7	138.9	135.1	135.1	131.4	127.8
75°	118.4	118.4	116.6	114.8	112.9	112.9	111.1	109.2	105.5	103.7	101.9
77.5°	90.7	90.7	90.7	88.9	87.0	87.0	87.0	83.4	79.6	79.6	77.8
80°	66.7	66.7	64.8	64.8	62.9	62.9	62.9	61.1	59.3	57.4	55.5
82.5°	44.4	44.4	44.4	44.4	42.6	42.6	42.6	40.8	38.8	38.8	38.8
85°	25.9	25.9	25.9	25.9	24.1	24.1	24.1	24.1	24.1	22.3	22.3
87.5°	11.1	9.3	11.1	9.3	11.1	9.3	11.1	9.3	9.3	9.3	9.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584166

CATALOG NUMBER: HCC8S25D010BZ-HM82555840-81WWWB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1303.4	1303.4	1303.4	1303.4	1303.4	1303.4	1303.4	1303.4	1303.4	1303.4	1303.4
2.5°	1318.1	1316.3	1314.5	1312.6	1312.6	1310.8	1307.1	1305.2	1303.4	1301.5	1301.5
5°	1325.6	1323.7	1320.1	1316.3	1314.5	1310.8	1307.1	1303.4	1299.6	1294.1	1292.2
7.5°	1331.2	1325.6	1321.9	1314.5	1312.6	1308.9	1303.4	1297.8	1290.4	1283.0	1277.5
10°	1331.2	1323.7	1318.1	1308.9	1305.2	1301.5	1294.1	1284.9	1275.5	1268.2	1259.0
12.5°	1327.4	1318.1	1308.9	1299.6	1294.1	1288.6	1277.5	1268.2	1257.0	1246.0	1238.5
15°	1314.5	1303.4	1292.2	1281.1	1275.5	1268.2	1257.0	1244.1	1233.0	1221.9	1209.0
17.5°	1290.4	1279.3	1266.3	1253.4	1246.0	1240.5	1223.8	1214.4	1197.9	1186.7	1175.6
20°	1259.0	1246.0	1229.3	1216.4	1207.1	1201.5	1188.6	1171.9	1158.9	1142.3	1131.2
22.5°	1218.2	1201.5	1184.9	1171.9	1162.7	1155.3	1138.6	1121.9	1110.9	1096.0	1083.1
25°	1170.0	1153.4	1136.8	1118.3	1108.9	1101.6	1086.8	1071.9	1057.2	1040.5	1029.3
27.5°	1112.7	1094.2	1079.3	1062.7	1053.4	1042.3	1025.7	1010.8	996.1	984.9	970.2
30°	1049.8	1029.3	1014.6	997.9	988.7	979.4	962.7	947.9	935.0	922.0	914.5
32.5°	973.8	959.0	944.2	927.6	920.1	914.5	897.9	883.1	868.3	857.2	851.6
35°	901.6	885.0	871.9	857.2	848.0	842.4	827.5	814.6	807.2	794.3	786.9
37.5°	825.7	812.8	797.9	783.1	777.6	772.0	760.9	747.9	736.8	727.6	723.9
40°	746.1	735.0	722.0	712.7	707.3	701.7	692.4	683.2	675.7	666.5	662.8
42.5°	670.2	662.8	651.6	640.6	635.0	633.1	622.1	614.6	611.0	607.2	603.6
45°	601.7	590.6	583.2	575.8	570.2	566.6	561.0	555.4	551.7	548.1	544.3
47.5°	535.0	525.8	518.4	512.9	507.3	505.5	501.7	496.2	492.4	492.4	492.4
50°	473.9	466.5	459.1	455.4	453.6	449.9	446.2	444.4	442.4	442.4	442.4
52.5°	420.3	412.8	407.3	403.6	403.6	399.9	396.2	394.3	394.3	394.3	394.3
55°	370.3	364.8	361.0	357.3	353.6	351.7	351.7	351.7	349.9	349.9	351.7
57.5°	325.8	322.2	316.6	312.9	311.0	311.0	309.2	307.3	309.2	311.0	312.9
60°	285.2	281.4	279.6	274.0	274.0	274.0	272.1	272.1	272.1	274.0	275.8
62.5°	248.1	246.2	242.6	240.6	238.8	238.8	237.0	237.0	237.0	237.0	238.8
65°	214.7	211.0	207.4	207.4	207.4	205.5	205.5	201.8	203.6	203.6	201.8
67.5°	183.3	179.5	177.7	175.9	174.0	174.0	172.2	170.3	168.5	168.5	168.5
70°	153.7	150.0	150.0	146.3	146.3	144.5	142.5	142.5	140.7	138.9	137.0
72.5°	124.0	122.2	120.4	118.4	118.4	118.4	116.6	114.8	112.9	111.1	107.4
75°	98.1	98.1	94.4	92.6	92.6	90.7	88.9	87.0	85.2	83.4	81.4
77.5°	75.9	74.0	70.3	68.5	68.5	68.5	66.7	64.8	62.9	61.1	59.3
80°	55.5	53.7	51.8	50.0	50.0	50.0	48.2	48.2	46.3	46.3	46.3
82.5°	37.0	37.0	35.2	35.2	35.2	35.2	33.3	33.3	33.3	33.3	33.3
85°	22.3	22.3	20.3	20.3	20.3	20.3	20.3	20.3	20.3	20.3	20.3
87.5°	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584166

CATALOG NUMBER: HCC8S25D010BZ-HM82555840-81WWWB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1303.4	1303.4	1303.4	1303.4	1303.4	1303.4	1303.4	1303.4	1303.4	1303.4	1303.4
2.5°	1297.8	1297.8	1294.1	1292.2	1290.4	1292.2	1288.6	1286.7	1284.9	1284.9	1283.0
5°	1286.7	1284.9	1277.5	1275.5	1273.7	1271.9	1268.2	1264.5	1260.8	1259.0	1257.0
7.5°	1271.9	1266.3	1259.0	1257.0	1255.2	1249.7	1244.1	1240.5	1234.9	1233.0	1229.3
10°	1251.6	1244.1	1238.5	1233.0	1229.3	1223.8	1218.2	1212.6	1205.2	1203.4	1197.9
12.5°	1227.5	1218.2	1207.1	1205.2	1199.7	1192.3	1184.9	1179.4	1173.8	1170.0	1164.5
15°	1197.9	1188.6	1177.4	1171.9	1166.4	1160.8	1151.5	1144.2	1138.6	1133.0	1127.5
17.5°	1162.7	1151.5	1142.3	1136.8	1133.0	1123.8	1116.3	1107.1	1101.6	1096.0	1090.4
20°	1120.1	1110.9	1097.8	1092.3	1090.4	1083.1	1073.7	1070.1	1062.7	1057.2	1053.4
22.5°	1071.9	1062.7	1051.6	1047.9	1040.5	1036.7	1027.5	1023.8	1020.1	1014.6	1012.6
25°	1018.2	1009.0	999.7	997.9	992.3	988.7	983.1	977.6	977.6	972.0	972.0
27.5°	962.7	953.5	946.1	942.3	940.5	936.8	931.2	929.4	927.6	925.7	925.7
30°	903.5	892.4	888.6	886.8	885.0	881.3	879.4	875.7	877.5	879.4	877.5
32.5°	840.5	836.8	829.5	825.7	827.5	825.7	822.0	825.7	823.9	827.5	829.5
35°	779.4	775.8	772.0	772.0	768.4	768.4	768.4	770.2	773.8	775.8	779.4
37.5°	720.2	714.7	712.7	710.9	712.7	712.7	712.7	716.5	720.2	723.9	729.4
40°	657.2	653.6	653.6	653.6	653.6	659.1	657.2	660.9	664.7	670.2	675.7
42.5°	598.0	598.0	599.8	599.8	599.8	599.8	603.6	609.2	614.6	620.2	625.7
45°	542.5	542.5	542.5	546.1	546.1	548.1	555.4	559.1	562.8	568.4	573.9
47.5°	490.6	490.6	492.4	494.3	496.2	499.9	503.5	509.1	514.7	518.4	524.0
50°	442.4	444.4	448.0	451.8	451.8	453.6	459.1	462.9	466.5	472.1	473.9
52.5°	396.2	399.9	403.6	405.4	407.3	411.0	412.8	418.4	420.3	425.9	427.7
55°	353.6	355.5	361.0	362.8	362.8	366.6	370.3	374.0	379.5	379.5	383.3
57.5°	314.7	316.6	320.3	322.2	320.3	325.8	327.7	331.4	333.2	336.9	338.8
60°	275.8	279.6	281.4	281.4	283.2	285.2	288.8	288.8	292.5	296.2	296.2
62.5°	238.8	240.6	242.6	244.4	246.2	244.4	250.0	250.0	253.6	255.5	259.2
65°	203.6	205.5	205.5	207.4	207.4	209.2	209.2	211.0	212.9	216.6	218.5
67.5°	168.5	168.5	168.5	170.3	168.5	170.3	170.3	172.2	172.2	175.9	177.7
70°	137.0	135.1	133.3	133.3	133.3	133.3	131.4	133.3	133.3	135.1	135.1
72.5°	105.5	103.7	101.9	99.9	99.9	98.1	96.3	98.1	98.1	99.9	99.9
75°	79.6	75.9	75.9	75.9	74.0	74.0	74.0	75.9	75.9	75.9	77.8
77.5°	59.3	59.3	57.4	57.4	57.4	59.3	59.3	61.1	61.1	61.1	61.1
80°	44.4	46.3	46.3	46.3	46.3	48.2	48.2	48.2	48.2	50.0	50.0
82.5°	33.3	33.3	33.3	33.3	35.2	35.2	35.2	35.2	35.2	35.2	35.2
85°	20.3	22.3	22.3	20.3	22.3	22.3	22.3	22.3	22.3	22.3	22.3
87.5°	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584166

CATALOG NUMBER: HCC8S25D010BZ-HM82555840-81WWWB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1303.4	1303.4	1303.4	1303.4	1303.4	1303.4	1303.4	1303.4
2.5°	1281.1	1281.1	1281.1	1281.1	1279.3	1279.3	1279.3	1277.5
5°	1253.4	1253.4	1253.4	1249.7	1251.6	1251.6	1247.8	1249.7
7.5°	1225.6	1223.8	1221.9	1221.9	1220.0	1218.2	1216.4	1218.2
10°	1194.1	1188.6	1188.6	1186.7	1186.7	1183.0	1183.0	1184.9
12.5°	1158.9	1155.3	1155.3	1153.4	1151.5	1149.7	1147.9	1147.9
15°	1123.8	1120.1	1118.3	1116.3	1114.5	1110.9	1112.7	1110.9
17.5°	1088.6	1083.1	1083.1	1081.2	1079.3	1075.7	1075.7	1073.7
20°	1047.9	1046.0	1042.3	1044.2	1042.3	1038.6	1036.7	1036.7
22.5°	1007.2	1007.2	1005.3	1005.3	1003.4	1001.6	999.7	999.7
25°	968.2	966.4	968.2	968.2	962.7	962.7	962.7	964.6
27.5°	923.8	925.7	923.8	923.8	923.8	923.8	925.7	923.8
30°	879.4	879.4	879.4	881.3	885.0	883.1	883.1	881.3
32.5°	831.3	833.1	833.1	834.9	836.8	840.5	840.5	842.4
35°	783.1	786.9	788.7	786.9	792.3	792.3	796.1	796.1
37.5°	733.2	735.0	738.7	740.5	744.3	746.1	747.9	747.9
40°	679.4	686.8	688.8	690.6	696.1	696.1	698.0	701.7
42.5°	629.5	636.9	638.7	640.6	644.2	649.8	648.0	651.6
45°	581.3	586.9	588.7	590.6	596.1	598.0	598.0	603.6
47.5°	529.5	533.2	535.0	538.7	542.5	546.1	549.9	548.1
50°	477.6	483.2	487.0	488.8	494.3	496.2	498.0	499.9
52.5°	431.3	435.1	436.9	438.8	444.4	446.2	448.0	451.8
55°	386.9	388.8	392.5	390.7	396.2	398.0	399.9	403.6
57.5°	342.5	344.3	346.3	346.3	349.9	353.6	355.5	357.3
60°	299.9	303.7	305.5	305.5	305.5	309.2	309.2	309.2
62.5°	261.1	261.1	262.9	262.9	266.6	266.6	266.6	266.6
65°	220.3	222.1	224.1	224.1	227.7	225.9	229.6	227.7
67.5°	177.7	177.7	181.5	181.5	179.5	181.5	181.5	181.5
70°	135.1	135.1	137.0	137.0	137.0	137.0	137.0	137.0
72.5°	99.9	99.9	99.9	101.9	99.9	99.9	101.9	99.9
75°	77.8	77.8	77.8	77.8	77.8	77.8	77.8	77.8
77.5°	61.1	61.1	62.9	62.9	62.9	62.9	62.9	62.9
80°	50.0	50.0	50.0	50.0	51.8	50.0	50.0	50.0
82.5°	37.0	35.2	37.0	35.2	37.0	37.0	37.0	37.0
85°	22.3	22.3	22.3	22.3	22.3	22.3	22.3	22.3
87.5°	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)