

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584158

Luminaire Tested: **HCC8W25D010MB-HM82555840-81RWWH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584158
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W25D010MB-HM82555840-81RWWH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2562.2 lumens
Efficiency: N/A
Efficacy: 95.6 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584158
CATALOG NUMBER: HCC8W25D010MB-HM82555840-81RWWH

Luminous Intensity Polar Plot





TEST NUMBER: P584158

CATALOG NUMBER: HCC8W25D010MB-HM82555840-81RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|----|-----|---|--|---|
| RF | 20 | | | | | 20 | | | | | 20 | | | | | 20 | | | | | 20 | | | | | |
| RC | 80 | | | | | 70 | | | | | 50 | | | | | 30 | | | | | 10 | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | | 100 | | | |
| 1 | 111 | 107 | 104 | 100 | 108 | 105 | 102 | 99 | 101 | 98 | 96 | 97 | 95 | 93 | 93 | 92 | 90 | 88 | | | | | 88 | | | |
| 2 | 103 | 96 | 90 | 85 | 100 | 94 | 89 | 84 | 90 | 86 | 82 | 87 | 84 | 80 | 84 | 81 | 79 | 77 | | | | | 77 | | | |
| 3 | 95 | 86 | 79 | 73 | 92 | 84 | 78 | 73 | 81 | 76 | 71 | 79 | 74 | 70 | 76 | 72 | 69 | 67 | | | | | 67 | | | |
| 4 | 88 | 77 | 70 | 64 | 86 | 76 | 69 | 63 | 74 | 67 | 63 | 71 | 66 | 62 | 69 | 65 | 61 | 59 | | | | | 59 | | | |
| 5 | 81 | 70 | 62 | 56 | 79 | 69 | 62 | 56 | 67 | 60 | 55 | 65 | 59 | 55 | 63 | 58 | 54 | 52 | | | | | 52 | | | |
| 6 | 76 | 64 | 56 | 50 | 74 | 63 | 55 | 50 | 61 | 54 | 49 | 60 | 54 | 49 | 58 | 53 | 49 | 47 | | | | | 47 | | | |
| 7 | 71 | 58 | 51 | 45 | 69 | 58 | 50 | 45 | 56 | 49 | 45 | 55 | 49 | 44 | 54 | 48 | 44 | 42 | | | | | 42 | | | |
| 8 | 66 | 54 | 46 | 41 | 65 | 53 | 46 | 41 | 52 | 45 | 40 | 51 | 45 | 40 | 50 | 44 | 40 | 38 | | | | | 38 | | | |
| 9 | 62 | 50 | 42 | 37 | 61 | 49 | 42 | 37 | 48 | 41 | 37 | 47 | 41 | 37 | 46 | 41 | 36 | 35 | | | | | 35 | | | |
| 10 | 58 | 46 | 39 | 34 | 57 | 46 | 39 | 34 | 45 | 38 | 34 | 44 | 38 | 34 | 43 | 38 | 34 | 32 | | | | | 32 | | | |

AVERAGE LUMINANCE (cd/sqm):

| | 0° | 90° | 180° |
|-----|-------|-------|-------|
| 0° | 42144 | 42144 | 42144 |
| 5° | 42933 | 41961 | 40986 |
| 10° | 43605 | 41229 | 39488 |
| 15° | 44046 | 40202 | 37779 |
| 20° | 43877 | 38653 | 36035 |
| 25° | 42721 | 36419 | 34024 |
| 30° | 40688 | 33762 | 32050 |
| 35° | 36737 | 30816 | 29765 |
| 40° | 32280 | 27654 | 27582 |
| 45° | 27862 | 24312 | 25359 |
| 50° | 24255 | 21324 | 22744 |
| 55° | 21505 | 18515 | 19811 |
| 60° | 19193 | 15646 | 16442 |
| 65° | 17293 | 12703 | 12973 |
| 70° | 15354 | 9521 | 7682 |
| 75° | 13237 | 5516 | 3312 |
| 80° | 10211 | 1971 | 994 |
| 85° | 6545 | 637 | 637 |



TEST NUMBER: P584158
 CATALOG NUMBER: HCC8W25D010MB-HM82555840-81RWWH

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 128.3 | 5.0 |
| 10°-20° | 357.2 | 13.9 |
| 20°-30° | 505.2 | 19.7 |
| 30°-40° | 532.3 | 20.8 |
| 40°-50° | 452.4 | 17.7 |
| 50°-60° | 325.8 | 12.7 |
| 60°-70° | 187.9 | 7.3 |
| 70°-80° | 64.3 | 2.5 |
| 80°-90° | 8.8 | 0.3 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 990.6 | 38.7 |
| 0°-40° | 1522.9 | 59.4 |
| 0°-60° | 2301.1 | 89.8 |
| 0°-90° | 2562.2 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 2562.2 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | 45° | 90° | 135° | 180° | Flux |
|-----|------|------|------|------|------|------|
| 0° | 1367 | 1367 | 1367 | 1367 | 1367 | |
| 5° | 1387 | 1378 | 1356 | 1332 | 1324 | 133 |
| 15° | 1380 | 1337 | 1259 | 1204 | 1183 | 388 |
| 25° | 1256 | 1191 | 1070 | 1015 | 1000 | 576 |
| 35° | 976 | 919 | 819 | 789 | 791 | 608 |
| 45° | 639 | 609 | 558 | 561 | 582 | 496 |
| 55° | 400 | 368 | 344 | 357 | 368 | 360 |
| 65° | 237 | 204 | 174 | 170 | 178 | 236 |
| 75° | 111 | 83 | 46 | 30 | 28 | 117 |
| 85° | 18 | 11 | 2 | 2 | 2 | 25 |
| 90° | 0 | 0 | 0 | 0 | 0 | |



TEST NUMBER: P584158

CATALOG NUMBER: HCC8W25D010MB-HM82555840-81RWWH

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° | 90° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1366.7 | 1366.7 | 1366.7 | 1366.7 | 1366.7 | 1366.7 | 1366.7 | 1366.7 | 1366.7 | 1366.7 | 1366.7 |
| 2.5° | 1379.7 | 1381.5 | 1379.7 | 1379.7 | 1377.8 | 1376.0 | 1374.1 | 1372.3 | 1368.5 | 1364.9 | 1364.9 |
| 5° | 1387.0 | 1390.8 | 1387.0 | 1387.0 | 1381.5 | 1377.8 | 1374.1 | 1368.5 | 1361.1 | 1355.6 | 1355.6 |
| 7.5° | 1392.6 | 1392.6 | 1392.6 | 1387.0 | 1383.4 | 1377.8 | 1368.5 | 1359.3 | 1350.0 | 1340.8 | 1337.1 |
| 10° | 1392.6 | 1392.6 | 1390.8 | 1383.4 | 1379.7 | 1368.5 | 1359.3 | 1346.4 | 1333.3 | 1320.4 | 1316.7 |
| 12.5° | 1387.0 | 1389.0 | 1385.2 | 1377.8 | 1368.5 | 1355.6 | 1342.6 | 1325.9 | 1311.2 | 1296.3 | 1288.9 |
| 15° | 1379.7 | 1377.8 | 1374.1 | 1364.9 | 1353.8 | 1337.1 | 1324.1 | 1305.6 | 1285.2 | 1266.7 | 1259.3 |
| 17.5° | 1361.1 | 1361.1 | 1355.6 | 1346.4 | 1331.5 | 1313.0 | 1292.7 | 1272.2 | 1250.1 | 1229.6 | 1220.4 |
| 20° | 1337.1 | 1337.1 | 1329.7 | 1318.6 | 1303.8 | 1279.7 | 1257.5 | 1233.4 | 1207.5 | 1187.1 | 1177.9 |
| 22.5° | 1301.9 | 1303.8 | 1294.5 | 1281.5 | 1264.8 | 1237.1 | 1214.9 | 1185.2 | 1159.3 | 1135.3 | 1127.8 |
| 25° | 1255.6 | 1259.3 | 1250.1 | 1237.1 | 1214.9 | 1190.8 | 1163.0 | 1135.3 | 1105.6 | 1081.6 | 1070.4 |
| 27.5° | 1201.9 | 1203.8 | 1194.4 | 1181.5 | 1159.3 | 1133.3 | 1105.6 | 1076.0 | 1048.2 | 1022.3 | 1011.2 |
| 30° | 1142.7 | 1135.3 | 1131.5 | 1114.8 | 1090.8 | 1068.6 | 1037.0 | 1013.0 | 983.3 | 961.2 | 948.2 |
| 32.5° | 1059.3 | 1063.0 | 1051.9 | 1039.0 | 1020.5 | 994.5 | 968.6 | 940.7 | 913.0 | 896.3 | 887.0 |
| 35° | 975.9 | 979.7 | 974.1 | 961.2 | 940.7 | 918.6 | 892.6 | 872.3 | 848.2 | 827.9 | 818.6 |
| 37.5° | 889.0 | 889.0 | 885.2 | 877.8 | 863.0 | 842.6 | 816.7 | 796.3 | 776.0 | 759.3 | 753.7 |
| 40° | 801.9 | 798.2 | 796.3 | 790.7 | 777.8 | 759.3 | 742.6 | 726.0 | 705.6 | 694.4 | 687.0 |
| 42.5° | 716.7 | 716.7 | 712.9 | 707.5 | 694.4 | 685.2 | 668.5 | 650.0 | 635.3 | 624.1 | 624.1 |
| 45° | 638.9 | 640.7 | 635.3 | 631.5 | 624.1 | 609.3 | 594.5 | 581.5 | 568.5 | 561.1 | 557.5 |
| 47.5° | 570.4 | 570.4 | 564.9 | 561.1 | 553.7 | 540.8 | 527.8 | 516.7 | 507.4 | 501.8 | 500.0 |
| 50° | 505.6 | 505.6 | 505.6 | 496.3 | 487.1 | 477.8 | 468.6 | 455.6 | 450.0 | 446.3 | 444.5 |
| 52.5° | 450.0 | 448.1 | 448.1 | 440.7 | 431.5 | 420.4 | 411.1 | 400.0 | 394.5 | 390.8 | 392.6 |
| 55° | 400.0 | 400.0 | 398.1 | 388.9 | 379.6 | 368.5 | 359.3 | 350.0 | 346.4 | 342.6 | 344.4 |
| 56° | 379.6 | 379.6 | 377.8 | 370.4 | 359.3 | 350.0 | 338.9 | 329.7 | 324.1 | 325.9 | 325.9 |
| 57° | 364.9 | 361.1 | 361.1 | 351.8 | 342.6 | 329.7 | 320.4 | 311.2 | 307.4 | 305.6 | 305.6 |
| 58° | 346.4 | 344.4 | 342.6 | 333.3 | 324.1 | 313.0 | 303.7 | 294.5 | 288.9 | 288.9 | 287.1 |
| 59° | 327.7 | 327.7 | 324.1 | 316.7 | 307.4 | 296.3 | 287.1 | 277.8 | 272.2 | 270.4 | 270.4 |
| 60° | 311.2 | 313.0 | 307.4 | 300.0 | 292.6 | 279.6 | 268.6 | 261.1 | 255.5 | 253.7 | 253.7 |
| 61° | 296.3 | 296.3 | 292.6 | 283.3 | 274.1 | 264.8 | 253.7 | 244.5 | 240.8 | 237.0 | 237.0 |
| 62° | 283.3 | 279.6 | 277.8 | 268.6 | 259.3 | 248.1 | 238.9 | 229.6 | 224.1 | 220.4 | 222.2 |
| 63° | 266.6 | 264.8 | 261.1 | 253.7 | 244.5 | 233.4 | 222.2 | 214.9 | 209.3 | 203.7 | 205.5 |
| 64° | 253.7 | 251.9 | 246.3 | 238.9 | 229.6 | 218.5 | 207.4 | 200.0 | 196.3 | 190.8 | 188.9 |
| 65° | 237.0 | 235.2 | 233.4 | 224.1 | 214.9 | 203.7 | 194.4 | 187.0 | 181.5 | 177.8 | 174.1 |
| 66° | 222.2 | 224.1 | 220.4 | 212.9 | 201.9 | 192.6 | 179.7 | 172.3 | 168.5 | 163.0 | 159.2 |
| 67° | 209.3 | 209.3 | 205.5 | 198.2 | 187.0 | 177.8 | 168.5 | 159.2 | 153.8 | 148.2 | 146.3 |
| 67.5° | 201.9 | 201.9 | 198.2 | 188.9 | 181.5 | 170.3 | 161.1 | 153.8 | 146.3 | 142.6 | 138.9 |
| 68° | 194.4 | 194.4 | 192.6 | 185.2 | 175.9 | 164.8 | 155.6 | 146.3 | 138.9 | 133.3 | 131.5 |
| 69° | 181.5 | 183.3 | 179.7 | 172.3 | 163.0 | 151.8 | 142.6 | 135.1 | 127.8 | 122.2 | 118.6 |
| 70° | 170.3 | 168.5 | 164.8 | 157.4 | 148.2 | 140.7 | 131.5 | 122.2 | 114.8 | 107.4 | 105.6 |
| 71° | 155.6 | 155.6 | 151.8 | 146.3 | 137.1 | 127.8 | 118.6 | 111.1 | 103.7 | 94.5 | 92.6 |
| 72° | 144.5 | 144.5 | 140.7 | 133.3 | 125.9 | 116.6 | 107.4 | 98.1 | 92.6 | 83.4 | 79.6 |
| 72.5° | 137.1 | 138.9 | 135.1 | 127.8 | 120.4 | 109.2 | 101.9 | 94.5 | 85.2 | 77.8 | 74.0 |
| 73° | 133.3 | 131.5 | 129.7 | 122.2 | 113.0 | 105.6 | 96.3 | 88.9 | 79.6 | 72.2 | 68.5 |



TEST NUMBER: P584158
 CATALOG NUMBER: HCC8W25D010MB-HM82555840-81RWWH

CANDELA DISTRIBUTION (continued):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° | 90° |
|-------|------|------|------|------|------|------|------|------|------|------|------|
| 77.5° | 83.4 | 83.4 | 81.5 | 74.0 | 66.7 | 59.3 | 51.9 | 44.4 | 37.0 | 29.6 | 25.9 |
| 80° | 57.5 | 59.3 | 55.5 | 51.9 | 46.3 | 38.8 | 31.5 | 25.9 | 18.5 | 14.8 | 11.1 |
| 82.5° | 37.0 | 37.0 | 35.2 | 31.5 | 27.8 | 22.3 | 18.5 | 12.9 | 9.3 | 7.4 | 5.6 |
| 85° | 18.5 | 20.3 | 18.5 | 16.7 | 12.9 | 11.1 | 9.3 | 5.6 | 3.7 | 1.8 | 1.8 |
| 87.5° | 7.4 | 7.4 | 7.4 | 5.6 | 5.6 | 3.7 | 1.8 | 1.8 | 1.8 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



TEST NUMBER: P584158

CATALOG NUMBER: HCC8W25D010MB-HM82555840-81RWWH

CANDELA DISTRIBUTION (continued):

| | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1366.7 | 1366.7 | 1366.7 | 1366.7 | 1366.7 | 1366.7 | 1366.7 | 1366.7 | 1366.7 | 1366.7 |
| 2.5° | 1361.1 | 1361.1 | 1357.4 | 1355.6 | 1353.8 | 1351.9 | 1350.0 | 1348.2 | 1348.2 | 1350.0 |
| 5° | 1350.0 | 1346.4 | 1338.9 | 1337.1 | 1331.5 | 1329.7 | 1325.9 | 1324.1 | 1325.9 | 1324.1 |
| 7.5° | 1333.3 | 1325.9 | 1316.7 | 1313.0 | 1305.6 | 1301.9 | 1296.3 | 1296.3 | 1292.7 | 1294.5 |
| 10° | 1311.2 | 1300.1 | 1288.9 | 1281.5 | 1276.0 | 1270.4 | 1266.7 | 1263.0 | 1261.1 | 1261.1 |
| 12.5° | 1283.4 | 1270.4 | 1259.3 | 1248.2 | 1239.0 | 1235.2 | 1227.8 | 1227.8 | 1224.1 | 1222.3 |
| 15° | 1251.9 | 1235.2 | 1222.3 | 1211.1 | 1203.8 | 1196.4 | 1190.8 | 1187.1 | 1183.4 | 1183.4 |
| 17.5° | 1211.1 | 1196.4 | 1183.4 | 1170.4 | 1159.3 | 1153.8 | 1148.2 | 1142.7 | 1142.7 | 1138.9 |
| 20° | 1166.7 | 1150.0 | 1138.9 | 1126.0 | 1116.8 | 1107.4 | 1100.1 | 1100.1 | 1096.3 | 1098.1 |
| 22.5° | 1116.8 | 1096.3 | 1085.2 | 1076.0 | 1066.7 | 1059.3 | 1051.9 | 1051.9 | 1050.0 | 1048.2 |
| 25° | 1061.1 | 1044.5 | 1031.5 | 1020.5 | 1014.9 | 1007.4 | 1005.6 | 1001.8 | 1000.0 | 1000.0 |
| 27.5° | 1001.8 | 988.9 | 972.3 | 966.7 | 959.3 | 955.6 | 955.6 | 953.7 | 950.1 | 951.9 |
| 30° | 938.9 | 924.2 | 914.8 | 911.1 | 903.7 | 903.7 | 901.9 | 898.2 | 898.2 | 900.1 |
| 32.5° | 877.8 | 863.0 | 855.6 | 853.8 | 846.4 | 846.4 | 844.4 | 846.4 | 846.4 | 848.2 |
| 35° | 811.2 | 798.2 | 796.3 | 790.7 | 788.9 | 788.9 | 788.9 | 792.7 | 796.3 | 790.7 |
| 37.5° | 748.1 | 738.9 | 733.4 | 731.6 | 733.4 | 733.4 | 735.2 | 740.8 | 738.9 | 737.0 |
| 40° | 683.4 | 675.9 | 672.3 | 672.3 | 675.9 | 679.7 | 679.7 | 685.2 | 687.0 | 685.2 |
| 42.5° | 618.6 | 613.0 | 613.0 | 614.8 | 618.6 | 620.4 | 626.0 | 631.5 | 633.3 | 635.3 |
| 45° | 557.5 | 557.5 | 557.5 | 559.3 | 561.1 | 564.9 | 572.2 | 577.8 | 579.6 | 581.5 |
| 47.5° | 498.2 | 496.3 | 501.8 | 503.8 | 509.3 | 511.1 | 516.7 | 524.1 | 525.9 | 527.8 |
| 50° | 442.7 | 446.3 | 448.1 | 453.7 | 457.4 | 457.4 | 464.8 | 468.6 | 474.1 | 474.1 |
| 52.5° | 390.8 | 396.3 | 398.1 | 403.7 | 405.5 | 407.5 | 411.1 | 416.7 | 420.4 | 420.4 |
| 55° | 344.4 | 346.4 | 350.0 | 351.8 | 357.4 | 359.3 | 362.9 | 364.9 | 370.4 | 368.5 |
| 56° | 324.1 | 327.7 | 329.7 | 333.3 | 337.0 | 338.9 | 342.6 | 344.4 | 348.2 | 350.0 |
| 57° | 305.6 | 307.4 | 313.0 | 314.8 | 318.5 | 318.5 | 320.4 | 325.9 | 325.9 | 327.7 |
| 58° | 287.1 | 290.7 | 292.6 | 294.5 | 298.2 | 300.0 | 303.7 | 305.6 | 307.4 | 305.6 |
| 59° | 270.4 | 272.2 | 274.1 | 274.1 | 277.8 | 277.8 | 283.3 | 287.1 | 288.9 | 288.9 |
| 60° | 253.7 | 253.7 | 255.5 | 257.4 | 261.1 | 263.0 | 263.0 | 266.6 | 266.6 | 266.6 |
| 61° | 237.0 | 237.0 | 238.9 | 240.8 | 242.6 | 242.6 | 246.3 | 246.3 | 248.1 | 250.1 |
| 62° | 222.2 | 220.4 | 220.4 | 222.2 | 222.2 | 226.0 | 227.8 | 229.6 | 231.4 | 229.6 |
| 63° | 205.5 | 203.7 | 203.7 | 203.7 | 203.7 | 207.4 | 207.4 | 209.3 | 212.9 | 211.1 |
| 64° | 187.0 | 187.0 | 187.0 | 187.0 | 188.9 | 188.9 | 192.6 | 194.4 | 196.3 | 198.2 |
| 65° | 174.1 | 170.3 | 168.5 | 168.5 | 170.3 | 172.3 | 174.1 | 175.9 | 177.8 | 177.8 |
| 66° | 159.2 | 155.6 | 153.8 | 153.8 | 153.8 | 153.8 | 157.4 | 157.4 | 161.1 | 161.1 |
| 67° | 142.6 | 138.9 | 137.1 | 135.1 | 135.1 | 135.1 | 140.7 | 138.9 | 138.9 | 138.9 |
| 67.5° | 137.1 | 131.5 | 129.7 | 127.8 | 125.9 | 129.7 | 127.8 | 129.7 | 129.7 | 127.8 |
| 68° | 129.7 | 125.9 | 122.2 | 118.6 | 118.6 | 118.6 | 120.4 | 122.2 | 120.4 | 118.6 |
| 69° | 114.8 | 113.0 | 107.4 | 103.7 | 101.9 | 103.7 | 101.9 | 103.7 | 101.9 | 103.7 |
| 70° | 101.9 | 96.3 | 90.7 | 88.9 | 87.0 | 87.0 | 87.0 | 85.2 | 87.0 | 85.2 |
| 71° | 88.9 | 83.4 | 77.8 | 74.0 | 72.2 | 72.2 | 70.4 | 72.2 | 70.4 | 72.2 |
| 72° | 76.0 | 70.4 | 62.9 | 59.3 | 59.3 | 59.3 | 59.3 | 57.5 | 59.3 | 57.5 |
| 72.5° | 70.4 | 62.9 | 57.5 | 53.7 | 51.9 | 51.9 | 51.9 | 51.9 | 50.0 | 51.9 |
| 73° | 64.8 | 57.5 | 50.0 | 48.2 | 48.2 | 48.2 | 46.3 | 44.4 | 46.3 | 46.3 |



TEST NUMBER: P584158
 CATALOG NUMBER: HCC8W25D010MB-HM82555840-81RWWH

CANDELA DISTRIBUTION (continued):

| | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|------|------|------|------|------|------|------|------|------|------|
| 77.5° | 22.3 | 16.7 | 14.8 | 14.8 | 14.8 | 14.8 | 14.8 | 14.8 | 12.9 | 12.9 |
| 80° | 9.3 | 7.4 | 5.6 | 5.6 | 5.6 | 5.6 | 5.6 | 5.6 | 5.6 | 5.6 |
| 82.5° | 3.7 | 3.7 | 3.7 | 3.7 | 3.7 | 3.7 | 3.7 | 3.7 | 3.7 | 3.7 |
| 85° | 1.8 | 1.8 | 1.8 | 1.8 | 1.8 | 1.8 | 1.8 | 1.8 | 1.8 | 1.8 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



| | | | | | | | | | | | |
|-----|-------|-------|-------|-------|-------|------|------|------|------|------|------|
| 74° | 120.4 | 120.4 | 116.6 | 111.1 | 101.9 | 92.6 | 85.2 | 77.8 | 68.5 | 59.3 | 55.5 |
| 75° | 111.1 | 109.2 | 105.6 | 100.0 | 92.6 | 83.4 | 76.0 | 66.7 | 59.3 | 50.0 | 46.3 |

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



| | | | | | | | | | | |
|-----|------|------|------|------|------|------|------|------|------|------|
| 74° | 53.7 | 44.4 | 40.8 | 37.0 | 37.0 | 37.0 | 35.2 | 35.2 | 35.2 | 37.0 |
| 75° | 42.6 | 35.2 | 31.5 | 27.8 | 29.6 | 27.8 | 29.6 | 27.8 | 27.8 | 27.8 |

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)