

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583983

Luminaire Tested: **HCC8S20D010BZ-HM80520827-81WWWB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583983  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S20D010BZ-HM80520827-81WWWB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2061.4 lumens  
Efficiency: N/A  
Efficacy: 103.1 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 20  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583983  
CATALOG NUMBER: HCC8S20D010BZ-HM80520827-81WWWB

### Luminous Intensity Polar Plot





TEST NUMBER: P583983

CATALOG NUMBER: HCC8S20D010BZ-HM80520827-81WWWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75								
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65								
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57								
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50								
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45								
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40								
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37								
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33								
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	31604	31604	31604
5°	32765	31502	30419
10°	33689	31227	29177
15°	34440	30673	27886
20°	34495	29478	26754
25°	33834	27839	25807
30°	32089	25815	24675
35°	29159	23513	23565
40°	25493	21097	22212
45°	22092	18796	20697
50°	19347	16695	18858
55°	17220	14795	17064
60°	15535	13290	14993
65°	14024	11689	13068
70°	12595	9845	9710
75°	11092	7804	7280
80°	9305	6464	6997
85°	7182	5661	6192



TEST NUMBER: P583983  
 CATALOG NUMBER: HCC8S20D010BZ-HM80520827-81WWWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	96.7	4.7
10°-20°	272.3	13.2
20°-30°	389.2	18.9
30°-40°	413.6	20.1
40°-50°	356.1	17.3
50°-60°	266.2	12.9
60°-70°	169.8	8.2
70°-80°	77.3	3.7
80°-90°	20.3	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	758.2	36.8
0°-40°	1171.8	56.8
0°-60°	1794.1	87.0
0°-90°	2061.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2061.4	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1025	1025	1025	1025	1025	
5°	1058	1044	1018	992	983	101
15°	1079	1042	961	895	874	304
25°	994	932	818	769	758	455
35°	775	721	625	609	626	482
45°	507	479	431	442	475	394
55°	320	294	275	298	317	288
65°	192	170	160	167	179	192
75°	93	80	66	60	61	99
85°	20	18	16	18	18	25
90°	0	0	0	0	0	



TEST NUMBER: P583983

CATALOG NUMBER: HCC8S20D010BZ-HM80520827-81WWWB

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1024.9	1024.9	1024.9	1024.9	1024.9	1024.9	1024.9	1024.9	1024.9	1024.9	1024.9
2.5°	1043.8	1041.0	1042.4	1041.0	1042.4	1042.4	1039.5	1039.5	1039.5	1039.5	1035.1
5°	1058.5	1056.9	1056.9	1055.5	1054.1	1055.5	1054.1	1052.6	1049.7	1048.2	1043.8
7.5°	1067.1	1067.1	1067.1	1067.1	1065.7	1064.3	1062.9	1059.9	1056.9	1054.1	1051.2
10°	1075.9	1077.4	1075.9	1074.4	1073.0	1070.1	1068.6	1065.7	1061.3	1056.9	1054.1
12.5°	1080.2	1080.2	1078.8	1078.8	1075.9	1074.4	1070.1	1065.7	1061.3	1056.9	1049.7
15°	1078.8	1078.8	1077.4	1075.9	1071.5	1070.1	1067.1	1062.9	1055.5	1049.7	1042.4
17.5°	1070.1	1068.6	1065.7	1065.7	1059.9	1058.5	1055.5	1049.7	1042.4	1033.7	1024.9
20°	1051.2	1051.2	1049.7	1048.2	1042.4	1038.0	1035.1	1027.9	1022.1	1011.8	1003.2
22.5°	1024.9	1027.9	1024.9	1022.1	1014.7	1013.3	1009.0	1000.2	991.5	979.8	969.6
25°	994.4	992.9	991.5	988.5	982.7	979.8	974.0	965.2	956.5	943.5	931.8
27.5°	955.1	949.3	949.3	943.5	939.1	934.7	931.8	923.0	911.4	901.2	886.6
30°	901.2	902.7	895.4	893.9	886.6	883.8	877.9	869.1	859.0	847.4	835.7
32.5°	843.0	838.6	838.6	832.7	826.9	822.6	821.1	811.0	802.2	790.5	778.9
35°	774.6	774.6	770.2	768.7	762.9	760.0	755.7	749.7	739.6	729.4	720.7
37.5°	707.5	704.6	703.2	700.3	696.0	691.6	691.6	681.3	679.9	668.3	656.6
40°	633.3	636.3	633.3	628.9	627.5	624.6	623.2	617.2	613.0	602.7	595.5
42.5°	570.7	567.8	567.8	566.3	560.5	560.5	557.5	554.7	547.4	544.5	535.8
45°	506.6	509.6	505.2	506.6	500.8	500.8	500.8	495.0	489.2	484.9	478.9
47.5°	451.3	452.8	452.8	448.5	446.9	446.9	444.1	441.1	436.7	431.0	426.6
50°	403.3	404.7	401.9	400.3	397.5	396.0	396.0	390.2	387.2	381.4	378.5
52.5°	359.6	359.6	358.1	358.1	353.8	353.8	350.8	346.4	343.6	340.7	333.4
55°	320.3	320.3	318.8	317.4	317.4	313.0	311.6	307.2	304.2	298.5	294.1
57.5°	282.5	283.9	282.5	281.0	279.5	278.1	275.2	270.8	267.8	263.5	260.6
60°	251.9	251.9	250.5	248.9	246.1	244.6	243.1	240.2	235.8	233.0	228.6
62.5°	222.8	221.3	219.9	218.4	215.5	215.5	212.5	209.7	205.3	202.4	199.4
65°	192.2	192.2	190.8	190.8	189.2	186.4	184.9	183.4	177.7	176.1	170.3
67.5°	164.5	166.0	163.1	163.1	160.2	160.2	158.7	154.4	152.8	150.0	147.0
70°	139.7	139.7	139.7	138.3	135.3	133.9	132.5	129.5	128.1	125.2	122.3
72.5°	115.0	115.0	113.6	113.6	112.1	110.6	109.2	106.3	106.3	103.4	100.5
75°	93.1	93.1	91.7	90.3	88.8	88.8	87.3	85.9	83.0	81.6	80.0
77.5°	71.4	71.4	71.4	69.9	68.4	68.4	68.4	65.5	62.6	62.6	61.1
80°	52.4	52.4	50.9	50.9	49.5	49.5	49.5	48.0	46.6	45.2	43.7
82.5°	35.0	35.0	35.0	35.0	33.5	33.5	33.5	32.0	30.6	30.6	30.6
85°	20.3	20.3	20.3	20.3	18.9	18.9	18.9	18.9	18.9	17.5	17.5
87.5°	8.7	7.3	8.7	7.3	8.7	7.3	8.7	7.3	7.3	7.3	7.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583983

CATALOG NUMBER: HCC8S20D010BZ-HM80520827-81WWWB

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1024.9	1024.9	1024.9	1024.9	1024.9	1024.9	1024.9	1024.9	1024.9	1024.9	1024.9
2.5°	1036.6	1035.1	1033.7	1032.2	1032.2	1030.8	1027.9	1026.4	1024.9	1023.5	1023.5
5°	1042.4	1041.0	1038.0	1035.1	1033.7	1030.8	1027.9	1024.9	1022.1	1017.7	1016.2
7.5°	1046.8	1042.4	1039.5	1033.7	1032.2	1029.3	1024.9	1020.5	1014.7	1009.0	1004.6
10°	1046.8	1041.0	1036.6	1029.3	1026.4	1023.5	1017.7	1010.4	1003.2	997.3	990.0
12.5°	1043.8	1036.6	1029.3	1022.1	1017.7	1013.3	1004.6	997.3	988.5	979.8	974.0
15°	1033.7	1024.9	1016.2	1007.4	1003.2	997.3	988.5	978.3	969.6	960.8	950.7
17.5°	1014.7	1006.0	995.8	985.7	979.8	975.4	962.4	955.1	941.9	933.2	924.4
20°	990.0	979.8	966.8	956.5	949.3	944.9	934.7	921.6	911.4	898.3	889.6
22.5°	958.0	944.9	931.8	921.6	914.3	908.5	895.4	882.2	873.5	861.9	851.7
25°	920.1	907.1	893.9	879.4	872.1	866.3	854.6	843.0	831.3	818.2	809.4
27.5°	875.0	860.4	848.8	835.7	828.3	819.7	806.6	794.9	783.3	774.6	762.9
30°	825.5	809.4	797.8	784.7	777.4	770.2	757.1	745.4	735.2	725.0	719.2
32.5°	765.8	754.1	742.5	729.4	723.6	719.2	706.1	694.4	682.8	674.1	669.7
35°	709.0	696.0	685.7	674.1	666.8	662.4	650.8	640.6	634.7	624.6	618.8
37.5°	649.3	639.1	627.5	615.8	611.4	607.1	598.3	588.2	579.4	572.2	569.3
40°	586.7	578.0	567.8	560.5	556.1	551.8	544.5	537.2	531.4	524.1	521.3
42.5°	527.1	521.3	512.5	503.8	499.4	497.9	489.2	483.3	480.5	477.5	474.6
45°	473.2	464.4	458.6	452.8	448.5	445.5	441.1	436.7	433.9	431.0	428.0
47.5°	420.8	413.5	407.7	403.3	398.9	397.5	394.6	390.2	387.2	387.2	387.2
50°	372.7	366.9	361.1	358.1	356.7	353.8	350.8	349.4	348.0	348.0	348.0
52.5°	330.5	324.7	320.3	317.4	317.4	314.5	311.6	310.2	310.2	310.2	310.2
55°	291.1	286.8	283.9	281.0	278.1	276.6	276.6	276.6	275.2	275.2	276.6
57.5°	256.3	253.3	248.9	246.1	244.6	244.6	243.1	241.7	243.1	244.6	246.1
60°	224.2	221.3	219.9	215.5	215.5	215.5	214.1	214.1	214.1	215.5	216.9
62.5°	195.0	193.6	190.8	189.2	187.8	187.8	186.4	186.4	186.4	186.4	187.8
65°	168.9	166.0	163.1	163.1	163.1	161.6	161.6	158.7	160.2	160.2	158.7
67.5°	144.1	141.2	139.7	138.3	136.9	136.9	135.3	133.9	132.5	132.5	132.5
70°	120.8	118.0	118.0	115.0	115.0	113.6	112.1	112.1	110.6	109.2	107.7
72.5°	97.5	96.1	94.7	93.1	93.1	93.1	91.7	90.3	88.8	87.3	84.4
75°	77.2	77.2	74.2	72.8	72.8	71.4	69.9	68.4	67.0	65.5	64.1
77.5°	59.7	58.3	55.3	53.9	53.9	53.9	52.4	50.9	49.5	48.0	46.6
80°	43.7	42.2	40.8	39.4	39.4	39.4	37.8	37.8	36.4	36.4	36.4
82.5°	29.1	29.1	27.7	27.7	27.7	27.7	26.2	26.2	26.2	26.2	26.2
85°	17.5	17.5	16.0	16.0	16.0	16.0	16.0	16.0	16.0	16.0	16.0
87.5°	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583983

CATALOG NUMBER: HCC8S20D010BZ-HM80520827-81WWWB

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1024.9	1024.9	1024.9	1024.9	1024.9	1024.9	1024.9	1024.9	1024.9	1024.9	1024.9
2.5°	1020.5	1020.5	1017.7	1016.2	1014.7	1016.2	1013.3	1011.8	1010.4	1010.4	1009.0
5°	1011.8	1010.4	1004.6	1003.2	1001.6	1000.2	997.3	994.4	991.5	990.0	988.5
7.5°	1000.2	995.8	990.0	988.5	987.1	982.7	978.3	975.4	971.1	969.6	966.8
10°	984.1	978.3	974.0	969.6	966.8	962.4	958.0	953.6	947.7	946.3	941.9
12.5°	965.2	958.0	949.3	947.7	943.5	937.6	931.8	927.4	923.0	920.1	915.7
15°	941.9	934.7	926.0	921.6	917.2	912.9	905.5	899.7	895.4	891.0	886.6
17.5°	914.3	905.5	898.3	893.9	891.0	883.8	877.9	870.7	866.3	861.9	857.5
20°	880.8	873.5	863.3	859.0	857.5	851.7	844.4	841.5	835.7	831.3	828.3
22.5°	843.0	835.7	826.9	824.0	818.2	815.3	808.0	805.1	802.2	797.8	796.3
25°	800.7	793.5	786.1	784.7	780.4	777.4	773.0	768.7	768.7	764.3	764.3
27.5°	757.1	749.7	744.0	741.0	739.6	736.6	732.4	730.8	729.4	728.0	728.0
30°	710.5	701.8	698.8	697.4	696.0	693.0	691.6	688.6	690.1	691.6	690.1
32.5°	661.0	658.0	652.2	649.3	650.8	649.3	646.4	649.3	647.9	650.8	652.2
35°	613.0	610.0	607.1	607.1	604.2	604.2	604.2	605.7	608.6	610.0	613.0
37.5°	566.3	561.9	560.5	559.1	560.5	560.5	560.5	563.5	566.3	569.3	573.6
40°	516.9	513.9	513.9	513.9	513.9	518.3	516.9	519.7	522.7	527.1	531.4
42.5°	470.2	470.2	471.7	471.7	471.7	471.7	474.6	478.9	483.3	487.7	492.1
45°	426.6	426.6	426.6	429.5	429.5	431.0	436.7	439.7	442.5	446.9	451.3
47.5°	385.8	385.8	387.2	388.8	390.2	393.1	396.0	400.3	404.7	407.7	412.0
50°	348.0	349.4	352.4	355.2	355.2	356.7	361.1	363.9	366.9	371.3	372.7
52.5°	311.6	314.5	317.4	318.8	320.3	323.2	324.7	329.1	330.5	334.9	336.3
55°	278.1	279.5	283.9	285.3	285.3	288.3	291.1	294.1	298.5	298.5	301.4
57.5°	247.5	248.9	251.9	253.3	251.9	256.3	257.7	260.6	262.0	265.0	266.4
60°	216.9	219.9	221.3	221.3	222.8	224.2	227.1	227.1	230.0	233.0	233.0
62.5°	187.8	189.2	190.8	192.2	193.6	192.2	196.6	196.6	199.4	200.9	203.8
65°	160.2	161.6	161.6	163.1	163.1	164.5	164.5	166.0	167.4	170.3	171.7
67.5°	132.5	132.5	132.5	133.9	132.5	133.9	133.9	135.3	135.3	138.3	139.7
70°	107.7	106.3	104.8	104.8	104.8	104.8	103.4	104.8	104.8	106.3	106.3
72.5°	83.0	81.6	80.0	78.6	78.6	77.2	75.6	77.2	77.2	78.6	78.6
75°	62.6	59.7	59.7	59.7	58.3	58.3	58.3	59.7	59.7	59.7	61.1
77.5°	46.6	46.6	45.2	45.2	45.2	46.6	46.6	48.0	48.0	48.0	48.0
80°	35.0	36.4	36.4	36.4	36.4	37.8	37.8	37.8	37.8	39.4	39.4
82.5°	26.2	26.2	26.2	26.2	27.7	27.7	27.7	27.7	27.7	27.7	27.7
85°	16.0	17.5	17.5	16.0	17.5	17.5	17.5	17.5	17.5	17.5	17.5
87.5°	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583983

CATALOG NUMBER: HCC8S20D010BZ-HM80520827-81WWWB

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1024.9	1024.9	1024.9	1024.9	1024.9	1024.9	1024.9	1024.9
2.5°	1007.4	1007.4	1007.4	1007.4	1006.0	1006.0	1006.0	1004.6
5°	985.7	985.7	985.7	982.7	984.1	984.1	981.3	982.7
7.5°	963.8	962.4	960.8	960.8	959.4	958.0	956.5	958.0
10°	939.1	934.7	934.7	933.2	933.2	930.4	930.4	931.8
12.5°	911.4	908.5	908.5	907.1	905.5	904.1	902.7	902.7
15°	883.8	880.8	879.4	877.9	876.5	873.5	875.0	873.5
17.5°	856.0	851.7	851.7	850.2	848.8	845.8	845.8	844.4
20°	824.0	822.6	819.7	821.1	819.7	816.8	815.3	815.3
22.5°	792.1	792.1	790.5	790.5	789.1	787.7	786.1	786.1
25°	761.4	760.0	761.4	761.4	757.1	757.1	757.1	758.5
27.5°	726.5	728.0	726.5	726.5	726.5	726.5	728.0	726.5
30°	691.6	691.6	691.6	693.0	696.0	694.4	694.4	693.0
32.5°	653.6	655.2	655.2	656.6	658.0	661.0	661.0	662.4
35°	615.8	618.8	620.2	618.8	623.2	623.2	626.0	626.0
37.5°	576.6	578.0	581.0	582.4	585.2	586.7	588.2	588.2
40°	534.3	540.2	541.6	543.0	547.4	547.4	548.9	551.8
42.5°	495.0	500.8	502.2	503.8	506.6	511.0	509.6	512.5
45°	457.2	461.6	463.0	464.4	468.8	470.2	470.2	474.6
47.5°	416.4	419.3	420.8	423.6	426.6	429.5	432.4	431.0
50°	375.6	380.0	382.8	384.4	388.8	390.2	391.6	393.1
52.5°	339.2	342.2	343.6	345.0	349.4	350.8	352.4	355.2
55°	304.2	305.8	308.6	307.2	311.6	313.0	314.5	317.4
57.5°	269.4	270.8	272.2	272.2	275.2	278.1	279.5	281.0
60°	235.8	238.8	240.2	240.2	240.2	243.1	243.1	243.1
62.5°	205.3	205.3	206.7	206.7	209.7	209.7	209.7	209.7
65°	173.3	174.7	176.1	176.1	179.1	177.7	180.5	179.1
67.5°	139.7	139.7	142.7	142.7	141.2	142.7	142.7	142.7
70°	106.3	106.3	107.7	107.7	107.7	107.7	107.7	107.7
72.5°	78.6	78.6	78.6	80.0	78.6	78.6	80.0	78.6
75°	61.1	61.1	61.1	61.1	61.1	61.1	61.1	61.1
77.5°	48.0	48.0	49.5	49.5	49.5	49.5	49.5	49.5
80°	39.4	39.4	39.4	39.4	40.8	39.4	39.4	39.4
82.5°	29.1	27.7	29.1	27.7	29.1	29.1	29.1	29.1
85°	17.5	17.5	17.5	17.5	17.5	17.5	17.5	17.5
87.5°	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)