

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583974

Luminaire Tested: **HCC8W20D010BZ-HM80520827-81RWWC**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583974  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-14)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W20D010BZ-HM80520827-81RWWC  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2073.1 lumens  
Efficiency: N/A  
Efficacy: 103.7 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 1.08 / 1.17  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 20  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583974  
CATALOG NUMBER: HCC8W20D010BZ-HM80520827-81RWWC

### Luminous Intensity Polar Plot





TEST NUMBER: P583974

CATALOG NUMBER: HCC8W20D010BZ-HM80520827-81RWWC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	85	82	79	77								
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67								
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	69	65	61	59								
5	81	70	62	56	80	69	62	56	67	61	56	65	59	55	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	33633	33633	33633
5°	34077	33492	33177
10°	34428	33150	32652
15°	34775	32451	31800
20°	34597	31257	30538
25°	33793	29383	28989
30°	32096	27278	27171
35°	29219	24890	25109
40°	25618	22277	23094
45°	22101	19816	21211
50°	19352	17395	19213
55°	17145	14951	16908
60°	15449	12575	14012
65°	13922	10091	10726
70°	12217	7357	5905
75°	10401	3813	1561
80°	8027	1030	249
85°	5130	0	0



TEST NUMBER: P583974  
 CATALOG NUMBER: HCC8W20D010BZ-HM80520827-81RWWC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	102.9	5.0
10°-20°	289.3	14.0
20°-30°	410.6	19.8
30°-40°	432.2	20.9
40°-50°	367.7	17.7
50°-60°	265.7	12.8
60°-70°	151.1	7.3
70°-80°	47.6	2.3
80°-90°	5.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	802.8	38.7
0°-40°	1235.1	59.6
0°-60°	1868.5	90.1
0°-90°	2073.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2073.1	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1091	1091	1091	1091	1091	
5°	1101	1095	1082	1075	1072	105
15°	1089	1062	1016	998	996	307
25°	993	944	864	849	852	455
35°	776	731	661	657	667	483
45°	507	488	454	466	486	394
55°	319	296	278	294	314	288
65°	191	164	138	137	147	189
75°	87	67	32	14	13	94
85°	14	9	0	0	0	19
90°	0	0	0	0	0	



TEST NUMBER: P583974

CATALOG NUMBER: HCC8W20D010BZ-HM80520827-81RWWC

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1090.7	1090.7	1090.7	1090.7	1090.7	1090.7	1090.7	1090.7	1090.7	1090.7	1090.7
2.5°	1096.5	1098.1	1095.1	1095.1	1098.1	1095.1	1096.5	1096.5	1095.1	1095.1	1093.7
5°	1100.9	1099.5	1099.5	1099.5	1100.9	1098.1	1096.5	1098.1	1095.1	1095.1	1095.1
7.5°	1102.5	1102.5	1100.9	1099.5	1099.5	1099.5	1098.1	1096.5	1095.1	1092.2	1090.7
10°	1099.5	1099.5	1100.9	1098.1	1098.1	1095.1	1095.1	1092.2	1092.2	1089.3	1085.0
12.5°	1096.5	1095.1	1095.1	1092.2	1092.2	1089.3	1089.3	1085.0	1083.4	1079.2	1074.8
15°	1089.3	1087.8	1085.0	1083.4	1082.0	1080.6	1077.6	1076.2	1071.8	1066.0	1061.7
17.5°	1074.8	1073.3	1071.8	1068.9	1066.0	1064.5	1063.1	1058.7	1052.9	1048.6	1041.2
20°	1054.3	1052.9	1052.9	1048.6	1047.0	1042.8	1041.2	1035.4	1031.1	1022.3	1016.5
22.5°	1026.7	1028.1	1025.3	1022.3	1019.4	1015.0	1012.1	1006.4	999.0	990.3	983.0
25°	993.2	994.7	991.7	988.9	984.5	981.5	978.6	969.8	962.6	952.5	943.7
27.5°	950.9	950.9	950.9	948.1	940.8	939.3	936.4	927.6	917.5	908.7	900.0
30°	901.4	900.0	900.0	895.6	892.6	886.9	882.5	875.3	867.9	857.8	847.6
32.5°	841.7	843.2	838.9	835.9	831.5	831.5	825.7	819.8	811.2	800.9	790.8
35°	776.2	777.6	774.8	773.3	766.1	764.5	763.1	755.8	750.0	742.7	731.1
37.5°	709.2	707.8	706.2	706.2	702.0	699.0	696.1	691.7	683.0	677.2	671.4
40°	636.4	636.4	636.4	635.0	633.4	630.6	629.1	626.2	620.4	614.5	610.1
42.5°	570.9	570.9	569.4	568.0	565.0	566.5	563.6	560.6	554.8	550.5	547.6
45°	506.8	506.8	506.8	508.3	505.3	500.9	500.9	498.1	495.1	492.2	487.8
47.5°	450.0	454.4	451.4	450.0	451.4	445.6	445.6	442.7	439.8	436.9	431.1
50°	403.4	403.4	403.4	400.5	399.0	399.0	394.7	391.7	390.3	387.3	381.5
52.5°	361.1	358.3	358.3	356.8	355.3	352.5	352.5	349.5	343.7	340.8	336.4
55°	318.9	318.9	317.5	316.1	314.5	313.1	311.7	307.3	304.4	300.0	295.6
57.5°	281.1	284.0	282.5	279.7	276.7	276.7	273.8	270.9	266.5	262.2	257.8
60°	250.5	249.0	249.0	247.5	244.7	243.3	241.7	237.3	233.0	228.6	224.2
62.5°	218.4	218.4	218.4	215.5	212.6	211.1	209.7	206.8	200.9	196.6	193.7
65°	190.8	189.4	187.8	186.4	185.0	182.0	180.6	177.7	173.3	168.9	164.5
67.5°	163.1	161.7	161.7	160.2	155.8	154.4	154.4	150.0	145.6	141.2	136.9
70°	135.5	135.5	135.5	132.5	131.1	129.7	128.1	125.3	120.9	116.5	112.2
72.5°	112.2	110.6	110.6	109.2	104.8	103.4	101.9	99.1	94.7	91.7	88.9
75°	87.3	87.3	85.9	84.5	83.0	81.6	80.1	77.2	72.8	68.4	67.0
77.5°	67.0	65.5	65.5	64.1	61.1	59.7	59.7	56.9	52.5	49.5	46.6
80°	45.2	46.6	45.2	43.7	42.2	40.8	39.4	37.8	35.0	32.0	29.1
82.5°	27.7	29.1	27.7	27.7	26.2	24.7	24.7	21.9	20.3	18.9	17.5
85°	14.5	14.5	14.5	14.5	13.1	13.1	13.1	11.7	10.2	8.7	8.7
87.5°	4.4	5.8	4.4	4.4	4.4	4.4	4.4	4.4	3.0	3.0	3.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583974

CATALOG NUMBER: HCC8W20D010BZ-HM80520827-81RWWC

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1090.7	1090.7	1090.7	1090.7	1090.7	1090.7	1090.7	1090.7	1090.7	1090.7	1090.7
2.5°	1095.1	1093.7	1092.2	1092.2	1092.2	1092.2	1092.2	1090.7	1089.3	1089.3	1089.3
5°	1092.2	1092.2	1092.2	1090.7	1089.3	1089.3	1086.4	1085.0	1083.4	1082.0	1080.6
7.5°	1089.3	1086.4	1085.0	1083.4	1082.0	1082.0	1079.2	1076.2	1076.2	1073.3	1070.4
10°	1080.6	1079.2	1076.2	1073.3	1071.8	1070.4	1067.5	1063.1	1061.7	1058.7	1055.8
12.5°	1070.4	1067.5	1064.5	1058.7	1057.3	1055.8	1050.0	1045.6	1042.8	1041.2	1034.0
15°	1057.3	1051.4	1047.0	1039.8	1038.4	1035.4	1031.1	1026.7	1020.9	1016.5	1013.6
17.5°	1034.0	1028.1	1020.9	1013.6	1010.6	1010.6	1003.4	997.6	990.3	987.3	981.5
20°	1006.4	999.0	993.2	984.5	980.1	975.7	971.4	962.6	956.8	952.5	945.1
22.5°	974.2	964.0	956.8	948.1	940.8	936.4	929.2	921.8	914.5	910.1	904.3
25°	933.4	924.8	913.1	904.3	900.0	894.2	885.4	878.1	870.9	863.6	860.6
27.5°	888.4	876.7	866.5	856.2	852.0	847.6	837.3	828.6	822.8	815.6	812.6
30°	838.9	827.2	815.6	806.8	802.5	795.1	789.3	779.1	771.8	766.1	758.7
32.5°	782.0	773.3	763.1	750.0	747.0	741.2	732.5	728.1	719.4	715.0	709.2
35°	720.9	715.0	704.8	694.7	690.3	687.3	680.1	671.4	665.5	661.2	658.3
37.5°	662.6	655.3	645.1	637.8	635.0	630.6	621.9	617.5	611.7	608.7	602.9
40°	600.0	592.7	585.4	581.1	576.7	573.7	568.0	563.6	557.8	553.4	551.9
42.5°	538.9	534.5	528.6	522.8	521.4	517.0	514.1	509.7	505.3	503.9	499.5
45°	483.4	479.1	473.3	467.5	466.1	463.1	461.7	457.3	454.4	454.4	454.4
47.5°	428.1	423.7	418.0	415.0	416.5	410.6	410.6	409.2	406.3	406.3	407.8
50°	378.6	372.8	371.4	368.4	365.5	362.6	364.1	359.7	359.7	362.6	361.1
52.5°	332.0	326.2	324.7	321.9	320.4	320.4	318.9	318.9	317.5	318.9	318.9
55°	289.8	285.5	282.5	279.7	278.1	278.1	278.1	276.7	275.3	278.1	279.7
57.5°	251.9	250.5	247.5	243.3	241.7	240.3	238.9	238.9	238.9	238.9	240.3
60°	218.4	215.5	212.6	208.3	208.3	206.8	205.3	203.9	203.9	203.9	203.9
62.5°	189.4	185.0	180.6	177.7	176.2	174.7	173.3	170.4	170.4	170.4	170.4
65°	160.2	155.8	153.0	150.0	147.0	147.0	144.2	142.7	139.8	138.3	135.5
67.5°	132.5	129.7	126.7	122.3	120.9	119.4	116.5	115.0	110.6	109.2	107.8
70°	107.8	103.4	100.5	97.5	96.1	93.3	90.3	87.3	84.5	81.6	78.6
72.5°	84.5	80.1	77.2	74.2	71.4	71.4	67.0	64.1	59.7	56.9	52.5
75°	62.6	58.3	55.3	50.9	49.5	48.1	43.7	40.8	36.4	32.0	29.1
77.5°	42.2	39.4	36.4	32.0	29.1	29.1	24.7	21.9	18.9	14.5	13.1
80°	26.2	23.3	20.3	17.5	17.5	14.5	13.1	10.2	7.3	5.8	4.4
82.5°	14.5	13.1	11.7	8.7	8.7	7.3	5.8	4.4	3.0	1.4	1.4
85°	7.3	5.8	4.4	4.4	3.0	3.0	3.0	1.4	1.4	0.0	0.0
87.5°	3.0	1.4	1.4	1.4	1.4	1.4	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P583974

CATALOG NUMBER: HCC8W20D010BZ-HM80520827-81RWWC

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1090.7	1090.7	1090.7	1090.7	1090.7	1090.7	1090.7	1090.7	1090.7	1090.7	1090.7
2.5°	1087.8	1087.8	1086.4	1086.4	1086.4	1085.0	1086.4	1085.0	1085.0	1085.0	1086.4
5°	1082.0	1079.2	1079.2	1077.6	1077.6	1076.2	1077.6	1076.2	1074.8	1073.3	1074.8
7.5°	1070.4	1067.5	1066.0	1064.5	1064.5	1064.5	1063.1	1061.7	1063.1	1058.7	1061.7
10°	1054.3	1052.9	1050.0	1048.6	1047.0	1048.6	1047.0	1044.2	1044.2	1044.2	1042.8
12.5°	1034.0	1031.1	1029.6	1028.1	1025.3	1025.3	1026.7	1023.7	1023.7	1020.9	1020.9
15°	1009.2	1006.4	1003.4	1003.4	1000.4	1000.4	999.0	999.0	997.6	996.1	996.1
17.5°	978.6	974.2	971.4	972.8	971.4	969.8	969.8	967.0	965.6	967.0	967.0
20°	942.2	939.3	936.4	937.8	935.0	933.4	935.0	930.6	932.0	932.0	932.0
22.5°	901.4	900.0	895.6	895.6	892.6	891.2	892.6	892.6	894.2	892.6	892.6
25°	856.2	853.4	850.4	850.4	849.0	847.6	849.0	850.4	849.0	850.4	850.4
27.5°	808.3	803.9	803.9	800.9	800.9	802.5	800.9	802.5	803.9	803.9	806.8
30°	755.8	754.4	752.9	751.4	751.4	752.9	752.9	752.9	754.4	757.3	757.3
32.5°	706.2	703.4	700.5	700.5	703.4	702.0	703.4	703.4	706.2	706.2	709.2
35°	652.5	652.5	649.5	650.9	650.9	650.9	650.9	653.9	656.8	658.3	661.2
37.5°	602.9	598.6	600.0	600.0	601.4	600.0	604.4	604.4	607.3	607.3	610.1
40°	549.0	549.0	550.5	549.0	550.5	550.5	553.4	556.2	557.8	560.6	562.2
42.5°	498.1	500.9	498.1	499.5	500.9	502.5	503.9	505.3	511.2	514.1	518.4
45°	451.4	452.9	454.4	455.8	454.4	457.3	458.7	461.7	466.1	467.5	468.9
47.5°	406.3	407.8	409.2	410.6	410.6	413.6	415.0	418.0	420.9	422.3	423.7
50°	362.6	365.5	367.0	367.0	368.4	371.4	374.2	374.2	377.2	381.5	383.0
52.5°	323.3	323.3	326.2	327.7	329.1	329.1	333.4	335.0	336.4	339.4	342.2
55°	279.7	284.0	285.5	285.5	288.3	291.2	292.7	294.2	294.2	300.0	300.0
57.5°	241.7	243.3	246.1	246.1	246.1	250.5	250.5	253.4	254.8	256.3	259.2
60°	203.9	206.8	206.8	208.3	206.8	209.7	211.1	214.1	215.5	217.0	218.4
62.5°	168.9	168.9	170.4	170.4	170.4	170.4	173.3	173.3	176.2	177.7	179.1
65°	135.5	135.5	135.5	135.5	135.5	135.5	135.5	135.5	136.9	136.9	139.8
67.5°	104.8	103.4	100.5	101.9	100.5	100.5	99.1	99.1	100.5	100.5	103.4
70°	75.8	74.2	71.4	71.4	69.9	68.4	67.0	65.5	64.1	64.1	64.1
72.5°	49.5	46.6	42.2	40.8	40.8	37.8	35.0	33.5	33.5	33.5	33.5
75°	24.7	21.9	18.9	17.5	17.5	14.5	16.1	14.5	14.5	14.5	14.5
77.5°	10.2	7.3	5.8	5.8	5.8	4.4	4.4	4.4	4.4	4.4	4.4
80°	3.0	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4
82.5°	1.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583974

CATALOG NUMBER: HCC8W20D010BZ-HM80520827-81RWWC

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1090.7	1090.7	1090.7	1090.7	1090.7	1090.7	1090.7	1090.7
2.5°	1085.0	1085.0	1082.0	1083.4	1083.4	1083.4	1083.4	1083.4
5°	1071.8	1073.3	1071.8	1073.3	1073.3	1071.8	1071.8	1071.8
7.5°	1058.7	1060.1	1058.7	1060.1	1060.1	1060.1	1058.7	1058.7
10°	1042.8	1042.8	1042.8	1042.8	1042.8	1041.2	1042.8	1042.8
12.5°	1020.9	1020.9	1020.9	1022.3	1022.3	1020.9	1020.9	1019.4
15°	997.6	994.7	996.1	997.6	996.1	996.1	996.1	996.1
17.5°	965.6	967.0	965.6	965.6	965.6	965.6	967.0	965.6
20°	932.0	932.0	933.4	932.0	932.0	932.0	932.0	930.6
22.5°	894.2	892.6	892.6	894.2	894.2	892.6	894.2	894.2
25°	852.0	853.4	852.0	852.0	853.4	853.4	853.4	852.0
27.5°	806.8	808.3	809.7	808.3	808.3	808.3	809.7	811.2
30°	760.1	763.1	760.1	760.1	763.1	761.7	763.1	763.1
32.5°	710.6	715.0	712.2	715.0	715.0	716.5	715.0	716.5
35°	661.2	665.5	665.5	665.5	667.0	668.4	668.4	667.0
37.5°	614.5	616.1	616.1	618.9	620.4	621.9	621.9	620.4
40°	566.5	569.4	570.9	570.9	570.9	573.7	576.7	573.7
42.5°	519.8	521.4	522.8	522.8	525.8	527.2	528.6	528.6
45°	474.8	477.6	479.1	480.6	482.0	485.0	483.4	486.4
47.5°	428.1	432.5	434.0	435.4	438.3	439.8	441.2	442.7
50°	385.9	388.9	388.9	391.7	396.1	396.1	399.0	400.5
52.5°	343.7	345.1	346.6	348.1	350.9	353.9	353.9	356.8
55°	302.9	304.4	304.4	305.8	307.3	313.1	314.5	314.5
57.5°	260.6	260.6	263.6	265.0	266.5	269.4	269.4	269.4
60°	219.9	221.4	221.4	222.8	224.2	227.2	228.6	227.2
62.5°	179.1	180.6	180.6	182.0	185.0	186.4	185.0	185.0
65°	141.2	142.7	142.7	144.2	147.0	147.0	145.6	147.0
67.5°	103.4	103.4	103.4	103.4	103.4	103.4	103.4	103.4
70°	65.5	64.1	62.6	64.1	64.1	64.1	62.6	65.5
72.5°	32.0	33.5	33.5	33.5	33.5	33.5	33.5	32.0
75°	14.5	14.5	13.1	13.1	13.1	14.5	14.5	13.1
77.5°	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4
80°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)