

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583982

Luminaire Tested: **HCC8W20D010BZ-HM80520827-81WWW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583982
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W20D010BZ-HM80520827-81WWW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1979.9 lumens
Efficiency: N/A
Efficacy: 99.0 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583982
CATALOG NUMBER: HCC8W20D010BZ-HM80520827-81WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583982

CATALOG NUMBER: HCC8W20D010BZ-HM80520827-81WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76								
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66								
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58								
5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51								
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	33081	33081	33081
5°	34241	32892	31586
10°	35004	32314	29809
15°	35503	31228	27838
20°	35395	29711	25839
25°	34521	27784	23725
30°	32705	25551	21766
35°	29754	23125	19782
40°	26133	20570	17873
45°	22790	18093	15935
50°	19827	15850	14032
55°	17688	13930	12209
60°	16066	12211	10417
65°	14447	10616	9449
70°	12866	9061	8529
75°	11271	7637	7280
80°	9572	6215	6464
85°	7182	4635	5130



TEST NUMBER: P583982
 CATALOG NUMBER: HCC8W20D010BZ-HM80520827-81WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.5	5.1
10°-20°	276.9	14.0
20°-30°	384.3	19.4
30°-40°	397.3	20.1
40°-50°	332.7	16.8
50°-60°	241.5	12.2
60°-70°	152.4	7.7
70°-80°	75.5	3.8
80°-90°	18.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	761.7	38.5
0°-40°	1159.0	58.5
0°-60°	1733.2	87.5
0°-90°	1979.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1979.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1073	1073	1073	1073	1073	
5°	1106	1093	1063	1034	1020	106
15°	1112	1070	978	900	872	313
25°	1015	949	817	728	697	465
35°	790	732	614	544	526	492
45°	523	485	415	374	365	404
55°	329	300	259	237	227	297
65°	198	173	146	128	130	197
75°	95	79	64	61	61	102
85°	20	16	13	14	14	25
90°	0	0	0	0	0	



TEST NUMBER: P583982

CATALOG NUMBER: HCC8W20D010BZ-HM80520827-81WWW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1072.8	1072.8	1072.8	1072.8	1072.8	1072.8	1072.8	1072.8	1072.8	1072.8	1072.8
2.5°	1090.3	1090.3	1091.7	1090.3	1090.3	1090.3	1088.9	1088.9	1087.3	1087.3	1084.5
5°	1106.2	1103.4	1106.2	1103.4	1103.4	1103.4	1101.9	1099.0	1097.5	1094.7	1093.2
7.5°	1113.6	1112.1	1112.1	1110.6	1110.6	1109.2	1107.8	1106.2	1100.4	1099.0	1094.7
10°	1117.9	1116.5	1116.5	1115.0	1112.1	1112.1	1109.2	1107.8	1100.4	1097.5	1091.7
12.5°	1116.5	1116.5	1116.5	1115.0	1110.6	1109.2	1106.2	1101.9	1096.1	1090.3	1084.5
15°	1112.1	1112.1	1109.2	1107.8	1103.4	1100.4	1099.0	1091.7	1085.9	1078.6	1069.8
17.5°	1097.5	1097.5	1096.1	1093.2	1088.9	1085.9	1082.9	1075.7	1069.8	1058.2	1049.5
20°	1078.6	1077.2	1075.7	1071.4	1067.0	1065.6	1061.2	1050.9	1043.7	1035.0	1023.3
22.5°	1050.9	1049.5	1048.1	1045.1	1037.9	1035.0	1032.0	1024.8	1011.7	1002.9	988.4
25°	1014.6	1014.6	1011.7	1007.3	1000.0	997.1	992.8	985.4	973.8	960.7	949.0
27.5°	972.3	970.9	966.5	963.6	957.8	953.4	946.2	937.4	925.7	915.6	901.0
30°	918.5	918.5	915.6	911.2	904.0	901.0	895.2	885.0	873.4	860.3	850.1
32.5°	857.4	857.4	853.0	850.1	845.7	838.4	837.0	825.4	815.1	804.9	793.4
35°	790.4	791.8	789.0	783.1	775.9	775.9	772.9	762.7	751.2	740.9	732.1
37.5°	723.5	719.1	717.6	714.8	710.4	704.5	701.6	697.3	687.1	679.8	666.6
40°	649.2	650.7	647.7	644.9	643.4	639.0	637.6	630.2	623.0	614.3	608.5
42.5°	582.3	582.3	582.3	579.3	576.5	572.1	570.6	566.3	557.5	551.6	542.9
45°	522.6	518.2	518.2	516.8	515.2	512.4	508.0	505.1	499.3	494.9	484.7
47.5°	464.3	465.8	464.3	462.9	458.5	457.1	455.7	449.8	444.0	439.6	432.4
50°	413.3	416.3	413.3	413.3	410.5	409.0	406.1	401.8	397.4	390.1	382.8
52.5°	371.1	371.1	369.7	368.3	363.9	361.0	359.6	358.0	350.8	345.0	339.1
55°	329.0	330.4	330.4	326.1	324.6	321.7	320.2	315.8	313.0	304.2	299.9
57.5°	292.5	291.1	292.5	289.7	286.8	283.8	282.4	279.4	275.2	269.3	263.5
60°	260.5	257.7	257.7	256.1	253.3	251.8	248.9	244.6	240.2	234.4	230.0
62.5°	228.5	227.1	225.6	224.2	221.3	219.9	218.3	213.9	209.6	205.2	200.8
65°	198.0	198.0	196.6	193.6	192.2	190.7	189.2	186.3	180.5	177.5	173.2
67.5°	170.3	168.9	168.9	166.0	163.0	161.6	161.6	158.6	154.3	149.9	147.0
70°	142.7	144.1	142.7	141.2	138.3	138.3	135.3	133.9	128.1	126.6	122.2
72.5°	118.0	118.0	116.4	116.4	113.6	112.1	112.1	109.2	106.3	103.3	100.5
75°	94.6	94.6	94.6	93.1	91.7	88.8	88.8	87.3	84.4	81.6	78.6
77.5°	74.2	72.8	72.8	71.3	69.9	68.4	68.4	66.9	64.1	62.6	59.7
80°	53.9	52.4	52.4	52.4	49.5	50.9	49.5	48.0	46.6	45.2	43.6
82.5°	35.0	36.4	36.4	35.0	33.5	33.5	33.5	32.0	32.0	30.6	29.1
85°	20.3	20.3	20.3	20.3	18.9	18.9	18.9	17.5	17.5	17.5	16.0
87.5°	8.7	8.7	8.7	8.7	8.7	8.7	7.3	7.3	7.3	7.3	7.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583982

CATALOG NUMBER: HCC8W20D010BZ-HM80520827-81WWW

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1072.8	1072.8	1072.8	1072.8	1072.8	1072.8	1072.8	1072.8	1072.8	1072.8	1072.8
2.5°	1084.5	1081.5	1080.1	1078.6	1078.6	1077.2	1075.7	1072.8	1072.8	1069.8	1068.4
5°	1090.3	1085.9	1082.9	1080.1	1078.6	1075.7	1072.8	1068.4	1067.0	1062.6	1058.2
7.5°	1091.7	1084.5	1081.5	1075.7	1072.8	1069.8	1064.0	1059.7	1053.9	1049.5	1043.7
10°	1085.9	1080.1	1072.8	1065.6	1064.0	1059.7	1050.9	1045.1	1037.9	1032.0	1023.3
12.5°	1077.2	1068.4	1061.2	1052.5	1048.1	1043.7	1035.0	1026.2	1016.0	1005.9	997.1
15°	1062.6	1052.5	1042.3	1032.0	1026.2	1021.8	1011.7	1001.5	991.2	978.2	969.5
17.5°	1040.8	1029.2	1018.9	1005.9	1000.0	995.6	982.6	970.9	957.8	944.7	936.0
20°	1013.1	998.6	987.0	972.3	967.9	960.7	947.6	934.5	920.0	905.4	895.2
22.5°	976.7	962.1	949.0	934.5	927.3	920.0	906.8	890.9	876.3	864.6	854.5
25°	934.5	921.4	905.4	892.3	883.5	874.8	860.3	847.1	834.0	816.6	806.4
27.5°	887.9	872.0	860.3	842.8	834.0	828.2	812.3	794.8	783.1	767.1	755.4
30°	835.6	821.0	807.9	790.4	781.7	775.9	761.3	745.3	733.7	717.6	706.0
32.5°	780.2	764.2	748.2	736.5	726.3	720.5	704.5	694.3	679.8	666.6	653.5
35°	720.5	704.5	692.9	676.8	671.0	665.2	652.1	639.0	625.9	614.3	604.1
37.5°	656.5	644.9	631.8	620.1	615.7	609.9	593.8	582.3	572.1	560.4	551.6
40°	593.8	583.7	574.9	563.3	556.0	551.6	540.1	529.9	518.2	511.0	502.2
42.5°	537.1	525.5	516.8	508.0	500.7	496.3	486.2	478.9	470.2	462.9	452.7
45°	477.4	471.6	461.5	454.1	449.8	444.0	436.6	428.0	420.7	414.9	407.6
47.5°	425.0	419.3	411.9	403.2	400.3	396.0	388.6	382.8	377.1	371.1	363.9
50°	377.1	369.7	363.9	358.0	355.2	350.8	343.5	340.7	336.3	330.4	326.1
52.5°	333.3	327.5	321.7	314.4	313.0	310.0	305.7	299.9	295.5	292.5	289.7
55°	294.1	288.2	283.8	278.0	276.6	273.6	267.8	264.9	262.0	259.1	256.1
57.5°	259.1	253.3	247.5	244.6	241.6	238.8	237.2	232.9	230.0	228.5	225.6
60°	227.1	221.3	216.9	212.5	211.1	209.6	206.7	203.8	200.8	198.0	196.6
62.5°	196.6	190.7	187.8	184.9	181.9	181.9	179.1	176.1	173.2	171.7	168.9
65°	168.9	166.0	161.6	157.2	155.8	155.8	151.4	149.9	148.5	145.5	142.7
67.5°	142.7	139.7	135.3	133.9	132.5	131.0	129.5	126.6	123.8	122.2	119.4
70°	119.4	116.4	113.6	112.1	110.6	109.2	106.3	104.8	101.9	100.5	98.9
72.5°	96.1	94.6	91.7	90.3	88.8	87.3	85.9	84.4	81.6	80.0	78.6
75°	77.2	75.6	72.8	71.3	69.9	69.9	68.4	65.5	64.1	64.1	62.6
77.5°	58.3	56.7	55.3	53.9	52.4	52.4	50.9	49.5	48.0	48.0	46.6
80°	42.2	40.8	39.4	39.4	39.4	37.8	36.4	36.4	35.0	35.0	33.5
82.5°	27.7	27.7	26.2	26.2	26.2	24.7	24.7	23.3	23.3	23.3	23.3
85°	16.0	16.0	16.0	14.5	14.5	14.5	14.5	14.5	14.5	13.1	14.5
87.5°	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3	5.8	5.8	5.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583982

CATALOG NUMBER: HCC8W20D010BZ-HM80520827-81WWW

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1072.8	1072.8	1072.8	1072.8	1072.8	1072.8	1072.8	1072.8	1072.8	1072.8	1072.8
2.5°	1067.0	1065.6	1062.6	1062.6	1059.7	1059.7	1058.2	1056.8	1055.3	1053.9	1052.5
5°	1056.8	1050.9	1048.1	1046.5	1043.7	1042.3	1037.9	1035.0	1033.5	1030.6	1027.6
7.5°	1037.9	1032.0	1026.2	1024.8	1023.3	1017.5	1013.1	1008.7	1005.9	1002.9	1000.0
10°	1016.0	1010.3	1002.9	1000.0	997.1	989.8	984.0	979.6	973.8	967.9	966.5
12.5°	989.8	981.1	972.3	969.5	965.1	957.8	952.0	944.7	940.3	933.1	931.7
15°	959.3	949.0	941.8	934.5	931.7	924.3	914.2	908.4	899.6	896.7	889.3
17.5°	922.9	912.6	902.5	899.6	895.2	885.0	874.8	867.6	858.8	854.5	850.1
20°	885.0	872.0	861.7	858.8	853.0	844.3	834.0	826.8	819.5	810.7	806.4
22.5°	841.3	826.8	818.1	810.7	809.3	799.2	787.4	781.7	775.9	768.5	762.7
25°	793.4	780.2	770.1	764.2	761.3	752.6	743.8	736.5	727.8	723.5	716.2
27.5°	743.8	735.1	722.0	716.2	711.8	704.5	694.3	689.9	681.2	675.4	671.0
30°	695.8	682.7	675.4	668.2	663.8	656.5	647.7	643.4	636.2	630.2	625.9
32.5°	643.4	634.6	624.5	621.5	615.7	608.5	602.6	595.4	589.6	583.7	582.3
35°	595.4	583.7	573.5	570.6	566.3	559.0	556.0	551.6	544.4	542.9	537.1
37.5°	542.9	537.1	525.5	521.1	519.6	513.8	508.0	505.1	500.7	496.3	494.9
40°	493.5	486.2	480.4	476.0	473.0	468.7	462.9	461.5	458.5	452.7	451.3
42.5°	446.9	439.6	433.8	432.4	428.0	423.6	420.7	416.3	414.9	413.3	410.5
45°	401.8	397.4	391.6	390.1	388.6	382.8	379.9	377.1	374.1	372.7	369.7
47.5°	361.0	356.6	352.2	350.8	347.9	346.4	342.1	340.7	336.3	334.7	333.3
50°	321.7	318.8	315.8	314.4	311.5	310.0	307.1	304.2	301.3	299.9	298.5
52.5°	286.8	283.8	281.0	279.4	278.0	275.2	272.2	269.3	267.8	266.4	264.9
55°	253.3	250.3	248.9	247.5	246.0	244.6	240.2	238.8	237.2	235.8	232.9
57.5°	222.7	219.9	216.9	216.9	215.5	213.9	211.1	208.2	208.2	205.2	202.4
60°	195.0	192.2	189.2	187.8	186.3	183.4	181.9	180.5	179.1	177.5	174.7
62.5°	166.0	164.5	161.6	161.6	158.6	157.2	155.8	154.3	152.8	149.9	148.5
65°	141.2	139.7	136.9	135.3	135.3	133.9	131.0	129.5	128.1	128.1	126.6
67.5°	118.0	116.4	113.6	112.1	112.1	110.6	109.2	109.2	107.7	106.3	107.7
70°	97.5	94.6	94.6	93.1	93.1	91.7	90.3	90.3	90.3	91.7	91.7
72.5°	77.2	75.6	74.2	74.2	74.2	74.2	72.8	72.8	74.2	75.6	75.6
75°	61.1	59.7	59.7	59.7	58.3	58.3	59.7	59.7	61.1	61.1	61.1
77.5°	45.2	45.2	45.2	45.2	45.2	45.2	46.6	46.6	48.0	48.0	48.0
80°	33.5	33.5	33.5	33.5	33.5	35.0	35.0	35.0	35.0	35.0	36.4
82.5°	23.3	23.3	23.3	23.3	23.3	23.3	23.3	24.7	24.7	24.7	24.7
85°	13.1	14.5	14.5	14.5	14.5	14.5	14.5	14.5	14.5	14.5	14.5
87.5°	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583982

CATALOG NUMBER: HCC8W20D010BZ-HM80520827-81WWW

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1072.8	1072.8	1072.8	1072.8	1072.8	1072.8	1072.8	1072.8
2.5°	1050.9	1050.9	1050.9	1052.5	1049.5	1049.5	1049.5	1049.5
5°	1026.2	1024.8	1023.3	1024.8	1021.8	1021.8	1020.4	1020.4
7.5°	995.6	994.2	992.8	992.8	989.8	989.8	988.4	987.0
10°	962.1	959.3	960.7	957.8	956.4	954.9	953.4	952.0
12.5°	925.7	922.9	921.4	918.5	915.6	914.2	915.6	912.6
15°	886.5	882.1	880.7	877.8	874.8	873.4	873.4	872.0
17.5°	842.8	839.9	838.4	835.6	834.0	831.2	829.8	828.2
20°	802.1	794.8	796.2	793.4	791.8	786.0	786.0	787.4
22.5°	757.0	752.6	749.6	746.8	745.3	742.4	742.4	740.9
25°	711.8	707.4	706.0	703.1	701.6	698.7	697.3	697.3
27.5°	668.2	662.3	662.3	659.4	656.5	655.1	653.5	652.1
30°	621.5	617.2	615.7	615.7	614.3	614.3	609.9	611.3
32.5°	577.9	574.9	573.5	570.6	570.6	569.1	569.1	564.8
35°	534.3	529.9	531.3	528.4	526.9	525.5	526.9	525.5
37.5°	491.9	489.1	489.1	486.2	486.2	484.7	483.3	486.2
40°	449.8	448.3	446.9	445.4	446.9	445.4	442.5	444.0
42.5°	407.6	407.6	406.1	406.1	404.7	404.7	404.7	404.7
45°	369.7	368.3	368.3	366.8	366.8	366.8	366.8	365.4
47.5°	331.9	330.4	330.4	330.4	329.0	329.0	327.5	329.0
50°	295.5	295.5	294.1	294.1	295.5	294.1	292.5	292.5
52.5°	262.0	262.0	260.5	260.5	259.1	257.7	259.1	259.1
55°	231.4	230.0	228.5	228.5	227.1	225.6	225.6	227.1
57.5°	202.4	200.8	199.4	199.4	196.6	195.0	195.0	195.0
60°	174.7	171.7	171.7	170.3	170.3	168.9	168.9	168.9
62.5°	148.5	147.0	147.0	147.0	147.0	145.5	145.5	145.5
65°	126.6	126.6	126.6	128.1	128.1	129.5	129.5	129.5
67.5°	109.2	110.6	110.6	110.6	112.1	112.1	112.1	110.6
70°	93.1	93.1	93.1	94.6	94.6	94.6	94.6	94.6
72.5°	77.2	77.2	77.2	77.2	77.2	77.2	77.2	77.2
75°	61.1	62.6	62.6	62.6	61.1	62.6	62.6	61.1
77.5°	48.0	48.0	48.0	48.0	48.0	48.0	48.0	48.0
80°	36.4	36.4	36.4	36.4	36.4	36.4	36.4	36.4
82.5°	24.7	24.7	24.7	24.7	24.7	24.7	24.7	24.7
85°	14.5	14.5	14.5	14.5	14.5	14.5	14.5	14.5
87.5°	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)