

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593633

Luminaire Tested: **HCC8S25D010MB-HM82555850-81WWW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593633
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S25D010MB-HM82555850-81WWW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2517.7 lumens
Efficiency: N/A
Efficacy: 93.9 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593633
CATALOG NUMBER: HCC8S25D010MB-HM82555850-81WWW

Luminous Intensity Polar Plot





TEST NUMBER: P593633

CATALOG NUMBER: HCC8S25D010MB-HM82555850-81WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76								
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66								
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58								
5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51								
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	42067	42067	42067
5°	43546	41828	40166
10°	44513	41094	37906
15°	45147	39710	35394
20°	45009	37780	32861
25°	43898	35331	30166
30°	41589	32495	27684
35°	37840	29404	25154
40°	33234	26153	22723
45°	28978	23004	20261
50°	25219	20158	17846
55°	22494	17714	15526
60°	20438	15529	13241
65°	18373	13506	12025
70°	16355	11522	10846
75°	14333	9698	9269
80°	12164	7885	8204
85°	9164	5909	6545



TEST NUMBER: P593633
 CATALOG NUMBER: HCC8S25D010MB-HM82555850-81WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.8	5.1
10°-20°	352.1	14.0
20°-30°	488.7	19.4
30°-40°	505.3	20.1
40°-50°	423.1	16.8
50°-60°	307.1	12.2
60°-70°	193.8	7.7
70°-80°	96.0	3.8
80°-90°	23.9	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	968.6	38.5
0°-40°	1473.8	58.5
0°-60°	2204.0	87.5
0°-90°	2517.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2517.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1364	1364	1364	1364	1364	
5°	1407	1390	1351	1314	1298	135
15°	1414	1360	1244	1144	1109	398
25°	1290	1207	1038	926	887	591
35°	1005	931	781	692	668	626
45°	664	616	528	476	465	514
55°	418	381	330	302	289	378
65°	252	220	185	163	165	251
75°	120	100	81	78	78	129
85°	26	20	17	18	18	31
90°	0	0	0	0	0	



TEST NUMBER: P593633

CATALOG NUMBER: HCC8S25D010MB-HM82555850-81WWW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1364.2	1364.2	1364.2	1364.2	1364.2	1364.2	1364.2	1364.2	1364.2	1364.2	1364.2
2.5°	1386.4	1386.4	1388.3	1386.4	1386.4	1386.4	1384.6	1384.6	1382.8	1382.8	1379.0
5°	1406.8	1403.1	1406.8	1403.1	1403.1	1403.1	1401.3	1397.5	1395.7	1392.0	1390.1
7.5°	1416.0	1414.2	1414.2	1412.3	1412.3	1410.5	1408.7	1406.8	1399.3	1397.5	1392.0
10°	1421.6	1419.8	1419.8	1417.9	1414.2	1414.2	1410.5	1408.7	1399.3	1395.7	1388.3
12.5°	1419.8	1419.8	1419.8	1417.9	1412.3	1410.5	1406.8	1401.3	1393.8	1386.4	1379.0
15°	1414.2	1414.2	1410.5	1408.7	1403.1	1399.3	1397.5	1388.3	1380.8	1371.6	1360.5
17.5°	1395.7	1395.7	1393.8	1390.1	1384.6	1380.8	1377.2	1367.9	1360.5	1345.7	1334.6
20°	1371.6	1369.8	1367.9	1362.3	1356.8	1354.9	1349.4	1336.4	1327.2	1316.1	1301.3
22.5°	1336.4	1334.6	1332.8	1329.0	1319.8	1316.1	1312.4	1303.2	1286.5	1275.3	1256.8
25°	1290.2	1290.2	1286.5	1280.9	1271.7	1268.0	1262.4	1253.2	1238.3	1221.7	1206.9
27.5°	1236.5	1234.7	1229.1	1225.4	1218.0	1212.4	1203.2	1192.1	1177.2	1164.3	1145.8
30°	1168.0	1168.0	1164.3	1158.7	1149.5	1145.8	1138.4	1125.4	1110.7	1094.0	1081.0
32.5°	1090.2	1090.2	1084.7	1081.0	1075.5	1066.1	1064.3	1049.6	1036.6	1023.7	1008.8
35°	1005.2	1007.0	1003.2	995.8	986.6	986.6	982.9	970.0	955.2	942.1	931.1
37.5°	920.0	914.4	912.6	908.9	903.3	895.9	892.2	886.6	873.7	864.5	847.8
40°	825.6	827.4	823.7	820.0	818.1	812.6	810.7	801.5	792.2	781.1	773.7
42.5°	740.4	740.4	740.4	736.7	733.1	727.5	725.6	720.0	709.0	701.5	690.5
45°	664.5	659.0	659.0	657.1	655.3	651.5	646.1	642.3	634.9	629.4	616.4
47.5°	590.5	592.4	590.5	588.6	583.0	581.2	579.4	572.0	564.5	559.0	549.8
50°	525.7	529.4	525.7	525.7	521.9	520.1	516.5	510.9	505.4	496.1	486.8
52.5°	472.0	472.0	470.2	468.3	462.8	459.0	457.2	455.4	446.1	438.7	431.3
55°	418.4	420.2	420.2	414.6	412.8	409.1	407.2	401.7	397.9	386.9	381.3
57.5°	372.0	370.2	372.0	368.4	364.7	360.9	359.1	355.3	349.9	342.4	335.0
60°	331.4	327.6	327.6	325.8	322.1	320.3	316.5	310.9	305.4	298.0	292.4
62.5°	290.6	288.8	286.9	285.0	281.4	279.5	277.7	272.1	266.5	261.0	255.4
65°	251.8	251.8	249.8	246.2	244.4	242.5	240.6	236.9	229.5	225.9	220.3
67.5°	216.6	214.7	214.7	211.0	207.4	205.4	205.4	201.8	196.2	190.7	186.9
70°	181.4	183.3	181.4	179.5	175.8	175.8	172.2	170.3	162.9	161.0	155.5
72.5°	149.9	149.9	148.1	148.1	144.3	142.5	142.5	138.8	135.1	131.4	127.8
75°	120.3	120.3	120.3	118.4	116.6	112.9	112.9	111.1	107.3	103.7	99.9
77.5°	94.4	92.6	92.6	90.7	88.8	87.0	87.0	85.2	81.4	79.6	75.9
80°	68.5	66.7	66.7	66.7	62.9	64.7	62.9	61.1	59.3	57.4	55.5
82.5°	44.4	46.2	46.2	44.4	42.6	42.6	42.6	40.8	40.8	38.8	37.0
85°	25.9	25.9	25.9	25.9	24.1	24.1	24.1	22.3	22.3	22.3	20.3
87.5°	11.1	11.1	11.1	11.1	11.1	11.1	9.2	9.2	9.2	9.2	9.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593633

CATALOG NUMBER: HCC8S25D010MB-HM82555850-81WWW

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1364.2	1364.2	1364.2	1364.2	1364.2	1364.2	1364.2	1364.2	1364.2	1364.2	1364.2
2.5°	1379.0	1375.3	1373.5	1371.6	1371.6	1369.8	1367.9	1364.2	1364.2	1360.5	1358.7
5°	1386.4	1380.8	1377.2	1373.5	1371.6	1367.9	1364.2	1358.7	1356.8	1351.3	1345.7
7.5°	1388.3	1379.0	1375.3	1367.9	1364.2	1360.5	1353.1	1347.6	1340.2	1334.6	1327.2
10°	1380.8	1373.5	1364.2	1354.9	1353.1	1347.6	1336.4	1329.0	1319.8	1312.4	1301.3
12.5°	1369.8	1358.7	1349.4	1338.2	1332.8	1327.2	1316.1	1305.0	1292.0	1279.1	1268.0
15°	1351.3	1338.2	1325.3	1312.4	1305.0	1299.4	1286.5	1273.5	1260.6	1243.9	1232.7
17.5°	1323.5	1308.7	1295.8	1279.1	1271.7	1266.1	1249.4	1234.7	1218.0	1201.3	1190.3
20°	1288.3	1269.8	1255.0	1236.5	1230.9	1221.7	1205.0	1188.3	1169.8	1151.3	1138.4
22.5°	1242.1	1223.5	1206.9	1188.3	1179.1	1169.8	1153.2	1132.8	1114.3	1099.5	1086.6
25°	1188.3	1171.8	1151.3	1134.7	1123.6	1112.5	1094.0	1077.3	1060.7	1038.4	1025.5
27.5°	1129.2	1108.7	1094.0	1071.7	1060.7	1053.2	1032.9	1010.6	995.8	975.5	960.6
30°	1062.5	1044.0	1027.3	1005.2	994.0	986.6	968.1	947.7	932.9	912.6	897.7
32.5°	992.2	971.8	951.4	936.7	923.6	916.2	895.9	883.0	864.5	847.8	831.1
35°	916.2	895.9	881.1	860.7	853.3	845.9	829.2	812.6	796.0	781.1	768.2
37.5°	834.8	820.0	803.4	788.6	783.0	775.5	755.2	740.4	727.5	712.6	701.5
40°	755.2	742.3	731.1	716.4	707.1	701.5	686.7	673.8	659.0	649.7	638.6
42.5°	683.0	668.2	657.1	646.1	636.8	631.2	618.2	609.0	597.9	588.6	575.7
45°	607.1	599.7	586.8	577.5	572.0	564.5	555.3	544.2	535.0	527.5	518.3
47.5°	540.5	533.1	523.9	512.7	509.0	503.4	494.2	486.8	479.5	472.0	462.8
50°	479.5	470.2	462.8	455.4	451.6	446.1	436.9	433.1	427.6	420.2	414.6
52.5°	423.9	416.4	409.1	399.9	397.9	394.3	388.7	381.3	375.8	372.0	368.4
55°	373.9	366.5	360.9	353.5	351.7	348.0	340.6	336.8	333.2	329.5	325.8
57.5°	329.5	322.1	314.7	310.9	307.3	303.6	301.7	296.2	292.4	290.6	286.9
60°	288.8	281.4	275.8	270.3	268.4	266.5	262.9	259.2	255.4	251.8	249.8
62.5°	249.8	242.5	238.8	235.1	231.3	231.3	227.7	224.0	220.3	218.4	214.7
65°	214.7	211.0	205.4	199.9	198.1	198.1	192.5	190.7	188.9	185.1	181.4
67.5°	181.4	177.7	172.2	170.3	168.4	166.6	164.8	161.0	157.3	155.5	151.8
70°	151.8	148.1	144.3	142.5	140.7	138.8	135.1	133.3	129.6	127.8	125.8
72.5°	122.2	120.3	116.6	114.8	112.9	111.1	109.2	107.3	103.7	101.8	99.9
75°	98.1	96.3	92.6	90.7	88.8	88.8	87.0	83.2	81.4	81.4	79.6
77.5°	74.0	72.2	70.3	68.5	66.7	66.7	64.7	62.9	61.1	61.1	59.3
80°	53.7	51.8	50.0	50.0	50.0	48.2	46.2	46.2	44.4	44.4	42.6
82.5°	35.2	35.2	33.3	33.3	33.3	31.5	31.5	29.6	29.6	29.6	29.6
85°	20.3	20.3	20.3	18.5	18.5	18.5	18.5	18.5	18.5	16.7	18.5
87.5°	9.2	9.2	9.2	9.2	9.2	9.2	9.2	9.2	7.4	7.4	7.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593633

CATALOG NUMBER: HCC8S25D010MB-HM82555850-81WWW

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1364.2	1364.2	1364.2	1364.2	1364.2	1364.2	1364.2	1364.2	1364.2	1364.2	1364.2
2.5°	1356.8	1354.9	1351.3	1351.3	1347.6	1347.6	1345.7	1343.8	1342.0	1340.2	1338.2
5°	1343.8	1336.4	1332.8	1330.9	1327.2	1325.3	1319.8	1316.1	1314.3	1310.5	1306.8
7.5°	1319.8	1312.4	1305.0	1303.2	1301.3	1293.8	1288.3	1282.8	1279.1	1275.3	1271.7
10°	1292.0	1284.6	1275.3	1271.7	1268.0	1258.7	1251.3	1245.8	1238.3	1230.9	1229.1
12.5°	1258.7	1247.6	1236.5	1232.7	1227.3	1218.0	1210.6	1201.3	1195.7	1186.5	1184.7
15°	1219.8	1206.9	1197.7	1188.3	1184.7	1175.4	1162.4	1155.1	1143.9	1140.2	1131.0
17.5°	1173.6	1160.6	1147.7	1143.9	1138.4	1125.4	1112.5	1103.2	1092.1	1086.6	1081.0
20°	1125.4	1108.7	1095.8	1092.1	1084.7	1073.6	1060.7	1051.4	1042.2	1031.1	1025.5
22.5°	1069.9	1051.4	1040.3	1031.1	1029.1	1016.2	1001.4	994.0	986.6	977.3	970.0
25°	1008.8	992.2	979.2	971.8	968.1	957.0	945.9	936.7	925.6	920.0	910.7
27.5°	945.9	934.8	918.2	910.7	905.1	895.9	883.0	877.4	866.3	858.9	853.3
30°	884.8	868.1	858.9	849.6	844.1	834.8	823.7	818.1	808.9	801.5	796.0
32.5°	818.1	807.1	794.0	790.4	783.0	773.7	766.3	757.0	749.6	742.3	740.4
35°	757.0	742.3	729.3	725.6	720.0	710.8	707.1	701.5	692.3	690.5	683.0
37.5°	690.5	683.0	668.2	662.7	660.8	653.4	646.1	642.3	636.8	631.2	629.4
40°	627.6	618.2	610.9	605.3	601.6	596.0	588.6	586.8	583.0	575.7	573.8
42.5°	568.3	559.0	551.6	549.8	544.2	538.6	535.0	529.4	527.5	525.7	521.9
45°	510.9	505.4	498.0	496.1	494.2	486.8	483.1	479.5	475.7	473.9	470.2
47.5°	459.0	453.5	447.9	446.1	442.4	440.5	435.0	433.1	427.6	425.8	423.9
50°	409.1	405.4	401.7	399.9	396.1	394.3	390.6	386.9	383.2	381.3	379.4
52.5°	364.7	360.9	357.3	355.3	353.5	349.9	346.1	342.4	340.6	338.8	336.8
55°	322.1	318.4	316.5	314.7	312.9	310.9	305.4	303.6	301.7	299.9	296.2
57.5°	283.2	279.5	275.8	275.8	273.9	272.1	268.4	264.7	264.7	261.0	257.3
60°	248.0	244.4	240.6	238.8	236.9	233.3	231.3	229.5	227.7	225.9	222.1
62.5°	211.0	209.2	205.4	205.4	201.8	199.9	198.1	196.2	194.3	190.7	188.9
65°	179.5	177.7	174.0	172.2	172.2	170.3	166.6	164.8	162.9	162.9	161.0
67.5°	149.9	148.1	144.3	142.5	142.5	140.7	138.8	138.8	137.0	135.1	137.0
70°	124.0	120.3	120.3	118.4	118.4	116.6	114.8	114.8	114.8	116.6	116.6
72.5°	98.1	96.3	94.4	94.4	94.4	94.4	92.6	92.6	94.4	96.3	96.3
75°	77.8	75.9	75.9	75.9	74.0	74.0	75.9	75.9	77.8	77.8	77.8
77.5°	57.4	57.4	57.4	57.4	57.4	57.4	59.3	59.3	61.1	61.1	61.1
80°	42.6	42.6	42.6	42.6	42.6	44.4	44.4	44.4	44.4	44.4	46.2
82.5°	29.6	29.6	29.6	29.6	29.6	29.6	29.6	31.5	31.5	31.5	31.5
85°	16.7	18.5	18.5	18.5	18.5	18.5	18.5	18.5	18.5	18.5	18.5
87.5°	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593633

CATALOG NUMBER: HCC8S25D010MB-HM82555850-81WWW

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1364.2	1364.2	1364.2	1364.2	1364.2	1364.2	1364.2	1364.2
2.5°	1336.4	1336.4	1336.4	1338.2	1334.6	1334.6	1334.6	1334.6
5°	1305.0	1303.2	1301.3	1303.2	1299.4	1299.4	1297.6	1297.6
7.5°	1266.1	1264.3	1262.4	1262.4	1258.7	1258.7	1256.8	1255.0
10°	1223.5	1219.8	1221.7	1218.0	1216.2	1214.2	1212.4	1210.6
12.5°	1177.2	1173.6	1171.8	1168.0	1164.3	1162.4	1164.3	1160.6
15°	1127.2	1121.7	1119.9	1116.2	1112.5	1110.7	1110.7	1108.7
17.5°	1071.7	1068.1	1066.1	1062.5	1060.7	1056.9	1055.1	1053.2
20°	1019.9	1010.6	1012.5	1008.8	1007.0	999.6	999.6	1001.4
22.5°	962.6	957.0	953.3	949.6	947.7	944.1	944.1	942.1
25°	905.1	899.7	897.7	894.1	892.2	888.5	886.6	886.6
27.5°	849.6	842.2	842.2	838.6	834.8	833.0	831.1	829.2
30°	790.4	784.8	783.0	783.0	781.1	781.1	775.5	777.5
32.5°	734.9	731.1	729.3	725.6	725.6	723.7	723.7	718.2
35°	679.3	673.8	675.6	672.0	670.0	668.2	670.0	668.2
37.5°	625.6	622.0	622.0	618.2	618.2	616.4	614.5	618.2
40°	572.0	570.1	568.3	566.5	568.3	566.5	562.7	564.5
42.5°	518.3	518.3	516.5	516.5	514.6	514.6	514.6	514.6
45°	470.2	468.3	468.3	466.4	466.4	466.4	466.4	464.6
47.5°	422.0	420.2	420.2	420.2	418.4	418.4	416.4	418.4
50°	375.8	375.8	373.9	373.9	375.8	373.9	372.0	372.0
52.5°	333.2	333.2	331.4	331.4	329.5	327.6	329.5	329.5
55°	294.4	292.4	290.6	290.6	288.8	286.9	286.9	288.8
57.5°	257.3	255.4	253.6	253.6	249.8	248.0	248.0	248.0
60°	222.1	218.4	218.4	216.6	216.6	214.7	214.7	214.7
62.5°	188.9	186.9	186.9	186.9	186.9	185.1	185.1	185.1
65°	161.0	161.0	161.0	162.9	162.9	164.8	164.8	164.8
67.5°	138.8	140.7	140.7	140.7	142.5	142.5	142.5	140.7
70°	118.4	118.4	118.4	120.3	120.3	120.3	120.3	120.3
72.5°	98.1	98.1	98.1	98.1	98.1	98.1	98.1	98.1
75°	77.8	79.6	79.6	79.6	77.8	79.6	79.6	77.8
77.5°	61.1	61.1	61.1	61.1	61.1	61.1	61.1	61.1
80°	46.2	46.2	46.2	46.2	46.2	46.2	46.2	46.2
82.5°	31.5	31.5	31.5	31.5	31.5	31.5	31.5	31.5
85°	18.5	18.5	18.5	18.5	18.5	18.5	18.5	18.5
87.5°	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)