

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593632

Luminaire Tested: **HCC8W25D010MW-HM82555850-81WWBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593632
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W25D010MW-HM82555850-81WWBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2306.7 lumens
Efficiency: N/A
Efficacy: 86.1 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593632
CATALOG NUMBER: HCC8W25D010MW-HM82555850-81WWBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593632

CATALOG NUMBER: HCC8W25D010MW-HM82555850-81WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77								
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67								
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59								
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47								
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43								
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39								
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	38185	38185	38185
5°	39764	38101	36498
10°	41094	37615	34716
15°	42133	36754	32917
20°	42217	35231	31283
25°	41503	33003	29662
30°	39285	30447	28279
35°	35815	27386	26547
40°	31144	24140	24515
45°	26719	20911	22441
50°	22821	18028	20158
55°	19999	15526	17515
60°	17811	13241	14727
65°	15804	10806	11747
70°	14020	8006	6672
75°	11688	4194	1990
80°	9199	1314	320
85°	6545	637	0



TEST NUMBER: P593632
 CATALOG NUMBER: HCC8W25D010MW-HM82555850-81WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.7	5.1
10°-20°	327.1	14.2
20°-30°	462.9	20.1
30°-40°	484.3	21.0
40°-50°	403.9	17.5
50°-60°	286.4	12.4
60°-70°	165.0	7.2
70°-80°	53.1	2.3
80°-90°	7.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	906.6	39.3
0°-40°	1390.9	60.3
0°-60°	2081.3	90.2
0°-90°	2306.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2306.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1238	1238	1238	1238	1238	
5°	1285	1268	1231	1194	1179	123
15°	1320	1266	1151	1061	1031	371
25°	1220	1129	970	892	872	557
35°	951	868	728	688	705	590
45°	613	563	480	485	515	475
55°	372	333	289	304	326	336
65°	217	181	148	148	161	216
75°	98	72	35	17	17	106
85°	18	9	2	0	0	23
90°	0	0	0	0	0	



TEST NUMBER: P593632

CATALOG NUMBER: HCC8W25D010MW-HM82555850-81WWBB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3
2.5°	1264.3	1262.4	1260.6	1262.4	1260.6	1262.4	1260.6	1260.6	1258.7	1256.8	1256.8
5°	1284.6	1282.8	1282.8	1282.8	1280.9	1279.1	1279.1	1277.3	1273.5	1271.7	1268.0
7.5°	1297.6	1299.4	1299.4	1299.4	1295.8	1295.8	1292.0	1288.4	1284.6	1280.9	1275.3
10°	1312.4	1312.4	1310.5	1308.7	1305.0	1303.2	1301.3	1297.6	1292.0	1284.6	1279.1
12.5°	1317.9	1317.9	1316.1	1312.4	1310.5	1308.7	1306.8	1301.3	1293.8	1284.6	1277.3
15°	1319.8	1316.1	1314.3	1312.4	1308.7	1303.2	1303.2	1295.8	1286.5	1275.3	1266.1
17.5°	1305.0	1306.8	1303.2	1299.4	1293.8	1290.2	1284.6	1279.1	1268.0	1255.0	1245.8
20°	1286.5	1284.6	1282.8	1277.3	1269.9	1268.0	1262.4	1253.2	1243.9	1229.1	1216.2
22.5°	1256.8	1255.0	1251.4	1247.6	1240.2	1236.5	1230.9	1219.8	1206.9	1192.1	1177.3
25°	1219.8	1216.2	1210.6	1203.2	1197.7	1193.9	1186.5	1175.4	1160.6	1143.9	1129.2
27.5°	1160.6	1166.2	1162.4	1151.3	1145.8	1138.4	1136.6	1121.8	1108.7	1092.1	1075.5
30°	1103.3	1103.3	1097.7	1092.1	1082.8	1077.3	1069.9	1058.8	1045.8	1025.5	1012.5
32.5°	1031.1	1029.2	1021.7	1019.9	1012.5	1001.4	999.6	984.7	971.8	957.0	940.3
35°	951.4	947.7	940.3	934.8	931.1	925.6	920.0	907.0	894.1	879.2	868.1
37.5°	860.7	860.7	858.9	849.7	845.9	842.2	836.6	823.7	816.3	801.5	790.4
40°	773.7	771.9	766.3	764.5	760.8	755.2	751.6	744.1	733.1	721.9	710.8
42.5°	688.5	690.5	683.1	684.9	677.5	673.8	672.0	660.8	655.3	644.1	634.9
45°	612.7	610.9	607.1	605.3	601.6	597.9	594.2	588.6	579.4	568.3	562.7
47.5°	542.4	536.8	536.8	535.0	533.1	525.7	523.9	518.3	512.7	501.6	494.2
50°	475.7	475.7	475.7	473.9	468.3	466.4	462.8	457.2	451.6	444.3	433.1
52.5°	422.0	422.0	422.0	420.2	412.8	411.0	409.1	401.7	394.3	388.7	381.3
55°	372.0	374.0	372.0	368.4	362.8	362.8	357.3	353.5	346.1	340.6	333.2
57.5°	329.5	329.5	325.8	323.9	320.3	318.4	314.7	310.9	301.7	296.2	286.9
60°	288.8	286.9	286.9	283.2	279.5	275.8	273.9	268.4	264.7	255.4	248.0
62.5°	251.8	251.8	248.0	248.0	240.6	240.6	238.8	233.3	227.7	218.4	214.7
65°	216.6	216.6	214.7	212.8	207.4	205.4	203.6	198.1	192.5	186.9	181.4
67.5°	185.1	185.1	181.4	179.5	175.8	174.0	170.3	166.6	161.0	155.5	149.9
70°	155.5	153.7	151.8	149.9	146.3	144.3	140.7	137.0	131.4	127.8	122.2
72.5°	125.8	125.8	124.0	120.3	118.4	116.6	114.8	111.1	105.5	99.9	96.3
75°	98.1	98.1	98.1	94.4	90.7	88.8	88.8	85.2	81.4	75.9	72.2
77.5°	75.9	74.0	72.2	72.2	68.5	66.7	64.7	62.9	57.4	55.5	51.8
80°	51.8	53.7	51.8	50.0	48.2	46.2	46.2	42.6	40.8	37.0	33.3
82.5°	35.2	33.3	33.3	31.5	31.5	29.6	29.6	25.9	24.1	22.3	20.3
85°	18.5	18.5	16.7	16.7	16.7	14.8	14.8	12.9	12.9	11.1	9.2
87.5°	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6	3.7	3.7	3.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593632

CATALOG NUMBER: HCC8W25D010MW-HM82555850-81WWBB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3
2.5°	1255.0	1251.4	1249.4	1249.4	1247.6	1245.8	1243.9	1242.1	1238.3	1238.3	1234.7
5°	1264.3	1260.6	1258.7	1253.2	1249.4	1249.4	1242.1	1240.2	1234.7	1230.9	1227.3
7.5°	1271.7	1264.3	1258.7	1253.2	1249.4	1245.8	1238.3	1230.9	1223.5	1216.2	1212.4
10°	1271.7	1264.3	1255.0	1245.8	1242.1	1238.3	1229.1	1218.0	1208.8	1201.3	1192.1
12.5°	1268.0	1256.8	1245.8	1238.3	1230.9	1225.4	1214.3	1203.2	1192.1	1177.3	1169.8
15°	1256.8	1242.1	1230.9	1218.0	1212.4	1203.2	1193.9	1177.3	1164.3	1151.3	1142.1
17.5°	1234.7	1216.2	1203.2	1190.3	1181.0	1175.4	1160.6	1145.8	1131.0	1116.2	1105.1
20°	1201.3	1184.7	1169.8	1153.2	1145.8	1138.4	1119.9	1105.1	1090.2	1073.6	1062.5
22.5°	1160.6	1143.9	1123.6	1110.7	1099.5	1090.2	1073.6	1056.9	1042.2	1027.3	1012.5
25°	1110.7	1094.0	1075.5	1055.1	1047.7	1038.4	1019.9	1003.2	986.6	970.0	957.0
27.5°	1056.9	1034.7	1019.9	997.7	990.3	981.1	960.6	942.1	927.4	914.4	899.7
30°	992.2	975.5	955.2	934.8	927.4	918.2	901.5	884.8	870.0	855.1	840.4
32.5°	921.8	905.1	884.8	870.0	858.9	851.5	834.8	820.0	805.2	790.4	777.5
35°	847.8	829.2	814.5	799.6	790.4	781.1	764.5	751.6	740.4	727.5	714.5
37.5°	771.9	759.0	744.1	727.5	718.2	710.8	697.9	683.1	673.8	662.7	653.4
40°	697.9	683.1	670.0	655.3	647.9	642.3	629.4	618.2	609.0	599.7	594.2
42.5°	622.0	609.0	596.0	586.8	581.2	575.7	566.5	553.5	547.9	538.6	533.1
45°	551.6	540.5	531.3	518.3	514.6	510.9	499.8	490.5	484.9	479.5	475.7
47.5°	484.9	477.5	466.4	459.0	453.5	449.8	442.4	435.0	429.5	425.8	422.0
50°	427.6	418.4	411.0	403.5	399.9	394.3	386.9	383.2	379.4	375.8	375.8
52.5°	374.0	364.7	357.3	351.7	348.0	344.3	338.8	336.9	333.2	333.2	331.4
55°	323.9	318.4	310.9	303.6	301.7	299.9	296.2	292.4	290.6	288.8	290.6
57.5°	281.4	275.8	268.4	262.9	261.0	259.2	257.3	253.6	251.8	251.8	251.8
60°	242.5	236.9	231.3	225.9	225.9	222.1	220.3	218.4	216.6	214.7	214.7
62.5°	207.4	201.8	196.2	192.5	190.7	188.9	185.1	183.3	181.4	181.4	179.5
65°	175.8	168.4	166.6	161.0	159.2	157.3	155.5	151.8	149.9	148.1	146.3
67.5°	144.3	140.7	135.1	131.4	129.6	127.8	125.8	122.2	120.3	118.4	114.8
70°	116.6	112.9	109.2	105.5	103.7	101.8	98.1	94.4	92.6	88.8	83.2
72.5°	90.7	87.0	83.2	79.6	77.8	75.9	72.2	68.5	64.7	61.1	57.4
75°	68.5	64.7	59.3	55.5	53.7	53.7	48.2	44.4	40.8	35.2	31.5
77.5°	48.2	42.6	40.8	37.0	35.2	31.5	27.7	24.1	20.3	18.5	14.8
80°	31.5	27.7	24.1	22.3	20.3	18.5	16.7	12.9	9.2	7.4	5.6
82.5°	18.5	16.7	14.8	12.9	11.1	9.2	7.4	7.4	5.6	3.7	1.8
85°	9.2	7.4	5.6	5.6	3.7	3.7	3.7	1.8	1.8	1.8	1.8
87.5°	3.7	1.8	1.8	1.8	1.8	1.8	1.8	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593632

CATALOG NUMBER: HCC8W25D010MW-HM82555850-81WWBB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3
2.5°	1232.9	1230.9	1229.1	1227.3	1227.3	1223.5	1223.5	1221.7	1218.0	1216.2	1216.2
5°	1221.7	1216.2	1212.4	1210.6	1208.8	1203.2	1201.3	1197.7	1193.9	1190.3	1188.3
7.5°	1205.0	1195.8	1192.1	1190.3	1184.7	1179.1	1175.4	1169.8	1164.3	1158.8	1156.9
10°	1184.7	1175.4	1166.2	1162.4	1156.9	1153.2	1145.8	1138.4	1132.8	1127.2	1121.8
12.5°	1158.8	1147.7	1138.4	1134.7	1129.2	1121.8	1110.7	1106.9	1097.7	1094.0	1086.6
15°	1129.2	1116.2	1106.9	1101.4	1095.8	1084.8	1077.3	1069.9	1060.7	1056.9	1049.6
17.5°	1092.1	1077.3	1068.1	1062.5	1058.8	1049.6	1038.4	1029.2	1019.9	1016.2	1010.7
20°	1047.7	1038.4	1025.5	1019.9	1016.2	1005.2	994.0	990.3	982.9	975.5	970.0
22.5°	997.7	988.5	975.5	970.0	968.1	958.8	949.6	944.1	938.5	932.9	927.4
25°	945.9	934.8	923.6	920.0	916.2	908.9	901.5	897.7	892.2	888.5	884.8
27.5°	890.3	879.2	870.0	864.5	860.7	855.1	851.5	847.8	844.1	840.4	838.6
30°	831.2	820.0	812.7	808.9	805.2	803.4	797.8	796.0	794.2	790.4	792.2
32.5°	771.9	762.6	755.2	749.6	749.6	746.0	744.1	744.1	742.3	742.3	742.3
35°	707.1	701.6	696.0	694.1	692.3	690.5	688.5	690.5	688.5	690.5	692.3
37.5°	647.9	642.3	638.6	636.8	634.9	636.8	634.9	634.9	636.8	640.5	642.3
40°	586.8	583.0	579.4	581.2	579.4	579.4	579.4	585.0	586.8	588.6	590.5
42.5°	529.4	525.7	523.9	523.9	525.7	523.9	527.5	529.4	533.1	538.6	542.4
45°	473.9	472.0	472.0	473.9	472.0	475.7	475.7	479.5	484.9	488.7	492.4
47.5°	422.0	422.0	422.0	423.9	423.9	425.8	429.5	431.3	435.0	438.7	442.4
50°	374.0	375.8	377.6	377.6	377.6	381.3	385.0	386.9	388.7	390.6	396.1
52.5°	331.4	333.2	333.2	335.0	336.9	338.8	340.6	344.3	346.1	349.9	351.7
55°	290.6	290.6	294.4	296.2	296.2	296.2	299.9	299.9	303.6	305.4	309.1
57.5°	251.8	253.6	253.6	255.4	255.4	257.3	259.2	261.0	262.9	264.7	266.5
60°	214.7	214.7	214.7	216.6	218.4	220.3	218.4	222.1	222.1	225.9	227.7
62.5°	179.5	181.4	181.4	181.4	181.4	181.4	181.4	183.3	185.1	186.9	188.9
65°	146.3	146.3	146.3	144.3	146.3	144.3	146.3	148.1	148.1	149.9	151.8
67.5°	112.9	112.9	109.2	109.2	111.1	111.1	111.1	111.1	109.2	112.9	112.9
70°	81.4	79.6	77.8	75.9	75.9	74.0	74.0	72.2	72.2	72.2	72.2
72.5°	53.7	50.0	46.2	44.4	42.6	42.6	38.8	37.0	38.8	38.8	38.8
75°	27.7	24.1	22.3	20.3	18.5	18.5	16.7	16.7	16.7	16.7	16.7
77.5°	11.1	9.2	7.4	7.4	5.6	5.6	5.6	5.6	5.6	5.6	5.6
80°	3.7	3.7	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8
82.5°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8
85°	1.8	0.0	0.0	1.8	0.0	1.8	1.8	1.8	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593632

CATALOG NUMBER: HCC8W25D010MW-HM82555850-81WWBB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3
2.5°	1214.3	1214.3	1212.4	1214.3	1210.6	1212.4	1210.6	1210.6
5°	1186.5	1182.8	1182.8	1182.8	1181.0	1181.0	1179.1	1179.1
7.5°	1153.2	1151.3	1149.5	1147.7	1145.8	1143.9	1143.9	1143.9
10°	1119.9	1116.2	1116.2	1114.3	1110.7	1108.7	1108.7	1108.7
12.5°	1081.0	1079.2	1077.3	1077.3	1069.9	1071.7	1069.9	1069.9
15°	1044.0	1042.2	1042.2	1036.6	1032.9	1032.9	1032.9	1031.1
17.5°	1005.2	1003.2	1001.4	997.7	994.0	994.0	992.2	994.0
20°	964.4	962.6	958.8	958.8	957.0	955.2	951.4	953.3
22.5°	923.6	920.0	918.2	918.2	916.2	916.2	912.6	912.6
25°	881.1	879.2	877.4	879.2	875.6	875.6	871.8	871.8
27.5°	836.6	834.8	834.8	834.8	833.0	834.8	833.0	833.0
30°	792.2	792.2	790.4	790.4	792.2	790.4	792.2	794.2
32.5°	744.1	744.1	746.0	746.0	747.8	747.8	747.8	747.8
35°	694.1	697.9	697.9	699.7	701.6	703.4	703.4	705.2
37.5°	647.9	649.7	651.5	653.4	657.1	657.1	657.1	657.1
40°	597.9	599.7	603.5	601.6	609.0	610.9	609.0	609.0
42.5°	546.0	549.8	551.6	555.3	557.1	560.9	562.7	562.7
45°	498.0	499.8	503.4	507.2	509.0	514.6	514.6	514.6
47.5°	447.9	451.6	453.5	457.2	459.0	464.6	466.4	464.6
50°	399.9	403.5	407.2	407.2	412.8	414.6	418.4	420.2
52.5°	353.5	355.5	359.1	360.9	364.7	368.4	370.2	372.0
55°	309.1	310.9	314.7	314.7	320.3	322.1	325.8	325.8
57.5°	268.4	270.3	273.9	272.1	275.8	279.5	279.5	277.7
60°	229.5	229.5	229.5	233.3	235.1	236.9	238.8	238.8
62.5°	188.9	192.5	194.3	194.3	196.2	198.1	198.1	196.2
65°	151.8	155.5	157.3	157.3	159.2	159.2	159.2	161.0
67.5°	114.8	114.8	114.8	116.6	114.8	114.8	114.8	114.8
70°	72.2	72.2	72.2	72.2	70.3	72.2	72.2	74.0
72.5°	38.8	38.8	38.8	38.8	38.8	38.8	38.8	38.8
75°	16.7	16.7	16.7	18.5	16.7	16.7	16.7	16.7
77.5°	7.4	5.6	7.4	7.4	5.6	5.6	5.6	5.6
80°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8
82.5°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8
85°	0.0	1.8	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)