

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583999

Luminaire Tested: **HCC8W20D010MW-HM80520830-81WWW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583999
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W20D010MW-HM80520830-81WWW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1969.1 lumens
Efficiency: N/A
Efficacy: 98.5 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583999
CATALOG NUMBER: HCC8W20D010MW-HM80520830-81WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583999

CATALOG NUMBER: HCC8W20D010MW-HM80520830-81WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76								
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66								
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58								
5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51								
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	32902	32902	32902
5°	34059	32712	31415
10°	34816	32139	29646
15°	35311	31059	27685
20°	35204	29547	25701
25°	34334	27634	23596
30°	32530	25413	21649
35°	29592	23001	19677
40°	25992	20453	17776
45°	22664	17993	15843
50°	19722	15764	13960
55°	17591	13854	12145
60°	15979	12143	10361
65°	14367	10565	9398
70°	12785	9007	8484
75°	11211	7589	7244
80°	9500	6180	6428
85°	7147	4599	5095



TEST NUMBER: P583999
 CATALOG NUMBER: HCC8W20D010MW-HM80520830-81WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.9	5.1
10°-20°	275.4	14.0
20°-30°	382.2	19.4
30°-40°	395.2	20.1
40°-50°	330.9	16.8
50°-60°	240.2	12.2
60°-70°	151.6	7.7
70°-80°	75.1	3.8
80°-90°	18.6	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	757.5	38.5
0°-40°	1152.7	58.5
0°-60°	1723.8	87.5
0°-90°	1969.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1969.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1067	1067	1067	1067	1067	
5°	1100	1087	1057	1028	1015	105
15°	1106	1064	973	895	867	311
25°	1009	944	812	724	694	462
35°	786	728	611	542	523	490
45°	520	482	413	372	363	402
55°	327	298	258	236	226	295
65°	197	172	145	127	129	196
75°	94	78	64	61	61	101
85°	20	16	13	14	14	25
90°	0	0	0	0	0	



TEST NUMBER: P583999

CATALOG NUMBER: HCC8W20D010MW-HM80520830-81WWW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0
2.5°	1084.4	1084.4	1085.8	1084.4	1084.4	1084.4	1082.9	1082.9	1081.4	1081.4	1078.6
5°	1100.3	1097.4	1100.3	1097.4	1097.4	1097.4	1096.0	1093.0	1091.6	1088.7	1087.2
7.5°	1107.5	1106.1	1106.1	1104.6	1104.6	1103.2	1101.7	1100.3	1094.5	1093.0	1088.7
10°	1111.9	1110.4	1110.4	1109.0	1106.1	1106.1	1103.2	1101.7	1094.5	1091.6	1085.8
12.5°	1110.4	1110.4	1110.4	1109.0	1104.6	1103.2	1100.3	1096.0	1090.2	1084.4	1078.6
15°	1106.1	1106.1	1103.2	1101.7	1097.4	1094.5	1093.0	1085.8	1080.0	1072.8	1064.0
17.5°	1091.6	1091.6	1090.2	1087.2	1082.9	1080.0	1077.2	1069.8	1064.0	1052.5	1043.8
20°	1072.8	1071.4	1069.8	1065.6	1061.2	1059.8	1055.4	1045.2	1038.0	1029.3	1017.7
22.5°	1045.2	1043.8	1042.4	1039.5	1032.2	1029.3	1026.4	1019.2	1006.1	997.5	983.1
25°	1009.1	1009.1	1006.1	1001.9	994.7	991.7	987.3	980.1	968.5	955.5	943.9
27.5°	967.1	965.7	961.3	958.4	952.6	948.3	941.0	932.4	920.8	910.6	896.2
30°	913.6	913.6	910.6	906.2	899.0	896.2	890.4	880.2	868.7	855.6	845.5
32.5°	852.7	852.7	848.3	845.5	841.1	833.9	832.5	820.9	810.7	800.6	789.0
35°	786.1	787.6	784.7	778.9	771.6	771.6	768.8	758.6	747.0	736.9	728.2
37.5°	719.5	715.2	713.7	710.9	706.5	700.7	697.9	693.5	683.3	676.1	663.1
40°	645.7	647.1	644.2	641.4	639.9	635.6	634.1	626.8	619.6	611.0	605.2
42.5°	579.1	579.1	579.1	576.2	573.3	569.0	567.5	563.2	554.5	548.7	540.1
45°	519.7	515.4	515.4	513.9	512.5	509.6	505.3	502.4	496.6	492.2	482.1
47.5°	461.8	463.2	461.8	460.4	456.0	454.6	453.2	447.4	441.6	437.2	430.0
50°	411.1	414.1	411.1	411.1	408.3	406.8	403.9	399.6	395.3	388.1	380.7
52.5°	369.1	369.1	367.7	366.3	361.9	359.1	357.6	356.1	348.9	343.1	337.3
55°	327.2	328.6	328.6	324.3	322.8	320.0	318.5	314.2	311.2	302.6	298.2
57.5°	291.0	289.6	291.0	288.1	285.2	282.3	280.8	278.0	273.6	267.8	262.0
60°	259.1	256.3	256.3	254.8	251.9	250.5	247.5	243.3	238.9	233.1	228.7
62.5°	227.3	225.9	224.3	222.9	220.1	218.6	217.1	212.8	208.5	204.1	199.8
65°	196.9	196.9	195.5	192.5	191.1	189.7	188.2	185.3	179.5	176.6	172.3
67.5°	169.4	168.0	168.0	165.0	162.2	160.8	160.8	157.8	153.4	149.2	146.2
70°	141.8	143.4	141.8	140.4	137.6	137.6	134.6	133.2	127.4	126.0	121.6
72.5°	117.3	117.3	115.8	115.8	112.9	111.5	111.5	108.6	105.7	102.8	99.9
75°	94.1	94.1	94.1	92.7	91.3	88.3	88.3	86.9	83.9	81.1	78.1
77.5°	73.9	72.3	72.3	70.9	69.5	68.1	68.1	66.5	63.7	62.3	59.3
80°	53.5	52.1	52.1	52.1	49.2	50.7	49.2	47.8	46.3	44.9	43.4
82.5°	34.8	36.2	36.2	34.8	33.3	33.3	33.3	31.8	31.8	30.4	29.0
85°	20.2	20.2	20.2	20.2	18.8	18.8	18.8	17.4	17.4	17.4	16.0
87.5°	8.6	8.6	8.6	8.6	8.6	8.6	7.2	7.2	7.2	7.2	7.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583999

CATALOG NUMBER: HCC8W20D010MW-HM80520830-81WWW

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0
2.5°	1078.6	1075.6	1074.2	1072.8	1072.8	1071.4	1069.8	1067.0	1067.0	1064.0	1062.6
5°	1084.4	1080.0	1077.2	1074.2	1072.8	1069.8	1067.0	1062.6	1061.2	1056.8	1052.5
7.5°	1085.8	1078.6	1075.6	1069.8	1067.0	1064.0	1058.2	1054.0	1048.2	1043.8	1038.0
10°	1080.0	1074.2	1067.0	1059.8	1058.2	1054.0	1045.2	1039.5	1032.2	1026.4	1017.7
12.5°	1071.4	1062.6	1055.4	1046.7	1042.4	1038.0	1029.3	1020.7	1010.5	1000.4	991.7
15°	1056.8	1046.7	1036.6	1026.4	1020.7	1016.3	1006.1	996.1	985.9	972.9	964.2
17.5°	1035.1	1023.5	1013.4	1000.4	994.7	990.3	977.3	965.7	952.6	939.6	930.9
20°	1007.7	993.1	981.5	967.1	962.7	955.5	942.5	929.4	915.0	900.4	890.4
22.5°	971.5	956.9	943.9	929.4	922.2	915.0	902.0	886.0	871.5	859.9	849.9
25°	929.4	916.4	900.4	887.4	878.8	870.1	855.6	842.5	829.5	812.2	802.1
27.5°	883.1	867.2	855.6	838.3	829.5	823.7	807.8	790.5	778.9	763.0	751.4
30°	830.9	816.5	803.5	786.1	777.4	771.6	757.2	741.2	729.6	713.7	702.1
32.5°	776.0	760.0	744.2	732.6	722.4	716.6	700.7	690.5	676.1	663.1	650.0
35°	716.6	700.7	689.1	673.1	667.4	661.6	648.6	635.6	622.6	611.0	600.8
37.5°	652.9	641.4	628.4	616.8	612.4	606.6	590.6	579.1	569.0	557.4	548.7
40°	590.6	580.6	571.9	560.3	553.1	548.7	537.1	526.9	515.4	508.1	499.5
42.5°	534.3	522.7	513.9	505.3	498.0	493.7	483.6	476.3	467.6	460.4	450.2
45°	474.8	469.0	459.0	451.6	447.4	441.6	434.3	425.6	418.4	412.6	405.3
47.5°	422.7	416.9	409.7	401.1	398.1	393.8	386.5	380.7	374.9	369.1	361.9
50°	374.9	367.7	361.9	356.1	353.3	348.9	341.7	338.8	334.4	328.6	324.3
52.5°	331.6	325.8	320.0	312.8	311.2	308.4	304.0	298.2	293.8	291.0	288.1
55°	292.4	286.6	282.3	276.5	275.1	272.2	266.4	263.5	260.6	257.7	254.8
57.5°	257.7	251.9	246.1	243.3	240.3	237.5	235.9	231.7	228.7	227.3	224.3
60°	225.9	220.1	215.7	211.3	209.9	208.5	205.5	202.7	199.8	196.9	195.5
62.5°	195.5	189.7	186.8	183.9	181.0	181.0	178.1	175.2	172.3	170.8	168.0
65°	168.0	165.0	160.8	156.4	155.0	155.0	150.6	149.2	147.6	144.8	141.8
67.5°	141.8	139.0	134.6	133.2	131.8	130.3	128.8	126.0	123.0	121.6	118.7
70°	118.7	115.8	112.9	111.5	110.0	108.6	105.7	104.3	101.3	99.9	98.5
72.5°	95.5	94.1	91.3	89.7	88.3	86.9	85.5	83.9	81.1	79.7	78.1
75°	76.7	75.3	72.3	70.9	69.5	69.5	68.1	65.1	63.7	63.7	62.3
77.5°	57.9	56.5	55.0	53.5	52.1	52.1	50.7	49.2	47.8	47.8	46.3
80°	42.0	40.5	39.1	39.1	39.1	37.6	36.2	36.2	34.8	34.8	33.3
82.5°	27.5	27.5	26.0	26.0	26.0	24.6	24.6	23.2	23.2	23.2	23.2
85°	16.0	16.0	16.0	14.4	14.4	14.4	14.4	14.4	14.4	13.0	14.4
87.5°	7.2	7.2	7.2	7.2	7.2	7.2	7.2	7.2	5.8	5.8	5.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583999

CATALOG NUMBER: HCC8W20D010MW-HM80520830-81WWW

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0
2.5°	1061.2	1059.8	1056.8	1056.8	1054.0	1054.0	1052.5	1051.0	1049.6	1048.2	1046.7
5°	1051.0	1045.2	1042.4	1040.9	1038.0	1036.6	1032.2	1029.3	1027.9	1025.0	1022.1
7.5°	1032.2	1026.4	1020.7	1019.2	1017.7	1011.9	1007.7	1003.3	1000.4	997.5	994.7
10°	1010.5	1004.7	997.5	994.7	991.7	984.5	978.7	974.3	968.5	962.7	961.3
12.5°	984.5	975.7	967.1	964.2	959.9	952.6	946.8	939.6	935.2	928.0	926.6
15°	954.1	943.9	936.7	929.4	926.6	919.4	909.2	903.4	894.7	891.8	884.6
17.5°	917.8	907.8	897.6	894.7	890.4	880.2	870.1	862.9	854.1	849.9	845.5
20°	880.2	867.2	857.1	854.1	848.3	839.7	829.5	822.3	815.1	806.4	802.1
22.5°	836.7	822.3	813.6	806.4	804.9	794.8	783.2	777.4	771.6	764.4	758.6
25°	789.0	776.0	765.8	760.0	757.2	748.4	739.8	732.6	723.9	719.5	712.3
27.5°	739.8	731.1	718.1	712.3	707.9	700.7	690.5	686.3	677.5	671.7	667.4
30°	692.1	678.9	671.7	664.5	660.1	652.9	644.2	639.9	632.6	626.8	622.6
32.5°	639.9	631.2	621.0	618.2	612.4	605.2	599.4	592.2	586.4	580.6	579.1
35°	592.2	580.6	570.4	567.5	563.2	555.9	553.1	548.7	541.5	540.1	534.3
37.5°	540.1	534.3	522.7	518.3	516.9	511.1	505.3	502.4	498.0	493.7	492.2
40°	490.8	483.6	477.8	473.4	470.6	466.2	460.4	459.0	456.0	450.2	448.8
42.5°	444.4	437.2	431.4	430.0	425.6	421.3	418.4	414.1	412.6	411.1	408.3
45°	399.6	395.3	389.5	388.1	386.5	380.7	377.9	374.9	372.1	370.7	367.7
47.5°	359.1	354.7	350.3	348.9	346.0	344.6	340.2	338.8	334.4	333.0	331.6
50°	320.0	317.0	314.2	312.8	309.8	308.4	305.4	302.6	299.6	298.2	296.8
52.5°	285.2	282.3	279.4	278.0	276.5	273.6	270.7	267.8	266.4	264.9	263.5
55°	251.9	249.0	247.5	246.1	244.7	243.3	238.9	237.5	235.9	234.5	231.7
57.5°	221.5	218.6	215.7	215.7	214.3	212.8	209.9	207.0	207.0	204.1	201.2
60°	194.0	191.1	188.2	186.8	185.3	182.4	181.0	179.5	178.1	176.6	173.8
62.5°	165.0	163.6	160.8	160.8	157.8	156.4	155.0	153.4	152.0	149.2	147.6
65°	140.4	139.0	136.0	134.6	134.6	133.2	130.3	128.8	127.4	127.4	126.0
67.5°	117.3	115.8	112.9	111.5	111.5	110.0	108.6	108.6	107.1	105.7	107.1
70°	97.0	94.1	94.1	92.7	92.7	91.3	89.7	89.7	89.7	91.3	91.3
72.5°	76.7	75.3	73.9	73.9	73.9	73.9	72.3	72.3	73.9	75.3	75.3
75°	60.8	59.3	59.3	59.3	57.9	57.9	59.3	59.3	60.8	60.8	60.8
77.5°	44.9	44.9	44.9	44.9	44.9	44.9	46.3	46.3	47.8	47.8	47.8
80°	33.3	33.3	33.3	33.3	33.3	34.8	34.8	34.8	34.8	34.8	36.2
82.5°	23.2	23.2	23.2	23.2	23.2	23.2	23.2	24.6	24.6	24.6	24.6
85°	13.0	14.4	14.4	14.4	14.4	14.4	14.4	14.4	14.4	14.4	14.4
87.5°	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583999

CATALOG NUMBER: HCC8W20D010MW-HM80520830-81WWW

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0	1067.0
2.5°	1045.2	1045.2	1045.2	1046.7	1043.8	1043.8	1043.8	1043.8
5°	1020.7	1019.2	1017.7	1019.2	1016.3	1016.3	1014.9	1014.9
7.5°	990.3	988.9	987.3	987.3	984.5	984.5	983.1	981.5
10°	956.9	954.1	955.5	952.6	951.2	949.7	948.3	946.8
12.5°	920.8	917.8	916.4	913.6	910.6	909.2	910.6	907.8
15°	881.7	877.3	875.9	873.0	870.1	868.7	868.7	867.2
17.5°	838.3	835.3	833.9	830.9	829.5	826.7	825.2	823.7
20°	797.7	790.5	791.9	789.0	787.6	781.8	781.8	783.2
22.5°	752.8	748.4	745.6	742.7	741.2	738.4	738.4	736.9
25°	707.9	703.6	702.1	699.3	697.9	694.9	693.5	693.5
27.5°	664.5	658.7	658.7	655.8	652.9	651.5	650.0	648.6
30°	618.2	613.8	612.4	612.4	611.0	611.0	606.6	608.0
32.5°	574.8	571.9	570.4	567.5	567.5	566.1	566.1	561.7
35°	531.3	526.9	528.5	525.5	524.1	522.7	524.1	522.7
37.5°	489.3	486.4	486.4	483.6	483.6	482.1	480.6	483.6
40°	447.4	445.9	444.4	443.0	444.4	443.0	440.1	441.6
42.5°	405.3	405.3	403.9	403.9	402.5	402.5	402.5	402.5
45°	367.7	366.3	366.3	364.9	364.9	364.9	364.9	363.3
47.5°	330.1	328.6	328.6	328.6	327.2	327.2	325.8	327.2
50°	293.8	293.8	292.4	292.4	293.8	292.4	291.0	291.0
52.5°	260.6	260.6	259.1	259.1	257.7	256.3	257.7	257.7
55°	230.1	228.7	227.3	227.3	225.9	224.3	224.3	225.9
57.5°	201.2	199.8	198.3	198.3	195.5	194.0	194.0	194.0
60°	173.8	170.8	170.8	169.4	169.4	168.0	168.0	168.0
62.5°	147.6	146.2	146.2	146.2	146.2	144.8	144.8	144.8
65°	126.0	126.0	126.0	127.4	127.4	128.8	128.8	128.8
67.5°	108.6	110.0	110.0	110.0	111.5	111.5	111.5	110.0
70°	92.7	92.7	92.7	94.1	94.1	94.1	94.1	94.1
72.5°	76.7	76.7	76.7	76.7	76.7	76.7	76.7	76.7
75°	60.8	62.3	62.3	62.3	60.8	62.3	62.3	60.8
77.5°	47.8	47.8	47.8	47.8	47.8	47.8	47.8	47.8
80°	36.2	36.2	36.2	36.2	36.2	36.2	36.2	36.2
82.5°	24.6	24.6	24.6	24.6	24.6	24.6	24.6	24.6
85°	14.4	14.4	14.4	14.4	14.4	14.4	14.4	14.4
87.5°	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)