

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P575619

Luminaire Tested: **HCC8S20D010MB-HM80520835-81RWWC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P575619
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S20D010MB-HM80520835-81RWWC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2145.0 lumens
Efficiency: N/A
Efficacy: 107.2 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.08 / 1.17
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P575619
CATALOG NUMBER: HCC8S20D010MB-HM80520835-81RWWC

Luminous Intensity Polar Plot





TEST NUMBER: P575619

CATALOG NUMBER: HCC8S20D010MB-HM80520835-81RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	85	82	79	77								
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67								
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	69	65	61	59								
5	81	70	62	56	80	69	62	56	67	61	56	65	59	55	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	34802	34802	34802
5°	35260	34656	34328
10°	35624	34302	33783
15°	35978	33575	32904
20°	35802	32336	31598
25°	34963	30404	29992
30°	33210	28218	28115
35°	30236	25752	25982
40°	26507	23049	23899
45°	22864	20501	21948
50°	20024	17999	19880
55°	17741	15473	17499
60°	15986	13013	14499
65°	14403	10441	11105
70°	12640	7609	6113
75°	10770	3944	1620
80°	8293	1065	266
85°	5307	0	0



TEST NUMBER: P575619
 CATALOG NUMBER: HCC8S20D010MB-HM80520835-81RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.5	5.0
10°-20°	299.3	14.0
20°-30°	424.9	19.8
30°-40°	447.2	20.9
40°-50°	380.5	17.7
50°-60°	274.9	12.8
60°-70°	156.4	7.3
70°-80°	49.3	2.3
80°-90°	6.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	830.7	38.7
0°-40°	1277.9	59.6
0°-60°	1933.3	90.1
0°-90°	2145.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2145.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1129	1129	1129	1129	1129	
5°	1139	1133	1120	1112	1109	109
15°	1127	1098	1052	1032	1031	317
25°	1028	976	894	878	882	471
35°	803	756	684	680	690	500
45°	524	505	470	482	503	408
55°	330	306	288	304	326	298
65°	197	170	143	142	152	196
75°	90	69	33	15	14	97
85°	15	9	0	0	0	19
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P575619

CATALOG NUMBER: HCC8S20D010MB-HM80520835-81RWWC

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1128.6	1128.6	1128.6	1128.6	1128.6	1128.6	1128.6	1128.6	1128.6	1128.6	1128.6
2.5°	1134.6	1136.1	1133.1	1133.1	1136.1	1133.1	1134.6	1134.6	1133.1	1133.1	1131.6
5°	1139.1	1137.7	1137.7	1137.7	1139.1	1136.1	1134.6	1136.1	1133.1	1133.1	1133.1
7.5°	1140.6	1140.6	1139.1	1137.7	1137.7	1137.7	1136.1	1134.6	1133.1	1130.1	1128.6
10°	1137.7	1137.7	1139.1	1136.1	1136.1	1133.1	1133.1	1130.1	1130.1	1127.0	1122.5
12.5°	1134.6	1133.1	1133.1	1130.1	1130.1	1127.0	1127.0	1122.5	1121.0	1116.5	1112.0
15°	1127.0	1125.6	1122.5	1121.0	1119.6	1118.1	1115.0	1113.6	1109.0	1102.9	1098.4
17.5°	1112.0	1110.5	1109.0	1106.0	1102.9	1101.5	1100.0	1095.5	1089.4	1085.0	1077.4
20°	1091.0	1089.4	1089.4	1085.0	1083.4	1078.9	1077.4	1071.4	1066.9	1057.8	1051.7
22.5°	1062.3	1063.8	1060.8	1057.8	1054.8	1050.2	1047.3	1041.2	1033.7	1024.7	1017.1
25°	1027.6	1029.2	1026.1	1023.1	1018.6	1015.6	1012.6	1003.5	996.0	985.4	976.5
27.5°	983.9	983.9	983.9	980.9	973.4	971.8	968.9	959.8	949.3	940.3	931.2
30°	932.7	931.2	931.2	926.7	923.6	917.6	913.1	905.6	898.1	887.6	876.9
32.5°	870.9	872.4	867.9	864.9	860.4	860.4	854.3	848.3	839.3	828.7	818.2
35°	803.2	804.6	801.6	800.1	792.5	791.1	789.6	782.0	776.0	768.4	756.4
37.5°	733.8	732.2	730.8	730.8	726.3	723.3	720.3	715.7	706.7	700.7	694.7
40°	658.5	658.5	658.5	657.0	655.4	652.5	650.9	648.0	641.9	635.9	631.3
42.5°	590.6	590.6	589.1	587.7	584.6	586.2	583.1	580.1	574.1	569.6	566.5
45°	524.3	524.3	524.3	525.9	522.9	518.3	518.3	515.4	512.3	509.3	504.8
47.5°	465.6	470.1	467.1	465.6	467.1	461.1	461.1	458.0	455.1	452.0	446.0
50°	417.4	417.4	417.4	414.4	412.9	412.9	408.4	405.3	403.8	400.8	394.8
52.5°	373.6	370.7	370.7	369.1	367.6	364.6	364.6	361.7	355.7	352.6	348.1
55°	330.0	330.0	328.5	326.9	325.5	324.0	322.4	318.0	314.9	310.4	305.9
57.5°	290.8	293.8	292.3	289.4	286.3	286.3	283.3	280.3	275.8	271.3	266.7
60°	259.2	257.7	257.7	256.1	253.2	251.6	250.1	245.6	241.1	236.5	232.0
62.5°	226.0	226.0	226.0	223.0	220.0	218.4	217.0	213.9	207.9	203.4	200.3
65°	197.4	195.9	194.3	192.9	191.4	188.3	186.9	183.8	179.3	174.8	170.3
67.5°	168.8	167.3	167.3	165.7	161.2	159.7	159.7	155.2	150.7	146.2	141.6
70°	140.2	140.2	140.2	137.1	135.6	134.2	132.6	129.5	125.1	120.6	116.1
72.5°	116.1	114.5	114.5	113.0	108.5	107.0	105.4	102.5	98.0	94.9	92.0
75°	90.4	90.4	88.9	87.3	85.9	84.4	82.9	79.9	75.3	70.8	69.3
77.5°	69.3	67.8	67.8	66.3	63.2	61.8	61.8	58.7	54.3	51.2	48.2
80°	46.7	48.2	46.7	45.2	43.7	42.2	40.7	39.1	36.2	33.1	30.1
82.5°	28.6	30.1	28.6	28.6	27.1	25.6	25.6	22.6	21.0	19.6	18.1
85°	15.0	15.0	15.0	15.0	13.6	13.6	13.6	12.1	10.5	9.0	9.0
87.5°	4.5	6.0	4.5	4.5	4.5	4.5	4.5	4.5	3.0	3.0	3.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P575619

CATALOG NUMBER: HCC8S20D010MB-HM80520835-81RWWC

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1128.6	1128.6	1128.6	1128.6	1128.6	1128.6	1128.6	1128.6	1128.6	1128.6	1128.6
2.5°	1133.1	1131.6	1130.1	1130.1	1130.1	1130.1	1130.1	1128.6	1127.0	1127.0	1127.0
5°	1130.1	1130.1	1130.1	1128.6	1127.0	1127.0	1124.1	1122.5	1121.0	1119.6	1118.1
7.5°	1127.0	1124.1	1122.5	1121.0	1119.6	1119.6	1116.5	1113.6	1113.6	1110.5	1107.5
10°	1118.1	1116.5	1113.6	1110.5	1109.0	1107.5	1104.5	1100.0	1098.4	1095.5	1092.4
12.5°	1107.5	1104.5	1101.5	1095.5	1093.9	1092.4	1086.4	1081.9	1078.9	1077.4	1069.8
15°	1093.9	1087.9	1083.4	1075.9	1074.3	1071.4	1066.9	1062.3	1056.2	1051.7	1048.8
17.5°	1069.8	1063.8	1056.2	1048.8	1045.7	1045.7	1038.2	1032.1	1024.7	1021.6	1015.6
20°	1041.2	1033.7	1027.6	1018.6	1014.0	1009.5	1005.1	996.0	989.9	985.4	977.9
22.5°	1008.0	997.5	989.9	980.9	973.4	968.9	961.3	953.8	946.3	941.7	935.7
25°	965.8	956.8	944.8	935.7	931.2	925.2	916.2	908.6	901.0	893.6	890.5
27.5°	919.1	907.1	896.5	886.0	881.5	876.9	866.4	857.4	851.4	843.8	840.8
30°	867.9	855.9	843.8	834.7	830.2	822.7	816.6	806.1	798.6	792.5	785.1
32.5°	809.2	800.1	789.6	776.0	773.0	767.0	757.9	753.4	744.3	739.8	733.8
35°	745.8	739.8	729.3	718.8	714.3	711.2	703.6	694.7	688.6	684.1	681.1
37.5°	685.6	678.1	667.5	660.0	657.0	652.5	643.4	638.9	632.8	629.9	623.9
40°	620.8	613.2	605.8	601.2	596.7	593.7	587.7	583.1	577.1	572.6	571.0
42.5°	557.5	552.9	546.9	541.0	539.5	535.0	531.9	527.4	522.9	521.4	516.9
45°	500.2	495.7	489.7	483.7	482.1	479.2	477.6	473.2	470.1	470.1	470.1
47.5°	443.0	438.5	432.5	429.4	431.0	424.9	424.9	423.4	420.4	420.4	421.9
50°	391.7	385.7	384.3	381.2	378.2	375.2	376.7	372.2	372.2	375.2	373.6
52.5°	343.6	337.6	336.0	333.0	331.6	331.6	330.0	330.0	328.5	330.0	330.0
55°	299.9	295.4	292.3	289.4	287.8	287.8	287.8	286.3	284.7	287.8	289.4
57.5°	260.6	259.2	256.1	251.6	250.1	248.6	247.2	247.2	247.2	247.2	248.6
60°	226.0	223.0	220.0	215.5	215.5	213.9	212.4	211.0	211.0	211.0	211.0
62.5°	195.9	191.4	186.9	183.8	182.3	180.8	179.3	176.4	176.4	176.4	176.4
65°	165.7	161.2	158.3	155.2	152.2	152.2	149.2	147.6	144.7	143.1	140.2
67.5°	137.1	134.2	131.1	126.6	125.1	123.5	120.6	119.0	114.5	113.0	111.5
70°	111.5	107.0	104.0	100.9	99.4	96.5	93.4	90.4	87.3	84.4	81.3
72.5°	87.3	82.9	79.9	76.8	73.9	73.9	69.3	66.3	61.8	58.7	54.3
75°	64.8	60.3	57.2	52.7	51.2	49.8	45.2	42.2	37.7	33.1	30.1
77.5°	43.7	40.7	37.7	33.1	30.1	30.1	25.6	22.6	19.6	15.0	13.6
80°	27.1	24.1	21.0	18.1	18.1	15.0	13.6	10.5	7.6	6.0	4.5
82.5°	15.0	13.6	12.1	9.0	9.0	7.6	6.0	4.5	3.0	1.5	1.5
85°	7.6	6.0	4.5	4.5	3.0	3.0	3.0	1.5	1.5	0.0	0.0
87.5°	3.0	1.5	1.5	1.5	1.5	1.5	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P575619

CATALOG NUMBER: HCC8S20D010MB-HM80520835-81RWWC

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1128.6	1128.6	1128.6	1128.6	1128.6	1128.6	1128.6	1128.6	1128.6	1128.6	1128.6
2.5°	1125.6	1125.6	1124.1	1124.1	1124.1	1122.5	1124.1	1122.5	1122.5	1122.5	1124.1
5°	1119.6	1116.5	1116.5	1115.0	1115.0	1113.6	1115.0	1113.6	1112.0	1110.5	1112.0
7.5°	1107.5	1104.5	1102.9	1101.5	1101.5	1101.5	1100.0	1098.4	1100.0	1095.5	1098.4
10°	1091.0	1089.4	1086.4	1085.0	1083.4	1085.0	1083.4	1080.3	1080.3	1080.3	1078.9
12.5°	1069.8	1066.9	1065.3	1063.8	1060.8	1060.8	1062.3	1059.3	1059.3	1056.2	1056.2
15°	1044.2	1041.2	1038.2	1038.2	1035.2	1035.2	1033.7	1033.7	1032.1	1030.7	1030.7
17.5°	1012.6	1008.0	1005.1	1006.6	1005.1	1003.5	1003.5	1000.6	999.0	1000.6	1000.6
20°	974.9	971.8	968.9	970.4	967.3	965.8	967.3	962.9	964.4	964.4	964.4
22.5°	932.7	931.2	926.7	926.7	923.6	922.2	923.6	923.6	925.2	923.6	923.6
25°	886.0	883.0	880.0	880.0	878.5	876.9	878.5	880.0	878.5	880.0	880.0
27.5°	836.3	831.8	831.8	828.7	828.7	830.2	828.7	830.2	831.8	831.8	834.7
30°	782.0	780.5	779.1	777.5	777.5	779.1	779.1	779.1	780.5	783.5	783.5
32.5°	730.8	727.8	724.8	724.8	727.8	726.3	727.8	727.8	730.8	730.8	733.8
35°	675.0	675.0	672.1	673.5	673.5	673.5	673.5	676.6	679.5	681.1	684.1
37.5°	623.9	619.2	620.8	620.8	622.3	620.8	625.3	625.3	628.4	628.4	631.3
40°	568.1	568.1	569.6	568.1	569.6	569.6	572.6	575.6	577.1	580.1	581.7
42.5°	515.4	518.3	515.4	516.9	518.3	519.8	521.4	522.9	528.9	531.9	536.4
45°	467.1	468.7	470.1	471.6	470.1	473.2	474.7	477.6	482.1	483.7	485.2
47.5°	420.4	421.9	423.4	424.9	424.9	427.9	429.4	432.5	435.4	437.0	438.5
50°	375.2	378.2	379.7	379.7	381.2	384.3	387.2	387.2	390.3	394.8	396.3
52.5°	334.5	334.5	337.6	339.0	340.5	340.5	345.0	346.6	348.1	351.1	354.1
55°	289.4	293.8	295.4	295.4	298.3	301.4	302.8	304.4	304.4	310.4	310.4
57.5°	250.1	251.6	254.6	254.6	254.6	259.2	259.2	262.2	263.7	265.2	268.2
60°	211.0	213.9	213.9	215.5	213.9	217.0	218.4	221.5	223.0	224.5	226.0
62.5°	174.8	174.8	176.4	176.4	176.4	176.4	179.3	179.3	182.3	183.8	185.3
65°	140.2	140.2	140.2	140.2	140.2	140.2	140.2	140.2	141.6	141.6	144.7
67.5°	108.5	107.0	104.0	105.4	104.0	104.0	102.5	102.5	104.0	104.0	107.0
70°	78.4	76.8	73.9	73.9	72.3	70.8	69.3	67.8	66.3	66.3	66.3
72.5°	51.2	48.2	43.7	42.2	42.2	39.1	36.2	34.6	34.6	34.6	34.6
75°	25.6	22.6	19.6	18.1	18.1	15.0	16.5	15.0	15.0	15.0	15.0
77.5°	10.5	7.6	6.0	6.0	6.0	4.5	4.5	4.5	4.5	4.5	4.5
80°	3.0	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5
82.5°	1.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P575619

CATALOG NUMBER: HCC8S20D010MB-HM80520835-81RWWC

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1128.6	1128.6	1128.6	1128.6	1128.6	1128.6	1128.6	1128.6
2.5°	1122.5	1122.5	1119.6	1121.0	1121.0	1121.0	1121.0	1121.0
5°	1109.0	1110.5	1109.0	1110.5	1110.5	1109.0	1109.0	1109.0
7.5°	1095.5	1096.9	1095.5	1096.9	1096.9	1096.9	1095.5	1095.5
10°	1078.9	1078.9	1078.9	1078.9	1078.9	1077.4	1078.9	1078.9
12.5°	1056.2	1056.2	1056.2	1057.8	1057.8	1056.2	1056.2	1054.8
15°	1032.1	1029.2	1030.7	1032.1	1030.7	1030.7	1030.7	1030.7
17.5°	999.0	1000.6	999.0	999.0	999.0	999.0	1000.6	999.0
20°	964.4	964.4	965.8	964.4	964.4	964.4	964.4	962.9
22.5°	925.2	923.6	923.6	925.2	925.2	923.6	925.2	925.2
25°	881.5	883.0	881.5	881.5	883.0	883.0	883.0	881.5
27.5°	834.7	836.3	837.8	836.3	836.3	836.3	837.8	839.3
30°	786.5	789.6	786.5	786.5	789.6	788.0	789.6	789.6
32.5°	735.3	739.8	736.9	739.8	739.8	741.4	739.8	741.4
35°	684.1	688.6	688.6	688.6	690.2	691.6	691.6	690.2
37.5°	635.9	637.3	637.3	640.4	641.9	643.4	643.4	641.9
40°	586.2	589.1	590.6	590.6	590.6	593.7	596.7	593.7
42.5°	537.9	539.5	541.0	541.0	544.0	545.5	546.9	546.9
45°	491.2	494.2	495.7	497.3	498.8	501.8	500.2	503.3
47.5°	443.0	447.5	449.0	450.6	453.5	455.1	456.6	458.0
50°	399.3	402.4	402.4	405.3	409.8	409.8	412.9	414.4
52.5°	355.7	357.1	358.6	360.2	363.1	366.2	366.2	369.1
55°	313.5	314.9	314.9	316.4	318.0	324.0	325.5	325.5
57.5°	269.7	269.7	272.7	274.2	275.8	278.7	278.7	278.7
60°	227.5	229.1	229.1	230.5	232.0	235.1	236.5	235.1
62.5°	185.3	186.9	186.9	188.3	191.4	192.9	191.4	191.4
65°	146.2	147.6	147.6	149.2	152.2	152.2	150.7	152.2
67.5°	107.0	107.0	107.0	107.0	107.0	107.0	107.0	107.0
70°	67.8	66.3	64.8	66.3	66.3	66.3	64.8	67.8
72.5°	33.1	34.6	34.6	34.6	34.6	34.6	34.6	33.1
75°	15.0	15.0	13.6	13.6	13.6	15.0	15.0	13.6
77.5°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5
80°	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)