

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584013

Luminaire Tested: **HCC8S20D010MW-HM80520835-81WWWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584013
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S20D010MW-HM80520835-81WWWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2132.9 lumens
Efficiency: N/A
Efficacy: 106.6 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584013
CATALOG NUMBER: HCC8S20D010MW-HM80520835-81WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584013

CATALOG NUMBER: HCC8S20D010MW-HM80520835-81WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75								
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65								
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57								
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50								
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45								
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40								
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37								
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33								
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	32702	32702	32702
5°	33898	32592	31474
10°	34857	32311	30185
15°	35637	31739	28856
20°	35690	30499	27683
25°	35004	28801	26702
30°	33203	26712	25530
35°	30168	24326	24382
40°	26378	21830	22981
45°	22860	19445	21416
50°	20014	17270	19511
55°	17817	15306	17655
60°	16072	13747	15511
65°	14505	12090	13520
70°	13037	10188	10053
75°	11497	8066	7530
80°	9643	6695	7227
85°	7430	5838	6404



TEST NUMBER: P584013

CATALOG NUMBER: HCC8S20D010MW-HM80520835-81WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.0	4.7
10°-20°	281.8	13.2
20°-30°	402.7	18.9
30°-40°	427.9	20.1
40°-50°	368.4	17.3
50°-60°	275.4	12.9
60°-70°	175.7	8.2
70°-80°	80.0	3.7
80°-90°	21.0	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	784.5	36.8
0°-40°	1212.4	56.8
0°-60°	1856.3	87.0
0°-90°	2132.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2132.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1060	1060	1060	1060	1060	
5°	1095	1080	1053	1026	1017	105
15°	1116	1079	994	926	904	314
25°	1029	964	846	795	785	471
35°	801	746	646	630	648	499
45°	524	496	446	458	491	408
55°	331	304	285	309	328	298
65°	199	176	166	173	185	198
75°	96	83	68	62	63	102
85°	21	18	16	18	18	25
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584013

CATALOG NUMBER: HCC8S20D010MW-HM80520835-81WWWB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1060.5	1060.5	1060.5	1060.5	1060.5	1060.5	1060.5	1060.5	1060.5	1060.5	1060.5
2.5°	1080.1	1077.0	1078.6	1077.0	1078.6	1078.6	1075.5	1075.5	1075.5	1075.5	1071.0
5°	1095.1	1093.6	1093.6	1092.2	1090.6	1092.2	1090.6	1089.1	1086.1	1084.6	1080.1
7.5°	1104.2	1104.2	1104.2	1104.2	1102.7	1101.2	1099.6	1096.7	1093.6	1090.6	1087.6
10°	1113.2	1114.7	1113.2	1111.7	1110.3	1107.2	1105.6	1102.7	1098.2	1093.6	1090.6
12.5°	1117.7	1117.7	1116.3	1116.3	1113.2	1111.7	1107.2	1102.7	1098.2	1093.6	1086.1
15°	1116.3	1116.3	1114.7	1113.2	1108.7	1107.2	1104.2	1099.6	1092.2	1086.1	1078.6
17.5°	1107.2	1105.6	1102.7	1102.7	1096.7	1095.1	1092.2	1086.1	1078.6	1069.6	1060.5
20°	1087.6	1087.6	1086.1	1084.6	1078.6	1074.1	1071.0	1063.6	1057.5	1046.9	1037.9
22.5°	1060.5	1063.6	1060.5	1057.5	1050.0	1048.4	1043.9	1034.8	1025.9	1013.8	1003.3
25°	1028.8	1027.4	1025.9	1022.8	1016.8	1013.8	1007.8	998.8	989.7	976.1	964.0
27.5°	988.2	982.1	982.1	976.1	971.6	967.1	964.0	955.1	943.0	932.5	917.4
30°	932.5	934.0	926.5	924.9	917.4	914.4	908.4	899.3	888.7	876.7	864.6
32.5°	872.2	867.7	867.7	861.7	855.6	851.2	849.6	839.1	830.0	817.9	805.9
35°	801.4	801.4	796.9	795.4	789.3	786.4	781.8	775.7	765.2	754.7	745.6
37.5°	732.1	729.1	727.6	724.6	720.1	715.6	715.6	704.9	703.5	691.5	679.4
40°	655.3	658.3	655.3	650.8	649.3	646.2	644.8	638.8	634.1	623.6	616.1
42.5°	590.5	587.5	587.5	586.0	580.0	580.0	576.9	574.0	566.4	563.3	554.4
45°	524.2	527.3	522.7	524.2	518.2	518.2	518.2	512.2	506.1	501.6	495.6
47.5°	467.0	468.5	468.5	463.9	462.5	462.5	459.4	456.5	451.9	445.9	441.4
50°	417.2	418.8	415.7	414.3	411.2	409.7	409.7	403.7	400.7	394.7	391.7
52.5°	372.1	372.1	370.6	370.6	366.1	366.1	363.0	358.5	355.5	352.5	344.9
55°	331.4	331.4	329.9	328.4	328.4	323.9	322.3	317.8	314.9	308.9	304.2
57.5°	292.2	293.7	292.2	290.8	289.2	287.7	284.7	280.1	277.2	272.7	269.6
60°	260.6	260.6	259.1	257.6	254.6	253.1	251.5	248.6	244.1	241.0	236.5
62.5°	230.5	229.0	227.4	226.0	222.9	222.9	220.0	216.9	212.4	209.3	206.4
65°	198.8	198.8	197.4	197.4	195.9	192.8	191.4	189.8	183.8	182.3	176.2
67.5°	170.2	171.7	168.7	168.7	165.7	165.7	164.2	159.7	158.2	155.2	152.1
70°	144.6	144.6	144.6	143.1	140.1	138.5	137.1	134.0	132.6	129.5	126.6
72.5°	119.0	119.0	117.5	117.5	116.0	114.5	113.0	109.9	109.9	107.0	103.9
75°	96.5	96.5	94.9	93.4	91.8	91.8	90.4	88.9	85.8	84.4	82.9
77.5°	73.8	73.8	73.8	72.3	70.8	70.8	70.8	67.7	64.8	64.8	63.2
80°	54.3	54.3	52.7	52.7	51.2	51.2	51.2	49.8	48.2	46.7	45.2
82.5°	36.2	36.2	36.2	36.2	34.6	34.6	34.6	33.1	31.7	31.7	31.7
85°	21.0	21.0	21.0	21.0	19.6	19.6	19.6	19.6	19.6	18.1	18.1
87.5°	9.0	7.6	9.0	7.6	9.0	7.6	9.0	7.6	7.6	7.6	7.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584013

CATALOG NUMBER: HCC8S20D010MW-HM80520835-81WWWB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1060.5	1060.5	1060.5	1060.5	1060.5	1060.5	1060.5	1060.5	1060.5	1060.5	1060.5
2.5°	1072.5	1071.0	1069.6	1068.1	1068.1	1066.5	1063.6	1062.0	1060.5	1059.0	1059.0
5°	1078.6	1077.0	1074.1	1071.0	1069.6	1066.5	1063.6	1060.5	1057.5	1052.9	1051.5
7.5°	1083.1	1078.6	1075.5	1069.6	1068.1	1065.0	1060.5	1056.0	1050.0	1043.9	1039.5
10°	1083.1	1077.0	1072.5	1065.0	1062.0	1059.0	1052.9	1045.5	1037.9	1031.9	1024.3
12.5°	1080.1	1072.5	1065.0	1057.5	1052.9	1048.4	1039.5	1031.9	1022.8	1013.8	1007.8
15°	1069.6	1060.5	1051.5	1042.4	1037.9	1031.9	1022.8	1012.3	1003.3	994.2	983.7
17.5°	1050.0	1040.9	1030.3	1019.8	1013.8	1009.3	995.7	988.2	974.7	965.6	956.6
20°	1024.3	1013.8	1000.2	989.7	982.1	977.6	967.1	953.5	943.0	929.4	920.4
22.5°	991.2	977.6	964.0	953.5	946.0	940.0	926.5	912.9	903.9	891.8	881.2
25°	952.0	938.5	924.9	909.9	902.3	896.3	884.3	872.2	860.1	846.5	837.6
27.5°	905.3	890.3	878.2	864.6	857.2	848.1	834.5	822.4	810.4	801.4	789.3
30°	854.1	837.6	825.5	811.9	804.5	796.9	783.3	771.3	760.7	750.2	744.2
32.5°	792.4	780.4	768.3	754.7	748.7	744.2	730.6	718.5	706.5	697.5	692.9
35°	733.7	720.1	709.6	697.5	689.9	685.4	673.4	662.9	656.8	646.2	640.2
37.5°	671.8	661.3	649.3	637.2	632.7	628.1	619.1	608.6	599.5	592.1	589.0
40°	607.1	598.1	587.5	580.0	575.4	570.9	563.3	555.9	549.9	542.3	539.2
42.5°	545.3	539.2	530.2	521.3	516.7	515.2	506.1	500.1	497.1	494.1	491.1
45°	489.6	480.5	474.5	468.5	463.9	461.0	456.5	451.9	448.9	445.9	442.9
47.5°	435.3	427.8	421.7	417.2	412.8	411.2	408.3	403.7	400.7	400.7	400.7
50°	385.7	379.7	373.6	370.6	369.0	366.1	363.0	361.6	360.0	360.0	360.0
52.5°	342.0	335.9	331.4	328.4	328.4	325.4	322.3	320.9	320.9	320.9	320.9
55°	301.3	296.8	293.7	290.8	287.7	286.2	286.2	286.2	284.7	284.7	286.2
57.5°	265.1	262.2	257.6	254.6	253.1	253.1	251.5	250.1	251.5	253.1	254.6
60°	232.0	229.0	227.4	222.9	222.9	222.9	221.4	221.4	221.4	222.9	224.5
62.5°	201.9	200.3	197.4	195.9	194.3	194.3	192.8	192.8	192.8	192.8	194.3
65°	174.7	171.7	168.7	168.7	168.7	167.3	167.3	164.2	165.7	165.7	164.2
67.5°	149.2	146.1	144.6	143.1	141.6	141.6	140.1	138.5	137.1	137.1	137.1
70°	125.1	122.0	122.0	119.0	119.0	117.5	116.0	116.0	114.5	113.0	111.5
72.5°	100.9	99.4	97.9	96.5	96.5	96.5	94.9	93.4	91.8	90.4	87.3
75°	79.8	79.8	76.8	75.3	75.3	73.8	72.3	70.8	69.3	67.7	66.3
77.5°	61.8	60.3	57.2	55.8	55.8	55.8	54.3	52.7	51.2	49.8	48.2
80°	45.2	43.7	42.2	40.7	40.7	40.7	39.1	39.1	37.7	37.7	37.7
82.5°	30.1	30.1	28.6	28.6	28.6	28.6	27.1	27.1	27.1	27.1	27.1
85°	18.1	18.1	16.5	16.5	16.5	16.5	16.5	16.5	16.5	16.5	16.5
87.5°	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584013

CATALOG NUMBER: HCC8S20D010MW-HM80520835-81WWWB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1060.5	1060.5	1060.5	1060.5	1060.5	1060.5	1060.5	1060.5	1060.5	1060.5	1060.5
2.5°	1056.0	1056.0	1052.9	1051.5	1050.0	1051.5	1048.4	1046.9	1045.5	1045.5	1043.9
5°	1046.9	1045.5	1039.5	1037.9	1036.4	1034.8	1031.9	1028.8	1025.9	1024.3	1022.8
7.5°	1034.8	1030.3	1024.3	1022.8	1021.4	1016.8	1012.3	1009.3	1004.8	1003.3	1000.2
10°	1018.3	1012.3	1007.8	1003.3	1000.2	995.7	991.2	986.7	980.7	979.2	974.7
12.5°	998.8	991.2	982.1	980.7	976.1	970.1	964.0	959.5	955.1	952.0	947.5
15°	974.7	967.1	958.0	953.5	949.0	944.5	937.0	930.9	926.5	922.0	917.4
17.5°	946.0	937.0	929.4	924.9	922.0	914.4	908.4	900.8	896.3	891.8	887.2
20°	911.3	903.9	893.2	888.7	887.2	881.2	873.7	870.7	864.6	860.1	857.2
22.5°	872.2	864.6	855.6	852.6	846.5	843.6	836.0	833.1	830.0	825.5	824.0
25°	828.5	821.0	813.5	811.9	807.4	804.5	799.9	795.4	795.4	790.9	790.9
27.5°	783.3	775.7	769.7	766.8	765.2	762.3	757.7	756.2	754.7	753.2	753.2
30°	735.1	726.1	723.0	721.6	720.1	717.0	715.6	712.5	714.0	715.6	714.0
32.5°	683.9	680.8	674.8	671.8	673.4	671.8	668.9	671.8	670.3	673.4	674.8
35°	634.1	631.2	628.1	628.1	625.2	625.2	625.2	626.7	629.7	631.2	634.1
37.5°	586.0	581.4	580.0	578.5	580.0	580.0	580.0	583.0	586.0	589.0	593.5
40°	534.7	531.8	531.8	531.8	531.8	536.3	534.7	537.8	540.8	545.3	549.9
42.5°	486.5	486.5	488.0	488.0	488.0	488.0	491.1	495.6	500.1	504.6	509.2
45°	441.4	441.4	441.4	444.4	444.4	445.9	451.9	455.0	457.9	462.5	467.0
47.5°	399.2	399.2	400.7	402.2	403.7	406.7	409.7	414.3	418.8	421.7	426.3
50°	360.0	361.6	364.5	367.6	367.6	369.0	373.6	376.6	379.7	384.2	385.7
52.5°	322.3	325.4	328.4	329.9	331.4	334.4	335.9	340.4	342.0	346.4	348.0
55°	287.7	289.2	293.7	295.3	295.3	298.2	301.3	304.2	308.9	308.9	311.8
57.5°	256.1	257.6	260.6	262.2	260.6	265.1	266.7	269.6	271.2	274.1	275.6
60°	224.5	227.4	229.0	229.0	230.5	232.0	235.0	235.0	238.1	241.0	241.0
62.5°	194.3	195.9	197.4	198.8	200.3	198.8	203.3	203.3	206.4	207.9	210.9
65°	165.7	167.3	167.3	168.7	168.7	170.2	170.2	171.7	173.3	176.2	177.8
67.5°	137.1	137.1	137.1	138.5	137.1	138.5	138.5	140.1	140.1	143.1	144.6
70°	111.5	109.9	108.5	108.5	108.5	108.5	107.0	108.5	108.5	109.9	109.9
72.5°	85.8	84.4	82.9	81.3	81.3	79.8	78.4	79.8	79.8	81.3	81.3
75°	64.8	61.8	61.8	61.8	60.3	60.3	60.3	61.8	61.8	61.8	63.2
77.5°	48.2	48.2	46.7	46.7	46.7	48.2	48.2	49.8	49.8	49.8	49.8
80°	36.2	37.7	37.7	37.7	37.7	39.1	39.1	39.1	39.1	40.7	40.7
82.5°	27.1	27.1	27.1	27.1	28.6	28.6	28.6	28.6	28.6	28.6	28.6
85°	16.5	18.1	18.1	16.5	18.1	18.1	18.1	18.1	18.1	18.1	18.1
87.5°	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584013

CATALOG NUMBER: HCC8S20D010MW-HM80520835-81WWWB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1060.5	1060.5	1060.5	1060.5	1060.5	1060.5	1060.5	1060.5
2.5°	1042.4	1042.4	1042.4	1042.4	1040.9	1040.9	1040.9	1039.5
5°	1019.8	1019.8	1019.8	1016.8	1018.3	1018.3	1015.3	1016.8
7.5°	997.3	995.7	994.2	994.2	992.8	991.2	989.7	991.2
10°	971.6	967.1	967.1	965.6	965.6	962.6	962.6	964.0
12.5°	943.0	940.0	940.0	938.5	937.0	935.4	934.0	934.0
15°	914.4	911.3	909.9	908.4	906.8	903.9	905.3	903.9
17.5°	885.8	881.2	881.2	879.8	878.2	875.2	875.2	873.7
20°	852.6	851.2	848.1	849.6	848.1	845.1	843.6	843.6
22.5°	819.5	819.5	817.9	817.9	816.4	815.0	813.5	813.5
25°	787.8	786.4	787.8	787.8	783.3	783.3	783.3	784.8
27.5°	751.6	753.2	751.6	751.6	751.6	751.6	753.2	751.6
30°	715.6	715.6	715.6	717.0	720.1	718.5	718.5	717.0
32.5°	676.3	677.9	677.9	679.4	680.8	683.9	683.9	685.4
35°	637.2	640.2	641.7	640.2	644.8	644.8	647.7	647.7
37.5°	596.6	598.1	601.0	602.6	605.5	607.1	608.6	608.6
40°	552.8	558.8	560.4	561.9	566.4	566.4	568.0	570.9
42.5°	512.2	518.2	519.7	521.3	524.2	528.7	527.3	530.2
45°	473.0	477.5	479.1	480.5	485.1	486.5	486.5	491.1
47.5°	430.8	433.8	435.3	438.4	441.4	444.4	447.4	445.9
50°	388.6	393.1	396.2	397.7	402.2	403.7	405.2	406.7
52.5°	350.9	354.0	355.5	357.0	361.6	363.0	364.5	367.6
55°	314.9	316.3	319.4	317.8	322.3	323.9	325.4	328.4
57.5°	278.7	280.1	281.7	281.7	284.7	287.7	289.2	290.8
60°	244.1	247.0	248.6	248.6	248.6	251.5	251.5	251.5
62.5°	212.4	212.4	213.9	213.9	216.9	216.9	216.9	216.9
65°	179.3	180.7	182.3	182.3	185.3	183.8	186.8	185.3
67.5°	144.6	144.6	147.6	147.6	146.1	147.6	147.6	147.6
70°	109.9	109.9	111.5	111.5	111.5	111.5	111.5	111.5
72.5°	81.3	81.3	81.3	82.9	81.3	81.3	82.9	81.3
75°	63.2	63.2	63.2	63.2	63.2	63.2	63.2	63.2
77.5°	49.8	49.8	51.2	51.2	51.2	51.2	51.2	51.2
80°	40.7	40.7	40.7	40.7	42.2	40.7	40.7	40.7
82.5°	30.1	28.6	30.1	28.6	30.1	30.1	30.1	30.1
85°	18.1	18.1	18.1	18.1	18.1	18.1	18.1	18.1
87.5°	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)