

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584029

Luminaire Tested: **HCC8W20D010MW-HM80520840-81WWW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584029
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W20D010MW-HM80520840-81WWW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2200.9 lumens
Efficiency: N/A
Efficacy: 110.0 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584029
CATALOG NUMBER: HCC8W20D010MW-HM80520840-81WWW

Luminous Intensity Polar Plot





TEST NUMBER: P584029

CATALOG NUMBER: HCC8W20D010MW-HM80520840-81WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76								
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66								
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58								
5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51								
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	36772	36772	36772
5°	38067	36566	35114
10°	38915	35921	33134
15°	39468	34714	30941
20°	39346	33029	28727
25°	38376	30887	26369
30°	36354	28403	24198
35°	33078	25703	21988
40°	29051	22864	19865
45°	25337	20113	17710
50°	22048	17625	15606
55°	19661	15489	13575
60°	17867	13574	11576
65°	16060	11806	10507
70°	14299	10071	9485
75°	12534	8483	8102
80°	10637	6908	7174
85°	8031	5130	5732



TEST NUMBER: P584029
 CATALOG NUMBER: HCC8W20D010MW-HM80520840-81WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.7	5.1
10°-20°	307.8	14.0
20°-30°	427.2	19.4
30°-40°	441.7	20.1
40°-50°	369.8	16.8
50°-60°	268.5	12.2
60°-70°	169.4	7.7
70°-80°	83.9	3.8
80°-90°	20.9	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	846.7	38.5
0°-40°	1288.4	58.5
0°-60°	1926.7	87.5
0°-90°	2200.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2200.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1192	1192	1192	1192	1192	
5°	1230	1215	1181	1149	1134	118
15°	1236	1189	1087	1000	969	348
25°	1128	1055	908	809	775	517
35°	879	814	683	605	584	547
45°	581	539	461	416	406	449
55°	366	333	288	264	252	330
65°	220	192	162	142	144	219
75°	105	87	71	68	68	113
85°	23	18	14	16	16	28
90°	0	0	0	0	0	



TEST NUMBER: P584029

CATALOG NUMBER: HCC8W20D010MW-HM80520840-81WWW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1192.5	1192.5	1192.5	1192.5	1192.5	1192.5	1192.5	1192.5	1192.5	1192.5	1192.5
2.5°	1212.0	1212.0	1213.6	1212.0	1212.0	1212.0	1210.4	1210.4	1208.7	1208.7	1205.5
5°	1229.8	1226.6	1229.8	1226.6	1226.6	1226.6	1224.9	1221.7	1220.1	1216.9	1215.2
7.5°	1237.9	1236.3	1236.3	1234.6	1234.6	1233.1	1231.4	1229.8	1223.4	1221.7	1216.9
10°	1242.8	1241.1	1241.1	1239.4	1236.3	1236.3	1233.1	1231.4	1223.4	1220.1	1213.6
12.5°	1241.1	1241.1	1241.1	1239.4	1234.6	1233.1	1229.8	1224.9	1218.5	1212.0	1205.5
15°	1236.3	1236.3	1233.1	1231.4	1226.6	1223.4	1221.7	1213.6	1207.2	1199.0	1189.3
17.5°	1220.1	1220.1	1218.5	1215.2	1210.4	1207.2	1203.9	1195.8	1189.3	1176.4	1166.6
20°	1199.0	1197.5	1195.8	1191.0	1186.1	1184.5	1179.6	1168.3	1160.3	1150.6	1137.6
22.5°	1168.3	1166.6	1165.1	1161.8	1153.8	1150.6	1147.2	1139.2	1124.7	1114.9	1098.7
25°	1127.9	1127.9	1124.7	1119.7	1111.7	1108.5	1103.6	1095.5	1082.6	1067.9	1055.1
27.5°	1080.9	1079.3	1074.4	1071.2	1064.7	1059.9	1051.7	1042.1	1029.2	1017.8	1001.6
30°	1021.0	1021.0	1017.8	1013.0	1004.8	1001.6	995.1	983.8	970.9	956.4	945.0
32.5°	953.0	953.0	948.2	945.0	940.2	932.0	930.5	917.5	906.1	894.9	881.9
35°	878.7	880.2	877.0	870.5	862.5	862.5	859.2	848.0	835.0	823.6	813.9
37.5°	804.2	799.4	797.7	794.5	789.7	783.2	780.0	775.0	763.8	755.7	741.1
40°	721.7	723.3	720.1	716.9	715.2	710.4	708.7	700.7	692.5	682.8	676.3
42.5°	647.3	647.3	647.3	644.1	640.8	635.9	634.3	629.4	619.7	613.2	603.5
45°	581.0	576.1	576.1	574.5	572.8	569.6	564.8	561.4	555.1	550.2	538.9
47.5°	516.2	517.8	516.2	514.5	509.7	508.1	506.5	500.0	493.5	488.6	480.6
50°	459.6	462.8	459.6	459.6	456.4	454.7	451.4	446.6	441.7	433.7	425.5
52.5°	412.6	412.6	411.0	409.4	404.5	401.3	399.6	398.1	389.9	383.6	377.1
55°	365.7	367.4	367.4	362.5	360.9	357.6	356.0	351.2	347.9	338.2	333.3
57.5°	325.3	323.6	325.3	322.0	318.8	315.6	313.9	310.6	305.8	299.4	292.9
60°	289.7	286.4	286.4	284.7	281.6	279.9	276.7	271.9	267.0	260.5	255.7
62.5°	254.0	252.5	250.8	249.2	246.0	244.3	242.7	237.8	233.0	228.1	223.3
65°	220.1	220.1	218.4	215.2	213.6	211.9	210.4	207.1	200.7	197.4	192.5
67.5°	189.4	187.7	187.7	184.5	181.2	179.7	179.7	176.4	171.5	166.7	163.5
70°	158.6	160.2	158.6	157.0	153.8	153.8	150.5	148.8	142.4	140.8	135.9
72.5°	131.1	131.1	129.4	129.4	126.2	124.6	124.6	121.4	118.1	114.9	111.7
75°	105.2	105.2	105.2	103.5	101.9	98.7	98.7	97.0	93.9	90.7	87.3
77.5°	82.5	80.8	80.8	79.3	77.7	76.0	76.0	74.5	71.2	69.6	66.3
80°	59.9	58.3	58.3	58.3	55.0	56.6	55.0	53.4	51.8	50.1	48.6
82.5°	38.9	40.4	40.4	38.9	37.2	37.2	37.2	35.6	35.6	33.9	32.4
85°	22.7	22.7	22.7	22.7	21.0	21.0	21.0	19.4	19.4	19.4	17.8
87.5°	9.7	9.7	9.7	9.7	9.7	9.7	8.0	8.0	8.0	8.0	8.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584029

CATALOG NUMBER: HCC8W20D010MW-HM80520840-81WWW

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1192.5	1192.5	1192.5	1192.5	1192.5	1192.5	1192.5	1192.5	1192.5	1192.5	1192.5
2.5°	1205.5	1202.3	1200.7	1199.0	1199.0	1197.5	1195.8	1192.5	1192.5	1189.3	1187.7
5°	1212.0	1207.2	1203.9	1200.7	1199.0	1195.8	1192.5	1187.7	1186.1	1181.3	1176.4
7.5°	1213.6	1205.5	1202.3	1195.8	1192.5	1189.3	1182.8	1178.0	1171.6	1166.6	1160.3
10°	1207.2	1200.7	1192.5	1184.5	1182.8	1178.0	1168.3	1161.8	1153.8	1147.2	1137.6
12.5°	1197.5	1187.7	1179.6	1169.9	1165.1	1160.3	1150.6	1140.7	1129.5	1118.2	1108.5
15°	1181.3	1169.9	1158.6	1147.2	1140.7	1135.9	1124.7	1113.3	1102.0	1087.4	1077.7
17.5°	1156.9	1144.1	1132.7	1118.2	1111.7	1106.8	1092.3	1079.3	1064.7	1050.2	1040.5
20°	1126.2	1110.0	1097.1	1080.9	1076.1	1067.9	1053.4	1038.9	1022.7	1006.5	995.1
22.5°	1085.8	1069.6	1055.1	1038.9	1030.7	1022.7	1008.1	990.3	974.1	961.2	949.9
25°	1038.9	1024.3	1006.5	991.9	982.2	972.5	956.4	941.8	927.2	907.8	896.4
27.5°	987.1	969.2	956.4	936.9	927.2	920.8	902.9	883.5	870.5	852.8	839.8
30°	928.8	912.6	898.1	878.7	869.0	862.5	846.3	828.5	815.6	797.7	784.8
32.5°	867.4	849.5	831.8	818.8	807.4	801.0	783.2	771.8	755.7	741.1	726.6
35°	801.0	783.2	770.2	752.5	746.0	739.5	724.9	710.4	695.8	682.8	671.5
37.5°	729.8	716.9	702.2	689.3	684.5	678.0	660.1	647.3	635.9	623.0	613.2
40°	660.1	648.9	639.2	626.2	618.2	613.2	600.3	589.0	576.1	568.0	558.3
42.5°	597.1	584.1	574.5	564.8	556.6	551.8	540.4	532.4	522.7	514.5	503.3
45°	530.7	524.3	513.0	504.8	500.0	493.5	485.4	475.8	467.6	461.2	453.1
47.5°	472.4	466.1	457.9	448.2	445.0	440.2	432.0	425.5	419.1	412.6	404.5
50°	419.1	411.0	404.5	398.1	394.8	389.9	381.9	378.6	373.7	367.4	362.5
52.5°	370.6	364.1	357.6	349.5	347.9	344.7	339.8	333.3	328.5	325.3	322.0
55°	326.8	320.4	315.6	309.1	307.4	304.2	297.7	294.6	291.2	288.1	284.7
57.5°	288.1	281.6	275.1	271.9	268.7	265.4	263.7	258.9	255.7	254.0	250.8
60°	252.5	246.0	241.1	236.3	234.6	233.0	229.8	226.6	223.3	220.1	218.4
62.5°	218.4	211.9	208.7	205.5	202.2	202.2	199.0	195.7	192.5	190.9	187.7
65°	187.7	184.5	179.7	174.8	173.2	173.2	168.3	166.7	165.0	161.8	158.6
67.5°	158.6	155.3	150.5	148.8	147.3	145.6	144.0	140.8	137.6	135.9	132.7
70°	132.7	129.4	126.2	124.6	122.9	121.4	118.1	116.5	113.2	111.7	110.0
72.5°	106.9	105.2	101.9	100.4	98.7	97.0	95.5	93.9	90.7	89.0	87.3
75°	85.8	84.2	80.8	79.3	77.7	77.7	76.0	72.8	71.2	71.2	69.6
77.5°	64.8	63.1	61.5	59.9	58.3	58.3	56.6	55.0	53.4	53.4	51.8
80°	46.9	45.3	43.7	43.7	43.7	42.1	40.4	40.4	38.9	38.9	37.2
82.5°	30.7	30.7	29.1	29.1	29.1	27.5	27.5	25.9	25.9	25.9	25.9
85°	17.8	17.8	17.8	16.2	16.2	16.2	16.2	16.2	16.2	14.5	16.2
87.5°	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0	6.5	6.5	6.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584029

CATALOG NUMBER: HCC8W20D010MW-HM80520840-81WWW

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1192.5	1192.5	1192.5	1192.5	1192.5	1192.5	1192.5	1192.5	1192.5	1192.5	1192.5
2.5°	1186.1	1184.5	1181.3	1181.3	1178.0	1178.0	1176.4	1174.8	1173.1	1171.6	1169.9
5°	1174.8	1168.3	1165.1	1163.4	1160.3	1158.6	1153.8	1150.6	1148.9	1145.6	1142.4
7.5°	1153.8	1147.2	1140.7	1139.2	1137.6	1131.1	1126.2	1121.4	1118.2	1114.9	1111.7
10°	1129.5	1123.0	1114.9	1111.7	1108.5	1100.3	1093.8	1089.0	1082.6	1076.1	1074.4
12.5°	1100.3	1090.6	1080.9	1077.7	1072.8	1064.7	1058.2	1050.2	1045.4	1037.2	1035.7
15°	1066.4	1055.1	1046.9	1038.9	1035.7	1027.5	1016.2	1009.8	1000.0	996.8	988.7
17.5°	1025.9	1014.6	1003.3	1000.0	995.1	983.8	972.5	964.4	954.7	949.9	945.0
20°	983.8	969.2	957.9	954.7	948.2	938.5	927.2	919.1	911.0	901.3	896.4
22.5°	935.3	919.1	909.4	901.3	899.7	888.4	875.4	869.0	862.5	854.3	848.0
25°	881.9	867.4	856.0	849.5	846.3	836.6	826.9	818.8	809.1	804.2	796.1
27.5°	826.9	817.1	802.6	796.1	791.2	783.2	771.8	767.0	757.3	750.8	746.0
30°	773.5	759.0	750.8	742.8	737.9	729.8	720.1	715.2	707.2	700.7	695.8
32.5°	715.2	705.5	694.2	691.0	684.5	676.3	670.0	661.8	655.3	648.9	647.3
35°	661.8	648.9	637.6	634.3	629.4	621.4	618.2	613.2	605.2	603.5	597.1
37.5°	603.5	597.1	584.1	579.3	577.6	571.3	564.8	561.4	556.6	551.8	550.2
40°	548.6	540.4	534.0	529.2	525.9	521.0	514.5	513.0	509.7	503.3	501.6
42.5°	496.8	488.6	482.3	480.6	475.8	470.9	467.6	462.8	461.2	459.6	456.4
45°	446.6	441.7	435.3	433.7	432.0	425.5	422.3	419.1	415.8	414.3	411.0
47.5°	401.3	396.4	391.6	389.9	386.8	385.1	380.2	378.6	373.7	372.2	370.6
50°	357.6	354.4	351.2	349.5	346.3	344.7	341.5	338.2	335.0	333.3	331.7
52.5°	318.8	315.6	312.3	310.6	309.1	305.8	302.6	299.4	297.7	296.1	294.6
55°	281.6	278.4	276.7	275.1	273.5	271.9	267.0	265.4	263.7	262.2	258.9
57.5°	247.6	244.3	241.1	241.1	239.5	237.8	234.6	231.4	231.4	228.1	224.9
60°	216.8	213.6	210.4	208.7	207.1	203.9	202.2	200.7	199.0	197.4	194.2
62.5°	184.5	182.9	179.7	179.7	176.4	174.8	173.2	171.5	169.9	166.7	165.0
65°	157.0	155.3	152.1	150.5	150.5	148.8	145.6	144.0	142.4	142.4	140.8
67.5°	131.1	129.4	126.2	124.6	124.6	122.9	121.4	121.4	119.7	118.1	119.7
70°	108.4	105.2	105.2	103.5	103.5	101.9	100.4	100.4	100.4	101.9	101.9
72.5°	85.8	84.2	82.5	82.5	82.5	82.5	80.8	80.8	82.5	84.2	84.2
75°	68.0	66.3	66.3	66.3	64.8	64.8	66.3	66.3	68.0	68.0	68.0
77.5°	50.1	50.1	50.1	50.1	50.1	50.1	51.8	51.8	53.4	53.4	53.4
80°	37.2	37.2	37.2	37.2	37.2	38.9	38.9	38.9	38.9	38.9	40.4
82.5°	25.9	25.9	25.9	25.9	25.9	25.9	25.9	27.5	27.5	27.5	27.5
85°	14.5	16.2	16.2	16.2	16.2	16.2	16.2	16.2	16.2	16.2	16.2
87.5°	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584029

CATALOG NUMBER: HCC8W20D010MW-HM80520840-81WWW

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1192.5	1192.5	1192.5	1192.5	1192.5	1192.5	1192.5	1192.5
2.5°	1168.3	1168.3	1168.3	1169.9	1166.6	1166.6	1166.6	1166.6
5°	1140.7	1139.2	1137.6	1139.2	1135.9	1135.9	1134.4	1134.4
7.5°	1106.8	1105.2	1103.6	1103.6	1100.3	1100.3	1098.7	1097.1
10°	1069.6	1066.4	1067.9	1064.7	1063.1	1061.6	1059.9	1058.2
12.5°	1029.2	1025.9	1024.3	1021.0	1017.8	1016.2	1017.8	1014.6
15°	985.4	980.6	978.9	975.7	972.5	970.9	970.9	969.2
17.5°	936.9	933.7	932.0	928.8	927.2	924.0	922.3	920.8
20°	891.6	883.5	885.1	881.9	880.2	873.9	873.9	875.4
22.5°	841.5	836.6	833.3	830.1	828.5	825.3	825.3	823.6
25°	791.2	786.4	784.8	781.5	780.0	776.7	775.0	775.0
27.5°	742.8	736.3	736.3	733.1	729.8	728.1	726.6	724.9
30°	691.0	686.2	684.5	684.5	682.8	682.8	678.0	679.6
32.5°	642.4	639.2	637.6	634.3	634.3	632.7	632.7	627.9
35°	593.8	589.0	590.6	587.3	585.8	584.1	585.8	584.1
37.5°	546.9	543.7	543.7	540.4	540.4	538.9	537.2	540.4
40°	500.0	498.4	496.8	495.1	496.8	495.1	491.9	493.5
42.5°	453.1	453.1	451.4	451.4	449.9	449.9	449.9	449.9
45°	411.0	409.4	409.4	407.8	407.8	407.8	407.8	406.1
47.5°	368.9	367.4	367.4	367.4	365.7	365.7	364.1	365.7
50°	328.5	328.5	326.8	326.8	328.5	326.8	325.3	325.3
52.5°	291.2	291.2	289.7	289.7	288.1	286.4	288.1	288.1
55°	257.3	255.7	254.0	254.0	252.5	250.8	250.8	252.5
57.5°	224.9	223.3	221.7	221.7	218.4	216.8	216.8	216.8
60°	194.2	190.9	190.9	189.4	189.4	187.7	187.7	187.7
62.5°	165.0	163.5	163.5	163.5	163.5	161.8	161.8	161.8
65°	140.8	140.8	140.8	142.4	142.4	144.0	144.0	144.0
67.5°	121.4	122.9	122.9	122.9	124.6	124.6	124.6	122.9
70°	103.5	103.5	103.5	105.2	105.2	105.2	105.2	105.2
72.5°	85.8	85.8	85.8	85.8	85.8	85.8	85.8	85.8
75°	68.0	69.6	69.6	69.6	68.0	69.6	69.6	68.0
77.5°	53.4	53.4	53.4	53.4	53.4	53.4	53.4	53.4
80°	40.4	40.4	40.4	40.4	40.4	40.4	40.4	40.4
82.5°	27.5	27.5	27.5	27.5	27.5	27.5	27.5	27.5
85°	16.2	16.2	16.2	16.2	16.2	16.2	16.2	16.2
87.5°	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)