

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593586

Luminaire Tested: **HCC8S20D010SL-HM80520850-81MDH**

Issue Date: 10/21/2021

### Test Information

Test Method: LM-41-14  
 Report Number: P593586  
 TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-5)  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Issue Date: 10/21/2021  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: HALO COMMERCIAL  
 Catalog Number: HCC8S20D010SL-HM80520850-81MDH  
 Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, HAZE TRIM  
 Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT  
 CYLINDER  
 Ballast/Driver: ELECTRONIC DRIVER

### Summary


Lumens per Lamp: N/A  
 Luminaire Lumens: 2390.3 lumens  
 Efficiency: N/A  
 Efficacy: 119.5 lumens/watt  
 Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.81  
 Luminous Opening: Circular (Dia: 0.67' x H: 0')  
 CIE Type: Direct

Input Watts (W): 20  
 Input Voltage (V): NR  
 Input Current (A<sub>in</sub>): NR  
 Voltage Rise (V): NR  
 Power Factor: NR  
 Total Harmonic Distortion (THDi): NR  
 Frequency (hertz): 60  
 Stabilization Time: NR  
 Operation Time: NR  
 Ambient Temperature (°C): NR  
 Test Distance: 25 FT



TEST NUMBER: P593586  
CATALOG NUMBER: HCC8S20D010SL-HM80520850-81MDH

### Luminous Intensity Polar Plot





TEST NUMBER: P593586  
 CATALOG NUMBER: HCC8S20D010SL-HM80520850-81MDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71			
6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	67	66			
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62			
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58			
9	76	67	61	57	75	66	61	57	65	60	56	64	60	56	63	59	56	55			
10	73	63	57	54	72	63	57	53	62	57	53	61	56	53	60	56	53	52			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	109312
5°	99613
10°	85112
15°	74224
20°	66156
25°	58685
30°	48048
35°	27593
40°	12241
45°	7130
50°	4111
55°	2349
60°	1295
65°	825
70°	586
75°	381
80°	302
85°	601



TEST NUMBER: P593586  
 CATALOG NUMBER: HCC8S20D010SL-HM80520850-81MDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	291.3	12.2
10°-20°	653.6	27.3
20°-30°	782.3	32.7
30°-40°	473.3	19.8
40°-50°	132.6	5.5
50°-60°	41.2	1.7
60°-70°	11.7	0.5
70°-80°	3.2	0.1
80°-90°	1.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1727.2	72.3
0°-40°	2200.5	92.1
0°-60°	2374.2	99.3
0°-90°	2390.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2390.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3545	
5°	3218	291
15°	2325	654
25°	1725	782
35°	733	473
45°	164	133
55°	44	41
65°	11	12
75°	3	3
85°	2	1
90°	0	



TEST NUMBER: P593586  
CATALOG NUMBER: HCC8S20D010SL-HM80520850-81MDH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3544.9
2.5°	3444.7
5°	3218.1
7.5°	2962.6
10°	2718.2
12.5°	2504.7
15°	2325.0
17.5°	2166.5
20°	2016.0
22.5°	1876.9
25°	1724.8
27.5°	1553.3
30°	1349.4
32.5°	1085.7
35°	733.0
37.5°	456.3
40°	304.1
42.5°	218.4
45°	163.5
47.5°	119.7
50°	85.7
52.5°	59.8
55°	43.7
57.5°	29.1
60°	21.0
62.5°	14.5
65°	11.3
67.5°	8.0
70°	6.5
72.5°	3.2
75°	3.2
77.5°	1.7
80°	1.7
82.5°	1.7
85°	1.7
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)