

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584225

Luminaire Tested: **HCC8W25D010SL-HM82555940-81RWWC**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584225  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-14)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W25D010SL-HM82555940-81RWWC  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2509.0 lumens  
Efficiency: N/A  
Efficacy: 93.6 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 1.08 / 1.17  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584225  
CATALOG NUMBER: HCC8W25D010SL-HM82555940-81RWWC

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584225

CATALOG NUMBER: HCC8W25D010SL-HM82555940-81RWWC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	85	82	79	77								
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67								
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	69	65	61	59								
5	81	70	62	56	80	69	62	56	67	61	56	65	59	55	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	40710	40710	40710
5°	41246	40537	40157
10°	41670	40120	39516
15°	42086	39276	38488
20°	41876	37826	36960
25°	40897	35562	35082
30°	38847	33007	32886
35°	35367	30119	30386
40°	31004	26962	27952
45°	26745	23981	25673
50°	23420	21055	23252
55°	20747	18096	20467
60°	18693	15215	16960
65°	16848	12222	12988
70°	14777	8899	7150
75°	12593	4611	1882
80°	9714	1261	302
85°	6262	0	0



TEST NUMBER: P584225  
 CATALOG NUMBER: HCC8W25D010SL-HM82555940-81RWWC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	124.6	5.0
10°-20°	350.1	14.0
20°-30°	497.0	19.8
30°-40°	523.1	20.9
40°-50°	445.0	17.7
50°-60°	321.6	12.8
60°-70°	182.9	7.3
70°-80°	57.6	2.3
80°-90°	7.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	971.7	38.7
0°-40°	1494.8	59.6
0°-60°	2261.5	90.1
0°-90°	2509.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2509.0	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1320	1320	1320	1320	1320	
5°	1332	1325	1310	1301	1297	127
15°	1318	1285	1230	1207	1206	371
25°	1202	1142	1045	1028	1031	551
35°	940	885	800	795	807	585
45°	613	590	550	564	589	477
55°	386	358	337	356	381	348
65°	231	199	168	166	178	229
75°	106	81	39	18	16	114
85°	18	11	0	0	0	23
90°	0	0	0	0	0	



TEST NUMBER: P584225

CATALOG NUMBER: HCC8W25D010SL-HM82555940-81RWWC

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1320.2	1320.2	1320.2	1320.2	1320.2	1320.2	1320.2	1320.2	1320.2	1320.2	1320.2
2.5°	1327.2	1328.9	1325.4	1325.4	1328.9	1325.4	1327.2	1327.2	1325.4	1325.4	1323.7
5°	1332.5	1330.8	1330.8	1330.8	1332.5	1328.9	1327.2	1328.9	1325.4	1325.4	1325.4
7.5°	1334.3	1334.3	1332.5	1330.8	1330.8	1330.8	1328.9	1327.2	1325.4	1321.9	1320.2
10°	1330.8	1330.8	1332.5	1328.9	1328.9	1325.4	1325.4	1321.9	1321.9	1318.3	1313.1
12.5°	1327.2	1325.4	1325.4	1321.9	1321.9	1318.3	1318.3	1313.1	1311.3	1306.0	1300.8
15°	1318.3	1316.6	1313.1	1311.3	1309.6	1307.9	1304.3	1302.5	1297.3	1290.2	1284.9
17.5°	1300.8	1299.0	1297.3	1293.7	1290.2	1288.4	1286.7	1281.3	1274.4	1269.0	1260.2
20°	1276.1	1274.4	1274.4	1269.0	1267.3	1262.0	1260.2	1253.2	1247.8	1237.3	1230.3
22.5°	1242.6	1244.4	1240.9	1237.3	1233.8	1228.5	1224.9	1217.9	1209.1	1198.5	1189.7
25°	1202.0	1203.9	1200.3	1196.8	1191.4	1187.9	1184.4	1173.9	1165.0	1152.7	1142.1
27.5°	1150.9	1150.9	1150.9	1147.5	1138.6	1136.9	1133.3	1122.8	1110.4	1099.9	1089.3
30°	1091.0	1089.3	1089.3	1084.0	1080.5	1073.4	1068.1	1059.3	1050.5	1038.1	1025.8
32.5°	1018.7	1020.6	1015.2	1011.7	1006.4	1006.4	999.4	992.3	981.7	969.4	957.1
35°	939.5	941.2	937.6	935.9	927.0	925.3	923.6	914.7	907.7	898.9	884.8
37.5°	858.4	856.6	854.8	854.8	849.6	846.0	842.5	837.2	826.7	819.6	812.6
40°	770.2	770.2	770.2	768.5	766.7	763.2	761.4	757.9	750.8	743.8	738.5
42.5°	690.9	690.9	689.2	687.4	683.8	685.7	682.1	678.6	671.5	666.3	662.8
45°	613.3	613.3	613.3	615.1	611.6	606.4	606.4	602.8	599.3	595.8	590.4
47.5°	544.6	549.9	546.3	544.6	546.3	539.4	539.4	535.9	532.3	528.8	521.7
50°	488.2	488.2	488.2	484.7	482.9	482.9	477.6	474.1	472.4	468.9	461.8
52.5°	437.1	433.6	433.6	431.9	430.0	426.5	426.5	423.0	415.9	412.5	407.1
55°	385.9	385.9	384.2	382.5	380.7	379.0	377.2	371.9	368.4	363.1	357.8
57.5°	340.2	343.7	342.0	338.4	334.9	334.9	331.4	327.8	322.5	317.3	312.0
60°	303.1	301.4	301.4	299.6	296.1	294.4	292.5	287.3	282.1	276.7	271.5
62.5°	264.4	264.4	264.4	260.9	257.3	255.5	253.8	250.3	243.2	238.0	234.4
65°	230.9	229.1	227.4	225.6	223.8	220.3	218.6	215.1	209.7	204.5	199.1
67.5°	197.4	195.6	195.6	193.9	188.6	186.8	186.8	181.6	176.2	171.0	165.6
70°	163.9	163.9	163.9	160.4	158.7	156.9	155.2	151.6	146.3	141.0	135.7
72.5°	135.7	134.0	134.0	132.1	126.9	125.2	123.4	119.8	114.6	111.1	107.5
75°	105.7	105.7	104.0	102.2	100.5	98.7	96.9	93.4	88.2	82.8	81.1
77.5°	81.1	79.3	79.3	77.6	74.0	72.2	72.2	68.7	63.5	59.9	56.4
80°	54.7	56.4	54.7	52.9	51.1	49.3	47.6	45.8	42.3	38.7	35.2
82.5°	33.5	35.2	33.5	33.5	31.8	30.0	30.0	26.4	24.7	22.9	21.2
85°	17.7	17.7	17.7	17.7	15.8	15.8	15.8	14.1	12.3	10.6	10.6
87.5°	5.2	7.1	5.2	5.2	5.2	5.2	5.2	5.2	3.5	3.5	3.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584225

CATALOG NUMBER: HCC8W25D010SL-HM82555940-81RWWC

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1320.2	1320.2	1320.2	1320.2	1320.2	1320.2	1320.2	1320.2	1320.2	1320.2	1320.2
2.5°	1325.4	1323.7	1321.9	1321.9	1321.9	1321.9	1321.9	1320.2	1318.3	1318.3	1318.3
5°	1321.9	1321.9	1321.9	1320.2	1318.3	1318.3	1314.8	1313.1	1311.3	1309.6	1307.9
7.5°	1318.3	1314.8	1313.1	1311.3	1309.6	1309.6	1306.0	1302.5	1302.5	1299.0	1295.4
10°	1307.9	1306.0	1302.5	1299.0	1297.3	1295.4	1291.9	1286.7	1284.9	1281.3	1277.8
12.5°	1295.4	1291.9	1288.4	1281.3	1279.6	1277.8	1270.8	1265.5	1262.0	1260.2	1251.4
15°	1279.6	1272.6	1267.3	1258.4	1256.7	1253.2	1247.8	1242.6	1235.5	1230.3	1226.8
17.5°	1251.4	1244.4	1235.5	1226.8	1223.2	1223.2	1214.3	1207.4	1198.5	1195.0	1187.9
20°	1217.9	1209.1	1202.0	1191.4	1186.2	1181.0	1175.6	1165.0	1158.0	1152.7	1143.9
22.5°	1179.1	1166.8	1158.0	1147.5	1138.6	1133.3	1124.5	1115.7	1106.9	1101.6	1094.5
25°	1129.8	1119.2	1105.1	1094.5	1089.3	1082.2	1071.6	1062.8	1054.0	1045.2	1041.6
27.5°	1075.1	1061.0	1048.7	1036.4	1031.1	1025.8	1013.5	1002.9	995.8	987.1	983.5
30°	1015.2	1001.1	987.1	976.5	971.1	962.4	955.3	943.0	934.1	927.0	918.3
32.5°	946.5	935.9	923.6	907.7	904.2	897.1	886.6	881.3	870.7	865.4	858.4
35°	872.5	865.4	853.1	840.7	835.5	831.9	823.2	812.6	805.5	800.1	796.7
37.5°	802.0	793.2	780.8	772.0	768.5	763.2	752.6	747.3	740.2	736.7	729.7
40°	726.2	717.3	708.6	703.2	698.0	694.4	687.4	682.1	675.1	669.8	668.0
42.5°	652.2	646.8	639.8	632.8	631.0	625.7	622.2	616.9	611.6	609.8	604.6
45°	585.2	579.8	572.9	565.8	564.0	560.5	558.8	553.4	549.9	549.9	549.9
47.5°	518.2	512.9	505.9	502.4	504.1	497.0	497.0	495.3	491.8	491.8	493.5
50°	458.3	451.2	449.4	446.0	442.4	438.9	440.6	435.4	435.4	438.9	437.1
52.5°	401.9	394.8	393.0	389.5	387.8	387.8	385.9	385.9	384.2	385.9	385.9
55°	350.7	345.5	342.0	338.4	336.6	336.6	336.6	334.9	333.1	336.6	338.4
57.5°	305.0	303.1	299.6	294.4	292.5	290.8	289.0	289.0	289.0	289.0	290.8
60°	264.4	260.9	257.3	252.1	252.1	250.3	248.6	246.7	246.7	246.7	246.7
62.5°	229.1	223.8	218.6	215.1	213.3	211.5	209.7	206.2	206.2	206.2	206.2
65°	193.9	188.6	185.1	181.6	178.0	178.0	174.5	172.7	169.2	167.5	163.9
67.5°	160.4	156.9	153.3	148.1	146.3	144.6	141.0	139.2	134.0	132.1	130.4
70°	130.4	125.2	121.7	118.1	116.3	112.8	109.2	105.7	102.2	98.7	95.2
72.5°	102.2	96.9	93.4	89.9	86.3	86.3	81.1	77.6	72.2	68.7	63.5
75°	75.8	70.5	67.0	61.7	59.9	58.2	52.9	49.3	44.1	38.7	35.2
77.5°	51.1	47.6	44.1	38.7	35.2	35.2	30.0	26.4	22.9	17.7	15.8
80°	31.8	28.2	24.7	21.2	21.2	17.7	15.8	12.3	8.8	7.1	5.2
82.5°	17.7	15.8	14.1	10.6	10.6	8.8	7.1	5.2	3.5	1.7	1.7
85°	8.8	7.1	5.2	5.2	3.5	3.5	3.5	1.7	1.7	0.0	0.0
87.5°	3.5	1.7	1.7	1.7	1.7	1.7	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584225

CATALOG NUMBER: HCC8W25D010SL-HM82555940-81RWWC

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1320.2	1320.2	1320.2	1320.2	1320.2	1320.2	1320.2	1320.2	1320.2	1320.2	1320.2
2.5°	1316.6	1316.6	1314.8	1314.8	1314.8	1313.1	1314.8	1313.1	1313.1	1313.1	1314.8
5°	1309.6	1306.0	1306.0	1304.3	1304.3	1302.5	1304.3	1302.5	1300.8	1299.0	1300.8
7.5°	1295.4	1291.9	1290.2	1288.4	1288.4	1288.4	1286.7	1284.9	1286.7	1281.3	1284.9
10°	1276.1	1274.4	1270.8	1269.0	1267.3	1269.0	1267.3	1263.8	1263.8	1263.8	1262.0
12.5°	1251.4	1247.8	1246.1	1244.4	1240.9	1240.9	1242.6	1239.1	1239.1	1235.5	1235.5
15°	1221.4	1217.9	1214.3	1214.3	1210.9	1210.9	1209.1	1209.1	1207.4	1205.6	1205.6
17.5°	1184.4	1179.1	1175.6	1177.4	1175.6	1173.9	1173.9	1170.4	1168.5	1170.4	1170.4
20°	1140.4	1136.9	1133.3	1135.1	1131.5	1129.8	1131.5	1126.3	1128.0	1128.0	1128.0
22.5°	1091.0	1089.3	1084.0	1084.0	1080.5	1078.7	1080.5	1080.5	1082.2	1080.5	1080.5
25°	1036.4	1032.9	1029.3	1029.3	1027.5	1025.8	1027.5	1029.3	1027.5	1029.3	1029.3
27.5°	978.2	973.0	973.0	969.4	969.4	971.1	969.4	971.1	973.0	973.0	976.5
30°	914.7	913.0	911.2	909.5	909.5	911.2	911.2	911.2	913.0	916.6	916.6
32.5°	854.8	851.3	847.8	847.8	851.3	849.6	851.3	851.3	854.8	854.8	858.4
35°	789.7	789.7	786.1	787.8	787.8	787.8	787.8	791.4	794.9	796.7	800.1
37.5°	729.7	724.4	726.2	726.2	727.9	726.2	731.5	731.5	735.0	735.0	738.5
40°	664.5	664.5	666.3	664.5	666.3	666.3	669.8	673.2	675.1	678.6	680.3
42.5°	602.8	606.4	602.8	604.6	606.4	608.1	609.8	611.6	618.7	622.2	627.4
45°	546.3	548.2	549.9	551.7	549.9	553.4	555.2	558.8	564.0	565.8	567.5
47.5°	491.8	493.5	495.3	497.0	497.0	500.5	502.4	505.9	509.4	511.1	512.9
50°	438.9	442.4	444.2	444.2	446.0	449.4	452.9	452.9	456.5	461.8	463.5
52.5°	391.3	391.3	394.8	396.5	398.4	398.4	403.6	405.4	407.1	410.7	414.2
55°	338.4	343.7	345.5	345.5	349.0	352.5	354.3	356.0	356.0	363.1	363.1
57.5°	292.5	294.4	297.9	297.9	297.9	303.1	303.1	306.7	308.5	310.2	313.7
60°	246.7	250.3	250.3	252.1	250.3	253.8	255.5	259.0	260.9	262.6	264.4
62.5°	204.5	204.5	206.2	206.2	206.2	206.2	209.7	209.7	213.3	215.1	216.8
65°	163.9	163.9	163.9	163.9	163.9	163.9	163.9	163.9	165.6	165.6	169.2
67.5°	126.9	125.2	121.7	123.4	121.7	121.7	119.8	119.8	121.7	121.7	125.2
70°	91.7	89.9	86.3	86.3	84.6	82.8	81.1	79.3	77.6	77.6	77.6
72.5°	59.9	56.4	51.1	49.3	49.3	45.8	42.3	40.6	40.6	40.6	40.6
75°	30.0	26.4	22.9	21.2	21.2	17.7	19.4	17.7	17.7	17.7	17.7
77.5°	12.3	8.8	7.1	7.1	7.1	5.2	5.2	5.2	5.2	5.2	5.2
80°	3.5	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
82.5°	1.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584225

CATALOG NUMBER: HCC8W25D010SL-HM82555940-81RWWC

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1320.2	1320.2	1320.2	1320.2	1320.2	1320.2	1320.2	1320.2
2.5°	1313.1	1313.1	1309.6	1311.3	1311.3	1311.3	1311.3	1311.3
5°	1297.3	1299.0	1297.3	1299.0	1299.0	1297.3	1297.3	1297.3
7.5°	1281.3	1283.1	1281.3	1283.1	1283.1	1283.1	1281.3	1281.3
10°	1262.0	1262.0	1262.0	1262.0	1262.0	1260.2	1262.0	1262.0
12.5°	1235.5	1235.5	1235.5	1237.3	1237.3	1235.5	1235.5	1233.8
15°	1207.4	1203.9	1205.6	1207.4	1205.6	1205.6	1205.6	1205.6
17.5°	1168.5	1170.4	1168.5	1168.5	1168.5	1168.5	1170.4	1168.5
20°	1128.0	1128.0	1129.8	1128.0	1128.0	1128.0	1128.0	1126.3
22.5°	1082.2	1080.5	1080.5	1082.2	1082.2	1080.5	1082.2	1082.2
25°	1031.1	1032.9	1031.1	1031.1	1032.9	1032.9	1032.9	1031.1
27.5°	976.5	978.2	980.0	978.2	978.2	978.2	980.0	981.7
30°	920.1	923.6	920.1	920.1	923.6	921.8	923.6	923.6
32.5°	860.2	865.4	861.9	865.4	865.4	867.1	865.4	867.1
35°	800.1	805.5	805.5	805.5	807.2	809.0	809.0	807.2
37.5°	743.8	745.6	745.6	749.1	750.8	752.6	752.6	750.8
40°	685.7	689.2	690.9	690.9	690.9	694.4	698.0	694.4
42.5°	629.3	631.0	632.8	632.8	636.3	638.0	639.8	639.8
45°	574.6	578.1	579.8	581.7	583.4	586.9	585.2	588.7
47.5°	518.2	523.4	525.3	527.0	530.5	532.3	534.0	535.9
50°	467.1	470.6	470.6	474.1	479.4	479.4	482.9	484.7
52.5°	415.9	417.7	419.4	421.3	424.8	428.3	428.3	431.9
55°	366.6	368.4	368.4	370.1	371.9	379.0	380.7	380.7
57.5°	315.5	315.5	319.1	320.8	322.5	326.0	326.0	326.0
60°	266.1	267.9	267.9	269.6	271.5	275.0	276.7	275.0
62.5°	216.8	218.6	218.6	220.3	223.8	225.6	223.8	223.8
65°	171.0	172.7	172.7	174.5	178.0	178.0	176.2	178.0
67.5°	125.2	125.2	125.2	125.2	125.2	125.2	125.2	125.2
70°	79.3	77.6	75.8	77.6	77.6	77.6	75.8	79.3
72.5°	38.7	40.6	40.6	40.6	40.6	40.6	40.6	38.7
75°	17.7	17.7	15.8	15.8	15.8	17.7	17.7	15.8
77.5°	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2
80°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)