

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584085

Luminaire Tested: **HCC8W20D010SL-HM80520940-81NDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584085
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W20D010SL-HM80520940-81NDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2113.8 lumens
Efficiency: N/A
Efficacy: 105.7 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.27
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584085
CATALOG NUMBER: HCC8W20D010SL-HM80520940-81NDC

Luminous Intensity Polar Plot





TEST NUMBER: P584085

CATALOG NUMBER: HCC8W20D010SL-HM80520940-81NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	112	110	108	112	110	108	107	106	105	103	102	101	100	99	98	97	96	96	96	96
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91	91	91	91
3	106	101	97	93	104	99	96	93	97	94	91	95	92	90	92	90	89	87	87	87	87
4	102	96	91	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83	83	83	83
5	98	92	87	83	97	91	86	83	89	85	82	87	84	82	86	83	81	80	80	80	80
6	95	88	83	79	93	87	82	79	86	82	79	84	81	78	83	80	78	76	76	76	76
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73	73	73	73
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71	71	71	71
9	85	78	73	70	84	77	73	70	76	72	70	76	72	69	75	72	69	68	68	68	68
10	83	75	70	67	82	75	70	67	74	70	67	73	69	67	73	69	67	66	66	66	66

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	397866
5°	255198
10°	115281
15°	69559
20°	53007
25°	42806
30°	31366
35°	11361
40°	4239
45°	1923
50°	614
55°	151
60°	86
65°	102
70°	0
75°	0
80°	249
85°	495



TEST NUMBER: P584085
 CATALOG NUMBER: HCC8W20D010SL-HM80520940-81NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	628.8	29.7
10°-20°	638.7	30.2
20°-30°	571.7	27.0
30°-40°	230.3	10.9
40°-50°	37.8	1.8
50°-60°	3.4	0.2
60°-70°	1.2	0.1
70°-80°	0.9	0.0
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1839.2	87.0
0°-40°	2069.5	97.9
0°-60°	2110.7	99.9
0°-90°	2114.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2113.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12902	
5°	8244	629
15°	2179	639
25°	1258	572
35°	302	230
45°	44	38
55°	3	3
65°	1	1
75°	0	1
85°	1	1
90°	0	



TEST NUMBER: P584085
CATALOG NUMBER: HCC8W20D010SL-HM80520940-81NDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	12902.5
0.5°	12862.6
1°	12696.1
1.5°	12428.5
2°	12022.9
2.5°	11543.3
3°	10942.7
3.5°	10283.8
4°	9632.0
4.5°	8901.9
5°	8244.4
5.5°	7528.5
6°	6947.9
6.5°	6343.1
7°	5867.7
7.5°	5365.3
8°	4961.2
8.5°	4555.5
9°	4250.9
9.5°	3915.1
10°	3681.7
12.5°	2715.4
15°	2178.9
17.5°	1861.5
20°	1615.3
22.5°	1418.9
25°	1258.1
27.5°	1097.3
30°	880.9
32.5°	566.4
35°	301.8
37.5°	166.5
40°	105.3
42.5°	69.7
45°	44.1
47.5°	27.1
50°	12.8
52.5°	4.3
55°	2.8
57.5°	1.4
60°	1.4
62.5°	1.4
65°	1.4



TEST NUMBER: P584085
CATALOG NUMBER: HCC8W20D010SL-HM80520940-81NDC

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	1.4
80°	1.4
82.5°	1.4
85°	1.4
87.5°	1.4
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



67.5°		1.4
70°		0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)