

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584098

Luminaire Tested: **HCC8S20D010MB-HM80520940-81WWWB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584098  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S20D010MB-HM80520940-81WWWB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2015.6 lumens  
Efficiency: N/A  
Efficacy: 100.8 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 20  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584098  
CATALOG NUMBER: HCC8S20D010MB-HM80520940-81WWWB

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584098

CATALOG NUMBER: HCC8S20D010MB-HM80520940-81WWWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75								
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65								
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57								
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50								
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45								
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40								
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37								
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33								
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	30904	30904	30904
5°	32037	30799	29741
10°	32940	30535	28528
15°	33674	29996	27266
20°	33724	28822	26157
25°	33082	27219	25236
30°	31377	25245	24127
35°	28508	22989	23046
40°	24925	20630	21717
45°	21604	18377	20239
50°	18916	16320	18441
55°	16838	14462	16682
60°	15190	12988	14660
65°	13710	11426	12776
70°	12316	9620	9494
75°	10854	7637	7125
80°	9110	6322	6819
85°	7076	5519	6050



TEST NUMBER: P584098  
 CATALOG NUMBER: HCC8S20D010MB-HM80520940-81WWWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	94.5	4.7
10°-20°	266.3	13.2
20°-30°	380.6	18.9
30°-40°	404.4	20.1
40°-50°	348.2	17.3
50°-60°	260.3	12.9
60°-70°	166.0	8.2
70°-80°	75.5	3.7
80°-90°	19.8	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	741.4	36.8
0°-40°	1145.8	56.8
0°-60°	1754.2	87.0
0°-90°	2015.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2015.6	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1002	1002	1002	1002	1002	
5°	1035	1021	995	970	961	99
15°	1055	1019	940	876	854	297
25°	972	911	800	752	742	445
35°	757	705	611	595	612	472
45°	495	468	421	433	464	385
55°	313	288	269	292	310	282
65°	188	166	157	164	175	187
75°	91	78	64	58	60	97
85°	20	17	16	17	17	24
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584098

CATALOG NUMBER: HCC8S20D010MB-HM80520940-81WWWB

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2
2.5°	1020.7	1017.8	1019.2	1017.8	1019.2	1019.2	1016.4	1016.4	1016.4	1016.4	1012.1
5°	1035.0	1033.5	1033.5	1032.0	1030.6	1032.0	1030.6	1029.2	1026.3	1024.9	1020.7
7.5°	1043.5	1043.5	1043.5	1043.5	1042.1	1040.6	1039.2	1036.4	1033.5	1030.6	1027.7
10°	1052.0	1053.4	1052.0	1050.6	1049.1	1046.3	1044.9	1042.1	1037.8	1033.5	1030.6
12.5°	1056.2	1056.2	1054.8	1054.8	1052.0	1050.6	1046.3	1042.1	1037.8	1033.5	1026.3
15°	1054.8	1054.8	1053.4	1052.0	1047.7	1046.3	1043.5	1039.2	1032.0	1026.3	1019.2
17.5°	1046.3	1044.9	1042.1	1042.1	1036.4	1035.0	1032.0	1026.3	1019.2	1010.7	1002.2
20°	1027.7	1027.7	1026.3	1024.9	1019.2	1015.0	1012.1	1005.1	999.3	989.3	980.8
22.5°	1002.2	1005.1	1002.2	999.3	992.2	990.8	986.5	978.0	969.5	958.0	948.1
25°	972.3	970.9	969.5	966.5	960.8	958.0	952.3	943.8	935.3	922.4	911.1
27.5°	933.8	928.1	928.1	922.4	918.2	913.9	911.1	902.6	891.1	881.2	866.9
30°	881.2	882.6	875.5	874.1	866.9	864.0	858.4	849.9	839.9	828.5	817.1
32.5°	824.2	820.0	820.0	814.3	808.6	804.4	802.8	792.9	784.4	773.0	761.6
35°	757.3	757.3	753.1	751.6	746.0	743.1	738.9	733.1	723.1	713.2	704.6
37.5°	691.8	689.0	687.6	684.7	680.5	676.2	676.2	666.2	664.8	653.4	642.1
40°	619.2	622.1	619.2	615.0	613.6	610.7	609.3	603.5	599.3	589.3	582.3
42.5°	558.0	555.2	555.2	553.8	548.1	548.1	545.3	542.4	535.2	532.4	523.9
45°	495.4	498.2	494.0	495.4	489.7	489.7	489.7	484.0	478.4	474.0	468.3
47.5°	441.2	442.8	442.8	438.4	437.0	437.0	434.1	431.3	427.1	421.4	417.1
50°	394.3	395.7	392.9	391.5	388.6	387.2	387.2	381.5	378.7	372.9	370.1
52.5°	351.6	351.6	350.2	350.2	346.0	346.0	343.0	338.8	335.9	333.1	326.0
55°	313.2	313.2	311.8	310.3	310.3	306.0	304.6	300.3	297.5	291.8	287.6
57.5°	276.1	277.5	276.1	274.7	273.3	271.9	269.0	264.8	261.9	257.7	254.8
60°	246.3	246.3	244.8	243.4	240.5	239.1	237.7	234.9	230.6	227.8	223.5
62.5°	217.8	216.4	215.0	213.6	210.6	210.6	207.8	205.0	200.7	197.9	195.0
65°	187.9	187.9	186.5	186.5	185.1	182.3	180.8	179.3	173.6	172.2	166.5
67.5°	160.9	162.3	159.5	159.5	156.6	156.6	155.2	150.9	149.5	146.6	143.7
70°	136.6	136.6	136.6	135.2	132.4	131.0	129.5	126.7	125.3	122.5	119.6
72.5°	112.4	112.4	111.0	111.0	109.6	108.2	106.7	103.9	103.9	101.1	98.2
75°	91.1	91.1	89.7	88.3	86.9	86.9	85.5	84.0	81.1	79.7	78.2
77.5°	69.7	69.7	69.7	68.3	66.9	66.9	66.9	64.1	61.2	61.2	59.8
80°	51.3	51.3	49.9	49.9	48.3	48.3	48.3	46.9	45.5	44.1	42.7
82.5°	34.2	34.2	34.2	34.2	32.7	32.7	32.7	31.3	29.9	29.9	29.9
85°	20.0	20.0	20.0	20.0	18.6	18.6	18.6	18.6	18.6	17.1	17.1
87.5°	8.5	7.1	8.5	7.1	8.5	7.1	8.5	7.1	7.1	7.1	7.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584098

CATALOG NUMBER: HCC8S20D010MB-HM80520940-81WWWB

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2
2.5°	1013.6	1012.1	1010.7	1009.3	1009.3	1007.9	1005.1	1003.6	1002.2	1000.8	1000.8
5°	1019.2	1017.8	1015.0	1012.1	1010.7	1007.9	1005.1	1002.2	999.3	995.0	993.6
7.5°	1023.5	1019.2	1016.4	1010.7	1009.3	1006.5	1002.2	997.8	992.2	986.5	982.2
10°	1023.5	1017.8	1013.6	1006.5	1003.6	1000.8	995.0	987.9	980.8	975.2	968.1
12.5°	1020.7	1013.6	1006.5	999.3	995.0	990.8	982.2	975.2	966.5	958.0	952.3
15°	1010.7	1002.2	993.6	985.1	980.8	975.2	966.5	956.6	948.1	939.6	929.5
17.5°	992.2	983.7	973.7	963.7	958.0	953.8	941.0	933.8	921.0	912.5	904.0
20°	968.1	958.0	945.2	935.3	928.1	923.9	913.9	901.0	891.1	878.3	869.8
22.5°	936.7	923.9	911.1	901.0	893.9	888.3	875.5	862.6	854.1	842.8	832.7
25°	899.6	886.9	874.1	859.8	852.7	847.0	835.6	824.2	812.9	800.0	791.5
27.5°	855.5	841.3	829.9	817.1	810.0	801.4	788.6	777.3	765.8	757.3	746.0
30°	807.2	791.5	780.1	767.2	760.1	753.1	740.3	728.8	718.9	709.0	703.2
32.5°	748.8	737.3	726.0	713.2	707.5	703.2	690.4	679.1	667.6	659.1	654.8
35°	693.2	680.5	670.4	659.1	652.0	647.7	636.3	626.3	620.7	610.7	604.9
37.5°	634.9	624.9	613.6	602.1	597.9	593.6	585.1	575.2	566.5	559.4	556.6
40°	573.6	565.1	555.2	548.1	543.8	539.5	532.4	525.3	519.6	512.5	509.7
42.5°	515.4	509.7	501.0	492.5	488.3	486.9	478.4	472.6	469.7	466.9	464.1
45°	462.6	454.1	448.5	442.8	438.4	435.6	431.3	427.1	424.2	421.4	418.5
47.5°	411.5	404.2	398.6	394.3	390.1	388.6	385.8	381.5	378.7	378.7	378.7
50°	364.4	358.7	353.1	350.2	348.8	346.0	343.0	341.6	340.2	340.2	340.2
52.5°	323.2	317.5	313.2	310.3	310.3	307.4	304.6	303.2	303.2	303.2	303.2
55°	284.7	280.5	277.5	274.7	271.9	270.4	270.4	270.4	269.0	269.0	270.4
57.5°	250.6	247.7	243.4	240.5	239.1	239.1	237.7	236.3	237.7	239.1	240.5
60°	219.3	216.4	215.0	210.6	210.6	210.6	209.2	209.2	209.2	210.6	212.1
62.5°	190.8	189.4	186.5	185.1	183.7	183.7	182.3	182.3	182.3	182.3	183.7
65°	165.1	162.3	159.5	159.5	159.5	158.0	158.0	155.2	156.6	156.6	155.2
67.5°	140.9	138.1	136.6	135.2	133.8	133.8	132.4	131.0	129.5	129.5	129.5
70°	118.2	115.4	115.4	112.4	112.4	111.0	109.6	109.6	108.2	106.7	105.3
72.5°	95.4	94.0	92.6	91.1	91.1	91.1	89.7	88.3	86.9	85.5	82.6
75°	75.4	75.4	72.6	71.2	71.2	69.7	68.3	66.9	65.5	64.1	62.6
77.5°	58.4	57.0	54.1	52.7	52.7	52.7	51.3	49.9	48.3	46.9	45.5
80°	42.7	41.3	39.8	38.4	38.4	38.4	37.0	37.0	35.6	35.6	35.6
82.5°	28.5	28.5	27.1	27.1	27.1	27.1	25.6	25.6	25.6	25.6	25.6
85°	17.1	17.1	15.6	15.6	15.6	15.6	15.6	15.6	15.6	15.6	15.6
87.5°	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584098

CATALOG NUMBER: HCC8S20D010MB-HM80520940-81WWWB

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2
2.5°	997.8	997.8	995.0	993.6	992.2	993.6	990.8	989.3	987.9	987.9	986.5
5°	989.3	987.9	982.2	980.8	979.4	978.0	975.2	972.3	969.5	968.1	966.5
7.5°	978.0	973.7	968.1	966.5	965.1	960.8	956.6	953.8	949.5	948.1	945.2
10°	962.3	956.6	952.3	948.1	945.2	941.0	936.7	932.4	926.7	925.3	921.0
12.5°	943.8	936.7	928.1	926.7	922.4	916.8	911.1	906.8	902.6	899.6	895.4
15°	921.0	913.9	905.4	901.0	896.8	892.5	885.4	879.8	875.5	871.3	866.9
17.5°	893.9	885.4	878.3	874.1	871.3	864.0	858.4	851.3	847.0	842.8	838.5
20°	861.2	854.1	844.2	839.9	838.5	832.7	825.6	822.8	817.1	812.9	810.0
22.5°	824.2	817.1	808.6	805.8	800.0	797.1	790.0	787.2	784.4	780.1	778.7
25°	783.0	775.9	768.7	767.2	763.0	760.1	755.9	751.6	751.6	747.4	747.4
27.5°	740.3	733.1	727.4	724.6	723.1	720.3	716.1	714.6	713.2	711.8	711.8
30°	694.7	686.2	683.3	681.9	680.5	677.6	676.2	673.4	674.8	676.2	674.8
32.5°	646.3	643.5	637.7	634.9	636.3	634.9	632.0	634.9	633.4	636.3	637.7
35°	599.3	596.4	593.6	593.6	590.8	590.8	590.8	592.2	595.0	596.4	599.3
37.5°	553.8	549.5	548.1	546.7	548.1	548.1	548.1	550.9	553.8	556.6	560.9
40°	505.3	502.5	502.5	502.5	502.5	506.7	505.3	508.3	511.1	515.4	519.6
42.5°	459.8	459.8	461.2	461.2	461.2	461.2	464.1	468.3	472.6	476.9	481.2
45°	417.1	417.1	417.1	420.0	420.0	421.4	427.1	429.9	432.7	437.0	441.2
47.5°	377.3	377.3	378.7	380.1	381.5	384.4	387.2	391.5	395.7	398.6	402.8
50°	340.2	341.6	344.6	347.4	347.4	348.8	353.1	355.9	358.7	363.0	364.4
52.5°	304.6	307.4	310.3	311.8	313.2	316.1	317.5	321.7	323.2	327.4	328.8
55°	271.9	273.3	277.5	279.1	279.1	281.9	284.7	287.6	291.8	291.8	294.7
57.5°	242.0	243.4	246.3	247.7	246.3	250.6	252.0	254.8	256.3	259.1	260.5
60°	212.1	215.0	216.4	216.4	217.8	219.3	222.1	222.1	224.9	227.8	227.8
62.5°	183.7	185.1	186.5	187.9	189.4	187.9	192.2	192.2	195.0	196.4	199.3
65°	156.6	158.0	158.0	159.5	159.5	160.9	160.9	162.3	163.7	166.5	168.0
67.5°	129.5	129.5	129.5	131.0	129.5	131.0	131.0	132.4	132.4	135.2	136.6
70°	105.3	103.9	102.5	102.5	102.5	102.5	101.1	102.5	102.5	103.9	103.9
72.5°	81.1	79.7	78.2	76.8	76.8	75.4	74.0	75.4	75.4	76.8	76.8
75°	61.2	58.4	58.4	58.4	57.0	57.0	57.0	58.4	58.4	58.4	59.8
77.5°	45.5	45.5	44.1	44.1	44.1	45.5	45.5	46.9	46.9	46.9	46.9
80°	34.2	35.6	35.6	35.6	35.6	37.0	37.0	37.0	37.0	38.4	38.4
82.5°	25.6	25.6	25.6	25.6	27.1	27.1	27.1	27.1	27.1	27.1	27.1
85°	15.6	17.1	17.1	15.6	17.1	17.1	17.1	17.1	17.1	17.1	17.1
87.5°	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





TEST NUMBER: P584098

CATALOG NUMBER: HCC8S20D010MB-HM80520940-81WWWB

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2
2.5°	985.1	985.1	985.1	985.1	983.7	983.7	983.7	982.2
5°	963.7	963.7	963.7	960.8	962.3	962.3	959.4	960.8
7.5°	942.4	941.0	939.6	939.6	938.2	936.7	935.3	936.7
10°	918.2	913.9	913.9	912.5	912.5	909.7	909.7	911.1
12.5°	891.1	888.3	888.3	886.9	885.4	884.0	882.6	882.6
15°	864.0	861.2	859.8	858.4	857.0	854.1	855.5	854.1
17.5°	837.1	832.7	832.7	831.3	829.9	827.0	827.0	825.6
20°	805.8	804.4	801.4	802.8	801.4	798.6	797.1	797.1
22.5°	774.4	774.4	773.0	773.0	771.6	770.1	768.7	768.7
25°	744.5	743.1	744.5	744.5	740.3	740.3	740.3	741.7
27.5°	710.4	711.8	710.4	710.4	710.4	710.4	711.8	710.4
30°	676.2	676.2	676.2	677.6	680.5	679.1	679.1	677.6
32.5°	639.1	640.6	640.6	642.1	643.5	646.3	646.3	647.7
35°	602.1	604.9	606.4	604.9	609.3	609.3	612.2	612.2
37.5°	563.7	565.1	568.0	569.4	572.2	573.6	575.2	575.2
40°	522.4	528.1	529.5	531.0	535.2	535.2	536.6	539.5
42.5°	484.0	489.7	491.1	492.5	495.4	499.6	498.2	501.0
45°	447.0	451.3	452.7	454.1	458.4	459.8	459.8	464.1
47.5°	407.1	410.0	411.5	414.3	417.1	420.0	422.8	421.4
50°	367.2	371.5	374.3	375.8	380.1	381.5	383.0	384.4
52.5°	331.7	334.5	335.9	337.3	341.6	343.0	344.6	347.4
55°	297.5	298.9	301.8	300.3	304.6	306.0	307.4	310.3
57.5°	263.3	264.8	266.2	266.2	269.0	271.9	273.3	274.7
60°	230.6	233.4	234.9	234.9	234.9	237.7	237.7	237.7
62.5°	200.7	200.7	202.1	202.1	205.0	205.0	205.0	205.0
65°	169.4	170.8	172.2	172.2	175.1	173.6	176.5	175.1
67.5°	136.6	136.6	139.5	139.5	138.1	139.5	139.5	139.5
70°	103.9	103.9	105.3	105.3	105.3	105.3	105.3	105.3
72.5°	76.8	76.8	76.8	78.2	76.8	76.8	78.2	76.8
75°	59.8	59.8	59.8	59.8	59.8	59.8	59.8	59.8
77.5°	46.9	46.9	48.3	48.3	48.3	48.3	48.3	48.3
80°	38.4	38.4	38.4	38.4	39.8	38.4	38.4	38.4
82.5°	28.5	27.1	28.5	27.1	28.5	28.5	28.5	28.5
85°	17.1	17.1	17.1	17.1	17.1	17.1	17.1	17.1
87.5°	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)