

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584087

Luminaire Tested: **HCC8S20D010BZ-HM80520940-81NDW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584087  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-3)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S20D010BZ-HM80520940-81NDW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1906.1 lumens  
Efficiency: N/A  
Efficacy: 95.3 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.92  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 20  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584087  
CATALOG NUMBER: HCC8S20D010BZ-HM80520940-81NDW

### Luminous Intensity Polar Plot





TEST NUMBER: P584087  
 CATALOG NUMBER: HCC8S20D010BZ-HM80520940-81NDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90																											
2	105	99	94	90	102	97	92	88	94	90	87	91	87	85	88	85	83	81																											
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73																											
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	72	68	67																											
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61																											
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56																											
7	77	66	59	54	76	66	59	54	64	58	54	63	58	54	62	57	53	52																											
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48																											
9	69	58	51	47	68	57	51	47	56	51	46	55	50	46	55	50	46	45																											
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42																											

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	47506
5°	47381
10°	46592
15°	45910
20°	44813
25°	42537
30°	35083
35°	18065
40°	12096
45°	10370
50°	8947
55°	7812
60°	6938
65°	6239
70°	5644
75°	5087
80°	4546
85°	4529



TEST NUMBER: P584087  
 CATALOG NUMBER: HCC8S20D010BZ-HM80520940-81NDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	144.7	7.6
10°-20°	404.6	21.2
20°-30°	560.6	29.4
30°-40°	336.8	17.7
40°-50°	184.4	9.7
50°-60°	130.9	6.9
60°-70°	85.0	4.5
70°-80°	45.4	2.4
80°-90°	13.6	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1110.0	58.2
0°-40°	1446.7	75.9
0°-60°	1762.0	92.4
0°-90°	1906.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1906.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1541	
5°	1531	145
15°	1438	405
25°	1250	561
35°	480	337
45°	238	184
55°	145	131
65°	86	85
75°	43	45
85°	13	14
90°	0	



TEST NUMBER: P584087  
CATALOG NUMBER: HCC8S20D010BZ-HM80520940-81NDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1540.6
2.5°	1537.8
5°	1530.7
7.5°	1513.6
10°	1488.0
12.5°	1463.8
15°	1438.1
17.5°	1405.4
20°	1365.6
22.5°	1317.1
25°	1250.2
27.5°	1144.8
30°	985.3
32.5°	722.0
35°	479.9
37.5°	354.6
40°	300.5
42.5°	266.3
45°	237.8
47.5°	210.8
50°	186.5
52.5°	163.7
55°	145.3
57.5°	128.1
60°	112.5
62.5°	98.2
65°	85.5
67.5°	72.6
70°	62.6
72.5°	51.3
75°	42.7
77.5°	34.2
80°	25.6
82.5°	18.6
85°	12.8
87.5°	5.7
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)