

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584249

Luminaire Tested: **HCC8S30D010MW-HM82555827-81WWBB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584249  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S30D010MW-HM82555827-81WWBB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2768.4 lumens  
Efficiency: N/A  
Efficacy: 98.9 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584249  
CATALOG NUMBER: HCC8S30D010MW-HM82555827-81WWBB

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584249

CATALOG NUMBER: HCC8S30D010MW-HM82555827-81WWBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77								
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67								
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59								
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47								
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43								
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39								
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	45829	45829	45829
5°	47725	45728	43803
10°	49320	45146	41667
15°	50568	44116	39503
20°	50667	42283	37544
25°	49811	39607	35599
30°	47147	36543	33937
35°	42986	32867	31862
40°	37380	28975	29422
45°	32070	25093	26933
50°	27392	21636	24193
55°	24010	18634	21015
60°	21376	15893	17669
65°	18964	12973	14104
70°	16824	9620	8006
75°	14023	5028	2383
80°	11045	1580	408
85°	7855	814	0



TEST NUMBER: P584249  
 CATALOG NUMBER: HCC8S30D010MW-HM82555827-81WWBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	140.0	5.1
10°-20°	392.5	14.2
20°-30°	555.6	20.1
30°-40°	581.2	21.0
40°-50°	484.8	17.5
50°-60°	343.8	12.4
60°-70°	198.0	7.2
70°-80°	63.7	2.3
80°-90°	8.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1088.1	39.3
0°-40°	1669.3	60.3
0°-60°	2497.9	90.2
0°-90°	2768.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2768.4	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1486	1486	1486	1486	1486	
5°	1542	1522	1477	1433	1415	148
15°	1584	1520	1382	1273	1237	445
25°	1464	1355	1164	1071	1046	668
35°	1142	1042	873	826	846	708
45°	735	675	575	582	618	570
55°	447	400	347	364	391	403
65°	260	218	178	178	193	260
75°	118	87	42	20	20	128
85°	22	11	2	0	0	28
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584249

CATALOG NUMBER: HCC8S30D010MW-HM82555827-81WWBB

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1486.2	1486.2	1486.2	1486.2	1486.2	1486.2	1486.2	1486.2	1486.2	1486.2	1486.2
2.5°	1517.3	1515.1	1512.9	1515.1	1512.9	1515.1	1512.9	1512.9	1510.6	1508.5	1508.5
5°	1541.8	1539.5	1539.5	1539.5	1537.4	1535.1	1535.1	1532.9	1528.5	1526.2	1521.8
7.5°	1557.4	1559.5	1559.5	1559.5	1555.1	1555.1	1550.7	1546.2	1541.8	1537.4	1530.7
10°	1575.1	1575.1	1572.9	1570.7	1566.2	1564.0	1561.8	1557.4	1550.7	1541.8	1535.1
12.5°	1581.7	1581.7	1579.6	1575.1	1572.9	1570.7	1568.4	1561.8	1552.8	1541.8	1532.9
15°	1584.0	1579.6	1577.3	1575.1	1570.7	1564.0	1564.0	1555.1	1544.0	1530.7	1519.5
17.5°	1566.2	1568.4	1564.0	1559.5	1552.8	1548.4	1541.8	1535.1	1521.8	1506.2	1495.2
20°	1544.0	1541.8	1539.5	1532.9	1523.9	1521.8	1515.1	1504.0	1492.9	1475.1	1459.6
22.5°	1508.5	1506.2	1501.8	1497.3	1488.5	1484.0	1477.3	1464.0	1448.4	1430.7	1412.9
25°	1464.0	1459.6	1453.0	1444.0	1437.4	1432.9	1424.1	1410.7	1392.9	1372.9	1355.1
27.5°	1392.9	1399.6	1395.2	1381.9	1375.2	1366.3	1364.0	1346.3	1330.7	1310.8	1290.8
30°	1324.1	1324.1	1317.4	1310.8	1299.6	1292.9	1284.1	1270.7	1255.2	1230.7	1215.2
32.5°	1237.4	1235.3	1226.3	1224.1	1215.2	1201.8	1199.7	1181.9	1166.3	1148.6	1128.6
35°	1141.9	1137.4	1128.6	1121.9	1117.4	1110.8	1104.1	1088.5	1073.1	1055.2	1041.9
37.5°	1033.0	1033.0	1030.9	1019.7	1015.3	1010.8	1004.1	988.7	979.7	961.9	948.6
40°	928.6	926.3	919.7	917.6	913.0	906.4	902.0	893.1	879.7	866.4	853.1
42.5°	826.5	828.6	819.8	822.0	813.0	808.6	806.4	793.1	786.4	773.1	762.0
45°	735.4	733.1	728.6	726.5	722.0	717.6	713.2	706.5	695.3	682.0	675.4
47.5°	651.0	644.2	644.2	642.1	639.8	630.9	628.7	622.1	615.4	602.0	593.2
50°	571.0	571.0	571.0	568.7	562.0	559.8	555.4	548.7	542.1	533.1	519.8
52.5°	506.5	506.5	506.5	504.3	495.5	493.2	490.9	482.1	473.2	466.6	457.6
55°	446.6	448.7	446.6	442.1	435.4	435.4	428.8	424.4	415.4	408.8	399.9
57.5°	395.5	395.5	390.9	388.8	384.3	382.1	377.6	373.2	362.2	355.5	344.3
60°	346.6	344.3	344.3	339.9	335.4	331.0	328.8	322.1	317.7	306.5	297.7
62.5°	302.1	302.1	297.7	297.7	288.8	288.8	286.5	279.9	273.2	262.2	257.7
65°	259.9	259.9	257.7	255.5	248.9	246.6	244.3	237.7	231.0	224.4	217.7
67.5°	222.1	222.1	217.7	215.4	211.0	208.8	204.4	200.0	193.3	186.6	179.9
70°	186.6	184.4	182.2	179.9	175.5	173.2	168.8	164.4	157.8	153.3	146.6
72.5°	151.1	151.1	148.9	144.3	142.2	139.9	137.7	133.3	126.6	120.0	115.6
75°	117.7	117.7	117.7	113.3	108.9	106.7	106.7	102.1	97.7	91.1	86.7
77.5°	91.1	88.8	86.7	86.7	82.2	80.0	77.8	75.5	68.8	66.7	62.2
80°	62.2	64.4	62.2	59.9	57.8	55.5	55.5	51.1	48.9	44.5	40.0
82.5°	42.2	40.0	40.0	37.8	37.8	35.6	35.6	31.2	28.9	26.6	24.5
85°	22.2	22.2	20.0	20.0	20.0	17.7	17.7	15.6	15.6	13.3	11.1
87.5°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	4.4	4.4	4.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584249

CATALOG NUMBER: HCC8S30D010MW-HM82555827-81WWBB

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1486.2	1486.2	1486.2	1486.2	1486.2	1486.2	1486.2	1486.2	1486.2	1486.2	1486.2
2.5°	1506.2	1501.8	1499.6	1499.6	1497.3	1495.2	1492.9	1490.6	1486.2	1486.2	1481.7
5°	1517.3	1512.9	1510.6	1504.0	1499.6	1499.6	1490.6	1488.5	1481.7	1477.3	1472.9
7.5°	1526.2	1517.3	1510.6	1504.0	1499.6	1495.2	1486.2	1477.3	1468.4	1459.6	1455.1
10°	1526.2	1517.3	1506.2	1495.2	1490.6	1486.2	1475.1	1461.8	1450.7	1441.8	1430.7
12.5°	1521.8	1508.5	1495.2	1486.2	1477.3	1470.7	1457.4	1444.0	1430.7	1412.9	1404.1
15°	1508.5	1490.6	1477.3	1461.8	1455.1	1444.0	1432.9	1412.9	1397.3	1381.9	1370.7
17.5°	1481.7	1459.6	1444.0	1428.5	1417.4	1410.7	1392.9	1375.2	1357.4	1339.6	1326.3
20°	1441.8	1421.8	1404.1	1384.0	1375.2	1366.3	1344.0	1326.3	1308.5	1288.5	1275.2
22.5°	1392.9	1372.9	1348.4	1333.0	1319.7	1308.5	1288.5	1268.5	1250.7	1233.0	1215.2
25°	1333.0	1312.9	1290.8	1266.3	1257.4	1246.3	1224.1	1204.1	1184.1	1164.1	1148.6
27.5°	1268.5	1241.9	1224.1	1197.4	1188.5	1177.5	1153.0	1130.7	1113.0	1097.4	1079.7
30°	1190.8	1170.8	1146.3	1121.9	1113.0	1101.8	1081.9	1061.9	1044.2	1026.3	1008.6
32.5°	1106.4	1086.4	1061.9	1044.2	1030.9	1021.9	1002.0	984.1	966.4	948.6	933.0
35°	1017.4	995.3	977.5	959.8	948.6	937.5	917.6	902.0	888.7	873.1	857.5
37.5°	926.3	910.9	893.1	873.1	862.0	853.1	837.5	819.8	808.6	795.3	784.3
40°	837.5	819.8	804.2	786.4	777.6	770.8	755.4	742.1	730.9	719.8	713.2
42.5°	746.5	730.9	715.3	704.2	697.6	690.9	679.8	664.3	657.6	646.5	639.8
45°	662.0	648.7	637.5	622.1	617.6	613.2	599.9	588.7	582.0	575.4	571.0
47.5°	582.0	573.2	559.8	551.0	544.3	539.8	531.0	522.1	515.4	510.9	506.5
50°	513.2	502.1	493.2	484.3	479.9	473.2	464.3	459.9	455.4	451.0	451.0
52.5°	448.7	437.7	428.8	422.1	417.7	413.2	406.5	404.4	399.9	399.9	397.7
55°	388.8	382.1	373.2	364.3	362.2	359.9	355.5	351.0	348.7	346.6	348.7
57.5°	337.7	331.0	322.1	315.4	313.2	311.0	308.8	304.4	302.1	302.1	302.1
60°	291.1	284.4	277.8	271.0	271.0	266.6	264.3	262.2	259.9	257.7	257.7
62.5°	248.9	242.2	235.5	231.0	228.8	226.6	222.1	220.0	217.7	217.7	215.4
65°	211.0	202.1	200.0	193.3	191.1	188.8	186.6	182.2	179.9	177.8	175.5
67.5°	173.2	168.8	162.2	157.8	155.5	153.3	151.1	146.6	144.3	142.2	137.7
70°	139.9	135.5	131.0	126.6	124.4	122.2	117.7	113.3	111.1	106.7	100.0
72.5°	108.9	104.4	100.0	95.5	93.3	91.1	86.7	82.2	77.8	73.4	68.8
75°	82.2	77.8	71.1	66.7	64.4	64.4	57.8	53.3	48.9	42.2	37.8
77.5°	57.8	51.1	48.9	44.5	42.2	37.8	33.3	28.9	24.5	22.2	17.7
80°	37.8	33.3	28.9	26.6	24.5	22.2	20.0	15.6	11.1	8.9	6.7
82.5°	22.2	20.0	17.7	15.6	13.3	11.1	8.9	8.9	6.7	4.4	2.3
85°	11.1	8.9	6.7	6.7	4.4	4.4	4.4	2.3	2.3	2.3	2.3
87.5°	4.4	2.3	2.3	2.3	2.3	2.3	2.3	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584249

CATALOG NUMBER: HCC8S30D010MW-HM82555827-81WWBB

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1486.2	1486.2	1486.2	1486.2	1486.2	1486.2	1486.2	1486.2	1486.2	1486.2	1486.2
2.5°	1479.6	1477.3	1475.1	1472.9	1472.9	1468.4	1468.4	1466.3	1461.8	1459.6	1459.6
5°	1466.3	1459.6	1455.1	1453.0	1450.7	1444.0	1441.8	1437.4	1432.9	1428.5	1426.2
7.5°	1446.3	1435.1	1430.7	1428.5	1421.8	1415.1	1410.7	1404.1	1397.3	1390.7	1388.5
10°	1421.8	1410.7	1399.6	1395.2	1388.5	1384.0	1375.2	1366.3	1359.6	1353.0	1346.3
12.5°	1390.7	1377.3	1366.3	1361.9	1355.1	1346.3	1333.0	1328.5	1317.4	1312.9	1304.1
15°	1355.1	1339.6	1328.5	1321.8	1315.2	1301.8	1292.9	1284.1	1272.9	1268.5	1259.6
17.5°	1310.8	1292.9	1281.9	1275.2	1270.7	1259.6	1246.3	1235.3	1224.1	1219.7	1213.0
20°	1257.4	1246.3	1230.7	1224.1	1219.7	1206.4	1193.0	1188.5	1179.6	1170.8	1164.1
22.5°	1197.4	1186.3	1170.8	1164.1	1161.9	1150.8	1139.7	1133.0	1126.3	1119.7	1113.0
25°	1135.3	1121.9	1108.6	1104.1	1099.7	1090.8	1081.9	1077.5	1070.8	1066.4	1061.9
27.5°	1068.6	1055.2	1044.2	1037.5	1033.0	1026.3	1021.9	1017.4	1013.0	1008.6	1006.4
30°	997.5	984.1	975.2	970.8	966.4	964.2	957.5	955.2	953.1	948.6	950.8
32.5°	926.3	915.3	906.4	899.7	899.7	895.3	893.1	893.1	890.8	890.8	890.8
35°	848.6	841.9	835.3	833.1	830.9	828.6	826.5	828.6	826.5	828.6	830.9
37.5°	777.6	770.8	766.4	764.2	762.0	764.2	762.0	762.0	764.2	768.7	770.8
40°	704.2	699.8	695.3	697.6	695.3	695.3	695.3	702.0	704.2	706.5	708.6
42.5°	635.4	630.9	628.7	628.7	630.9	628.7	633.1	635.4	639.8	646.5	651.0
45°	568.7	566.6	566.6	568.7	566.6	571.0	571.0	575.4	582.0	586.5	590.9
47.5°	506.5	506.5	506.5	508.8	508.8	510.9	515.4	517.6	522.1	526.5	531.0
50°	448.7	451.0	453.2	453.2	453.2	457.6	462.0	464.3	466.6	468.7	475.4
52.5°	397.7	399.9	399.9	402.1	404.4	406.5	408.8	413.2	415.4	419.8	422.1
55°	348.7	348.7	353.3	355.5	355.5	355.5	359.9	359.9	364.3	366.6	371.0
57.5°	302.1	304.4	304.4	306.5	306.5	308.8	311.0	313.2	315.4	317.7	320.0
60°	257.7	257.7	257.7	259.9	262.2	264.3	262.2	266.6	266.6	271.0	273.2
62.5°	215.4	217.7	217.7	217.7	217.7	217.7	217.7	220.0	222.1	224.4	226.6
65°	175.5	175.5	175.5	173.2	175.5	173.2	175.5	177.8	177.8	179.9	182.2
67.5°	135.5	135.5	131.0	131.0	133.3	133.3	133.3	133.3	131.0	135.5	135.5
70°	97.7	95.5	93.3	91.1	91.1	88.8	88.8	86.7	86.7	86.7	86.7
72.5°	64.4	59.9	55.5	53.3	51.1	51.1	46.6	44.5	46.6	46.6	46.6
75°	33.3	28.9	26.6	24.5	22.2	22.2	20.0	20.0	20.0	20.0	20.0
77.5°	13.3	11.1	8.9	8.9	6.7	6.7	6.7	6.7	6.7	6.7	6.7
80°	4.4	4.4	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
82.5°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
85°	2.3	0.0	0.0	2.3	0.0	2.3	2.3	2.3	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584249

CATALOG NUMBER: HCC8S30D010MW-HM82555827-81WWBB

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1486.2	1486.2	1486.2	1486.2	1486.2	1486.2	1486.2	1486.2
2.5°	1457.4	1457.4	1455.1	1457.4	1453.0	1455.1	1453.0	1453.0
5°	1424.1	1419.5	1419.5	1419.5	1417.4	1417.4	1415.1	1415.1
7.5°	1384.0	1381.9	1379.6	1377.3	1375.2	1372.9	1372.9	1372.9
10°	1344.0	1339.6	1339.6	1337.4	1333.0	1330.7	1330.7	1330.7
12.5°	1297.4	1295.2	1292.9	1292.9	1284.1	1286.3	1284.1	1284.1
15°	1253.0	1250.7	1250.7	1244.1	1239.7	1239.7	1239.7	1237.4
17.5°	1206.4	1204.1	1201.8	1197.4	1193.0	1193.0	1190.8	1193.0
20°	1157.5	1155.2	1150.8	1150.8	1148.6	1146.3	1141.9	1144.1
22.5°	1108.6	1104.1	1101.8	1101.8	1099.7	1099.7	1095.2	1095.2
25°	1057.5	1055.2	1053.0	1055.2	1050.8	1050.8	1046.3	1046.3
27.5°	1004.1	1002.0	1002.0	1002.0	999.7	1002.0	999.7	999.7
30°	950.8	950.8	948.6	948.6	950.8	948.6	950.8	953.1
32.5°	893.1	893.1	895.3	895.3	897.5	897.5	897.5	897.5
35°	833.1	837.5	837.5	839.8	841.9	844.2	844.2	846.4
37.5°	777.6	779.7	782.0	784.3	788.7	788.7	788.7	788.7
40°	717.6	719.8	724.2	722.0	730.9	733.1	730.9	730.9
42.5°	655.4	659.8	662.0	666.4	668.7	673.1	675.4	675.4
45°	597.6	599.9	604.2	608.8	610.9	617.6	617.6	617.6
47.5°	537.7	542.1	544.3	548.7	551.0	557.6	559.8	557.6
50°	479.9	484.3	488.8	488.8	495.5	497.6	502.1	504.3
52.5°	424.4	426.5	431.0	433.2	437.7	442.1	444.3	446.6
55°	371.0	373.2	377.6	377.6	384.3	386.5	390.9	390.9
57.5°	322.1	324.4	328.8	326.6	331.0	335.4	335.4	333.3
60°	275.5	275.5	275.5	279.9	282.1	284.4	286.5	286.5
62.5°	226.6	231.0	233.3	233.3	235.5	237.7	237.7	235.5
65°	182.2	186.6	188.8	188.8	191.1	191.1	191.1	193.3
67.5°	137.7	137.7	137.7	139.9	137.7	137.7	137.7	137.7
70°	86.7	86.7	86.7	86.7	84.4	86.7	86.7	88.8
72.5°	46.6	46.6	46.6	46.6	46.6	46.6	46.6	46.6
75°	20.0	20.0	20.0	22.2	20.0	20.0	20.0	20.0
77.5°	8.9	6.7	8.9	8.9	6.7	6.7	6.7	6.7
80°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
82.5°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
85°	0.0	2.3	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)