

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584242

Luminaire Tested: **HCC8W30D010MB-HM82555827-81RWWC**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584242  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-14)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W30D010MB-HM82555827-81RWWC  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3163.9 lumens  
Efficiency: N/A  
Efficacy: 113.0 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 1.08 / 1.17  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584242  
CATALOG NUMBER: HCC8W30D010MB-HM82555827-81RWWC

### Luminous Intensity Polar Plot





TEST NUMBER: P584242

CATALOG NUMBER: HCC8W30D010MB-HM82555827-81RWWC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	84	82	79	77			
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67			
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	69	65	61	59			
5	81	70	62	56	80	69	62	56	67	61	56	65	59	55	63	58	54	52			
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47			
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	51333	51333	51333
5°	52012	51118	50635
10°	52542	50597	49830
15°	53074	49527	48534
20°	52806	47700	46608
25°	51570	44844	44238
30°	48988	41624	41468
35°	44593	37987	38318
40°	39099	33994	35250
45°	33727	30239	32371
50°	29537	26548	29326
55°	26171	22822	25811
60°	23577	19193	21382
65°	21247	15410	16381
70°	18627	11225	9016
75°	15894	5826	2383
80°	12217	1580	408
85°	7855	0	0



TEST NUMBER: P584242  
 CATALOG NUMBER: HCC8W30D010MB-HM82555827-81RWWC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	157.1	5.0
10°-20°	441.5	14.0
20°-30°	626.7	19.8
30°-40°	659.7	20.9
40°-50°	561.2	17.7
50°-60°	405.5	12.8
60°-70°	230.7	7.3
70°-80°	72.7	2.3
80°-90°	8.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1225.3	38.7
0°-40°	1885.0	59.6
0°-60°	2851.7	90.1
0°-90°	3163.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3163.9	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1665	1665	1665	1665	1665	
5°	1680	1671	1651	1640	1636	160
15°	1662	1620	1551	1522	1520	468
25°	1516	1440	1318	1296	1300	694
35°	1185	1116	1009	1002	1018	737
45°	773	745	693	711	742	601
55°	487	451	424	449	480	439
65°	291	251	211	209	224	289
75°	133	102	49	22	20	143
85°	22	13	0	0	0	29
90°	0	0	0	0	0	



TEST NUMBER: P584242

CATALOG NUMBER: HCC8W30D010MB-HM82555827-81RWWC

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1664.7	1664.7	1664.7	1664.7	1664.7	1664.7	1664.7	1664.7	1664.7	1664.7	1664.7
2.5°	1673.6	1675.8	1671.4	1671.4	1675.8	1671.4	1673.6	1673.6	1671.4	1671.4	1669.1
5°	1680.3	1678.0	1678.0	1678.0	1680.3	1675.8	1673.6	1675.8	1671.4	1671.4	1671.4
7.5°	1682.4	1682.4	1680.3	1678.0	1678.0	1678.0	1675.8	1673.6	1671.4	1667.0	1664.7
10°	1678.0	1678.0	1680.3	1675.8	1675.8	1671.4	1671.4	1667.0	1667.0	1662.5	1655.8
12.5°	1673.6	1671.4	1671.4	1667.0	1667.0	1662.5	1662.5	1655.8	1653.5	1646.9	1640.2
15°	1662.5	1660.2	1655.8	1653.5	1651.4	1649.1	1644.7	1642.5	1635.8	1626.9	1620.3
17.5°	1640.2	1638.1	1635.8	1631.3	1626.9	1624.6	1622.5	1615.9	1606.9	1600.3	1589.1
20°	1609.2	1606.9	1606.9	1600.3	1598.0	1591.4	1589.1	1580.3	1573.5	1560.2	1551.4
22.5°	1566.9	1569.1	1564.7	1560.2	1555.8	1549.1	1544.6	1535.8	1524.7	1511.3	1500.3
25°	1515.7	1518.0	1513.6	1509.1	1502.4	1498.0	1493.6	1480.2	1469.1	1453.6	1440.2
27.5°	1451.3	1451.3	1451.3	1446.9	1435.8	1433.6	1429.1	1415.7	1400.2	1386.8	1373.5
30°	1375.8	1373.5	1373.5	1366.9	1362.5	1353.6	1346.9	1335.7	1324.7	1309.1	1293.5
32.5°	1284.6	1286.9	1280.2	1275.8	1269.1	1269.1	1260.2	1251.3	1238.0	1222.4	1206.8
35°	1184.6	1186.9	1182.5	1180.2	1169.0	1166.9	1164.6	1153.6	1144.7	1133.5	1115.8
37.5°	1082.3	1080.2	1077.9	1077.9	1071.3	1066.9	1062.4	1055.7	1042.4	1033.5	1024.6
40°	971.3	971.3	971.3	969.0	966.8	962.4	960.1	955.7	946.8	937.9	931.2
42.5°	871.3	871.3	869.0	866.8	862.4	864.5	860.1	855.7	846.8	840.1	835.6
45°	773.4	773.4	773.4	775.7	771.2	764.5	764.5	760.1	755.7	751.2	744.6
47.5°	686.8	693.4	689.0	686.8	689.0	680.1	680.1	675.7	671.2	666.8	657.9
50°	615.7	615.7	615.7	611.3	609.0	609.0	602.3	597.8	595.7	591.2	582.4
52.5°	551.2	546.7	546.7	544.6	542.3	537.9	537.9	533.4	524.5	520.1	513.4
55°	486.8	486.8	484.5	482.3	480.1	477.9	475.6	468.9	464.5	457.9	451.2
57.5°	429.0	433.4	431.1	426.7	422.3	422.3	417.8	413.4	406.8	400.1	393.4
60°	382.3	380.0	380.0	377.9	373.3	371.2	368.9	362.3	355.6	349.0	342.3
62.5°	333.4	333.4	333.4	329.0	324.5	322.2	320.1	315.6	306.8	300.1	295.6
65°	291.2	288.9	286.7	284.5	282.3	277.9	275.6	271.2	264.4	257.8	251.1
67.5°	249.0	246.7	246.7	244.5	237.8	235.5	235.5	228.9	222.2	215.6	208.9
70°	206.6	206.6	206.6	202.2	200.0	197.8	195.6	191.2	184.4	177.8	171.1
72.5°	171.1	169.0	169.0	166.7	160.0	157.8	155.5	151.1	144.5	140.1	135.5
75°	133.4	133.4	131.1	128.9	126.6	124.5	122.2	117.8	111.2	104.5	102.3
77.5°	102.3	100.0	100.0	97.7	93.3	91.1	91.1	86.7	80.0	75.6	71.1
80°	68.8	71.1	68.8	66.7	64.4	62.2	60.0	57.8	53.4	48.9	44.5
82.5°	42.2	44.5	42.2	42.2	40.0	37.8	37.8	33.3	31.2	28.9	26.6
85°	22.2	22.2	22.2	22.2	20.0	20.0	20.0	17.8	15.6	13.3	13.3
87.5°	6.7	8.9	6.7	6.7	6.7	6.7	6.7	6.7	4.4	4.4	4.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584242

CATALOG NUMBER: HCC8W30D010MB-HM82555827-81RWWC

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1664.7	1664.7	1664.7	1664.7	1664.7	1664.7	1664.7	1664.7	1664.7	1664.7	1664.7
2.5°	1671.4	1669.1	1667.0	1667.0	1667.0	1667.0	1667.0	1664.7	1662.5	1662.5	1662.5
5°	1667.0	1667.0	1667.0	1664.7	1662.5	1662.5	1658.1	1655.8	1653.5	1651.4	1649.1
7.5°	1662.5	1658.1	1655.8	1653.5	1651.4	1651.4	1646.9	1642.5	1642.5	1638.1	1633.6
10°	1649.1	1646.9	1642.5	1638.1	1635.8	1633.6	1629.2	1622.5	1620.3	1615.9	1611.3
12.5°	1633.6	1629.2	1624.6	1615.9	1613.6	1611.3	1602.4	1595.8	1591.4	1589.1	1578.0
15°	1613.6	1604.7	1598.0	1587.0	1584.7	1580.3	1573.5	1566.9	1558.1	1551.4	1546.9
17.5°	1578.0	1569.1	1558.1	1546.9	1542.5	1542.5	1531.3	1522.5	1511.3	1506.9	1498.0
20°	1535.8	1524.7	1515.7	1502.4	1495.8	1489.1	1482.4	1469.1	1460.2	1453.6	1442.5
22.5°	1486.8	1471.4	1460.2	1446.9	1435.8	1429.1	1418.0	1406.9	1395.8	1389.1	1380.2
25°	1424.7	1411.3	1393.5	1380.2	1373.5	1364.6	1351.3	1340.2	1329.1	1318.0	1313.5
27.5°	1355.8	1338.0	1322.4	1306.8	1300.2	1293.5	1277.9	1264.6	1255.7	1244.6	1240.2
30°	1280.2	1262.4	1244.6	1231.3	1224.7	1213.5	1204.6	1189.1	1177.9	1169.0	1158.0
32.5°	1193.5	1180.2	1164.6	1144.7	1140.1	1131.3	1117.9	1111.2	1097.9	1091.3	1082.3
35°	1100.2	1091.3	1075.7	1060.1	1053.5	1049.1	1038.0	1024.6	1015.8	1009.1	1004.6
37.5°	1011.2	1000.2	984.6	973.4	969.0	962.4	949.1	942.4	933.5	929.1	920.2
40°	915.6	904.6	893.4	886.8	880.1	875.7	866.8	860.1	851.2	844.5	842.4
42.5°	822.3	815.7	806.7	797.9	795.7	789.0	784.6	777.8	771.2	769.0	762.4
45°	737.9	731.2	722.3	713.4	711.3	706.7	704.6	697.9	693.4	693.4	693.4
47.5°	653.5	646.8	637.9	633.4	635.6	626.7	626.7	624.6	620.1	620.1	622.3
50°	577.9	568.9	566.8	562.3	557.9	553.4	555.6	549.0	549.0	553.4	551.2
52.5°	506.8	497.8	495.6	491.2	488.9	488.9	486.8	486.8	484.5	486.8	486.8
55°	442.3	435.6	431.1	426.7	424.5	424.5	424.5	422.3	420.1	424.5	426.7
57.5°	384.5	382.3	377.9	371.2	368.9	366.7	364.5	364.5	364.5	364.5	366.7
60°	333.4	329.0	324.5	317.8	317.8	315.6	313.4	311.2	311.2	311.2	311.2
62.5°	288.9	282.3	275.6	271.2	269.0	266.7	264.4	260.0	260.0	260.0	260.0
65°	244.5	237.8	233.4	228.9	224.5	224.5	220.1	217.8	213.4	211.2	206.6
67.5°	202.2	197.8	193.3	186.7	184.4	182.3	177.8	175.6	169.0	166.7	164.4
70°	164.4	157.8	153.4	148.9	146.7	142.2	137.8	133.4	128.9	124.5	120.0
72.5°	128.9	122.2	117.8	113.3	108.9	108.9	102.3	97.7	91.1	86.7	80.0
75°	95.6	88.9	84.4	77.8	75.6	73.4	66.7	62.2	55.5	48.9	44.5
77.5°	64.4	60.0	55.5	48.9	44.5	44.5	37.8	33.3	28.9	22.2	20.0
80°	40.0	35.6	31.2	26.6	26.6	22.2	20.0	15.6	11.1	8.9	6.7
82.5°	22.2	20.0	17.8	13.3	13.3	11.1	8.9	6.7	4.4	2.3	2.3
85°	11.1	8.9	6.7	6.7	4.4	4.4	4.4	2.3	2.3	0.0	0.0
87.5°	4.4	2.3	2.3	2.3	2.3	2.3	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584242

CATALOG NUMBER: HCC8W30D010MB-HM82555827-81RWWC

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1664.7	1664.7	1664.7	1664.7	1664.7	1664.7	1664.7	1664.7	1664.7	1664.7	1664.7
2.5°	1660.2	1660.2	1658.1	1658.1	1658.1	1655.8	1658.1	1655.8	1655.8	1655.8	1658.1
5°	1651.4	1646.9	1646.9	1644.7	1644.7	1642.5	1644.7	1642.5	1640.2	1638.1	1640.2
7.5°	1633.6	1629.2	1626.9	1624.6	1624.6	1624.6	1622.5	1620.3	1622.5	1615.9	1620.3
10°	1609.2	1606.9	1602.4	1600.3	1598.0	1600.3	1598.0	1593.6	1593.6	1593.6	1591.4
12.5°	1578.0	1573.5	1571.4	1569.1	1564.7	1564.7	1566.9	1562.5	1562.5	1558.1	1558.1
15°	1540.2	1535.8	1531.3	1531.3	1526.9	1526.9	1524.7	1524.7	1522.5	1520.3	1520.3
17.5°	1493.6	1486.8	1482.4	1484.7	1482.4	1480.2	1480.2	1475.8	1473.5	1475.8	1475.8
20°	1438.0	1433.6	1429.1	1431.3	1426.9	1424.7	1426.9	1420.3	1422.4	1422.4	1422.4
22.5°	1375.8	1373.5	1366.9	1366.9	1362.5	1360.2	1362.5	1362.5	1364.6	1362.5	1362.5
25°	1306.8	1302.4	1298.0	1298.0	1295.8	1293.5	1295.8	1298.0	1295.8	1298.0	1298.0
27.5°	1233.5	1226.8	1226.8	1222.4	1222.4	1224.7	1222.4	1224.7	1226.8	1226.8	1231.3
30°	1153.6	1151.3	1149.0	1146.8	1146.8	1149.0	1149.0	1149.0	1151.3	1155.7	1155.7
32.5°	1077.9	1073.5	1069.0	1069.0	1073.5	1071.3	1073.5	1073.5	1077.9	1077.9	1082.3
35°	995.7	995.7	991.3	993.5	993.5	993.5	993.5	997.9	1002.3	1004.6	1009.1
37.5°	920.2	913.5	915.6	915.6	917.9	915.6	922.3	922.3	926.8	926.8	931.2
40°	837.9	837.9	840.1	837.9	840.1	840.1	844.5	849.1	851.2	855.7	857.9
42.5°	760.1	764.5	760.1	762.4	764.5	766.8	769.0	771.2	780.1	784.6	791.3
45°	689.0	691.2	693.4	695.7	693.4	697.9	700.1	704.6	711.3	713.4	715.7
47.5°	620.1	622.3	624.6	626.7	626.7	631.2	633.4	637.9	642.3	644.6	646.8
50°	553.4	557.9	560.1	560.1	562.3	566.8	571.2	571.2	575.6	582.4	584.5
52.5°	493.4	493.4	497.8	500.1	502.4	502.4	509.0	511.2	513.4	517.8	522.3
55°	426.7	433.4	435.6	435.6	440.0	444.6	446.7	449.0	449.0	457.9	457.9
57.5°	368.9	371.2	375.6	375.6	375.6	382.3	382.3	386.8	388.9	391.2	395.6
60°	311.2	315.6	315.6	317.8	315.6	320.1	322.2	326.7	329.0	331.1	333.4
62.5°	257.8	257.8	260.0	260.0	260.0	260.0	264.4	264.4	269.0	271.2	273.4
65°	206.6	206.6	206.6	206.6	206.6	206.6	206.6	206.6	208.9	208.9	213.4
67.5°	160.0	157.8	153.4	155.5	153.4	153.4	151.1	151.1	153.4	153.4	157.8
70°	115.6	113.3	108.9	108.9	106.7	104.5	102.3	100.0	97.7	97.7	97.7
72.5°	75.6	71.1	64.4	62.2	62.2	57.8	53.4	51.1	51.1	51.1	51.1
75°	37.8	33.3	28.9	26.6	26.6	22.2	24.5	22.2	22.2	22.2	22.2
77.5°	15.6	11.1	8.9	8.9	8.9	6.7	6.7	6.7	6.7	6.7	6.7
80°	4.4	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
82.5°	2.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584242

CATALOG NUMBER: HCC8W30D010MB-HM82555827-81RWWC

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1664.7	1664.7	1664.7	1664.7	1664.7	1664.7	1664.7	1664.7
2.5°	1655.8	1655.8	1651.4	1653.5	1653.5	1653.5	1653.5	1653.5
5°	1635.8	1638.1	1635.8	1638.1	1638.1	1635.8	1635.8	1635.8
7.5°	1615.9	1618.0	1615.9	1618.0	1618.0	1618.0	1615.9	1615.9
10°	1591.4	1591.4	1591.4	1591.4	1591.4	1589.1	1591.4	1591.4
12.5°	1558.1	1558.1	1558.1	1560.2	1560.2	1558.1	1558.1	1555.8
15°	1522.5	1518.0	1520.3	1522.5	1520.3	1520.3	1520.3	1520.3
17.5°	1473.5	1475.8	1473.5	1473.5	1473.5	1473.5	1475.8	1473.5
20°	1422.4	1422.4	1424.7	1422.4	1422.4	1422.4	1422.4	1420.3
22.5°	1364.6	1362.5	1362.5	1364.6	1364.6	1362.5	1364.6	1364.6
25°	1300.2	1302.4	1300.2	1300.2	1302.4	1302.4	1302.4	1300.2
27.5°	1231.3	1233.5	1235.7	1233.5	1233.5	1233.5	1235.7	1238.0
30°	1160.2	1164.6	1160.2	1160.2	1164.6	1162.4	1164.6	1164.6
32.5°	1084.6	1091.3	1086.9	1091.3	1091.3	1093.5	1091.3	1093.5
35°	1009.1	1015.8	1015.8	1015.8	1017.9	1020.2	1020.2	1017.9
37.5°	937.9	940.1	940.1	944.5	946.8	949.1	949.1	946.8
40°	864.5	869.0	871.3	871.3	871.3	875.7	880.1	875.7
42.5°	793.4	795.7	797.9	797.9	802.3	804.6	806.7	806.7
45°	724.6	729.0	731.2	733.5	735.6	740.2	737.9	742.3
47.5°	653.5	660.1	662.3	664.5	669.1	671.2	673.4	675.7
50°	589.0	593.4	593.4	597.8	604.5	604.5	609.0	611.3
52.5°	524.5	526.7	529.0	531.2	535.6	540.0	540.0	544.6
55°	462.3	464.5	464.5	466.7	468.9	477.9	480.1	480.1
57.5°	397.8	397.8	402.2	404.5	406.8	411.2	411.2	411.2
60°	335.7	337.8	337.8	340.1	342.3	346.7	349.0	346.7
62.5°	273.4	275.6	275.6	277.9	282.3	284.5	282.3	282.3
65°	215.6	217.8	217.8	220.1	224.5	224.5	222.2	224.5
67.5°	157.8	157.8	157.8	157.8	157.8	157.8	157.8	157.8
70°	100.0	97.7	95.6	97.7	97.7	97.7	95.6	100.0
72.5°	48.9	51.1	51.1	51.1	51.1	51.1	51.1	48.9
75°	22.2	22.2	20.0	20.0	20.0	22.2	22.2	20.0
77.5°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7
80°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)