

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584250

Luminaire Tested: **HCC8W30D010MB-HM82555827-81WWW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584250
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W30D010MB-HM82555827-81WWW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3021.7 lumens
Efficiency: N/A
Efficacy: 107.9 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584250
CATALOG NUMBER: HCC8W30D010MB-HM82555827-81WWW

Luminous Intensity Polar Plot





TEST NUMBER: P584250

CATALOG NUMBER: HCC8W30D010MB-HM82555827-81WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76								
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66								
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58								
5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51								
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	50488	50488	50488
5°	52263	50198	48208
10°	53421	49320	45490
15°	54185	47659	42481
20°	54021	45347	39437
25°	52683	42404	36208
30°	49913	38996	33221
35°	45414	35291	30191
40°	39884	31386	27276
45°	34783	27609	24316
50°	30266	24193	21425
55°	26994	21263	18634
60°	24521	18631	15893
65°	22043	16206	14425
70°	19628	13821	13010
75°	17192	11640	11116
80°	14597	9465	9856
85°	11039	7076	7855



TEST NUMBER: P584250
 CATALOG NUMBER: HCC8W30D010MB-HM82555827-81WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.4	5.1
10°-20°	422.6	14.0
20°-30°	586.5	19.4
30°-40°	606.4	20.1
40°-50°	507.8	16.8
50°-60°	368.6	12.2
60°-70°	232.6	7.7
70°-80°	115.2	3.8
80°-90°	28.6	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1162.4	38.5
0°-40°	1768.8	58.5
0°-60°	2645.2	87.5
0°-90°	3021.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3021.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1637	1637	1637	1637	1637	
5°	1688	1668	1622	1577	1557	161
15°	1697	1633	1493	1373	1331	478
25°	1548	1448	1246	1111	1064	710
35°	1206	1117	938	831	802	751
45°	798	740	633	571	558	617
55°	502	458	396	362	347	453
65°	302	264	222	196	198	301
75°	144	120	98	93	93	155
85°	31	24	20	22	22	38
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584250

CATALOG NUMBER: HCC8W30D010MB-HM82555827-81WWW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1637.3	1637.3	1637.3	1637.3	1637.3	1637.3	1637.3	1637.3	1637.3	1637.3	1637.3
2.5°	1663.9	1663.9	1666.1	1663.9	1663.9	1663.9	1661.7	1661.7	1659.5	1659.5	1655.1
5°	1688.4	1684.0	1688.4	1684.0	1684.0	1684.0	1681.7	1677.3	1675.1	1670.7	1668.4
7.5°	1699.4	1697.3	1697.3	1695.0	1695.0	1692.8	1690.6	1688.4	1679.5	1677.3	1670.7
10°	1706.1	1704.0	1704.0	1701.7	1697.3	1697.3	1692.8	1690.6	1679.5	1675.1	1666.1
12.5°	1704.0	1704.0	1704.0	1701.7	1695.0	1692.8	1688.4	1681.7	1672.8	1663.9	1655.1
15°	1697.3	1697.3	1692.8	1690.6	1684.0	1679.5	1677.3	1666.1	1657.2	1646.2	1632.9
17.5°	1675.1	1675.1	1672.8	1668.4	1661.7	1657.2	1652.8	1641.8	1632.9	1615.0	1601.7
20°	1646.2	1643.9	1641.8	1635.1	1628.5	1626.2	1619.5	1604.0	1592.9	1579.5	1561.8
22.5°	1604.0	1601.7	1599.6	1595.0	1584.0	1579.5	1575.1	1564.0	1544.0	1530.6	1508.5
25°	1548.4	1548.4	1544.0	1537.3	1526.2	1521.8	1515.1	1504.0	1486.2	1466.3	1448.4
27.5°	1484.0	1481.7	1475.1	1470.7	1461.8	1455.1	1444.0	1430.7	1412.9	1397.3	1375.2
30°	1401.8	1401.8	1397.3	1390.7	1379.6	1375.2	1366.3	1350.7	1333.0	1312.9	1297.4
32.5°	1308.5	1308.5	1301.8	1297.4	1290.8	1279.6	1277.3	1259.6	1244.1	1228.5	1210.8
35°	1206.4	1208.5	1204.1	1195.2	1184.1	1184.1	1179.6	1164.1	1146.3	1130.7	1117.4
37.5°	1104.1	1097.4	1095.2	1090.8	1084.1	1075.2	1070.8	1064.2	1048.6	1037.5	1017.4
40°	990.8	993.1	988.5	984.1	981.9	975.2	973.1	961.9	950.8	937.5	928.6
42.5°	888.7	888.7	888.7	884.1	879.7	873.1	870.8	864.2	850.8	841.9	828.6
45°	797.6	790.9	790.9	788.7	786.4	782.0	775.3	770.8	762.0	755.4	739.8
47.5°	708.6	710.9	708.6	706.5	699.8	697.6	695.3	686.4	677.6	671.0	659.8
50°	630.9	635.4	630.9	630.9	626.5	624.2	619.8	613.2	606.5	595.3	584.3
52.5°	566.4	566.4	564.3	562.0	555.4	551.0	548.7	546.5	535.4	526.5	517.6
55°	502.1	504.3	504.3	497.6	495.5	490.9	488.8	482.0	477.6	464.3	457.6
57.5°	446.6	444.3	446.6	442.1	437.7	433.2	431.0	426.5	419.8	411.0	402.1
60°	397.6	393.2	393.2	390.9	386.5	384.3	379.9	373.2	366.6	357.7	351.0
62.5°	348.7	346.6	344.3	342.1	337.7	335.4	333.3	326.6	320.0	313.2	306.5
65°	302.1	302.1	299.9	295.5	293.2	291.1	288.8	284.4	275.5	271.0	264.3
67.5°	259.9	257.7	257.7	253.3	248.9	246.6	246.6	242.2	235.5	228.8	224.4
70°	217.7	220.0	217.7	215.4	211.0	211.0	206.6	204.4	195.5	193.3	186.6
72.5°	179.9	179.9	177.8	177.8	173.2	171.1	171.1	166.6	162.2	157.8	153.3
75°	144.3	144.3	144.3	142.2	139.9	135.5	135.5	133.3	128.9	124.4	120.0
77.5°	113.3	111.1	111.1	108.9	106.7	104.4	104.4	102.1	97.7	95.5	91.1
80°	82.2	80.0	80.0	80.0	75.5	77.8	75.5	73.4	71.1	68.8	66.7
82.5°	53.3	55.5	55.5	53.3	51.1	51.1	51.1	48.9	48.9	46.6	44.5
85°	31.2	31.2	31.2	31.2	28.9	28.9	28.9	26.6	26.6	26.6	24.5
87.5°	13.3	13.3	13.3	13.3	13.3	13.3	11.1	11.1	11.1	11.1	11.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584250

CATALOG NUMBER: HCC8W30D010MB-HM82555827-81WWW

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1637.3	1637.3	1637.3	1637.3	1637.3	1637.3	1637.3	1637.3	1637.3	1637.3	1637.3
2.5°	1655.1	1650.6	1648.4	1646.2	1646.2	1643.9	1641.8	1637.3	1637.3	1632.9	1630.6
5°	1663.9	1657.2	1652.8	1648.4	1646.2	1641.8	1637.3	1630.6	1628.5	1621.7	1615.0
7.5°	1666.1	1655.1	1650.6	1641.8	1637.3	1632.9	1623.9	1617.3	1608.4	1601.7	1592.9
10°	1657.2	1648.4	1637.3	1626.2	1623.9	1617.3	1604.0	1595.0	1584.0	1575.1	1561.8
12.5°	1643.9	1630.6	1619.5	1606.2	1599.6	1592.9	1579.5	1566.2	1550.7	1535.1	1521.8
15°	1621.7	1606.2	1590.6	1575.1	1566.2	1559.5	1544.0	1528.5	1512.9	1492.9	1479.6
17.5°	1588.4	1570.7	1555.1	1535.1	1526.2	1519.5	1499.6	1481.7	1461.8	1441.8	1428.5
20°	1546.2	1523.9	1506.2	1484.0	1477.3	1466.3	1446.2	1426.2	1404.0	1381.9	1366.3
22.5°	1490.6	1468.4	1448.4	1426.2	1415.1	1404.0	1384.0	1359.6	1337.4	1319.6	1304.1
25°	1426.2	1406.2	1381.9	1361.8	1348.4	1335.1	1312.9	1292.9	1272.9	1246.3	1230.7
27.5°	1355.1	1330.7	1312.9	1286.3	1272.9	1264.0	1239.7	1213.0	1195.2	1170.8	1153.0
30°	1275.2	1253.0	1233.0	1206.4	1192.9	1184.1	1161.9	1137.4	1119.7	1095.2	1077.5
32.5°	1190.8	1166.3	1141.9	1124.1	1108.5	1099.7	1075.2	1059.6	1037.5	1017.4	997.5
35°	1099.7	1075.2	1057.5	1033.0	1024.1	1015.3	995.3	975.2	955.2	937.5	922.0
37.5°	1002.0	984.1	964.2	946.3	939.7	930.9	906.4	888.7	873.1	855.2	841.9
40°	906.4	890.8	877.5	859.8	848.6	841.9	824.2	808.6	790.9	779.7	766.4
42.5°	819.7	802.0	788.7	775.3	764.2	757.5	742.1	730.9	717.6	706.5	690.9
45°	728.6	719.8	704.2	693.1	686.4	677.6	666.4	653.1	642.1	633.1	622.1
47.5°	648.7	639.8	628.7	615.4	610.9	604.2	593.2	584.3	575.4	566.4	555.4
50°	575.4	564.3	555.4	546.5	542.1	535.4	524.2	519.8	513.2	504.3	497.6
52.5°	508.8	499.9	490.9	479.9	477.6	473.2	466.6	457.6	451.0	446.6	442.1
55°	448.7	439.8	433.2	424.4	422.1	417.7	408.8	404.4	399.9	395.5	390.9
57.5°	395.5	386.5	377.6	373.2	368.8	364.3	362.2	355.4	351.0	348.7	344.3
60°	346.6	337.7	331.0	324.4	322.1	320.0	315.4	311.0	306.5	302.1	299.9
62.5°	299.9	291.1	286.5	282.1	277.8	277.8	273.2	268.8	264.3	262.2	257.7
65°	257.7	253.3	246.6	239.9	237.7	237.7	231.0	228.8	226.6	222.1	217.7
67.5°	217.7	213.3	206.6	204.4	202.1	200.0	197.7	193.3	188.8	186.6	182.2
70°	182.2	177.8	173.2	171.1	168.8	166.6	162.2	159.9	155.5	153.3	151.1
72.5°	146.6	144.3	139.9	137.7	135.5	133.3	131.0	128.9	124.4	122.2	120.0
75°	117.7	115.6	111.1	108.9	106.7	106.7	104.4	100.0	97.7	97.7	95.5
77.5°	88.8	86.7	84.4	82.2	80.0	80.0	77.8	75.5	73.4	73.4	71.1
80°	64.4	62.2	59.9	59.9	59.9	57.8	55.5	55.5	53.3	53.3	51.1
82.5°	42.2	42.2	40.0	40.0	40.0	37.8	37.8	35.6	35.6	35.6	35.6
85°	24.5	24.5	24.5	22.2	22.2	22.2	22.2	22.2	22.2	20.0	22.2
87.5°	11.1	11.1	11.1	11.1	11.1	11.1	11.1	11.1	8.9	8.9	8.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584250

CATALOG NUMBER: HCC8W30D010MB-HM82555827-81WWW

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1637.3	1637.3	1637.3	1637.3	1637.3	1637.3	1637.3	1637.3	1637.3	1637.3	1637.3
2.5°	1628.5	1626.2	1621.7	1621.7	1617.3	1617.3	1615.0	1612.9	1610.6	1608.4	1606.2
5°	1612.9	1604.0	1599.6	1597.3	1592.9	1590.6	1584.0	1579.5	1577.3	1572.8	1568.4
7.5°	1584.0	1575.1	1566.2	1564.0	1561.8	1552.8	1546.2	1539.5	1535.1	1530.6	1526.2
10°	1550.7	1541.8	1530.6	1526.2	1521.8	1510.6	1501.8	1495.0	1486.2	1477.3	1475.1
12.5°	1510.6	1497.3	1484.0	1479.6	1472.9	1461.8	1452.8	1441.8	1435.1	1424.1	1421.8
15°	1464.0	1448.4	1437.4	1426.2	1421.8	1410.6	1395.2	1386.3	1372.9	1368.4	1357.4
17.5°	1408.5	1392.9	1377.3	1372.9	1366.3	1350.7	1335.1	1324.1	1310.8	1304.1	1297.4
20°	1350.7	1330.7	1315.2	1310.8	1301.8	1288.5	1272.9	1261.9	1250.7	1237.4	1230.7
22.5°	1284.0	1261.9	1248.6	1237.4	1235.1	1219.7	1201.8	1192.9	1184.1	1172.9	1164.1
25°	1210.8	1190.8	1175.2	1166.3	1161.9	1148.6	1135.3	1124.1	1110.8	1104.1	1093.0
27.5°	1135.3	1121.9	1101.8	1093.0	1086.4	1075.2	1059.6	1053.0	1039.7	1030.7	1024.1
30°	1061.9	1041.9	1030.7	1019.7	1013.0	1002.0	988.5	981.9	970.8	961.9	955.2
32.5°	981.9	968.6	953.1	948.6	939.7	928.6	919.7	908.6	899.7	890.8	888.7
35°	908.6	890.8	875.3	870.8	864.2	853.1	848.6	841.9	830.9	828.6	819.7
37.5°	828.6	819.7	802.0	795.3	793.1	784.3	775.3	770.8	764.2	757.5	755.4
40°	753.1	742.1	733.1	726.5	722.0	715.3	706.5	704.2	699.8	690.9	688.7
42.5°	682.0	671.0	662.0	659.8	653.1	646.5	642.1	635.4	633.1	630.9	626.5
45°	613.2	606.5	597.6	595.3	593.2	584.3	579.9	575.4	571.0	568.7	564.3
47.5°	551.0	544.3	537.7	535.4	531.0	528.7	522.1	519.8	513.2	510.9	508.8
50°	490.9	486.5	482.0	479.9	475.4	473.2	468.7	464.3	459.9	457.6	455.4
52.5°	437.7	433.2	428.8	426.5	424.4	419.8	415.4	411.0	408.8	406.5	404.4
55°	386.5	382.1	379.9	377.6	375.5	373.2	366.6	364.3	362.2	359.9	355.4
57.5°	339.9	335.4	331.0	331.0	328.8	326.6	322.1	317.7	317.7	313.2	308.8
60°	297.7	293.2	288.8	286.5	284.4	279.9	277.8	275.5	273.2	271.0	266.6
62.5°	253.3	251.0	246.6	246.6	242.2	239.9	237.7	235.5	233.3	228.8	226.6
65°	215.4	213.3	208.8	206.6	206.6	204.4	200.0	197.7	195.5	195.5	193.3
67.5°	179.9	177.8	173.2	171.1	171.1	168.8	166.6	166.6	164.4	162.2	164.4
70°	148.9	144.3	144.3	142.2	142.2	139.9	137.7	137.7	137.7	139.9	139.9
72.5°	117.7	115.6	113.3	113.3	113.3	113.3	111.1	111.1	113.3	115.6	115.6
75°	93.3	91.1	91.1	91.1	88.8	88.8	91.1	91.1	93.3	93.3	93.3
77.5°	68.8	68.8	68.8	68.8	68.8	68.8	71.1	71.1	73.4	73.4	73.4
80°	51.1	51.1	51.1	51.1	51.1	53.3	53.3	53.3	53.3	53.3	55.5
82.5°	35.6	35.6	35.6	35.6	35.6	35.6	35.6	37.8	37.8	37.8	37.8
85°	20.0	22.2	22.2	22.2	22.2	22.2	22.2	22.2	22.2	22.2	22.2
87.5°	8.9	8.9	8.9	8.9	8.9	8.9	8.9	8.9	8.9	8.9	8.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584250

CATALOG NUMBER: HCC8W30D010MB-HM82555827-81WWW

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1637.3	1637.3	1637.3	1637.3	1637.3	1637.3	1637.3	1637.3
2.5°	1604.0	1604.0	1604.0	1606.2	1601.7	1601.7	1601.7	1601.7
5°	1566.2	1564.0	1561.8	1564.0	1559.5	1559.5	1557.4	1557.4
7.5°	1519.5	1517.3	1515.1	1515.1	1510.6	1510.6	1508.5	1506.2
10°	1468.4	1464.0	1466.3	1461.8	1459.6	1457.4	1455.1	1452.8
12.5°	1412.9	1408.5	1406.2	1401.8	1397.3	1395.2	1397.3	1392.9
15°	1353.0	1346.3	1344.0	1339.6	1335.1	1333.0	1333.0	1330.7
17.5°	1286.3	1281.9	1279.6	1275.2	1272.9	1268.5	1266.3	1264.0
20°	1224.1	1213.0	1215.2	1210.8	1208.5	1199.6	1199.6	1201.8
22.5°	1155.2	1148.6	1144.1	1139.7	1137.4	1133.0	1133.0	1130.7
25°	1086.4	1079.7	1077.5	1073.0	1070.8	1066.3	1064.2	1064.2
27.5°	1019.7	1010.8	1010.8	1006.4	1002.0	999.7	997.5	995.3
30°	948.6	941.9	939.7	939.7	937.5	937.5	930.9	933.0
32.5°	882.0	877.5	875.3	870.8	870.8	868.7	868.7	861.9
35°	815.3	808.6	810.9	806.4	804.2	802.0	804.2	802.0
37.5°	750.9	746.5	746.5	742.1	742.1	739.8	737.5	742.1
40°	686.4	684.3	682.0	679.8	682.0	679.8	675.4	677.6
42.5°	622.1	622.1	619.8	619.8	617.6	617.6	617.6	617.6
45°	564.3	562.0	562.0	559.8	559.8	559.8	559.8	557.6
47.5°	506.5	504.3	504.3	504.3	502.1	502.1	499.9	502.1
50°	451.0	451.0	448.7	448.7	451.0	448.7	446.6	446.6
52.5°	399.9	399.9	397.6	397.6	395.5	393.2	395.5	395.5
55°	353.3	351.0	348.7	348.7	346.6	344.3	344.3	346.6
57.5°	308.8	306.5	304.4	304.4	299.9	297.7	297.7	297.7
60°	266.6	262.2	262.2	259.9	259.9	257.7	257.7	257.7
62.5°	226.6	224.4	224.4	224.4	224.4	222.1	222.1	222.1
65°	193.3	193.3	193.3	195.5	195.5	197.7	197.7	197.7
67.5°	166.6	168.8	168.8	168.8	171.1	171.1	171.1	168.8
70°	142.2	142.2	142.2	144.3	144.3	144.3	144.3	144.3
72.5°	117.7	117.7	117.7	117.7	117.7	117.7	117.7	117.7
75°	93.3	95.5	95.5	95.5	93.3	95.5	95.5	93.3
77.5°	73.4	73.4	73.4	73.4	73.4	73.4	73.4	73.4
80°	55.5	55.5	55.5	55.5	55.5	55.5	55.5	55.5
82.5°	37.8	37.8	37.8	37.8	37.8	37.8	37.8	37.8
85°	22.2	22.2	22.2	22.2	22.2	22.2	22.2	22.2
87.5°	8.9	8.9	8.9	8.9	8.9	8.9	8.9	8.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)