

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593613

Luminaire Tested: **HCC8W20D010SL-HM80520950-81RWWC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593613
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W20D010SL-HM80520950-81RWWC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2027.0 lumens
Efficiency: N/A
Efficacy: 101.3 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.08 / 1.17
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593613
CATALOG NUMBER: HCC8W20D010SL-HM80520950-81RWWC

Luminous Intensity Polar Plot





TEST NUMBER: P593613

CATALOG NUMBER: HCC8W20D010SL-HM80520950-81RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	85	82	79	77								
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67								
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	69	65	61	59								
5	81	70	62	56	80	69	62	56	67	61	56	65	59	55	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	32887	32887	32887
5°	33319	32749	32440
10°	33660	32414	31923
15°	34002	31729	31094
20°	33829	30561	29859
25°	33041	28730	28342
30°	31384	26669	26570
35°	28572	24333	24548
40°	25046	21781	22582
45°	21608	19376	20741
50°	18920	17011	18786
55°	16763	14623	16537
60°	15104	12298	13697
65°	13608	9865	10492
70°	11937	7195	5779
75°	10187	3729	1525
80°	7831	1012	249
85°	5024	0	0



TEST NUMBER: P593613

CATALOG NUMBER: HCC8W20D010SL-HM80520950-81RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.6	5.0
10°-20°	282.9	14.0
20°-30°	401.5	19.8
30°-40°	422.6	20.9
40°-50°	359.5	17.7
50°-60°	259.8	12.8
60°-70°	147.8	7.3
70°-80°	46.6	2.3
80°-90°	5.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	785.0	38.7
0°-40°	1207.6	59.6
0°-60°	1827.0	90.1
0°-90°	2027.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2027.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1066	1066	1066	1066	1066	
5°	1076	1071	1058	1051	1048	103
15°	1065	1038	994	975	974	300
25°	971	923	844	830	833	445
35°	759	715	646	642	652	472
45°	496	477	444	456	476	385
55°	312	289	272	288	308	281
65°	186	161	135	134	144	185
75°	86	66	31	14	13	92
85°	14	8	0	0	0	18
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593613

CATALOG NUMBER: HCC8W20D010SL-HM80520950-81RWWC

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1066.5	1066.5	1066.5	1066.5	1066.5	1066.5	1066.5	1066.5	1066.5	1066.5	1066.5
2.5°	1072.2	1073.6	1070.8	1070.8	1073.6	1070.8	1072.2	1072.2	1070.8	1070.8	1069.4
5°	1076.4	1075.0	1075.0	1075.0	1076.4	1073.6	1072.2	1073.6	1070.8	1070.8	1070.8
7.5°	1077.9	1077.9	1076.4	1075.0	1075.0	1075.0	1073.6	1072.2	1070.8	1067.9	1066.5
10°	1075.0	1075.0	1076.4	1073.6	1073.6	1070.8	1070.8	1067.9	1067.9	1065.1	1060.8
12.5°	1072.2	1070.8	1070.8	1067.9	1067.9	1065.1	1065.1	1060.8	1059.4	1055.2	1050.9
15°	1065.1	1063.7	1060.8	1059.4	1058.0	1056.6	1053.8	1052.3	1048.0	1042.3	1038.0
17.5°	1050.9	1049.4	1048.0	1045.1	1042.3	1040.9	1039.5	1035.2	1029.5	1025.3	1018.1
20°	1030.9	1029.5	1029.5	1025.3	1023.8	1019.5	1018.1	1012.4	1008.1	999.6	993.9
22.5°	1003.9	1005.3	1002.5	999.6	996.8	992.5	989.7	983.9	976.8	968.3	961.2
25°	971.1	972.5	969.7	966.9	962.6	959.8	956.8	948.3	941.2	931.3	922.7
27.5°	929.9	929.9	929.9	926.9	919.8	918.4	915.6	907.1	897.0	888.5	880.0
30°	881.4	880.0	880.0	875.7	872.9	867.1	862.9	855.8	848.7	838.7	828.7
32.5°	823.0	824.4	820.2	817.4	813.1	813.1	807.4	801.6	793.1	783.2	773.1
35°	759.0	760.4	757.5	756.1	749.0	747.6	746.2	739.0	733.3	726.2	714.8
37.5°	693.5	692.1	690.6	690.6	686.4	683.4	680.6	676.3	667.8	662.2	656.5
40°	622.2	622.2	622.2	620.8	619.4	616.5	615.1	612.3	606.6	600.9	596.7
42.5°	558.1	558.1	556.7	555.3	552.5	553.9	551.0	548.2	542.5	538.3	535.4
45°	495.5	495.5	495.5	496.9	494.1	489.8	489.8	487.0	484.1	481.3	477.1
47.5°	439.9	444.3	441.4	439.9	441.4	435.7	435.7	432.8	430.0	427.2	421.5
50°	394.4	394.4	394.4	391.6	390.2	390.2	385.9	383.1	381.7	378.7	373.0
52.5°	353.2	350.3	350.3	348.8	347.4	344.6	344.6	341.7	336.0	333.2	329.0
55°	311.8	311.8	310.4	309.0	307.6	306.1	304.7	300.5	297.6	293.4	289.0
57.5°	274.8	277.7	276.2	273.4	270.6	270.6	267.7	264.9	260.6	256.3	252.0
60°	244.9	243.5	243.5	242.1	239.2	237.8	236.4	232.1	227.8	223.5	219.3
62.5°	213.6	213.6	213.6	210.8	207.9	206.5	205.1	202.2	196.4	192.2	189.4
65°	186.5	185.1	183.7	182.3	180.8	178.0	176.6	173.8	169.5	165.1	160.9
67.5°	159.5	158.0	158.0	156.6	152.4	150.9	150.9	146.7	142.4	138.2	133.8
70°	132.4	132.4	132.4	129.5	128.1	126.7	125.3	122.5	118.2	113.9	109.7
72.5°	109.7	108.3	108.3	106.9	102.5	101.1	99.6	96.8	92.6	89.7	86.9
75°	85.5	85.5	84.0	82.6	81.2	79.8	78.4	75.4	71.2	66.9	65.5
77.5°	65.5	64.1	64.1	62.6	59.8	58.4	58.4	55.6	51.3	48.5	45.5
80°	44.1	45.5	44.1	42.7	41.3	39.8	38.4	37.0	34.2	31.3	28.5
82.5°	27.1	28.5	27.1	27.1	25.6	24.2	24.2	21.4	20.0	18.6	17.1
85°	14.2	14.2	14.2	14.2	12.8	12.8	12.8	11.3	9.9	8.5	8.5
87.5°	4.3	5.7	4.3	4.3	4.3	4.3	4.3	4.3	2.8	2.8	2.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593613

CATALOG NUMBER: HCC8W20D010SL-HM80520950-81RWWC

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1066.5	1066.5	1066.5	1066.5	1066.5	1066.5	1066.5	1066.5	1066.5	1066.5	1066.5
2.5°	1070.8	1069.4	1067.9	1067.9	1067.9	1067.9	1067.9	1066.5	1065.1	1065.1	1065.1
5°	1067.9	1067.9	1067.9	1066.5	1065.1	1065.1	1062.3	1060.8	1059.4	1058.0	1056.6
7.5°	1065.1	1062.3	1060.8	1059.4	1058.0	1058.0	1055.2	1052.3	1052.3	1049.4	1046.5
10°	1056.6	1055.2	1052.3	1049.4	1048.0	1046.5	1043.7	1039.5	1038.0	1035.2	1032.4
12.5°	1046.5	1043.7	1040.9	1035.2	1033.8	1032.4	1026.7	1022.4	1019.5	1018.1	1011.0
15°	1033.8	1028.1	1023.8	1016.6	1015.2	1012.4	1008.1	1003.9	998.2	993.9	991.1
17.5°	1011.0	1005.3	998.2	991.1	988.2	988.2	981.1	975.4	968.3	965.5	959.8
20°	983.9	976.8	971.1	962.6	958.2	954.0	949.7	941.2	935.6	931.3	924.1
22.5°	952.6	942.6	935.6	926.9	919.8	915.6	908.5	901.4	894.2	889.9	884.3
25°	912.7	904.2	892.8	884.3	880.0	874.3	865.7	858.6	851.5	844.4	841.6
27.5°	868.7	857.2	847.3	837.2	833.0	828.7	818.8	810.3	804.5	797.4	794.5
30°	820.2	808.8	797.4	788.9	784.6	777.5	771.7	761.8	754.7	749.0	741.8
32.5°	764.6	756.1	746.2	733.3	730.5	724.8	716.3	711.9	703.4	699.2	693.5
35°	704.8	699.2	689.2	679.2	674.9	672.1	665.0	656.5	650.7	646.4	643.6
37.5°	647.9	640.8	630.8	623.6	620.8	616.5	608.0	603.8	598.1	595.3	589.5
40°	586.6	579.5	572.4	568.2	563.9	561.0	555.3	551.0	545.4	541.1	539.7
42.5°	526.8	522.6	516.9	511.2	509.8	505.5	502.7	498.3	494.1	492.7	488.4
45°	472.8	468.4	462.8	457.1	455.7	452.8	451.4	447.2	444.3	444.3	444.3
47.5°	418.7	414.4	408.6	405.8	407.2	401.5	401.5	400.1	397.3	397.3	398.7
50°	370.2	364.5	363.1	360.3	357.4	354.6	356.0	351.8	351.8	354.6	353.2
52.5°	324.7	318.9	317.5	314.6	313.2	313.2	311.8	311.8	310.4	311.8	311.8
55°	283.3	279.1	276.2	273.4	272.0	272.0	272.0	270.6	269.1	272.0	273.4
57.5°	246.3	244.9	242.1	237.8	236.4	235.0	233.6	233.6	233.6	233.6	235.0
60°	213.6	210.8	207.9	203.7	203.7	202.2	200.8	199.4	199.4	199.4	199.4
62.5°	185.1	180.8	176.6	173.8	172.3	170.9	169.5	166.5	166.5	166.5	166.5
65°	156.6	152.4	149.5	146.7	143.8	143.8	141.0	139.6	136.6	135.2	132.4
67.5°	129.5	126.7	123.9	119.6	118.2	116.8	113.9	112.5	108.3	106.9	105.3
70°	105.3	101.1	98.2	95.4	94.0	91.1	88.3	85.5	82.6	79.8	76.9
72.5°	82.6	78.4	75.4	72.6	69.7	69.7	65.5	62.6	58.4	55.6	51.3
75°	61.2	57.0	54.1	49.9	48.5	47.0	42.7	39.8	35.6	31.3	28.5
77.5°	41.3	38.4	35.6	31.3	28.5	28.5	24.2	21.4	18.6	14.2	12.8
80°	25.6	22.8	20.0	17.1	17.1	14.2	12.8	9.9	7.1	5.7	4.3
82.5°	14.2	12.8	11.3	8.5	8.5	7.1	5.7	4.3	2.8	1.4	1.4
85°	7.1	5.7	4.3	4.3	2.8	2.8	2.8	1.4	1.4	0.0	0.0
87.5°	2.8	1.4	1.4	1.4	1.4	1.4	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593613

CATALOG NUMBER: HCC8W20D010SL-HM80520950-81RWWC

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1066.5	1066.5	1066.5	1066.5	1066.5	1066.5	1066.5	1066.5	1066.5	1066.5	1066.5
2.5°	1063.7	1063.7	1062.3	1062.3	1062.3	1060.8	1062.3	1060.8	1060.8	1060.8	1062.3
5°	1058.0	1055.2	1055.2	1053.8	1053.8	1052.3	1053.8	1052.3	1050.9	1049.4	1050.9
7.5°	1046.5	1043.7	1042.3	1040.9	1040.9	1040.9	1039.5	1038.0	1039.5	1035.2	1038.0
10°	1030.9	1029.5	1026.7	1025.3	1023.8	1025.3	1023.8	1021.0	1021.0	1021.0	1019.5
12.5°	1011.0	1008.1	1006.7	1005.3	1002.5	1002.5	1003.9	1001.0	1001.0	998.2	998.2
15°	986.7	983.9	981.1	981.1	978.2	978.2	976.8	976.8	975.4	974.0	974.0
17.5°	956.8	952.6	949.7	951.2	949.7	948.3	948.3	945.5	944.1	945.5	945.5
20°	921.3	918.4	915.6	917.0	914.2	912.7	914.2	909.9	911.3	911.3	911.3
22.5°	881.4	880.0	875.7	875.7	872.9	871.5	872.9	872.9	874.3	872.9	872.9
25°	837.2	834.4	831.5	831.5	830.1	828.7	830.1	831.5	830.1	831.5	831.5
27.5°	790.3	786.0	786.0	783.2	783.2	784.6	783.2	784.6	786.0	786.0	788.9
30°	739.0	737.6	736.1	734.7	734.7	736.1	736.1	736.1	737.6	740.4	740.4
32.5°	690.6	687.8	684.9	684.9	687.8	686.4	687.8	687.8	690.6	690.6	693.5
35°	637.9	637.9	635.1	636.5	636.5	636.5	636.5	639.3	642.2	643.6	646.4
37.5°	589.5	585.2	586.6	586.6	588.0	586.6	590.9	590.9	593.8	593.8	596.7
40°	536.9	536.9	538.3	536.9	538.3	538.3	541.1	544.0	545.4	548.2	549.6
42.5°	487.0	489.8	487.0	488.4	489.8	491.2	492.7	494.1	499.7	502.7	507.0
45°	441.4	442.9	444.3	445.7	444.3	447.2	448.6	451.4	455.7	457.1	458.5
47.5°	397.3	398.7	400.1	401.5	401.5	404.4	405.8	408.6	411.6	413.0	414.4
50°	354.6	357.4	358.9	358.9	360.3	363.1	365.9	365.9	368.8	373.0	374.5
52.5°	316.1	316.1	318.9	320.4	321.9	321.9	326.1	327.5	329.0	331.8	334.6
55°	273.4	277.7	279.1	279.1	281.9	284.7	286.2	287.6	287.6	293.4	293.4
57.5°	236.4	237.8	240.7	240.7	240.7	244.9	244.9	247.7	249.2	250.6	253.4
60°	199.4	202.2	202.2	203.7	202.2	205.1	206.5	209.3	210.8	212.2	213.6
62.5°	165.1	165.1	166.5	166.5	166.5	166.5	169.5	169.5	172.3	173.8	175.2
65°	132.4	132.4	132.4	132.4	132.4	132.4	132.4	132.4	133.8	133.8	136.6
67.5°	102.5	101.1	98.2	99.6	98.2	98.2	96.8	96.8	98.2	98.2	101.1
70°	74.0	72.6	69.7	69.7	68.3	66.9	65.5	64.1	62.6	62.6	62.6
72.5°	48.5	45.5	41.3	39.8	39.8	37.0	34.2	32.7	32.7	32.7	32.7
75°	24.2	21.4	18.6	17.1	17.1	14.2	15.7	14.2	14.2	14.2	14.2
77.5°	9.9	7.1	5.7	5.7	5.7	4.3	4.3	4.3	4.3	4.3	4.3
80°	2.8	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4
82.5°	1.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593613

CATALOG NUMBER: HCC8W20D010SL-HM80520950-81RWWC

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1066.5	1066.5	1066.5	1066.5	1066.5	1066.5	1066.5	1066.5
2.5°	1060.8	1060.8	1058.0	1059.4	1059.4	1059.4	1059.4	1059.4
5°	1048.0	1049.4	1048.0	1049.4	1049.4	1048.0	1048.0	1048.0
7.5°	1035.2	1036.6	1035.2	1036.6	1036.6	1036.6	1035.2	1035.2
10°	1019.5	1019.5	1019.5	1019.5	1019.5	1018.1	1019.5	1019.5
12.5°	998.2	998.2	998.2	999.6	999.6	998.2	998.2	996.8
15°	975.4	972.5	974.0	975.4	974.0	974.0	974.0	974.0
17.5°	944.1	945.5	944.1	944.1	944.1	944.1	945.5	944.1
20°	911.3	911.3	912.7	911.3	911.3	911.3	911.3	909.9
22.5°	874.3	872.9	872.9	874.3	874.3	872.9	874.3	874.3
25°	833.0	834.4	833.0	833.0	834.4	834.4	834.4	833.0
27.5°	788.9	790.3	791.7	790.3	790.3	790.3	791.7	793.1
30°	743.2	746.2	743.2	743.2	746.2	744.7	746.2	746.2
32.5°	694.9	699.2	696.3	699.2	699.2	700.6	699.2	700.6
35°	646.4	650.7	650.7	650.7	652.1	653.5	653.5	652.1
37.5°	600.9	602.3	602.3	605.2	606.6	608.0	608.0	606.6
40°	553.9	556.7	558.1	558.1	558.1	561.0	563.9	561.0
42.5°	508.4	509.8	511.2	511.2	514.1	515.5	516.9	516.9
45°	464.2	467.0	468.4	469.8	471.3	474.2	472.8	475.6
47.5°	418.7	422.9	424.3	425.8	428.6	430.0	431.4	432.8
50°	377.3	380.1	380.1	383.1	387.3	387.3	390.2	391.6
52.5°	336.0	337.5	338.9	340.3	343.1	346.0	346.0	348.8
55°	296.2	297.6	297.6	299.0	300.5	306.1	307.6	307.6
57.5°	254.8	254.8	257.7	259.2	260.6	263.5	263.5	263.5
60°	215.0	216.4	216.4	217.8	219.3	222.1	223.5	222.1
62.5°	175.2	176.6	176.6	178.0	180.8	182.3	180.8	180.8
65°	138.2	139.6	139.6	141.0	143.8	143.8	142.4	143.8
67.5°	101.1	101.1	101.1	101.1	101.1	101.1	101.1	101.1
70°	64.1	62.6	61.2	62.6	62.6	62.6	61.2	64.1
72.5°	31.3	32.7	32.7	32.7	32.7	32.7	32.7	31.3
75°	14.2	14.2	12.8	12.8	12.8	14.2	14.2	12.8
77.5°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3
80°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)