

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584240

Luminaire Tested: **HCC8W30D010MW-HM82555827-81NDW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584240  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-3)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W30D010MW-HM82555827-81NDW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2975.0 lumens  
Efficiency: N/A  
Efficacy: 106.3 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.92  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584240  
CATALOG NUMBER: HCC8W30D010MW-HM82555827-81NDW

### Luminous Intensity Polar Plot





TEST NUMBER: P584240

CATALOG NUMBER: HCC8W30D010MW-HM82555827-81NDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90			90
2	105	99	94	90	102	97	92	88	94	90	87	91	87	85	88	85	83	81			81
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73			73
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	72	68	67			67
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61			61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			56
7	77	66	59	54	76	66	59	54	64	58	54	63	58	54	62	57	53	52			52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			48
9	69	58	51	47	68	57	51	47	56	51	46	55	50	46	55	50	46	45			45
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42			42

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	74155
5°	73956
10°	72725
15°	71660
20°	69943
25°	66395
30°	54763
35°	28195
40°	18875
45°	16188
50°	13970
55°	12188
60°	10830
65°	9734
70°	8809
75°	7947
80°	7103
85°	7076



TEST NUMBER: P584240  
 CATALOG NUMBER: HCC8W30D010MW-HM82555827-81NDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	225.9	7.6
10°-20°	631.6	21.2
20°-30°	875.1	29.4
30°-40°	525.6	17.7
40°-50°	287.7	9.7
50°-60°	204.4	6.9
60°-70°	132.7	4.5
70°-80°	70.9	2.4
80°-90°	21.2	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1732.5	58.2
0°-40°	2258.1	75.9
0°-60°	2750.2	92.4
0°-90°	2975.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2975.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2405	
5°	2389	226
15°	2245	632
25°	1951	875
35°	749	526
45°	371	288
55°	227	204
65°	133	133
75°	67	71
85°	20	21
90°	0	



TEST NUMBER: P584240  
CATALOG NUMBER: HCC8W30D010MW-HM82555827-81NDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2404.8
2.5°	2400.4
5°	2389.2
7.5°	2362.5
10°	2322.6
12.5°	2284.8
15°	2244.7
17.5°	2193.6
20°	2131.4
22.5°	2055.8
25°	1951.4
27.5°	1786.9
30°	1538.0
32.5°	1126.8
35°	749.0
37.5°	553.4
40°	468.9
42.5°	415.6
45°	371.2
47.5°	328.9
50°	291.2
52.5°	255.6
55°	226.7
57.5°	200.0
60°	175.6
62.5°	153.4
65°	133.4
67.5°	113.3
70°	97.7
72.5°	80.0
75°	66.7
77.5°	53.4
80°	40.0
82.5°	28.9
85°	20.0
87.5°	8.9
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)