

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584266

Luminaire Tested: **HCC8W30D010MW-HM82555830-81WWBB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584266  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W30D010MW-HM82555830-81WWBB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2703.3 lumens  
Efficiency: N/A  
Efficacy: 96.5 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584266  
CATALOG NUMBER: HCC8W30D010MW-HM82555830-81WWBB

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584266

CATALOG NUMBER: HCC8W30D010MW-HM82555830-81WWBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88					88			
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77					77			
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67					67			
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59					59			
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53					53			
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47					47			
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43					43			
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39					39			
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35					35			
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32					32			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	44753	44753	44753
5°	46601	44654	42775
10°	48161	44084	40690
15°	49380	43078	38577
20°	49479	41288	36661
25°	48644	38679	34766
30°	46036	35685	33136
35°	41973	32095	31117
40°	36506	28295	28733
45°	31311	24504	26301
50°	26745	21127	23627
55°	23440	18193	20526
60°	20870	15517	17262
65°	18526	12667	13768
70°	16436	9395	7826
75°	13701	4921	2323
80°	10797	1545	373
85°	7642	743	0



TEST NUMBER: P584266  
 CATALOG NUMBER: HCC8W30D010MW-HM82555830-81WWBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	136.8	5.1
10°-20°	383.3	14.2
20°-30°	542.5	20.1
30°-40°	567.6	21.0
40°-50°	473.4	17.5
50°-60°	335.7	12.4
60°-70°	193.4	7.2
70°-80°	62.2	2.3
80°-90°	8.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1062.6	39.3
0°-40°	1630.1	60.3
0°-60°	2439.2	90.2
0°-90°	2703.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2703.3	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1451	1451	1451	1451	1451	
5°	1506	1486	1443	1399	1382	144
15°	1547	1484	1349	1243	1208	435
25°	1430	1323	1137	1046	1022	652
35°	1115	1017	853	807	827	691
45°	718	660	562	568	603	556
55°	436	390	338	356	382	394
65°	254	213	174	174	189	254
75°	115	85	41	20	20	125
85°	22	11	2	0	0	27
90°	0	0	0	0	0	



TEST NUMBER: P584266

CATALOG NUMBER: HCC8W30D010MW-HM82555830-81WWBB

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1451.3	1451.3	1451.3	1451.3	1451.3	1451.3	1451.3	1451.3	1451.3	1451.3	1451.3
2.5°	1481.7	1479.5	1477.3	1479.5	1477.3	1479.5	1477.3	1477.3	1475.2	1473.1	1473.1
5°	1505.5	1503.4	1503.4	1503.4	1501.2	1499.1	1499.1	1496.8	1492.6	1490.4	1486.0
7.5°	1520.7	1522.9	1522.9	1522.9	1518.6	1518.6	1514.2	1509.9	1505.5	1501.2	1494.7
10°	1538.1	1538.1	1536.0	1533.8	1529.4	1527.3	1525.1	1520.7	1514.2	1505.5	1499.1
12.5°	1544.6	1544.6	1542.5	1538.1	1536.0	1533.8	1531.6	1525.1	1516.5	1505.5	1496.8
15°	1546.8	1542.5	1540.2	1538.1	1533.8	1527.3	1527.3	1518.6	1507.8	1494.7	1483.9
17.5°	1529.4	1531.6	1527.3	1522.9	1516.5	1512.1	1505.5	1499.1	1486.0	1470.8	1460.0
20°	1507.8	1505.5	1503.4	1496.8	1488.2	1486.0	1479.5	1468.7	1457.8	1440.5	1425.3
22.5°	1473.1	1470.8	1466.5	1462.2	1453.6	1449.2	1442.6	1429.7	1414.4	1397.1	1379.7
25°	1429.7	1425.3	1418.8	1410.2	1403.6	1399.2	1390.5	1377.6	1360.2	1340.7	1323.4
27.5°	1360.2	1366.8	1362.4	1349.4	1342.9	1334.2	1332.0	1314.7	1299.5	1280.0	1260.5
30°	1292.9	1292.9	1286.5	1280.0	1269.1	1262.6	1253.9	1240.8	1225.7	1201.8	1186.6
32.5°	1208.4	1206.2	1197.6	1195.3	1186.6	1173.7	1171.5	1154.2	1138.9	1121.6	1102.1
35°	1115.0	1110.8	1102.1	1095.5	1091.3	1084.7	1078.2	1063.0	1047.9	1030.5	1017.4
37.5°	1008.7	1008.7	1006.6	995.8	991.4	987.1	980.6	965.3	956.7	939.3	926.3
40°	906.9	904.6	898.2	895.9	891.6	885.1	880.8	872.1	859.1	846.1	833.0
42.5°	807.0	809.2	800.6	802.7	794.0	789.6	787.5	774.5	768.0	754.9	744.1
45°	718.0	715.9	711.6	709.4	705.1	700.7	696.4	689.9	679.0	666.0	659.5
47.5°	635.6	629.1	629.1	627.0	624.8	616.1	613.9	607.5	600.9	588.0	579.3
50°	557.5	557.5	557.5	555.4	548.8	546.7	542.3	535.9	529.3	520.7	507.6
52.5°	494.6	494.6	494.6	492.5	483.8	481.7	479.4	470.7	462.0	455.6	446.9
55°	436.0	438.3	436.0	431.7	425.2	425.2	418.6	414.4	405.7	399.1	390.5
57.5°	386.2	386.2	381.8	379.6	375.2	373.1	368.8	364.4	353.6	347.1	336.2
60°	338.4	336.2	336.2	332.0	327.6	323.3	321.0	314.6	310.2	299.4	290.7
62.5°	295.0	295.0	290.7	290.7	282.0	282.0	279.9	273.4	266.8	256.0	251.6
65°	253.9	253.9	251.6	249.5	243.0	240.8	238.6	232.1	225.7	219.1	212.6
67.5°	217.0	217.0	212.6	210.5	206.1	203.9	199.6	195.2	188.7	182.3	175.7
70°	182.3	180.0	177.9	175.7	171.3	169.2	164.9	160.5	154.0	149.7	143.2
72.5°	147.6	147.6	145.3	141.0	138.9	136.6	134.5	130.2	123.7	117.1	112.8
75°	115.0	115.0	115.0	110.7	106.3	104.2	104.2	99.8	95.5	88.9	84.7
77.5°	88.9	86.8	84.7	84.7	80.3	78.1	76.0	73.7	67.3	65.0	60.8
80°	60.8	62.9	60.8	58.6	56.4	54.2	54.2	49.9	47.7	43.4	39.0
82.5°	41.3	39.0	39.0	36.9	36.9	34.7	34.7	30.3	28.2	26.0	23.9
85°	21.6	21.6	19.5	19.5	19.5	17.4	17.4	15.2	15.2	13.0	10.8
87.5°	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	4.3	4.3	4.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584266

CATALOG NUMBER: HCC8W30D010MW-HM82555830-81WWBB

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1451.3	1451.3	1451.3	1451.3	1451.3	1451.3	1451.3	1451.3	1451.3	1451.3	1451.3
2.5°	1470.8	1466.5	1464.4	1464.4	1462.2	1460.0	1457.8	1455.7	1451.3	1451.3	1447.0
5°	1481.7	1477.3	1475.2	1468.7	1464.4	1464.4	1455.7	1453.6	1447.0	1442.6	1438.3
7.5°	1490.4	1481.7	1475.2	1468.7	1464.4	1460.0	1451.3	1442.6	1433.9	1425.3	1421.0
10°	1490.4	1481.7	1470.8	1460.0	1455.7	1451.3	1440.5	1427.5	1416.6	1407.9	1397.1
12.5°	1486.0	1473.1	1460.0	1451.3	1442.6	1436.2	1423.1	1410.2	1397.1	1379.7	1371.0
15°	1473.1	1455.7	1442.6	1427.5	1421.0	1410.2	1399.2	1379.7	1364.5	1349.4	1338.6
17.5°	1447.0	1425.3	1410.2	1394.9	1384.1	1377.6	1360.2	1342.9	1325.5	1308.1	1295.2
20°	1407.9	1388.4	1371.0	1351.5	1342.9	1334.2	1312.5	1295.2	1277.8	1258.2	1245.2
22.5°	1360.2	1340.7	1316.8	1301.6	1288.6	1277.8	1258.2	1238.7	1221.3	1204.0	1186.6
25°	1301.6	1282.1	1260.5	1236.6	1227.9	1217.1	1195.3	1175.8	1156.3	1136.8	1121.6
27.5°	1238.7	1212.7	1195.3	1169.3	1160.6	1149.8	1125.9	1104.2	1086.9	1071.6	1054.3
30°	1162.8	1143.2	1119.4	1095.5	1086.9	1076.0	1056.5	1036.9	1019.6	1002.2	984.8
32.5°	1080.3	1060.8	1036.9	1019.6	1006.6	997.9	978.4	961.1	943.7	926.3	911.1
35°	993.5	971.9	954.5	937.2	926.3	915.5	895.9	880.8	867.7	852.6	837.4
37.5°	904.6	889.5	872.1	852.6	841.7	833.0	817.9	800.6	789.6	776.7	765.8
40°	817.9	800.6	785.3	768.0	759.3	752.8	737.5	724.6	713.8	702.9	696.4
42.5°	729.0	713.8	698.5	687.7	681.2	674.6	663.8	648.6	642.2	631.2	624.8
45°	646.5	633.5	622.6	607.5	603.1	598.8	585.7	574.9	568.3	561.9	557.5
47.5°	568.3	559.7	546.7	538.0	531.5	527.2	518.5	509.8	503.3	498.9	494.6
50°	501.2	490.2	481.7	473.0	468.6	462.0	453.4	449.1	444.7	440.4	440.4
52.5°	438.3	427.3	418.6	412.2	407.8	403.5	397.0	394.9	390.5	390.5	388.3
55°	379.6	373.1	364.4	355.7	353.6	351.5	347.1	342.8	340.6	338.4	340.6
57.5°	329.7	323.3	314.6	308.1	305.9	303.7	301.5	297.2	295.0	295.0	295.0
60°	284.2	277.6	271.2	264.7	264.7	260.3	258.1	256.0	253.9	251.6	251.6
62.5°	243.0	236.5	230.0	225.7	223.4	221.3	217.0	214.7	212.6	212.6	210.5
65°	206.1	197.4	195.2	188.7	186.6	184.4	182.3	177.9	175.7	173.6	171.3
67.5°	169.2	164.9	158.4	154.0	151.8	149.7	147.6	143.2	141.0	138.9	134.5
70°	136.6	132.3	127.9	123.7	121.5	119.4	115.0	110.7	108.4	104.2	97.6
72.5°	106.3	102.0	97.6	93.3	91.1	88.9	84.7	80.3	76.0	71.6	67.3
75°	80.3	76.0	69.4	65.0	62.9	62.9	56.4	52.1	47.7	41.3	36.9
77.5°	56.4	49.9	47.7	43.4	41.3	36.9	32.6	28.2	23.9	21.6	17.4
80°	36.9	32.6	28.2	26.0	23.9	21.6	19.5	15.2	10.8	8.7	6.5
82.5°	21.6	19.5	17.4	15.2	13.0	10.8	8.7	8.7	6.5	4.3	2.1
85°	10.8	8.7	6.5	6.5	4.3	4.3	4.3	2.1	2.1	2.1	2.1
87.5°	4.3	2.1	2.1	2.1	2.1	2.1	2.1	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584266

CATALOG NUMBER: HCC8W30D010MW-HM82555830-81WWBB

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1451.3	1451.3	1451.3	1451.3	1451.3	1451.3	1451.3	1451.3	1451.3	1451.3	1451.3
2.5°	1444.9	1442.6	1440.5	1438.3	1438.3	1433.9	1433.9	1431.8	1427.5	1425.3	1425.3
5°	1431.8	1425.3	1421.0	1418.8	1416.6	1410.2	1407.9	1403.6	1399.2	1394.9	1392.8
7.5°	1412.3	1401.5	1397.1	1394.9	1388.4	1381.9	1377.6	1371.0	1364.5	1358.1	1355.8
10°	1388.4	1377.6	1366.8	1362.4	1355.8	1351.5	1342.9	1334.2	1327.6	1321.2	1314.7
12.5°	1358.1	1345.0	1334.2	1329.9	1323.4	1314.7	1301.6	1297.3	1286.5	1282.1	1273.4
15°	1323.4	1308.1	1297.3	1290.8	1284.2	1271.3	1262.6	1253.9	1243.1	1238.7	1230.0
17.5°	1280.0	1262.6	1251.8	1245.2	1240.8	1230.0	1217.1	1206.2	1195.3	1191.0	1184.5
20°	1227.9	1217.1	1201.8	1195.3	1191.0	1177.9	1165.0	1160.6	1151.9	1143.2	1136.8
22.5°	1169.3	1158.4	1143.2	1136.8	1134.5	1123.7	1112.9	1106.4	1099.8	1093.4	1086.9
25°	1108.5	1095.5	1082.6	1078.2	1073.9	1065.2	1056.5	1052.1	1045.6	1041.3	1036.9
27.5°	1043.5	1030.5	1019.6	1013.1	1008.7	1002.2	997.9	993.5	989.2	984.8	982.7
30°	974.0	961.1	952.4	948.0	943.7	941.6	935.0	932.9	930.6	926.3	928.5
32.5°	904.6	893.8	885.1	878.6	878.6	874.3	872.1	872.1	869.9	869.9	869.9
35°	828.7	822.2	815.7	813.5	811.4	809.2	807.0	809.2	807.0	809.2	811.4
37.5°	759.3	752.8	748.5	746.2	744.1	746.2	744.1	744.1	746.2	750.6	752.8
40°	687.7	683.3	679.0	681.2	679.0	679.0	679.0	685.6	687.7	689.9	692.0
42.5°	620.4	616.1	613.9	613.9	616.1	613.9	618.3	620.4	624.8	631.2	635.6
45°	555.4	553.2	553.2	555.4	553.2	557.5	557.5	561.9	568.3	572.7	577.0
47.5°	494.6	494.6	494.6	496.8	496.8	498.9	503.3	505.4	509.8	514.1	518.5
50°	438.3	440.4	442.5	442.5	442.5	446.9	451.2	453.4	455.6	457.8	464.3
52.5°	388.3	390.5	390.5	392.6	394.9	397.0	399.1	403.5	405.7	410.0	412.2
55°	340.6	340.6	344.9	347.1	347.1	347.1	351.5	351.5	355.7	358.0	362.3
57.5°	295.0	297.2	297.2	299.4	299.4	301.5	303.7	305.9	308.1	310.2	312.4
60°	251.6	251.6	251.6	253.9	256.0	258.1	256.0	260.3	260.3	264.7	266.8
62.5°	210.5	212.6	212.6	212.6	212.6	212.6	212.6	214.7	217.0	219.1	221.3
65°	171.3	171.3	171.3	169.2	171.3	169.2	171.3	173.6	173.6	175.7	177.9
67.5°	132.3	132.3	127.9	127.9	130.2	130.2	130.2	130.2	127.9	132.3	132.3
70°	95.5	93.3	91.1	88.9	88.9	86.8	86.8	84.7	84.7	84.7	84.7
72.5°	62.9	58.6	54.2	52.1	49.9	49.9	45.5	43.4	45.5	45.5	45.5
75°	32.6	28.2	26.0	23.9	21.6	21.6	19.5	19.5	19.5	19.5	19.5
77.5°	13.0	10.8	8.7	8.7	6.5	6.5	6.5	6.5	6.5	6.5	6.5
80°	4.3	4.3	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1
82.5°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1
85°	2.1	0.0	0.0	2.1	0.0	2.1	2.1	2.1	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584266

CATALOG NUMBER: HCC8W30D010MW-HM82555830-81WWBB

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1451.3	1451.3	1451.3	1451.3	1451.3	1451.3	1451.3	1451.3
2.5°	1423.1	1423.1	1421.0	1423.1	1418.8	1421.0	1418.8	1418.8
5°	1390.5	1386.3	1386.3	1386.3	1384.1	1384.1	1381.9	1381.9
7.5°	1351.5	1349.4	1347.1	1345.0	1342.9	1340.7	1340.7	1340.7
10°	1312.5	1308.1	1308.1	1306.0	1301.6	1299.5	1299.5	1299.5
12.5°	1266.9	1264.7	1262.6	1262.6	1253.9	1256.1	1253.9	1253.9
15°	1223.5	1221.3	1221.3	1214.9	1210.5	1210.5	1210.5	1208.4
17.5°	1177.9	1175.8	1173.7	1169.3	1165.0	1165.0	1162.8	1165.0
20°	1130.3	1128.1	1123.7	1123.7	1121.6	1119.4	1115.0	1117.2
22.5°	1082.6	1078.2	1076.0	1076.0	1073.9	1073.9	1069.5	1069.5
25°	1032.6	1030.5	1028.2	1030.5	1026.1	1026.1	1021.8	1021.8
27.5°	980.6	978.4	978.4	978.4	976.3	978.4	976.3	976.3
30°	928.5	928.5	926.3	926.3	928.5	926.3	928.5	930.6
32.5°	872.1	872.1	874.3	874.3	876.4	876.4	876.4	876.4
35°	813.5	817.9	817.9	820.1	822.2	824.3	824.3	826.6
37.5°	759.3	761.4	763.6	765.8	770.1	770.1	770.1	770.1
40°	700.7	702.9	707.2	705.1	713.8	715.9	713.8	713.8
42.5°	639.9	644.3	646.5	650.9	653.0	657.3	659.5	659.5
45°	583.6	585.7	590.1	594.4	596.6	603.1	603.1	603.1
47.5°	524.9	529.3	531.5	535.9	538.0	544.6	546.7	544.6
50°	468.6	473.0	477.3	477.3	483.8	485.9	490.2	492.5
52.5°	414.4	416.5	420.9	423.0	427.3	431.7	433.9	436.0
55°	362.3	364.4	368.8	368.8	375.2	377.5	381.8	381.8
57.5°	314.6	316.7	321.0	318.9	323.3	327.6	327.6	325.4
60°	269.0	269.0	269.0	273.4	275.5	277.6	279.9	279.9
62.5°	221.3	225.7	227.8	227.8	230.0	232.1	232.1	230.0
65°	177.9	182.3	184.4	184.4	186.6	186.6	186.6	188.7
67.5°	134.5	134.5	134.5	136.6	134.5	134.5	134.5	134.5
70°	84.7	84.7	84.7	84.7	82.4	84.7	84.7	86.8
72.5°	45.5	45.5	45.5	45.5	45.5	45.5	45.5	45.5
75°	19.5	19.5	19.5	21.6	19.5	19.5	19.5	19.5
77.5°	8.7	6.5	8.7	8.7	6.5	6.5	6.5	6.5
80°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1
82.5°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1
85°	0.0	2.1	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)