

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584259

Luminaire Tested: **HCC8W30D010SL-HM82555830-81RWWC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584259
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W30D010SL-HM82555830-81RWWC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3089.6 lumens
Efficiency: N/A
Efficacy: 110.3 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.08 / 1.17
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584259
CATALOG NUMBER: HCC8W30D010SL-HM82555830-81RWWC

Luminous Intensity Polar Plot





TEST NUMBER: P584259

CATALOG NUMBER: HCC8W30D010SL-HM82555830-81RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	84	82	79	77								
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67								
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	69	65	61	59								
5	81	70	62	56	80	69	62	56	67	61	56	65	59	55	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	50128	50128	50128
5°	50789	49917	49446
10°	51311	49404	48659
15°	51829	48362	47395
20°	51566	46578	45508
25°	50362	43789	43197
30°	47838	40649	40496
35°	43547	37091	37418
40°	38181	33197	34421
45°	32938	29528	31612
50°	28841	25924	28635
55°	25558	22284	25203
60°	23022	18742	20882
65°	20744	15045	16001
70°	18203	10954	8800
75°	15512	5695	2323
80°	11951	1545	373
85°	7713	0	0



TEST NUMBER: P584259
 CATALOG NUMBER: HCC8W30D010SL-HM82555830-81RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.4	5.0
10°-20°	431.2	14.0
20°-30°	612.0	19.8
30°-40°	644.2	20.9
40°-50°	548.0	17.7
50°-60°	396.0	12.8
60°-70°	225.3	7.3
70°-80°	71.0	2.3
80°-90°	8.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1196.5	38.7
0°-40°	1840.7	59.6
0°-60°	2784.7	90.1
0°-90°	3089.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3089.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1626	1626	1626	1626	1626	
5°	1641	1632	1613	1602	1597	157
15°	1624	1582	1515	1487	1485	457
25°	1480	1406	1287	1265	1270	678
35°	1157	1090	985	979	994	720
45°	755	727	677	694	725	587
55°	475	441	414	438	469	429
65°	284	245	206	204	219	282
75°	130	100	48	22	20	140
85°	22	13	0	0	0	28
90°	0	0	0	0	0	



TEST NUMBER: P584259

CATALOG NUMBER: HCC8W30D010SL-HM82555830-81RWWC

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1625.6	1625.6	1625.6	1625.6	1625.6	1625.6	1625.6	1625.6	1625.6	1625.6	1625.6
2.5°	1634.3	1636.4	1632.1	1632.1	1636.4	1632.1	1634.3	1634.3	1632.1	1632.1	1630.0
5°	1640.8	1638.7	1638.7	1638.7	1640.8	1636.4	1634.3	1636.4	1632.1	1632.1	1632.1
7.5°	1643.0	1643.0	1640.8	1638.7	1638.7	1638.7	1636.4	1634.3	1632.1	1627.7	1625.6
10°	1638.7	1638.7	1640.8	1636.4	1636.4	1632.1	1632.1	1627.7	1627.7	1623.5	1616.9
12.5°	1634.3	1632.1	1632.1	1627.7	1627.7	1623.5	1623.5	1616.9	1614.8	1608.2	1601.7
15°	1623.5	1621.3	1616.9	1614.8	1612.6	1610.4	1606.1	1604.0	1597.4	1588.7	1582.2
17.5°	1601.7	1599.6	1597.4	1593.0	1588.7	1586.5	1584.3	1577.8	1569.1	1562.7	1551.8
20°	1571.4	1569.1	1569.1	1562.7	1560.4	1554.0	1551.8	1543.1	1536.7	1523.6	1514.9
22.5°	1530.1	1532.3	1528.0	1523.6	1519.3	1512.8	1508.4	1499.7	1488.9	1475.9	1465.0
25°	1480.2	1482.3	1478.0	1473.6	1467.2	1462.8	1458.5	1445.5	1434.6	1419.4	1406.3
27.5°	1417.3	1417.3	1417.3	1412.9	1402.1	1399.9	1395.5	1382.6	1367.4	1354.3	1341.3
30°	1343.5	1341.3	1341.3	1334.8	1330.5	1321.8	1315.3	1304.3	1293.5	1278.3	1263.2
32.5°	1254.5	1256.7	1250.1	1245.8	1239.3	1239.3	1230.6	1221.9	1208.9	1193.8	1178.5
35°	1156.8	1158.9	1154.6	1152.5	1141.6	1139.4	1137.3	1126.5	1117.8	1106.8	1089.5
37.5°	1057.0	1054.8	1052.6	1052.6	1046.1	1041.8	1037.4	1031.0	1017.9	1009.2	1000.5
40°	948.5	948.5	948.5	946.3	944.1	939.8	937.6	933.2	924.6	915.9	909.3
42.5°	850.7	850.7	848.6	846.4	842.0	844.3	839.9	835.6	826.9	820.4	816.0
45°	755.3	755.3	755.3	757.5	753.1	746.6	746.6	742.3	737.9	733.6	727.1
47.5°	670.6	677.1	672.9	670.6	672.9	664.2	664.2	659.8	655.5	651.1	642.4
50°	601.2	601.2	601.2	596.9	594.7	594.7	588.2	583.8	581.7	577.3	568.6
52.5°	538.3	533.9	533.9	531.7	529.6	525.2	525.2	520.9	512.2	507.8	501.4
55°	475.4	475.4	473.1	471.0	468.8	466.7	464.4	458.0	453.6	447.1	440.6
57.5°	418.9	423.2	421.0	416.7	412.3	412.3	408.1	403.7	397.1	390.7	384.2
60°	373.3	371.1	371.1	368.9	364.7	362.4	360.3	353.7	347.3	340.8	334.2
62.5°	325.5	325.5	325.5	321.3	316.9	314.7	312.6	308.2	299.5	293.0	288.7
65°	284.3	282.1	280.0	277.8	275.6	271.3	269.1	264.8	258.3	251.7	245.3
67.5°	243.0	240.9	240.9	238.8	232.2	230.1	230.1	223.5	217.0	210.6	204.0
70°	201.9	201.9	201.9	197.5	195.4	193.2	191.0	186.7	180.1	173.6	167.2
72.5°	167.2	164.9	164.9	162.8	156.2	154.1	152.0	147.6	141.0	136.7	132.3
75°	130.2	130.2	128.1	125.9	123.7	121.5	119.4	115.0	108.6	102.0	99.9
77.5°	99.9	97.6	97.6	95.5	91.2	88.9	88.9	84.7	78.1	73.8	69.4
80°	67.3	69.4	67.3	65.2	62.9	60.8	58.6	56.5	52.1	47.8	43.4
82.5°	41.3	43.4	41.3	41.3	39.1	36.9	36.9	32.6	30.4	28.2	26.0
85°	21.8	21.8	21.8	21.8	19.5	19.5	19.5	17.4	15.2	13.1	13.1
87.5°	6.5	8.7	6.5	6.5	6.5	6.5	6.5	6.5	4.4	4.4	4.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584259

CATALOG NUMBER: HCC8W30D010SL-HM82555830-81RWWC

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1625.6	1625.6	1625.6	1625.6	1625.6	1625.6	1625.6	1625.6	1625.6	1625.6	1625.6
2.5°	1632.1	1630.0	1627.7	1627.7	1627.7	1627.7	1627.7	1625.6	1623.5	1623.5	1623.5
5°	1627.7	1627.7	1627.7	1625.6	1623.5	1623.5	1619.1	1616.9	1614.8	1612.6	1610.4
7.5°	1623.5	1619.1	1616.9	1614.8	1612.6	1612.6	1608.2	1604.0	1604.0	1599.6	1595.2
10°	1610.4	1608.2	1604.0	1599.6	1597.4	1595.2	1590.9	1584.3	1582.2	1577.8	1573.5
12.5°	1595.2	1590.9	1586.5	1577.8	1575.7	1573.5	1564.8	1558.3	1554.0	1551.8	1540.9
15°	1575.7	1567.0	1560.4	1549.6	1547.5	1543.1	1536.7	1530.1	1521.4	1514.9	1510.6
17.5°	1540.9	1532.3	1521.4	1510.6	1506.2	1506.2	1495.4	1486.7	1475.9	1471.5	1462.8
20°	1499.7	1488.9	1480.2	1467.2	1460.7	1454.1	1447.6	1434.6	1426.0	1419.4	1408.6
22.5°	1452.0	1436.8	1426.0	1412.9	1402.1	1395.5	1384.7	1373.9	1363.0	1356.5	1347.9
25°	1391.2	1378.2	1360.8	1347.9	1341.3	1332.6	1319.6	1308.7	1297.9	1287.0	1282.7
27.5°	1324.0	1306.6	1291.4	1276.2	1269.6	1263.2	1248.0	1234.9	1226.2	1215.4	1211.1
30°	1250.1	1232.8	1215.4	1202.4	1195.9	1185.1	1176.4	1161.2	1150.2	1141.6	1130.7
32.5°	1165.5	1152.5	1137.3	1117.8	1113.4	1104.7	1091.7	1085.2	1072.1	1065.7	1057.0
35°	1074.4	1065.7	1050.5	1035.3	1028.7	1024.4	1013.5	1000.5	991.9	985.3	981.0
37.5°	987.5	976.6	961.4	950.6	946.3	939.8	926.7	920.3	911.6	907.2	898.5
40°	894.2	883.3	872.5	865.9	859.4	855.1	846.4	839.9	831.2	824.7	822.6
42.5°	803.1	796.5	787.8	779.2	777.0	770.5	766.2	759.7	753.1	751.0	744.4
45°	720.5	714.0	705.3	696.6	694.5	690.2	688.0	681.5	677.1	677.1	677.1
47.5°	638.1	631.6	622.9	618.5	620.8	612.1	612.1	609.8	605.6	605.6	607.7
50°	564.3	555.6	553.5	549.1	544.8	540.4	542.5	536.1	536.1	540.4	538.3
52.5°	494.9	486.2	484.0	479.6	477.5	477.5	475.4	475.4	473.1	475.4	475.4
55°	431.8	425.4	421.0	416.7	414.5	414.5	414.5	412.3	410.2	414.5	416.7
57.5°	375.5	373.3	368.9	362.4	360.3	358.1	356.0	356.0	356.0	356.0	358.1
60°	325.5	321.3	316.9	310.3	310.3	308.2	306.0	303.9	303.9	303.9	303.9
62.5°	282.1	275.6	269.1	264.8	262.7	260.4	258.3	254.0	254.0	254.0	254.0
65°	238.8	232.2	227.9	223.5	219.3	219.3	214.9	212.7	208.3	206.2	201.9
67.5°	197.5	193.2	188.8	182.3	180.1	178.0	173.6	171.5	164.9	162.8	160.6
70°	160.6	154.1	149.8	145.4	143.3	138.9	134.6	130.2	125.9	121.5	117.2
72.5°	125.9	119.4	115.0	110.7	106.3	106.3	99.9	95.5	88.9	84.7	78.1
75°	93.3	86.8	82.5	76.0	73.8	71.6	65.2	60.8	54.2	47.8	43.4
77.5°	62.9	58.6	54.2	47.8	43.4	43.4	36.9	32.6	28.2	21.8	19.5
80°	39.1	34.7	30.4	26.0	26.0	21.8	19.5	15.2	10.8	8.7	6.5
82.5°	21.8	19.5	17.4	13.1	13.1	10.8	8.7	6.5	4.4	2.1	2.1
85°	10.8	8.7	6.5	6.5	4.4	4.4	4.4	2.1	2.1	0.0	0.0
87.5°	4.4	2.1	2.1	2.1	2.1	2.1	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584259

CATALOG NUMBER: HCC8W30D010SL-HM82555830-81RWWC

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1625.6	1625.6	1625.6	1625.6	1625.6	1625.6	1625.6	1625.6	1625.6	1625.6	1625.6
2.5°	1621.3	1621.3	1619.1	1619.1	1619.1	1616.9	1619.1	1616.9	1616.9	1616.9	1619.1
5°	1612.6	1608.2	1608.2	1606.1	1606.1	1604.0	1606.1	1604.0	1601.7	1599.6	1601.7
7.5°	1595.2	1590.9	1588.7	1586.5	1586.5	1586.5	1584.3	1582.2	1584.3	1577.8	1582.2
10°	1571.4	1569.1	1564.8	1562.7	1560.4	1562.7	1560.4	1556.2	1556.2	1556.2	1554.0
12.5°	1540.9	1536.7	1534.4	1532.3	1528.0	1528.0	1530.1	1525.7	1525.7	1521.4	1521.4
15°	1504.1	1499.7	1495.4	1495.4	1491.0	1491.0	1488.9	1488.9	1486.7	1484.6	1484.6
17.5°	1458.5	1452.0	1447.6	1449.7	1447.6	1445.5	1445.5	1441.1	1438.9	1441.1	1441.1
20°	1404.2	1399.9	1395.5	1397.7	1393.4	1391.2	1393.4	1386.8	1389.0	1389.0	1389.0
22.5°	1343.5	1341.3	1334.8	1334.8	1330.5	1328.2	1330.5	1330.5	1332.6	1330.5	1330.5
25°	1276.2	1271.9	1267.5	1267.5	1265.3	1263.2	1265.3	1267.5	1265.3	1267.5	1267.5
27.5°	1204.6	1198.0	1198.0	1193.8	1193.8	1195.9	1193.8	1195.9	1198.0	1198.0	1202.4
30°	1126.5	1124.2	1122.1	1119.9	1119.9	1122.1	1122.1	1122.1	1124.2	1128.6	1128.6
32.5°	1052.6	1048.3	1043.9	1043.9	1048.3	1046.1	1048.3	1048.3	1052.6	1052.6	1057.0
35°	972.4	972.4	968.0	970.1	970.1	970.1	970.1	974.5	978.8	981.0	985.3
37.5°	898.5	892.0	894.2	894.2	896.4	894.2	900.7	900.7	905.1	905.1	909.3
40°	818.3	818.3	820.4	818.3	820.4	820.4	824.7	829.1	831.2	835.6	837.8
42.5°	742.3	746.6	742.3	744.4	746.6	748.8	751.0	753.1	761.8	766.2	772.6
45°	672.9	675.0	677.1	679.3	677.1	681.5	683.7	688.0	694.5	696.6	698.9
47.5°	605.6	607.7	609.8	612.1	612.1	616.4	618.5	622.9	627.2	629.5	631.6
50°	540.4	544.8	546.9	546.9	549.1	553.5	557.8	557.8	562.2	568.6	570.8
52.5°	481.8	481.8	486.2	488.3	490.5	490.5	497.0	499.1	501.4	505.7	510.1
55°	416.7	423.2	425.4	425.4	429.7	434.1	436.2	438.4	438.4	447.1	447.1
57.5°	360.3	362.4	366.8	366.8	366.8	373.3	373.3	377.6	379.8	382.0	386.3
60°	303.9	308.2	308.2	310.3	308.2	312.6	314.7	319.0	321.3	323.4	325.5
62.5°	251.7	251.7	254.0	254.0	254.0	254.0	258.3	258.3	262.7	264.8	266.9
65°	201.9	201.9	201.9	201.9	201.9	201.9	201.9	201.9	204.0	204.0	208.3
67.5°	156.2	154.1	149.8	152.0	149.8	149.8	147.6	147.6	149.8	149.8	154.1
70°	112.8	110.7	106.3	106.3	104.2	102.0	99.9	97.6	95.5	95.5	95.5
72.5°	73.8	69.4	62.9	60.8	60.8	56.5	52.1	49.9	49.9	49.9	49.9
75°	36.9	32.6	28.2	26.0	26.0	21.8	23.9	21.8	21.8	21.8	21.8
77.5°	15.2	10.8	8.7	8.7	8.7	6.5	6.5	6.5	6.5	6.5	6.5
80°	4.4	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1
82.5°	2.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584259

CATALOG NUMBER: HCC8W30D010SL-HM82555830-81RWWC

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1625.6	1625.6	1625.6	1625.6	1625.6	1625.6	1625.6	1625.6
2.5°	1616.9	1616.9	1612.6	1614.8	1614.8	1614.8	1614.8	1614.8
5°	1597.4	1599.6	1597.4	1599.6	1599.6	1597.4	1597.4	1597.4
7.5°	1577.8	1580.1	1577.8	1580.1	1580.1	1580.1	1577.8	1577.8
10°	1554.0	1554.0	1554.0	1554.0	1554.0	1551.8	1554.0	1554.0
12.5°	1521.4	1521.4	1521.4	1523.6	1523.6	1521.4	1521.4	1519.3
15°	1486.7	1482.3	1484.6	1486.7	1484.6	1484.6	1484.6	1484.6
17.5°	1438.9	1441.1	1438.9	1438.9	1438.9	1438.9	1441.1	1438.9
20°	1389.0	1389.0	1391.2	1389.0	1389.0	1389.0	1389.0	1386.8
22.5°	1332.6	1330.5	1330.5	1332.6	1332.6	1330.5	1332.6	1332.6
25°	1269.6	1271.9	1269.6	1269.6	1271.9	1271.9	1271.9	1269.6
27.5°	1202.4	1204.6	1206.7	1204.6	1204.6	1204.6	1206.7	1208.9
30°	1132.9	1137.3	1132.9	1132.9	1137.3	1135.1	1137.3	1137.3
32.5°	1059.2	1065.7	1061.3	1065.7	1065.7	1067.8	1065.7	1067.8
35°	985.3	991.9	991.9	991.9	994.0	996.1	996.1	994.0
37.5°	915.9	918.0	918.0	922.4	924.6	926.7	926.7	924.6
40°	844.3	848.6	850.7	850.7	850.7	855.1	859.4	855.1
42.5°	774.9	777.0	779.2	779.2	783.6	785.7	787.8	787.8
45°	707.6	711.9	714.0	716.3	718.4	722.7	720.5	724.9
47.5°	638.1	644.6	646.8	649.0	653.2	655.5	657.6	659.8
50°	575.1	579.5	579.5	583.8	590.3	590.3	594.7	596.9
52.5°	512.2	514.4	516.5	518.8	523.0	527.4	527.4	531.7
55°	451.5	453.6	453.6	455.7	458.0	466.7	468.8	468.8
57.5°	388.4	388.4	392.8	395.0	397.1	401.5	401.5	401.5
60°	327.7	329.9	329.9	332.1	334.2	338.6	340.8	338.6
62.5°	266.9	269.1	269.1	271.3	275.6	277.8	275.6	275.6
65°	210.6	212.7	212.7	214.9	219.3	219.3	217.0	219.3
67.5°	154.1	154.1	154.1	154.1	154.1	154.1	154.1	154.1
70°	97.6	95.5	93.3	95.5	95.5	95.5	93.3	97.6
72.5°	47.8	49.9	49.9	49.9	49.9	49.9	49.9	47.8
75°	21.8	21.8	19.5	19.5	19.5	21.8	21.8	19.5
77.5°	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5
80°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)