

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584106

Luminaire Tested: **HCC8W25D010BZ-HM82555827-81RWWC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584106
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W25D010BZ-HM82555827-81RWWC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2351.4 lumens
Efficiency: N/A
Efficacy: 87.7 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.08 / 1.17
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584106
CATALOG NUMBER: HCC8W25D010BZ-HM82555827-81RWWC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584106

CATALOG NUMBER: HCC8W25D010BZ-HM82555827-81RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88		
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	85	82	79	77		
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67		
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	69	65	61	59		
5	81	70	62	56	80	69	62	56	67	61	56	65	59	55	63	58	54	52		
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47		
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42		
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38		
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35		
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	38151	38151	38151
5°	38655	37990	37631
10°	39052	37603	37036
15°	39445	36808	36071
20°	39244	35450	34640
25°	38332	33330	32877
30°	36408	30935	30818
35°	33142	28233	28482
40°	29055	25267	26201
45°	25067	22476	24059
50°	21948	19731	21789
55°	19451	16962	19182
60°	17521	14259	15893
65°	15790	11455	12171
70°	13857	8349	6708
75°	11807	4337	1775
80°	9110	1172	284
85°	5838	0	0



TEST NUMBER: P584106
 CATALOG NUMBER: HCC8W25D010BZ-HM82555827-81RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.7	5.0
10°-20°	328.2	14.0
20°-30°	465.8	19.8
30°-40°	490.3	20.9
40°-50°	417.1	17.7
50°-60°	301.4	12.8
60°-70°	171.4	7.3
70°-80°	54.0	2.3
80°-90°	6.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	910.7	38.7
0°-40°	1401.0	59.6
0°-60°	2119.4	90.1
0°-90°	2351.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2351.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1237	1237	1237	1237	1237	
5°	1249	1242	1227	1219	1216	119
15°	1236	1204	1153	1132	1130	348
25°	1127	1070	980	963	966	516
35°	880	829	750	745	757	548
45°	575	553	515	529	552	447
55°	362	335	316	334	357	326
65°	216	187	157	155	167	215
75°	99	76	36	16	15	107
85°	16	10	0	0	0	21
90°	0	0	0	0	0	



TEST NUMBER: P584106

CATALOG NUMBER: HCC8W25D010BZ-HM82555827-81RWWC

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1237.2	1237.2	1237.2	1237.2	1237.2	1237.2	1237.2	1237.2	1237.2	1237.2	1237.2
2.5°	1243.9	1245.5	1242.2	1242.2	1245.5	1242.2	1243.9	1243.9	1242.2	1242.2	1240.6
5°	1248.8	1247.2	1247.2	1247.2	1248.8	1245.5	1243.9	1245.5	1242.2	1242.2	1242.2
7.5°	1250.4	1250.4	1248.8	1247.2	1247.2	1247.2	1245.5	1243.9	1242.2	1238.8	1237.2
10°	1247.2	1247.2	1248.8	1245.5	1245.5	1242.2	1242.2	1238.8	1238.8	1235.6	1230.6
12.5°	1243.9	1242.2	1242.2	1238.8	1238.8	1235.6	1235.6	1230.6	1229.0	1224.0	1219.1
15°	1235.6	1233.9	1230.6	1229.0	1227.3	1225.7	1222.4	1220.8	1215.7	1209.2	1204.2
17.5°	1219.1	1217.4	1215.7	1212.4	1209.2	1207.5	1205.9	1200.9	1194.3	1189.3	1181.1
20°	1195.9	1194.3	1194.3	1189.3	1187.7	1182.8	1181.1	1174.4	1169.5	1159.6	1153.0
22.5°	1164.6	1166.2	1162.9	1159.6	1156.3	1151.3	1148.0	1141.5	1133.1	1123.3	1115.0
25°	1126.6	1128.2	1124.9	1121.6	1116.7	1113.3	1110.0	1100.2	1091.8	1080.3	1070.4
27.5°	1078.7	1078.7	1078.7	1075.4	1067.1	1065.4	1062.2	1052.2	1040.7	1030.7	1020.9
30°	1022.5	1020.9	1020.9	1015.9	1012.5	1006.0	1001.0	992.7	984.5	973.0	961.4
32.5°	954.8	956.5	951.4	948.1	943.2	943.2	936.6	930.0	920.1	908.5	897.0
35°	880.4	882.1	878.8	877.2	868.8	867.2	865.5	857.3	850.8	842.4	829.2
37.5°	804.4	802.8	801.1	801.1	796.2	792.9	789.6	784.6	774.7	768.2	761.5
40°	721.8	721.8	721.8	720.2	718.5	715.3	713.6	710.3	703.7	697.1	692.1
42.5°	647.6	647.6	645.9	644.2	640.9	642.5	639.2	636.0	629.4	624.5	621.1
45°	574.8	574.8	574.8	576.5	573.2	568.3	568.3	565.0	561.6	558.3	553.4
47.5°	510.4	515.4	512.1	510.4	512.1	505.5	505.5	502.2	498.8	495.5	489.0
50°	457.5	457.5	457.5	454.2	452.6	452.6	447.7	444.4	442.7	439.3	432.8
52.5°	409.7	406.4	406.4	404.7	403.1	399.8	399.8	396.4	389.8	386.5	381.6
55°	361.8	361.8	360.1	358.5	356.8	355.1	353.5	348.5	345.3	340.3	335.3
57.5°	318.9	322.1	320.5	317.1	313.8	313.8	310.5	307.2	302.3	297.4	292.4
60°	284.1	282.5	282.5	280.8	277.6	275.8	274.2	269.2	264.3	259.4	254.3
62.5°	247.8	247.8	247.8	244.5	241.2	239.5	237.9	234.5	227.9	223.0	219.7
65°	216.4	214.7	213.0	211.4	209.8	206.5	204.8	201.5	196.6	191.6	186.6
67.5°	185.0	183.4	183.4	181.7	176.8	175.1	175.1	170.1	165.2	160.2	155.3
70°	153.7	153.7	153.7	150.3	148.6	147.0	145.4	142.1	137.1	132.1	127.2
72.5°	127.2	125.5	125.5	123.9	119.0	117.3	115.7	112.4	107.3	104.1	100.8
75°	99.1	99.1	97.5	95.8	94.2	92.6	90.8	87.5	82.6	77.7	76.0
77.5°	76.0	74.4	74.4	72.7	69.3	67.7	67.7	64.4	59.5	56.2	52.9
80°	51.3	52.9	51.3	49.5	47.9	46.2	44.6	42.9	39.7	36.4	33.1
82.5°	31.4	33.1	31.4	31.4	29.7	28.0	28.0	24.8	23.1	21.5	19.8
85°	16.5	16.5	16.5	16.5	14.9	14.9	14.9	13.3	11.6	10.0	10.0
87.5°	4.9	6.6	4.9	4.9	4.9	4.9	4.9	4.9	3.3	3.3	3.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584106

CATALOG NUMBER: HCC8W25D010BZ-HM82555827-81RWWC

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1237.2	1237.2	1237.2	1237.2	1237.2	1237.2	1237.2	1237.2	1237.2	1237.2	1237.2
2.5°	1242.2	1240.6	1238.8	1238.8	1238.8	1238.8	1238.8	1237.2	1235.6	1235.6	1235.6
5°	1238.8	1238.8	1238.8	1237.2	1235.6	1235.6	1232.3	1230.6	1229.0	1227.3	1225.7
7.5°	1235.6	1232.3	1230.6	1229.0	1227.3	1227.3	1224.0	1220.8	1220.8	1217.4	1214.1
10°	1225.7	1224.0	1220.8	1217.4	1215.7	1214.1	1210.8	1205.9	1204.2	1200.9	1197.5
12.5°	1214.1	1210.8	1207.5	1200.9	1199.3	1197.5	1191.0	1186.0	1182.8	1181.1	1172.8
15°	1199.3	1192.6	1187.7	1179.5	1177.7	1174.4	1169.5	1164.6	1158.0	1153.0	1149.7
17.5°	1172.8	1166.2	1158.0	1149.7	1146.4	1146.4	1138.2	1131.5	1123.3	1120.0	1113.3
20°	1141.5	1133.1	1126.6	1116.7	1111.7	1106.7	1101.8	1091.8	1085.3	1080.3	1072.0
22.5°	1105.1	1093.5	1085.3	1075.4	1067.1	1062.2	1053.8	1045.6	1037.4	1032.4	1025.8
25°	1058.9	1048.9	1035.8	1025.8	1020.9	1014.3	1004.3	996.1	987.8	979.6	976.3
27.5°	1007.6	994.5	982.9	971.2	966.3	961.4	949.8	939.9	933.3	925.0	921.7
30°	951.4	938.3	925.0	915.2	910.1	901.9	895.3	883.7	875.5	868.8	860.6
32.5°	887.0	877.2	865.5	850.8	847.4	840.8	830.9	825.9	816.0	811.1	804.4
35°	817.7	811.1	799.5	787.9	783.0	779.7	771.4	761.5	754.9	750.0	746.6
37.5°	751.6	743.3	731.8	723.5	720.2	715.3	705.3	700.4	693.8	690.5	683.8
40°	680.5	672.3	664.0	659.1	654.1	650.9	644.2	639.2	632.7	627.7	626.1
42.5°	611.2	606.3	599.6	593.0	591.4	586.4	583.2	578.1	573.2	571.6	566.6
45°	548.4	543.5	536.8	530.3	528.6	525.3	523.7	518.6	515.4	515.4	515.4
47.5°	485.7	480.6	474.1	470.8	472.4	465.8	465.8	464.2	460.8	460.8	462.6
50°	429.5	422.9	421.3	417.9	414.6	411.3	412.9	408.0	408.0	411.3	409.7
52.5°	376.6	370.0	368.4	365.1	363.4	363.4	361.8	361.8	360.1	361.8	361.8
55°	328.7	323.8	320.5	317.1	315.5	315.5	315.5	313.8	312.2	315.5	317.1
57.5°	285.8	284.1	280.8	275.8	274.2	272.5	270.9	270.9	270.9	270.9	272.5
60°	247.8	244.5	241.2	236.3	236.3	234.5	232.9	231.2	231.2	231.2	231.2
62.5°	214.7	209.8	204.8	201.5	199.9	198.3	196.6	193.2	193.2	193.2	193.2
65°	181.7	176.8	173.4	170.1	166.8	166.8	163.5	161.9	158.6	157.0	153.7
67.5°	150.3	147.0	143.7	138.8	137.1	135.5	132.1	130.5	125.5	123.9	122.2
70°	122.2	117.3	114.0	110.6	109.0	105.7	102.4	99.1	95.8	92.6	89.2
72.5°	95.8	90.8	87.5	84.2	80.9	80.9	76.0	72.7	67.7	64.4	59.5
75°	71.0	66.1	62.8	57.8	56.2	54.5	49.5	46.2	41.3	36.4	33.1
77.5°	47.9	44.6	41.3	36.4	33.1	33.1	28.0	24.8	21.5	16.5	14.9
80°	29.7	26.4	23.1	19.8	19.8	16.5	14.9	11.6	8.2	6.6	4.9
82.5°	16.5	14.9	13.3	10.0	10.0	8.2	6.6	4.9	3.3	1.6	1.6
85°	8.2	6.6	4.9	4.9	3.3	3.3	3.3	1.6	1.6	0.0	0.0
87.5°	3.3	1.6	1.6	1.6	1.6	1.6	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584106

CATALOG NUMBER: HCC8W25D010BZ-HM82555827-81RWWC

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1237.2	1237.2	1237.2	1237.2	1237.2	1237.2	1237.2	1237.2	1237.2	1237.2	1237.2
2.5°	1233.9	1233.9	1232.3	1232.3	1232.3	1230.6	1232.3	1230.6	1230.6	1230.6	1232.3
5°	1227.3	1224.0	1224.0	1222.4	1222.4	1220.8	1222.4	1220.8	1219.1	1217.4	1219.1
7.5°	1214.1	1210.8	1209.2	1207.5	1207.5	1207.5	1205.9	1204.2	1205.9	1200.9	1204.2
10°	1195.9	1194.3	1191.0	1189.3	1187.7	1189.3	1187.7	1184.4	1184.4	1184.4	1182.8
12.5°	1172.8	1169.5	1167.9	1166.2	1162.9	1162.9	1164.6	1161.3	1161.3	1158.0	1158.0
15°	1144.7	1141.5	1138.2	1138.2	1134.8	1134.8	1133.1	1133.1	1131.5	1129.9	1129.9
17.5°	1110.0	1105.1	1101.8	1103.5	1101.8	1100.2	1100.2	1096.9	1095.1	1096.9	1096.9
20°	1068.7	1065.4	1062.2	1063.8	1060.5	1058.9	1060.5	1055.6	1057.2	1057.2	1057.2
22.5°	1022.5	1020.9	1015.9	1015.9	1012.5	1010.9	1012.5	1012.5	1014.3	1012.5	1012.5
25°	971.2	968.0	964.7	964.7	963.0	961.4	963.0	964.7	963.0	964.7	964.7
27.5°	916.8	911.9	911.9	908.5	908.5	910.1	908.5	910.1	911.9	911.9	915.2
30°	857.3	855.7	854.0	852.4	852.4	854.0	854.0	854.0	855.7	859.0	859.0
32.5°	801.1	797.8	794.6	794.6	797.8	796.2	797.8	797.8	801.1	801.1	804.4
35°	740.0	740.0	736.7	738.4	738.4	738.4	738.4	741.7	744.9	746.6	750.0
37.5°	683.8	678.9	680.5	680.5	682.2	680.5	685.5	685.5	688.9	688.9	692.1
40°	622.7	622.7	624.5	622.7	624.5	624.5	627.7	631.0	632.7	636.0	637.6
42.5°	565.0	568.3	565.0	566.6	568.3	569.9	571.6	573.2	579.8	583.2	588.1
45°	512.1	513.7	515.4	517.0	515.4	518.6	520.3	523.7	528.6	530.3	531.9
47.5°	460.8	462.6	464.2	465.8	465.8	469.1	470.8	474.1	477.4	479.0	480.6
50°	411.3	414.6	416.2	416.2	417.9	421.3	424.6	424.6	427.8	432.8	434.4
52.5°	366.7	366.7	370.0	371.7	373.3	373.3	378.2	380.0	381.6	384.9	388.2
55°	317.1	322.1	323.8	323.8	327.1	330.4	332.0	333.6	333.6	340.3	340.3
57.5°	274.2	275.8	279.2	279.2	279.2	284.1	284.1	287.4	289.1	290.7	294.0
60°	231.2	234.5	234.5	236.3	234.5	237.9	239.5	242.8	244.5	246.1	247.8
62.5°	191.6	191.6	193.2	193.2	193.2	193.2	196.6	196.6	199.9	201.5	203.2
65°	153.7	153.7	153.7	153.7	153.7	153.7	153.7	153.7	155.3	155.3	158.6
67.5°	119.0	117.3	114.0	115.7	114.0	114.0	112.4	112.4	114.0	114.0	117.3
70°	85.9	84.2	80.9	80.9	79.3	77.7	76.0	74.4	72.7	72.7	72.7
72.5°	56.2	52.9	47.9	46.2	46.2	42.9	39.7	38.0	38.0	38.0	38.0
75°	28.0	24.8	21.5	19.8	19.8	16.5	18.2	16.5	16.5	16.5	16.5
77.5°	11.6	8.2	6.6	6.6	6.6	4.9	4.9	4.9	4.9	4.9	4.9
80°	3.3	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
82.5°	1.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584106

CATALOG NUMBER: HCC8W25D010BZ-HM82555827-81RWWC

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1237.2	1237.2	1237.2	1237.2	1237.2	1237.2	1237.2	1237.2
2.5°	1230.6	1230.6	1227.3	1229.0	1229.0	1229.0	1229.0	1229.0
5°	1215.7	1217.4	1215.7	1217.4	1217.4	1215.7	1215.7	1215.7
7.5°	1200.9	1202.6	1200.9	1202.6	1202.6	1202.6	1200.9	1200.9
10°	1182.8	1182.8	1182.8	1182.8	1182.8	1181.1	1182.8	1182.8
12.5°	1158.0	1158.0	1158.0	1159.6	1159.6	1158.0	1158.0	1156.3
15°	1131.5	1128.2	1129.9	1131.5	1129.9	1129.9	1129.9	1129.9
17.5°	1095.1	1096.9	1095.1	1095.1	1095.1	1095.1	1096.9	1095.1
20°	1057.2	1057.2	1058.9	1057.2	1057.2	1057.2	1057.2	1055.6
22.5°	1014.3	1012.5	1012.5	1014.3	1014.3	1012.5	1014.3	1014.3
25°	966.3	968.0	966.3	966.3	968.0	968.0	968.0	966.3
27.5°	915.2	916.8	918.4	916.8	916.8	916.8	918.4	920.1
30°	862.3	865.5	862.3	862.3	865.5	863.9	865.5	865.5
32.5°	806.1	811.1	807.7	811.1	811.1	812.7	811.1	812.7
35°	750.0	754.9	754.9	754.9	756.6	758.2	758.2	756.6
37.5°	697.1	698.7	698.7	702.0	703.7	705.3	705.3	703.7
40°	642.5	645.9	647.6	647.6	647.6	650.9	654.1	650.9
42.5°	589.7	591.4	593.0	593.0	596.3	598.0	599.6	599.6
45°	538.5	541.8	543.5	545.1	546.8	550.1	548.4	551.7
47.5°	485.7	490.6	492.2	493.9	497.2	498.8	500.5	502.2
50°	437.7	441.1	441.1	444.4	449.3	449.3	452.6	454.2
52.5°	389.8	391.5	393.1	394.8	398.1	401.4	401.4	404.7
55°	343.6	345.3	345.3	346.9	348.5	355.1	356.8	356.8
57.5°	295.6	295.6	299.0	300.7	302.3	305.6	305.6	305.6
60°	249.4	251.1	251.1	252.7	254.3	257.7	259.4	257.7
62.5°	203.2	204.8	204.8	206.5	209.8	211.4	209.8	209.8
65°	160.2	161.9	161.9	163.5	166.8	166.8	165.2	166.8
67.5°	117.3	117.3	117.3	117.3	117.3	117.3	117.3	117.3
70°	74.4	72.7	71.0	72.7	72.7	72.7	71.0	74.4
72.5°	36.4	38.0	38.0	38.0	38.0	38.0	38.0	36.4
75°	16.5	16.5	14.9	14.9	14.9	16.5	16.5	14.9
77.5°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9
80°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)