

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584272

Luminaire Tested: **HCC8S30D010MW-HM82555835-81NDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584272
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S30D010MW-HM82555835-81NDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3415.3 lumens
Efficiency: N/A
Efficacy: 122.0 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.27
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584272
CATALOG NUMBER: HCC8S30D010MW-HM82555835-81NDC

Luminous Intensity Polar Plot





TEST NUMBER: P584272
 CATALOG NUMBER: HCC8S30D010MW-HM82555835-81NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	115	112	110	108	112	110	108	107	106	105	103	102	101	100	99	98	97	96	95	94	93	92	91	90	89	88	87	86	85	84	83	82	81	80	79	78	77	76	75	74	73	72	71	70	69	68	67							
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91	90	89	88	87	86	85	84	83	82	81	80	79	78	77	76	75	74	73	72	71	70	69	68	67												
3	106	101	97	93	104	99	96	93	97	94	91	95	92	90	92	90	89	87	86	85	84	83	82	81	80	79	78	77	76	75	74	73	72	71	70	69	68	67																
4	102	96	91	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83	82	81	80	79	78	77	76	75	74	73	72	71	70	69	68	67																				
5	98	92	87	83	97	91	86	83	89	85	82	87	84	82	86	83	81	80	79	78	77	76	75	74	73	72	71	70	69	68	67																							
6	95	88	83	79	93	87	82	79	86	82	79	84	81	78	83	80	78	76	75	74	73	72	71	70	69	68	67																											
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73	72	71	70	69	68	67																														
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71	70	69	68	67																																
9	85	78	73	70	84	77	73	70	76	72	70	76	72	69	75	72	69	68	67																																			
10	83	75	70	67	82	75	70	67	74	70	67	73	69	67	73	69	67																																					

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	642826
5°	412324
10°	186263
15°	112386
20°	85645
25°	69161
30°	50683
35°	18352
40°	6847
45°	3109
50°	993
55°	247
60°	142
65°	168
70°	0
75°	0
80°	408
85°	814



TEST NUMBER: P584272
 CATALOG NUMBER: HCC8S30D010MW-HM82555835-81NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1015.9	29.7
10°-20°	1031.9	30.2
20°-30°	923.7	27.0
30°-40°	372.1	10.9
40°-50°	61.0	1.8
50°-60°	5.5	0.2
60°-70°	2.0	0.1
70°-80°	1.5	0.0
80°-90°	2.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2971.5	87.0
0°-40°	3343.7	97.9
0°-60°	3410.2	99.9
0°-90°	3415.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3415.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	20846	
5°	13320	###
15°	3520	1032
25°	2033	924
35°	488	372
45°	71	61
55°	5	6
65°	2	2
75°	0	2
85°	2	2
90°	0	



TEST NUMBER: P584272
CATALOG NUMBER: HCC8S30D010MW-HM82555835-81NDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	20846.4
0.5°	20781.9
1°	20513.0
1.5°	20080.7
2°	19425.3
2.5°	18650.4
3°	17680.1
3.5°	16615.4
4°	15562.3
4.5°	14382.7
5°	13320.5
5.5°	12163.8
6°	11225.7
6.5°	10248.5
7°	9480.4
7.5°	8668.8
8°	8015.8
8.5°	7360.4
9°	6868.3
9.5°	6325.6
10°	5948.6
12.5°	4387.3
15°	3520.4
17.5°	3007.6
20°	2609.9
22.5°	2292.5
25°	2032.7
27.5°	1772.8
30°	1423.4
32.5°	915.2
35°	487.5
37.5°	269.1
40°	170.1
42.5°	112.7
45°	71.3
47.5°	43.6
50°	20.7
52.5°	6.9
55°	4.6
57.5°	2.3
60°	2.3
62.5°	2.3
65°	2.3



TEST NUMBER: P584272
CATALOG NUMBER: HCC8S30D010MW-HM82555835-81NDC

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	2.3
80°	2.3
82.5°	2.3
85°	2.3
87.5°	2.3
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



67.5°		2.3
70°		0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)