

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584283

Luminaire Tested: **HCC8W30D010SL-HM82555835-81WWBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584283
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W30D010SL-HM82555835-81WWBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2865.6 lumens
Efficiency: N/A
Efficacy: 102.3 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584283
CATALOG NUMBER: HCC8W30D010SL-HM82555835-81WWBB

Luminous Intensity Polar Plot





TEST NUMBER: P584283

CATALOG NUMBER: HCC8W30D010SL-HM82555835-81WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77								
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67								
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59								
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47								
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43								
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39								
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	47439	47439	47439
5°	49400	47338	45342
10°	51051	46730	43132
15°	52343	45664	40892
20°	52449	43769	38860
25°	51560	40996	36852
30°	48803	37829	35126
35°	44495	34023	32984
40°	38692	29989	30456
45°	33195	25974	27879
50°	28357	22394	25042
55°	24849	19284	21757
60°	22122	16454	18298
65°	19635	13418	14600
70°	17419	9945	8295
75°	14523	5195	2466
80°	11436	1634	408
85°	8102	814	0



TEST NUMBER: P584283
 CATALOG NUMBER: HCC8W30D010SL-HM82555835-81WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	145.0	5.1
10°-20°	406.3	14.2
20°-30°	575.1	20.1
30°-40°	601.6	21.0
40°-50°	501.8	17.5
50°-60°	355.9	12.4
60°-70°	205.0	7.2
70°-80°	65.9	2.3
80°-90°	9.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1126.3	39.3
0°-40°	1728.0	60.3
0°-60°	2585.6	90.2
0°-90°	2865.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2865.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1538	1538	1538	1538	1538	
5°	1596	1575	1529	1483	1465	153
15°	1640	1573	1430	1318	1281	461
25°	1515	1403	1205	1108	1083	692
35°	1182	1078	904	856	876	733
45°	761	699	596	602	639	590
55°	462	414	359	377	405	418
65°	269	225	184	184	200	269
75°	122	90	44	21	21	132
85°	23	12	2	0	0	29
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584283

CATALOG NUMBER: HCC8W30D010SL-HM82555835-81WWBB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1538.4	1538.4	1538.4	1538.4	1538.4	1538.4	1538.4	1538.4	1538.4	1538.4	1538.4
2.5°	1570.7	1568.3	1566.0	1568.3	1566.0	1568.3	1566.0	1566.0	1563.8	1561.4	1561.4
5°	1595.9	1593.6	1593.6	1593.6	1591.4	1589.0	1589.0	1586.7	1582.1	1579.8	1575.2
7.5°	1612.0	1614.3	1614.3	1614.3	1609.7	1609.7	1605.2	1600.5	1595.9	1591.4	1584.5
10°	1630.4	1630.4	1628.1	1625.8	1621.2	1618.9	1616.6	1612.0	1605.2	1595.9	1589.0
12.5°	1637.4	1637.4	1635.0	1630.4	1628.1	1625.8	1623.5	1616.6	1607.4	1595.9	1586.7
15°	1639.6	1635.0	1632.7	1630.4	1625.8	1618.9	1618.9	1609.7	1598.3	1584.5	1572.9
17.5°	1621.2	1623.5	1618.9	1614.3	1607.4	1602.8	1595.9	1589.0	1575.2	1559.1	1547.6
20°	1598.3	1595.9	1593.6	1586.7	1577.6	1575.2	1568.3	1556.9	1545.3	1526.9	1510.9
22.5°	1561.4	1559.1	1554.5	1550.0	1540.7	1536.2	1529.3	1515.4	1499.3	1480.9	1462.6
25°	1515.4	1510.9	1504.0	1494.7	1487.8	1483.3	1474.0	1460.2	1441.9	1421.1	1402.8
27.5°	1441.9	1448.8	1444.2	1430.4	1423.5	1414.2	1411.9	1393.5	1377.5	1356.8	1336.1
30°	1370.6	1370.6	1363.7	1356.8	1345.2	1338.3	1329.2	1315.4	1299.2	1274.0	1257.8
32.5°	1280.9	1278.5	1269.4	1267.1	1257.8	1244.1	1241.8	1223.4	1207.3	1188.9	1168.2
35°	1182.0	1177.3	1168.2	1161.3	1156.7	1149.8	1142.9	1126.8	1110.8	1092.3	1078.5
37.5°	1069.3	1069.3	1067.0	1055.5	1051.0	1046.3	1039.4	1023.4	1014.1	995.7	981.9
40°	961.2	958.9	952.0	949.8	945.1	938.2	933.6	924.4	910.7	896.9	883.1
42.5°	855.5	857.7	848.6	850.8	841.7	837.1	834.8	821.0	814.1	800.3	788.8
45°	761.2	758.8	754.3	751.9	747.4	742.8	738.1	731.2	719.8	706.0	699.1
47.5°	673.8	666.9	666.9	664.5	662.3	653.1	650.7	643.8	636.9	623.2	614.0
50°	591.1	591.1	591.1	588.7	581.8	579.5	574.9	568.0	561.1	551.9	538.1
52.5°	524.3	524.3	524.3	522.0	512.8	510.6	508.2	499.0	489.9	483.0	473.7
55°	462.2	464.5	462.2	457.6	450.7	450.7	443.9	439.2	430.1	423.2	413.9
57.5°	409.4	409.4	404.7	402.5	397.8	395.6	390.9	386.3	374.9	367.9	356.5
60°	358.7	356.5	356.5	351.8	347.2	342.7	340.3	333.4	328.9	317.3	308.2
62.5°	312.7	312.7	308.2	308.2	298.9	298.9	296.7	289.8	282.9	271.3	266.8
65°	269.1	269.1	266.8	264.4	257.5	255.3	252.9	246.0	239.1	232.2	225.3
67.5°	230.0	230.0	225.3	223.1	218.4	216.2	211.5	207.0	200.1	193.2	186.3
70°	193.2	190.8	188.6	186.3	181.7	179.4	174.8	170.1	163.2	158.7	151.7
72.5°	156.4	156.4	154.1	149.5	147.2	144.8	142.6	137.9	131.0	124.1	119.6
75°	121.9	121.9	121.9	117.2	112.7	110.3	110.3	105.8	101.2	94.3	89.7
77.5°	94.3	92.0	89.7	89.7	85.1	82.8	80.5	78.2	71.3	69.0	64.4
80°	64.4	66.7	64.4	62.1	59.8	57.5	57.5	52.9	50.5	46.0	41.4
82.5°	43.6	41.4	41.4	39.1	39.1	36.7	36.7	32.2	29.8	27.6	25.3
85°	22.9	22.9	20.7	20.7	20.7	18.4	18.4	16.1	16.1	13.8	11.5
87.5°	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9	4.6	4.6	4.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584283

CATALOG NUMBER: HCC8W30D010SL-HM82555835-81WWBB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1538.4	1538.4	1538.4	1538.4	1538.4	1538.4	1538.4	1538.4	1538.4	1538.4	1538.4
2.5°	1559.1	1554.5	1552.2	1552.2	1550.0	1547.6	1545.3	1543.1	1538.4	1538.4	1533.8
5°	1570.7	1566.0	1563.8	1556.9	1552.2	1552.2	1543.1	1540.7	1533.8	1529.3	1524.7
7.5°	1579.8	1570.7	1563.8	1556.9	1552.2	1547.6	1538.4	1529.3	1520.0	1510.9	1506.2
10°	1579.8	1570.7	1559.1	1547.6	1543.1	1538.4	1526.9	1513.1	1501.6	1492.4	1480.9
12.5°	1575.2	1561.4	1547.6	1538.4	1529.3	1522.3	1508.5	1494.7	1480.9	1462.6	1453.3
15°	1561.4	1543.1	1529.3	1513.1	1506.2	1494.7	1483.3	1462.6	1446.4	1430.4	1418.8
17.5°	1533.8	1510.9	1494.7	1478.6	1467.1	1460.2	1441.9	1423.5	1405.0	1386.6	1372.8
20°	1492.4	1471.7	1453.3	1432.6	1423.5	1414.2	1391.2	1372.8	1354.5	1333.8	1320.0
22.5°	1441.9	1421.1	1395.9	1379.7	1365.9	1354.5	1333.8	1313.0	1294.7	1276.3	1257.8
25°	1379.7	1359.0	1336.1	1310.8	1301.6	1290.1	1267.1	1246.4	1225.7	1204.9	1188.9
27.5°	1313.0	1285.4	1267.1	1239.5	1230.3	1218.8	1193.5	1170.5	1152.1	1136.0	1117.7
30°	1232.6	1211.9	1186.6	1161.3	1152.1	1140.6	1119.9	1099.2	1080.8	1062.4	1044.1
32.5°	1145.2	1124.6	1099.2	1080.8	1067.0	1057.9	1037.2	1018.7	1000.3	981.9	965.8
35°	1053.2	1030.3	1011.8	993.4	981.9	970.5	949.8	933.6	919.8	903.8	887.6
37.5°	958.9	942.9	924.4	903.8	892.2	883.1	866.9	848.6	837.1	823.3	811.7
40°	866.9	848.6	832.4	814.1	804.8	797.9	781.9	768.1	756.6	745.0	738.1
42.5°	772.6	756.6	740.5	729.0	722.1	715.2	703.7	687.6	680.7	669.2	662.3
45°	685.3	671.4	660.0	643.8	639.3	634.7	620.9	609.4	602.5	595.6	591.1
47.5°	602.5	593.3	579.5	570.2	563.3	558.8	549.6	540.4	533.5	528.9	524.3
50°	531.2	519.7	510.6	501.3	496.8	489.9	480.6	476.1	471.4	466.8	466.8
52.5°	464.5	453.0	443.9	437.0	432.3	427.7	420.8	418.5	413.9	413.9	411.6
55°	402.5	395.6	386.3	377.2	374.9	372.5	367.9	363.4	361.0	358.7	361.0
57.5°	349.6	342.7	333.4	326.5	324.2	322.0	319.6	315.1	312.7	312.7	312.7
60°	301.3	294.4	287.5	280.6	280.6	276.0	273.7	271.3	269.1	266.8	266.8
62.5°	257.5	250.6	243.7	239.1	236.8	234.6	230.0	227.7	225.3	225.3	223.1
65°	218.4	209.3	207.0	200.1	197.7	195.5	193.2	188.6	186.3	183.9	181.7
67.5°	179.4	174.8	167.9	163.2	161.0	158.7	156.4	151.7	149.5	147.2	142.6
70°	144.8	140.3	135.7	131.0	128.8	126.5	121.9	117.2	115.0	110.3	103.4
72.5°	112.7	108.1	103.4	98.9	96.5	94.3	89.7	85.1	80.5	75.9	71.3
75°	85.1	80.5	73.6	69.0	66.7	66.7	59.8	55.2	50.5	43.6	39.1
77.5°	59.8	52.9	50.5	46.0	43.6	39.1	34.5	29.8	25.3	22.9	18.4
80°	39.1	34.5	29.8	27.6	25.3	22.9	20.7	16.1	11.5	9.2	6.9
82.5°	22.9	20.7	18.4	16.1	13.8	11.5	9.2	9.2	6.9	4.6	2.3
85°	11.5	9.2	6.9	6.9	4.6	4.6	4.6	2.3	2.3	2.3	2.3
87.5°	4.6	2.3	2.3	2.3	2.3	2.3	2.3	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584283

CATALOG NUMBER: HCC8W30D010SL-HM82555835-81WWBB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1538.4	1538.4	1538.4	1538.4	1538.4	1538.4	1538.4	1538.4	1538.4	1538.4	1538.4
2.5°	1531.6	1529.3	1526.9	1524.7	1524.7	1520.0	1520.0	1517.8	1513.1	1510.9	1510.9
5°	1517.8	1510.9	1506.2	1504.0	1501.6	1494.7	1492.4	1487.8	1483.3	1478.6	1476.4
7.5°	1497.1	1485.5	1480.9	1478.6	1471.7	1464.8	1460.2	1453.3	1446.4	1439.5	1437.3
10°	1471.7	1460.2	1448.8	1444.2	1437.3	1432.6	1423.5	1414.2	1407.3	1400.4	1393.5
12.5°	1439.5	1425.7	1414.2	1409.7	1402.8	1393.5	1379.7	1375.2	1363.7	1359.0	1349.9
15°	1402.8	1386.6	1375.2	1368.3	1361.4	1347.6	1338.3	1329.2	1317.6	1313.0	1303.9
17.5°	1356.8	1338.3	1326.9	1320.0	1315.4	1303.9	1290.1	1278.5	1267.1	1262.5	1255.6
20°	1301.6	1290.1	1274.0	1267.1	1262.5	1248.7	1234.9	1230.3	1221.1	1211.9	1204.9
22.5°	1239.5	1228.0	1211.9	1204.9	1202.7	1191.1	1179.7	1172.8	1165.9	1159.0	1152.1
25°	1175.1	1161.3	1147.5	1142.9	1138.3	1129.1	1119.9	1115.3	1108.4	1103.7	1099.2
27.5°	1106.1	1092.3	1080.8	1073.9	1069.3	1062.4	1057.9	1053.2	1048.6	1044.1	1041.7
30°	1032.5	1018.7	1009.6	1004.9	1000.3	998.0	991.2	988.8	986.5	981.9	984.3
32.5°	958.9	947.4	938.2	931.3	931.3	926.7	924.4	924.4	922.2	922.2	922.2
35°	878.4	871.5	864.6	862.4	860.0	857.7	855.5	857.7	855.5	857.7	860.0
37.5°	804.8	797.9	793.4	791.0	788.8	791.0	788.8	788.8	791.0	795.7	797.9
40°	729.0	724.3	719.8	722.1	719.8	719.8	719.8	726.7	729.0	731.2	733.6
42.5°	657.6	653.1	650.7	650.7	653.1	650.7	655.4	657.6	662.3	669.2	673.8
45°	588.7	586.4	586.4	588.7	586.4	591.1	591.1	595.6	602.5	607.1	611.7
47.5°	524.3	524.3	524.3	526.6	526.6	528.9	533.5	535.8	540.4	545.0	549.6
50°	464.5	466.8	469.1	469.1	469.1	473.7	478.3	480.6	483.0	485.2	492.1
52.5°	411.6	413.9	413.9	416.3	418.5	420.8	423.2	427.7	430.1	434.6	437.0
55°	361.0	361.0	365.6	367.9	367.9	367.9	372.5	372.5	377.2	379.4	384.0
57.5°	312.7	315.1	315.1	317.3	317.3	319.6	322.0	324.2	326.5	328.9	331.1
60°	266.8	266.8	266.8	269.1	271.3	273.7	271.3	276.0	276.0	280.6	282.9
62.5°	223.1	225.3	225.3	225.3	225.3	225.3	225.3	227.7	230.0	232.2	234.6
65°	181.7	181.7	181.7	179.4	181.7	179.4	181.7	183.9	183.9	186.3	188.6
67.5°	140.3	140.3	135.7	135.7	137.9	137.9	137.9	137.9	135.7	140.3	140.3
70°	101.2	98.9	96.5	94.3	94.3	92.0	92.0	89.7	89.7	89.7	89.7
72.5°	66.7	62.1	57.5	55.2	52.9	52.9	48.3	46.0	48.3	48.3	48.3
75°	34.5	29.8	27.6	25.3	22.9	22.9	20.7	20.7	20.7	20.7	20.7
77.5°	13.8	11.5	9.2	9.2	6.9	6.9	6.9	6.9	6.9	6.9	6.9
80°	4.6	4.6	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
82.5°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
85°	2.3	0.0	0.0	2.3	0.0	2.3	2.3	2.3	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584283

CATALOG NUMBER: HCC8W30D010SL-HM82555835-81WWBB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1538.4	1538.4	1538.4	1538.4	1538.4	1538.4	1538.4	1538.4
2.5°	1508.5	1508.5	1506.2	1508.5	1504.0	1506.2	1504.0	1504.0
5°	1474.0	1469.5	1469.5	1469.5	1467.1	1467.1	1464.8	1464.8
7.5°	1432.6	1430.4	1428.1	1425.7	1423.5	1421.1	1421.1	1421.1
10°	1391.2	1386.6	1386.6	1384.4	1379.7	1377.5	1377.5	1377.5
12.5°	1343.0	1340.7	1338.3	1338.3	1329.2	1331.4	1329.2	1329.2
15°	1297.0	1294.7	1294.7	1287.8	1283.2	1283.2	1283.2	1280.9
17.5°	1248.7	1246.4	1244.1	1239.5	1234.9	1234.9	1232.6	1234.9
20°	1198.0	1195.8	1191.1	1191.1	1188.9	1186.6	1182.0	1184.2
22.5°	1147.5	1142.9	1140.6	1140.6	1138.3	1138.3	1133.7	1133.7
25°	1094.6	1092.3	1090.0	1092.3	1087.7	1087.7	1083.1	1083.1
27.5°	1039.4	1037.2	1037.2	1037.2	1034.8	1037.2	1034.8	1034.8
30°	984.3	984.3	981.9	981.9	984.3	981.9	984.3	986.5
32.5°	924.4	924.4	926.7	926.7	929.1	929.1	929.1	929.1
35°	862.4	866.9	866.9	869.3	871.5	873.8	873.8	876.2
37.5°	804.8	807.2	809.5	811.7	816.4	816.4	816.4	816.4
40°	742.8	745.0	749.7	747.4	756.6	758.8	756.6	756.6
42.5°	678.3	683.0	685.3	689.9	692.2	696.8	699.1	699.1
45°	618.6	620.9	625.5	630.1	632.4	639.3	639.3	639.3
47.5°	556.5	561.1	563.3	568.0	570.2	577.1	579.5	577.1
50°	496.8	501.3	505.9	505.9	512.8	515.1	519.7	522.0
52.5°	439.2	441.5	446.1	448.4	453.0	457.6	459.9	462.2
55°	384.0	386.3	390.9	390.9	397.8	400.1	404.7	404.7
57.5°	333.4	335.8	340.3	338.0	342.7	347.2	347.2	344.9
60°	285.1	285.1	285.1	289.8	292.0	294.4	296.7	296.7
62.5°	234.6	239.1	241.5	241.5	243.7	246.0	246.0	243.7
65°	188.6	193.2	195.5	195.5	197.7	197.7	197.7	200.1
67.5°	142.6	142.6	142.6	144.8	142.6	142.6	142.6	142.6
70°	89.7	89.7	89.7	89.7	87.4	89.7	89.7	92.0
72.5°	48.3	48.3	48.3	48.3	48.3	48.3	48.3	48.3
75°	20.7	20.7	20.7	22.9	20.7	20.7	20.7	20.7
77.5°	9.2	6.9	9.2	9.2	6.9	6.9	6.9	6.9
80°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
82.5°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
85°	0.0	2.3	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)