

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584123

Luminaire Tested: **HCC8S25D010MW-HM82555830-81RWWC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584123
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S25D010MW-HM82555830-81RWWC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2296.2 lumens
Efficiency: N/A
Efficacy: 85.7 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.08 / 1.17
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584123
CATALOG NUMBER: HCC8S25D010MW-HM82555830-81RWWC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584123

CATALOG NUMBER: HCC8S25D010MW-HM82555830-81RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	85	82	79	77								
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67								
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	69	65	61	59								
5	81	70	62	56	80	69	62	56	67	61	56	65	59	55	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	37253	37253	37253
5°	37749	37098	36749
10°	38135	36720	36165
15°	38516	35947	35225
20°	38325	34617	33823
25°	37430	32547	32105
30°	35553	30212	30095
35°	32363	27567	27808
40°	28375	24676	25585
45°	24478	21944	23492
50°	21434	19271	21281
55°	18989	16564	18730
60°	17114	13932	15523
65°	15417	11178	11893
70°	13524	8141	6537
75°	11533	4230	1739
80°	8879	1137	284
85°	5732	0	0



TEST NUMBER: P584123
 CATALOG NUMBER: HCC8S25D010MW-HM82555830-81RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.0	5.0
10°-20°	320.5	14.0
20°-30°	454.8	19.8
30°-40°	478.8	20.9
40°-50°	407.3	17.7
50°-60°	294.3	12.8
60°-70°	167.4	7.3
70°-80°	52.7	2.3
80°-90°	6.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	889.3	38.7
0°-40°	1368.0	59.6
0°-60°	2069.7	90.1
0°-90°	2296.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2296.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1208	1208	1208	1208	1208	
5°	1220	1213	1198	1190	1187	116
15°	1206	1176	1126	1105	1103	340
25°	1100	1045	957	940	944	504
35°	860	810	732	728	739	535
45°	561	540	503	516	539	436
55°	353	327	308	326	348	319
65°	211	182	153	152	163	210
75°	97	74	36	16	15	104
85°	16	10	0	0	0	21
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584123

CATALOG NUMBER: HCC8S25D010MW-HM82555830-81RWWC

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1208.1	1208.1	1208.1	1208.1	1208.1	1208.1	1208.1	1208.1	1208.1	1208.1	1208.1
2.5°	1214.7	1216.3	1213.1	1213.1	1216.3	1213.1	1214.7	1214.7	1213.1	1213.1	1211.5
5°	1219.5	1217.9	1217.9	1217.9	1219.5	1216.3	1214.7	1216.3	1213.1	1213.1	1213.1
7.5°	1221.1	1221.1	1219.5	1217.9	1217.9	1217.9	1216.3	1214.7	1213.1	1209.7	1208.1
10°	1217.9	1217.9	1219.5	1216.3	1216.3	1213.1	1213.1	1209.7	1209.7	1206.5	1201.7
12.5°	1214.7	1213.1	1213.1	1209.7	1209.7	1206.5	1206.5	1201.7	1200.1	1195.3	1190.5
15°	1206.5	1204.9	1201.7	1200.1	1198.5	1196.9	1193.7	1192.1	1187.2	1180.7	1175.9
17.5°	1190.5	1188.8	1187.2	1184.0	1180.7	1179.1	1177.5	1172.7	1166.2	1161.4	1153.4
20°	1167.9	1166.2	1166.2	1161.4	1159.8	1155.0	1153.4	1146.9	1142.0	1132.4	1126.0
22.5°	1137.2	1138.8	1135.6	1132.4	1129.2	1124.2	1121.0	1114.6	1106.6	1096.9	1088.8
25°	1100.1	1101.7	1098.5	1095.3	1090.4	1087.2	1084.0	1074.3	1066.3	1054.9	1045.3
27.5°	1053.3	1053.3	1053.3	1050.1	1042.1	1040.5	1037.2	1027.5	1016.2	1006.5	996.9
30°	998.5	996.9	996.9	992.0	988.8	982.4	977.6	969.4	961.4	950.1	938.8
32.5°	932.4	934.0	929.1	925.9	921.1	921.1	914.6	908.1	898.5	887.1	875.9
35°	859.7	861.4	858.1	856.5	848.5	846.9	845.2	837.2	830.7	822.6	809.8
37.5°	785.6	784.0	782.4	782.4	777.5	774.3	771.0	766.2	756.5	750.1	743.7
40°	704.9	704.9	704.9	703.3	701.7	698.5	696.9	693.6	687.2	680.7	675.9
42.5°	632.4	632.4	630.7	629.1	625.8	627.4	624.2	621.0	614.6	609.7	606.5
45°	561.3	561.3	561.3	562.9	559.7	554.9	554.9	551.7	548.5	545.2	540.4
47.5°	498.4	503.2	500.0	498.4	500.0	493.6	493.6	490.4	487.2	484.0	477.4
50°	446.8	446.8	446.8	443.6	442.0	442.0	437.1	433.9	432.3	429.1	422.6
52.5°	400.1	396.9	396.9	395.2	393.5	390.3	390.3	387.1	380.7	377.5	372.6
55°	353.2	353.2	351.6	350.0	348.4	346.8	345.2	340.4	337.2	332.3	327.4
57.5°	311.4	314.6	313.0	309.7	306.4	306.4	303.2	300.0	295.2	290.4	285.5
60°	277.5	275.8	275.8	274.2	271.0	269.4	267.7	262.9	258.1	253.3	248.5
62.5°	241.9	241.9	241.9	238.7	235.5	233.9	232.3	229.1	222.6	217.7	214.5
65°	211.3	209.7	208.1	206.5	204.9	201.6	200.0	196.8	192.0	187.1	182.3
67.5°	180.6	179.0	179.0	177.4	172.6	171.0	171.0	166.2	161.4	156.4	151.6
70°	150.0	150.0	150.0	146.8	145.2	143.6	142.0	138.7	133.9	129.0	124.2
72.5°	124.2	122.6	122.6	121.0	116.1	114.5	112.9	109.7	104.9	101.6	98.4
75°	96.8	96.8	95.1	93.5	91.9	90.3	88.7	85.5	80.7	75.9	74.2
77.5°	74.2	72.5	72.5	70.9	67.7	66.1	66.1	62.9	58.1	54.9	51.6
80°	50.0	51.6	50.0	48.4	46.8	45.2	43.5	41.9	38.7	35.5	32.3
82.5°	30.6	32.3	30.6	30.6	29.0	27.4	27.4	24.2	22.6	21.0	19.4
85°	16.2	16.2	16.2	16.2	14.6	14.6	14.6	12.9	11.3	9.6	9.6
87.5°	4.8	6.4	4.8	4.8	4.8	4.8	4.8	4.8	3.2	3.2	3.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584123

CATALOG NUMBER: HCC8S25D010MW-HM82555830-81RWWC

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1208.1	1208.1	1208.1	1208.1	1208.1	1208.1	1208.1	1208.1	1208.1	1208.1	1208.1
2.5°	1213.1	1211.5	1209.7	1209.7	1209.7	1209.7	1209.7	1208.1	1206.5	1206.5	1206.5
5°	1209.7	1209.7	1209.7	1208.1	1206.5	1206.5	1203.3	1201.7	1200.1	1198.5	1196.9
7.5°	1206.5	1203.3	1201.7	1200.1	1198.5	1198.5	1195.3	1192.1	1192.1	1188.8	1185.6
10°	1196.9	1195.3	1192.1	1188.8	1187.2	1185.6	1182.4	1177.5	1175.9	1172.7	1169.5
12.5°	1185.6	1182.4	1179.1	1172.7	1171.1	1169.5	1163.0	1158.2	1155.0	1153.4	1145.2
15°	1171.1	1164.6	1159.8	1151.7	1150.1	1146.9	1142.0	1137.2	1130.8	1126.0	1122.6
17.5°	1145.2	1138.8	1130.8	1122.6	1119.4	1119.4	1111.4	1105.0	1096.9	1093.6	1087.2
20°	1114.6	1106.6	1100.1	1090.4	1085.6	1080.7	1075.9	1066.3	1059.7	1054.9	1046.9
22.5°	1079.1	1067.9	1059.7	1050.1	1042.1	1037.2	1029.1	1021.1	1013.0	1008.2	1001.7
25°	1033.9	1024.3	1011.4	1001.7	996.9	990.4	980.8	972.6	964.6	956.6	953.3
27.5°	984.0	971.0	959.8	948.4	943.6	938.8	927.5	917.8	911.4	903.3	900.1
30°	929.1	916.2	903.3	893.7	888.7	880.7	874.3	863.0	854.9	848.5	840.4
32.5°	866.2	856.5	845.2	830.7	827.5	821.0	811.4	806.6	796.8	792.0	785.6
35°	798.4	792.0	780.7	769.4	764.6	761.4	753.3	743.7	737.1	732.3	729.1
37.5°	733.9	725.9	714.5	706.5	703.3	698.5	688.8	683.9	677.5	674.2	667.8
40°	664.6	656.6	648.4	643.6	638.8	635.6	629.1	624.2	617.8	613.0	611.4
42.5°	596.8	592.0	585.5	579.1	577.5	572.7	569.5	564.5	559.7	558.1	553.3
45°	535.5	530.7	524.2	517.8	516.2	513.0	511.4	506.5	503.2	503.2	503.2
47.5°	474.2	469.4	463.0	459.7	461.4	454.9	454.9	453.3	450.0	450.0	451.6
50°	419.4	412.9	411.3	408.1	404.9	401.7	403.3	398.5	398.5	401.7	400.1
52.5°	367.8	361.3	359.7	356.5	354.9	354.9	353.2	353.2	351.6	353.2	353.2
55°	321.0	316.2	313.0	309.7	308.1	308.1	308.1	306.4	304.8	308.1	309.7
57.5°	279.1	277.5	274.2	269.4	267.7	266.1	264.5	264.5	264.5	264.5	266.1
60°	241.9	238.7	235.5	230.7	230.7	229.1	227.5	225.9	225.9	225.9	225.9
62.5°	209.7	204.9	200.0	196.8	195.2	193.6	192.0	188.7	188.7	188.7	188.7
65°	177.4	172.6	169.4	166.2	163.0	163.0	159.6	158.0	154.8	153.2	150.0
67.5°	146.8	143.6	140.4	135.5	133.9	132.3	129.0	127.4	122.6	121.0	119.4
70°	119.4	114.5	111.3	108.1	106.5	103.3	100.0	96.8	93.5	90.3	87.1
72.5°	93.5	88.7	85.5	82.3	79.1	79.1	74.2	70.9	66.1	62.9	58.1
75°	69.3	64.5	61.3	56.5	54.9	53.2	48.4	45.2	40.3	35.5	32.3
77.5°	46.8	43.5	40.3	35.5	32.3	32.3	27.4	24.2	21.0	16.2	14.6
80°	29.0	25.8	22.6	19.4	19.4	16.2	14.6	11.3	8.0	6.4	4.8
82.5°	16.2	14.6	12.9	9.6	9.6	8.0	6.4	4.8	3.2	1.6	1.6
85°	8.0	6.4	4.8	4.8	3.2	3.2	3.2	1.6	1.6	0.0	0.0
87.5°	3.2	1.6	1.6	1.6	1.6	1.6	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584123

CATALOG NUMBER: HCC8S25D010MW-HM82555830-81RWWC

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1208.1	1208.1	1208.1	1208.1	1208.1	1208.1	1208.1	1208.1	1208.1	1208.1	1208.1
2.5°	1204.9	1204.9	1203.3	1203.3	1203.3	1201.7	1203.3	1201.7	1201.7	1201.7	1203.3
5°	1198.5	1195.3	1195.3	1193.7	1193.7	1192.1	1193.7	1192.1	1190.5	1188.8	1190.5
7.5°	1185.6	1182.4	1180.7	1179.1	1179.1	1179.1	1177.5	1175.9	1177.5	1172.7	1175.9
10°	1167.9	1166.2	1163.0	1161.4	1159.8	1161.4	1159.8	1156.6	1156.6	1156.6	1155.0
12.5°	1145.2	1142.0	1140.4	1138.8	1135.6	1135.6	1137.2	1134.0	1134.0	1130.8	1130.8
15°	1117.8	1114.6	1111.4	1111.4	1108.2	1108.2	1106.6	1106.6	1105.0	1103.4	1103.4
17.5°	1084.0	1079.1	1075.9	1077.5	1075.9	1074.3	1074.3	1071.1	1069.5	1071.1	1071.1
20°	1043.7	1040.5	1037.2	1038.8	1035.5	1033.9	1035.5	1030.7	1032.3	1032.3	1032.3
22.5°	998.5	996.9	992.0	992.0	988.8	987.2	988.8	988.8	990.4	988.8	988.8
25°	948.4	945.2	942.0	942.0	940.4	938.8	940.4	942.0	940.4	942.0	942.0
27.5°	895.3	890.5	890.5	887.1	887.1	888.7	887.1	888.7	890.5	890.5	893.7
30°	837.2	835.6	834.0	832.4	832.4	834.0	834.0	834.0	835.6	838.8	838.8
32.5°	782.4	779.1	775.9	775.9	779.1	777.5	779.1	779.1	782.4	782.4	785.6
35°	722.7	722.7	719.5	721.1	721.1	721.1	721.1	724.3	727.5	729.1	732.3
37.5°	667.8	663.0	664.6	664.6	666.2	664.6	669.4	669.4	672.6	672.6	675.9
40°	608.1	608.1	609.7	608.1	609.7	609.7	613.0	616.2	617.8	621.0	622.6
42.5°	551.7	554.9	551.7	553.3	554.9	556.5	558.1	559.7	566.1	569.5	574.3
45°	500.0	501.6	503.2	504.9	503.2	506.5	508.1	511.4	516.2	517.8	519.4
47.5°	450.0	451.6	453.3	454.9	454.9	458.1	459.7	463.0	466.2	467.8	469.4
50°	401.7	404.9	406.5	406.5	408.1	411.3	414.5	414.5	417.8	422.6	424.3
52.5°	358.1	358.1	361.3	362.9	364.5	364.5	369.4	371.0	372.6	375.9	379.1
55°	309.7	314.6	316.2	316.2	319.4	322.6	324.2	325.8	325.8	332.3	332.3
57.5°	267.7	269.4	272.6	272.6	272.6	277.5	277.5	280.7	282.3	283.9	287.1
60°	225.9	229.1	229.1	230.7	229.1	232.3	233.9	237.1	238.7	240.3	241.9
62.5°	187.1	187.1	188.7	188.7	188.7	188.7	192.0	192.0	195.2	196.8	198.4
65°	150.0	150.0	150.0	150.0	150.0	150.0	150.0	150.0	151.6	151.6	154.8
67.5°	116.1	114.5	111.3	112.9	111.3	111.3	109.7	109.7	111.3	111.3	114.5
70°	83.9	82.3	79.1	79.1	77.5	75.9	74.2	72.5	70.9	70.9	70.9
72.5°	54.9	51.6	46.8	45.2	45.2	41.9	38.7	37.1	37.1	37.1	37.1
75°	27.4	24.2	21.0	19.4	19.4	16.2	17.8	16.2	16.2	16.2	16.2
77.5°	11.3	8.0	6.4	6.4	6.4	4.8	4.8	4.8	4.8	4.8	4.8
80°	3.2	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
82.5°	1.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584123

CATALOG NUMBER: HCC8S25D010MW-HM82555830-81RWWC

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1208.1	1208.1	1208.1	1208.1	1208.1	1208.1	1208.1	1208.1
2.5°	1201.7	1201.7	1198.5	1200.1	1200.1	1200.1	1200.1	1200.1
5°	1187.2	1188.8	1187.2	1188.8	1188.8	1187.2	1187.2	1187.2
7.5°	1172.7	1174.3	1172.7	1174.3	1174.3	1174.3	1172.7	1172.7
10°	1155.0	1155.0	1155.0	1155.0	1155.0	1153.4	1155.0	1155.0
12.5°	1130.8	1130.8	1130.8	1132.4	1132.4	1130.8	1130.8	1129.2
15°	1105.0	1101.7	1103.4	1105.0	1103.4	1103.4	1103.4	1103.4
17.5°	1069.5	1071.1	1069.5	1069.5	1069.5	1069.5	1071.1	1069.5
20°	1032.3	1032.3	1033.9	1032.3	1032.3	1032.3	1032.3	1030.7
22.5°	990.4	988.8	988.8	990.4	990.4	988.8	990.4	990.4
25°	943.6	945.2	943.6	943.6	945.2	945.2	945.2	943.6
27.5°	893.7	895.3	896.9	895.3	895.3	895.3	896.9	898.5
30°	842.0	845.2	842.0	842.0	845.2	843.6	845.2	845.2
32.5°	787.2	792.0	788.8	792.0	792.0	793.6	792.0	793.6
35°	732.3	737.1	737.1	737.1	738.7	740.4	740.4	738.7
37.5°	680.7	682.3	682.3	685.5	687.2	688.8	688.8	687.2
40°	627.4	630.7	632.4	632.4	632.4	635.6	638.8	635.6
42.5°	575.9	577.5	579.1	579.1	582.3	583.9	585.5	585.5
45°	525.9	529.1	530.7	532.3	533.9	537.1	535.5	538.7
47.5°	474.2	479.0	480.6	482.4	485.6	487.2	488.8	490.4
50°	427.5	430.7	430.7	433.9	438.7	438.7	442.0	443.6
52.5°	380.7	382.3	383.9	385.5	388.7	391.9	391.9	395.2
55°	335.6	337.2	337.2	338.8	340.4	346.8	348.4	348.4
57.5°	288.7	288.7	292.0	293.6	295.2	298.4	298.4	298.4
60°	243.5	245.1	245.1	246.8	248.5	251.7	253.3	251.7
62.5°	198.4	200.0	200.0	201.6	204.9	206.5	204.9	204.9
65°	156.4	158.0	158.0	159.6	163.0	163.0	161.4	163.0
67.5°	114.5	114.5	114.5	114.5	114.5	114.5	114.5	114.5
70°	72.5	70.9	69.3	70.9	70.9	70.9	69.3	72.5
72.5°	35.5	37.1	37.1	37.1	37.1	37.1	37.1	35.5
75°	16.2	16.2	14.6	14.6	14.6	16.2	16.2	14.6
77.5°	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8
80°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)