

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584293

Luminaire Tested: **HCC8S30D010BZ-HM82555840-81RWWC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584293
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S30D010BZ-HM82555840-81RWWC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3547.0 lumens
Efficiency: N/A
Efficacy: 126.7 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.08 / 1.17
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584293
CATALOG NUMBER: HCC8S30D010BZ-HM82555840-81RWWC

Luminous Intensity Polar Plot





TEST NUMBER: P584293

CATALOG NUMBER: HCC8S30D010BZ-HM82555840-81RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	84	82	79	77								
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67								
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	69	65	61	59								
5	81	70	62	56	80	69	62	56	67	61	56	65	59	55	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	57550	57550	57550
5°	58308	57308	56767
10°	58904	56719	55864
15°	59500	55526	54408
20°	59199	53473	52249
25°	57817	50274	49594
30°	54920	46666	46488
35°	49995	42583	42960
40°	43833	38112	39521
45°	37813	33902	36292
50°	33111	29762	32871
55°	29332	25590	28940
60°	26427	21518	23972
65°	23816	17271	18365
70°	20890	12586	10107
75°	17812	6529	2681
80°	13727	1776	444
85°	8845	0	0



TEST NUMBER: P584293
 CATALOG NUMBER: HCC8S30D010BZ-HM82555840-81RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	176.1	5.0
10°-20°	495.0	14.0
20°-30°	702.6	19.8
30°-40°	739.6	20.9
40°-50°	629.2	17.7
50°-60°	454.6	12.8
60°-70°	258.6	7.3
70°-80°	81.5	2.3
80°-90°	9.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1373.7	38.7
0°-40°	2113.2	59.6
0°-60°	3197.0	90.1
0°-90°	3547.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3547.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1866	1866	1866	1866	1866	
5°	1884	1874	1851	1839	1834	180
15°	1864	1816	1739	1707	1704	525
25°	1699	1615	1478	1453	1458	778
35°	1328	1251	1131	1124	1141	826
45°	867	835	777	797	832	674
55°	546	506	476	503	538	492
65°	326	282	237	234	252	324
75°	150	115	55	25	22	161
85°	25	15	0	0	0	32
90°	0	0	0	0	0	



TEST NUMBER: P584293

CATALOG NUMBER: HCC8S30D010BZ-HM82555840-81RWWC

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1866.3	1866.3	1866.3	1866.3	1866.3	1866.3	1866.3	1866.3	1866.3	1866.3	1866.3
2.5°	1876.2	1878.7	1873.7	1873.7	1878.7	1873.7	1876.2	1876.2	1873.7	1873.7	1871.2
5°	1883.7	1881.2	1881.2	1881.2	1883.7	1878.7	1876.2	1878.7	1873.7	1873.7	1873.7
7.5°	1886.2	1886.2	1883.7	1881.2	1881.2	1881.2	1878.7	1876.2	1873.7	1868.8	1866.3
10°	1881.2	1881.2	1883.7	1878.7	1878.7	1873.7	1873.7	1868.8	1868.8	1863.8	1856.3
12.5°	1876.2	1873.7	1873.7	1868.8	1868.8	1863.8	1863.8	1856.3	1853.9	1846.4	1838.9
15°	1863.8	1861.3	1856.3	1853.9	1851.4	1848.9	1843.9	1841.4	1833.9	1823.9	1816.4
17.5°	1838.9	1836.4	1833.9	1828.9	1823.9	1821.4	1818.9	1811.4	1801.5	1794.1	1781.6
20°	1804.0	1801.5	1801.5	1794.1	1791.6	1784.1	1781.6	1771.6	1764.1	1749.1	1739.3
22.5°	1756.6	1759.1	1754.1	1749.1	1744.1	1736.8	1731.8	1721.8	1709.3	1694.3	1682.0
25°	1699.3	1701.8	1696.8	1691.8	1684.3	1679.5	1674.5	1659.5	1647.0	1629.5	1614.7
27.5°	1627.0	1627.0	1627.0	1622.2	1609.7	1607.2	1602.2	1587.2	1569.7	1554.9	1539.9
30°	1542.4	1539.9	1539.9	1532.4	1527.4	1517.4	1510.0	1497.5	1485.1	1467.6	1450.2
32.5°	1440.2	1442.7	1435.2	1430.2	1422.8	1422.8	1412.8	1402.8	1387.9	1370.4	1353.0
35°	1328.1	1330.6	1325.6	1323.1	1310.6	1308.1	1305.6	1293.2	1283.3	1270.8	1250.8
37.5°	1213.5	1211.0	1208.5	1208.5	1201.0	1196.0	1191.0	1183.5	1168.7	1158.7	1148.7
40°	1088.9	1088.9	1088.9	1086.4	1083.9	1078.9	1076.4	1071.4	1061.4	1051.6	1044.1
42.5°	976.8	976.8	974.3	971.8	966.8	969.3	964.3	959.3	949.3	941.8	936.9
45°	867.1	867.1	867.1	869.6	864.6	857.2	857.2	852.2	847.2	842.2	834.7
47.5°	770.0	777.4	772.4	770.0	772.4	762.5	762.5	757.5	752.5	747.5	737.5
50°	690.2	690.2	690.2	685.2	682.7	682.7	675.2	670.2	667.7	662.7	652.9
52.5°	617.9	612.9	612.9	610.4	607.9	602.9	602.9	598.1	588.1	583.1	575.6
55°	545.6	545.6	543.1	540.8	538.3	535.8	533.3	525.8	520.8	513.3	505.8
57.5°	481.0	485.8	483.4	478.5	473.5	473.5	468.5	463.5	456.0	448.5	441.0
60°	428.5	426.1	426.1	423.6	418.6	416.2	413.7	406.2	398.7	391.2	383.7
62.5°	373.7	373.7	373.7	368.8	363.8	361.3	358.8	353.8	343.9	336.4	331.4
65°	326.4	323.9	321.4	318.9	316.4	311.5	309.0	304.0	296.5	289.0	281.6
67.5°	279.1	276.6	276.6	274.1	266.6	264.1	264.1	256.7	249.2	241.7	234.2
70°	231.7	231.7	231.7	226.7	224.2	221.7	219.3	214.3	206.8	199.4	191.9
72.5°	191.9	189.4	189.4	186.9	179.4	176.9	174.4	169.4	161.9	156.9	152.0
75°	149.5	149.5	147.0	144.5	142.1	139.6	137.1	132.1	124.6	117.1	114.6
77.5°	114.6	112.1	112.1	109.6	104.6	102.1	102.1	97.1	89.7	84.8	79.8
80°	77.3	79.8	77.3	74.8	72.3	69.8	67.3	64.8	59.8	54.8	49.8
82.5°	47.3	49.8	47.3	47.3	44.8	42.3	42.3	37.3	34.8	32.3	29.8
85°	25.0	25.0	25.0	25.0	22.5	22.5	22.5	20.0	17.5	15.0	15.0
87.5°	7.5	10.0	7.5	7.5	7.5	7.5	7.5	7.5	5.0	5.0	5.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584293

CATALOG NUMBER: HCC8S30D010BZ-HM82555840-81RWWC

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1866.3	1866.3	1866.3	1866.3	1866.3	1866.3	1866.3	1866.3	1866.3	1866.3	1866.3
2.5°	1873.7	1871.2	1868.8	1868.8	1868.8	1868.8	1868.8	1866.3	1863.8	1863.8	1863.8
5°	1868.8	1868.8	1868.8	1866.3	1863.8	1863.8	1858.8	1856.3	1853.9	1851.4	1848.9
7.5°	1863.8	1858.8	1856.3	1853.9	1851.4	1851.4	1846.4	1841.4	1841.4	1836.4	1831.4
10°	1848.9	1846.4	1841.4	1836.4	1833.9	1831.4	1826.4	1818.9	1816.4	1811.4	1806.4
12.5°	1831.4	1826.4	1821.4	1811.4	1808.9	1806.4	1796.6	1789.1	1784.1	1781.6	1769.1
15°	1808.9	1799.0	1791.6	1779.1	1776.6	1771.6	1764.1	1756.6	1746.6	1739.3	1734.3
17.5°	1769.1	1759.1	1746.6	1734.3	1729.3	1729.3	1716.8	1706.8	1694.3	1689.3	1679.5
20°	1721.8	1709.3	1699.3	1684.3	1677.0	1669.5	1662.0	1647.0	1637.0	1629.5	1617.2
22.5°	1667.0	1649.5	1637.0	1622.2	1609.7	1602.2	1589.7	1577.2	1564.8	1557.4	1547.4
25°	1597.2	1582.2	1562.3	1547.4	1539.9	1529.9	1514.9	1502.5	1490.1	1477.6	1472.6
27.5°	1519.9	1500.0	1482.6	1465.1	1457.6	1450.2	1432.7	1417.8	1407.8	1395.4	1390.4
30°	1435.2	1415.3	1395.4	1380.4	1372.9	1360.5	1350.5	1333.1	1320.6	1310.6	1298.2
32.5°	1338.1	1323.1	1305.6	1283.3	1278.3	1268.3	1253.3	1245.8	1230.9	1223.5	1213.5
35°	1233.3	1223.5	1206.0	1188.5	1181.0	1176.0	1163.7	1148.7	1138.7	1131.2	1126.2
37.5°	1133.7	1121.2	1103.9	1091.4	1086.4	1078.9	1063.9	1056.4	1046.6	1041.6	1031.6
40°	1026.6	1014.1	1001.6	994.2	986.8	981.8	971.8	964.3	954.3	946.8	944.3
42.5°	922.0	914.5	904.5	894.5	892.0	884.6	879.6	872.1	864.6	862.1	854.7
45°	827.3	819.8	809.8	799.8	797.3	792.3	789.9	782.4	777.4	777.4	777.4
47.5°	732.5	725.1	715.1	710.2	712.7	702.7	702.7	700.2	695.2	695.2	697.7
50°	647.9	637.9	635.4	630.4	625.4	620.4	622.9	615.4	615.4	620.4	617.9
52.5°	568.1	558.1	555.6	550.6	548.1	548.1	545.6	545.6	543.1	545.6	545.6
55°	495.8	488.3	483.4	478.5	476.0	476.0	476.0	473.5	471.0	476.0	478.5
57.5°	431.0	428.5	423.6	416.2	413.7	411.2	408.7	408.7	408.7	408.7	411.2
60°	373.7	368.8	363.8	356.3	356.3	353.8	351.3	348.9	348.9	348.9	348.9
62.5°	323.9	316.4	309.0	304.0	301.5	299.0	296.5	291.5	291.5	291.5	291.5
65°	274.1	266.6	261.6	256.7	251.7	251.7	246.7	244.2	239.2	236.7	231.7
67.5°	226.7	221.7	216.8	209.3	206.8	204.3	199.4	196.9	189.4	186.9	184.4
70°	184.4	176.9	171.9	166.9	164.4	159.4	154.5	149.5	144.5	139.6	134.6
72.5°	144.5	137.1	132.1	127.1	122.1	122.1	114.6	109.6	102.1	97.1	89.7
75°	107.1	99.6	94.6	87.2	84.8	82.3	74.8	69.8	62.3	54.8	49.8
77.5°	72.3	67.3	62.3	54.8	49.8	49.8	42.3	37.3	32.3	25.0	22.5
80°	44.8	39.8	34.8	29.8	29.8	25.0	22.5	17.5	12.5	10.0	7.5
82.5°	25.0	22.5	20.0	15.0	15.0	12.5	10.0	7.5	5.0	2.5	2.5
85°	12.5	10.0	7.5	7.5	5.0	5.0	5.0	2.5	2.5	0.0	0.0
87.5°	5.0	2.5	2.5	2.5	2.5	2.5	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584293

CATALOG NUMBER: HCC8S30D010BZ-HM82555840-81RWWC

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1866.3	1866.3	1866.3	1866.3	1866.3	1866.3	1866.3	1866.3	1866.3	1866.3	1866.3
2.5°	1861.3	1861.3	1858.8	1858.8	1858.8	1856.3	1858.8	1856.3	1856.3	1856.3	1858.8
5°	1851.4	1846.4	1846.4	1843.9	1843.9	1841.4	1843.9	1841.4	1838.9	1836.4	1838.9
7.5°	1831.4	1826.4	1823.9	1821.4	1821.4	1821.4	1818.9	1816.4	1818.9	1811.4	1816.4
10°	1804.0	1801.5	1796.6	1794.1	1791.6	1794.1	1791.6	1786.6	1786.6	1786.6	1784.1
12.5°	1769.1	1764.1	1761.6	1759.1	1754.1	1754.1	1756.6	1751.6	1751.6	1746.6	1746.6
15°	1726.8	1721.8	1716.8	1716.8	1711.8	1711.8	1709.3	1709.3	1706.8	1704.3	1704.3
17.5°	1674.5	1667.0	1662.0	1664.5	1662.0	1659.5	1659.5	1654.5	1652.0	1654.5	1654.5
20°	1612.2	1607.2	1602.2	1604.7	1599.7	1597.2	1599.7	1592.2	1594.7	1594.7	1594.7
22.5°	1542.4	1539.9	1532.4	1532.4	1527.4	1524.9	1527.4	1527.4	1529.9	1527.4	1527.4
25°	1465.1	1460.1	1455.2	1455.2	1452.7	1450.2	1452.7	1455.2	1452.7	1455.2	1455.2
27.5°	1382.9	1375.4	1375.4	1370.4	1370.4	1372.9	1370.4	1372.9	1375.4	1375.4	1380.4
30°	1293.2	1290.7	1288.2	1285.7	1285.7	1288.2	1288.2	1288.2	1290.7	1295.7	1295.7
32.5°	1208.5	1203.5	1198.5	1198.5	1203.5	1201.0	1203.5	1203.5	1208.5	1208.5	1213.5
35°	1116.2	1116.2	1111.4	1113.7	1113.7	1113.7	1113.7	1118.7	1123.7	1126.2	1131.2
37.5°	1031.6	1024.1	1026.6	1026.6	1029.1	1026.6	1034.1	1034.1	1039.1	1039.1	1044.1
40°	939.4	939.4	941.8	939.4	941.8	941.8	946.8	951.8	954.3	959.3	961.8
42.5°	852.2	857.2	852.2	854.7	857.2	859.6	862.1	864.6	874.6	879.6	887.0
45°	772.4	774.9	777.4	779.9	777.4	782.4	784.9	789.9	797.3	799.8	802.3
47.5°	695.2	697.7	700.2	702.7	702.7	707.7	710.2	715.1	720.1	722.6	725.1
50°	620.4	625.4	627.9	627.9	630.4	635.4	640.4	640.4	645.4	652.9	655.4
52.5°	553.1	553.1	558.1	560.6	563.1	563.1	570.6	573.1	575.6	580.6	585.6
55°	478.5	485.8	488.3	488.3	493.3	498.3	500.8	503.3	503.3	513.3	513.3
57.5°	413.7	416.2	421.1	421.1	421.1	428.5	428.5	433.5	436.0	438.5	443.5
60°	348.9	353.8	353.8	356.3	353.8	358.8	361.3	366.3	368.8	371.2	373.7
62.5°	289.0	289.0	291.5	291.5	291.5	291.5	296.5	296.5	301.5	304.0	306.5
65°	231.7	231.7	231.7	231.7	231.7	231.7	231.7	231.7	234.2	234.2	239.2
67.5°	179.4	176.9	171.9	174.4	171.9	171.9	169.4	169.4	171.9	171.9	176.9
70°	129.6	127.1	122.1	122.1	119.6	117.1	114.6	112.1	109.6	109.6	109.6
72.5°	84.8	79.8	72.3	69.8	69.8	64.8	59.8	57.3	57.3	57.3	57.3
75°	42.3	37.3	32.3	29.8	29.8	25.0	27.5	25.0	25.0	25.0	25.0
77.5°	17.5	12.5	10.0	10.0	10.0	7.5	7.5	7.5	7.5	7.5	7.5
80°	5.0	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
82.5°	2.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584293

CATALOG NUMBER: HCC8S30D010BZ-HM82555840-81RWWC

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1866.3	1866.3	1866.3	1866.3	1866.3	1866.3	1866.3	1866.3
2.5°	1856.3	1856.3	1851.4	1853.9	1853.9	1853.9	1853.9	1853.9
5°	1833.9	1836.4	1833.9	1836.4	1836.4	1833.9	1833.9	1833.9
7.5°	1811.4	1813.9	1811.4	1813.9	1813.9	1813.9	1811.4	1811.4
10°	1784.1	1784.1	1784.1	1784.1	1784.1	1781.6	1784.1	1784.1
12.5°	1746.6	1746.6	1746.6	1749.1	1749.1	1746.6	1746.6	1744.1
15°	1706.8	1701.8	1704.3	1706.8	1704.3	1704.3	1704.3	1704.3
17.5°	1652.0	1654.5	1652.0	1652.0	1652.0	1652.0	1654.5	1652.0
20°	1594.7	1594.7	1597.2	1594.7	1594.7	1594.7	1594.7	1592.2
22.5°	1529.9	1527.4	1527.4	1529.9	1529.9	1527.4	1529.9	1529.9
25°	1457.6	1460.1	1457.6	1457.6	1460.1	1460.1	1460.1	1457.6
27.5°	1380.4	1382.9	1385.4	1382.9	1382.9	1382.9	1385.4	1387.9
30°	1300.6	1305.6	1300.6	1300.6	1305.6	1303.1	1305.6	1305.6
32.5°	1216.0	1223.5	1218.5	1223.5	1223.5	1226.0	1223.5	1226.0
35°	1131.2	1138.7	1138.7	1138.7	1141.2	1143.7	1143.7	1141.2
37.5°	1051.6	1054.0	1054.0	1058.9	1061.4	1063.9	1063.9	1061.4
40°	969.3	974.3	976.8	976.8	976.8	981.8	986.8	981.8
42.5°	889.5	892.0	894.5	894.5	899.5	902.0	904.5	904.5
45°	812.3	817.3	819.8	822.3	824.8	829.7	827.3	832.2
47.5°	732.5	740.0	742.5	745.0	750.0	752.5	755.0	757.5
50°	660.3	665.2	665.2	670.2	677.7	677.7	682.7	685.2
52.5°	588.1	590.6	593.1	595.6	600.4	605.4	605.4	610.4
55°	518.3	520.8	520.8	523.3	525.8	535.8	538.3	538.3
57.5°	446.0	446.0	451.0	453.5	456.0	461.0	461.0	461.0
60°	376.2	378.7	378.7	381.2	383.7	388.7	391.2	388.7
62.5°	306.5	309.0	309.0	311.5	316.4	318.9	316.4	316.4
65°	241.7	244.2	244.2	246.7	251.7	251.7	249.2	251.7
67.5°	176.9	176.9	176.9	176.9	176.9	176.9	176.9	176.9
70°	112.1	109.6	107.1	109.6	109.6	109.6	107.1	112.1
72.5°	54.8	57.3	57.3	57.3	57.3	57.3	57.3	54.8
75°	25.0	25.0	22.5	22.5	22.5	25.0	25.0	22.5
77.5°	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5
80°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)