

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584149

Luminaire Tested: **HCC8S25D010BZ-HM82555835-81WWWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584149
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S25D010BZ-HM82555835-81WWWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2420.4 lumens
Efficiency: N/A
Efficacy: 90.3 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584149
CATALOG NUMBER: HCC8S25D010BZ-HM82555835-81WWWB

Luminous Intensity Polar Plot





TEST NUMBER: P584149

CATALOG NUMBER: HCC8S25D010BZ-HM82555835-81WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87					87			
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75					75			
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65					65			
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57					57			
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50					50			
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45					45			
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40					40			
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37					37			
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33					33			
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30					30			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	37108	37108	37108
5°	38467	36987	35718
10°	39553	36663	34255
15°	40438	36017	32741
20°	40497	34610	31411
25°	39723	32684	30302
30°	37675	30312	28970
35°	34234	27608	27672
40°	29929	24772	26081
45°	25943	22066	24303
50°	22715	19597	22139
55°	20220	17365	20037
60°	18237	15597	17608
65°	16468	13717	15345
70°	14795	11558	11405
75°	13034	9162	8554
80°	10921	7583	8186
85°	8491	6652	7253



TEST NUMBER: P584149
 CATALOG NUMBER: HCC8S25D010BZ-HM82555835-81WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.5	4.7
10°-20°	319.8	13.2
20°-30°	457.0	18.9
30°-40°	485.6	20.1
40°-50°	418.1	17.3
50°-60°	312.6	12.9
60°-70°	199.4	8.2
70°-80°	90.7	3.7
80°-90°	23.8	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	890.3	36.8
0°-40°	1375.8	56.8
0°-60°	2106.5	87.0
0°-90°	2420.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2420.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1203	1203	1203	1203	1203	
5°	1243	1226	1195	1164	1154	119
15°	1267	1224	1128	1051	1026	357
25°	1168	1094	961	902	891	534
35°	909	846	733	714	735	566
45°	595	562	506	520	557	462
55°	376	345	323	350	373	338
65°	226	200	188	197	210	225
75°	109	94	77	70	72	116
85°	24	20	19	20	20	29
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584149

CATALOG NUMBER: HCC8S25D010BZ-HM82555835-81WWWB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1203.4	1203.4	1203.4	1203.4	1203.4	1203.4	1203.4	1203.4	1203.4	1203.4	1203.4
2.5°	1225.7	1222.3	1224.0	1222.3	1224.0	1224.0	1220.5	1220.5	1220.5	1220.5	1215.4
5°	1242.7	1241.0	1241.0	1239.3	1237.6	1239.3	1237.6	1235.9	1232.4	1230.7	1225.7
7.5°	1253.0	1253.0	1253.0	1253.0	1251.3	1249.5	1247.8	1244.4	1241.0	1237.6	1234.1
10°	1263.2	1265.0	1263.2	1261.5	1259.8	1256.4	1254.7	1251.3	1246.1	1241.0	1237.6
12.5°	1268.4	1268.4	1266.7	1266.7	1263.2	1261.5	1256.4	1251.3	1246.1	1241.0	1232.4
15°	1266.7	1266.7	1265.0	1263.2	1258.1	1256.4	1253.0	1247.8	1239.3	1232.4	1224.0
17.5°	1256.4	1254.7	1251.3	1251.3	1244.4	1242.7	1239.3	1232.4	1224.0	1213.7	1203.4
20°	1234.1	1234.1	1232.4	1230.7	1224.0	1218.8	1215.4	1206.9	1200.0	1188.0	1177.7
22.5°	1203.4	1206.9	1203.4	1200.0	1191.4	1189.7	1184.6	1174.3	1164.1	1150.5	1138.5
25°	1167.5	1165.8	1164.1	1160.6	1153.9	1150.5	1143.6	1133.3	1123.1	1107.7	1094.0
27.5°	1121.4	1114.5	1114.5	1107.7	1102.5	1097.4	1094.0	1083.8	1070.1	1058.1	1041.0
30°	1058.1	1059.8	1051.3	1049.6	1041.0	1037.6	1030.7	1020.5	1008.6	994.9	981.2
32.5°	989.8	984.6	984.6	977.8	970.9	965.8	964.1	952.1	941.9	928.2	914.5
35°	909.4	909.4	904.3	902.5	895.7	892.3	887.1	880.3	868.4	856.4	846.2
37.5°	830.7	827.3	825.6	822.2	817.1	811.9	811.9	800.0	798.3	784.6	770.9
40°	743.5	747.0	743.5	738.4	736.8	733.4	731.7	724.8	719.7	707.7	699.1
42.5°	670.0	666.7	666.7	665.0	658.2	658.2	654.7	651.3	642.7	639.3	629.1
45°	594.9	598.2	593.2	594.9	588.1	588.1	588.1	581.2	574.4	569.2	562.4
47.5°	529.9	531.6	531.6	526.4	524.8	524.8	521.4	518.0	512.9	506.0	500.9
50°	473.5	475.2	471.8	470.1	466.6	464.9	464.9	458.1	454.8	447.9	444.5
52.5°	422.2	422.2	420.5	420.5	415.4	415.4	412.0	406.8	403.4	400.0	391.4
55°	376.1	376.1	374.4	372.7	372.7	367.5	365.8	360.7	357.3	350.4	345.3
57.5°	331.6	333.3	331.6	329.9	328.2	326.5	323.0	317.9	314.6	309.4	306.0
60°	295.7	295.7	294.0	292.3	288.9	287.2	285.5	282.1	276.9	273.5	268.4
62.5°	261.5	259.8	258.1	256.4	252.9	252.9	249.5	246.1	241.1	237.6	234.2
65°	225.7	225.7	224.0	224.0	222.2	218.8	217.1	215.4	208.5	206.8	200.0
67.5°	193.1	194.8	191.4	191.4	188.0	188.0	186.3	181.2	179.4	176.0	172.7
70°	164.1	164.1	164.1	162.4	159.0	157.3	155.6	152.2	150.4	147.0	143.6
72.5°	135.0	135.0	133.3	133.3	131.6	129.9	128.2	124.8	124.8	121.3	117.9
75°	109.4	109.4	107.6	105.9	104.3	104.3	102.6	100.9	97.5	95.8	94.1
77.5°	83.8	83.8	83.8	82.1	80.4	80.4	80.4	76.9	73.5	73.5	71.8
80°	61.5	61.5	59.8	59.8	58.1	58.1	58.1	56.4	54.7	53.0	51.3
82.5°	41.0	41.0	41.0	41.0	39.3	39.3	39.3	37.6	35.8	35.8	35.8
85°	24.0	24.0	24.0	24.0	22.3	22.3	22.3	22.3	22.3	20.5	20.5
87.5°	10.3	8.6	10.3	8.6	10.3	8.6	10.3	8.6	8.6	8.6	8.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584149

CATALOG NUMBER: HCC8S25D010BZ-HM82555835-81WWWB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1203.4	1203.4	1203.4	1203.4	1203.4	1203.4	1203.4	1203.4	1203.4	1203.4	1203.4
2.5°	1217.1	1215.4	1213.7	1212.0	1212.0	1210.3	1206.9	1205.1	1203.4	1201.7	1201.7
5°	1224.0	1222.3	1218.8	1215.4	1213.7	1210.3	1206.9	1203.4	1200.0	1194.9	1193.2
7.5°	1229.0	1224.0	1220.5	1213.7	1212.0	1208.6	1203.4	1198.3	1191.4	1184.6	1179.5
10°	1229.0	1222.3	1217.1	1208.6	1205.1	1201.7	1194.9	1186.3	1177.7	1170.9	1162.3
12.5°	1225.7	1217.1	1208.6	1200.0	1194.9	1189.7	1179.5	1170.9	1160.6	1150.5	1143.6
15°	1213.7	1203.4	1193.2	1182.9	1177.7	1170.9	1160.6	1148.8	1138.5	1128.2	1116.2
17.5°	1191.4	1181.2	1169.2	1157.3	1150.5	1145.3	1129.9	1121.4	1106.0	1095.7	1085.5
20°	1162.3	1150.5	1135.1	1123.1	1114.5	1109.4	1097.4	1082.1	1070.1	1054.7	1044.4
22.5°	1124.8	1109.4	1094.0	1082.1	1073.5	1066.7	1051.3	1035.9	1025.6	1012.0	1000.0
25°	1080.4	1065.0	1049.6	1032.4	1023.9	1017.1	1003.4	989.8	976.1	960.6	950.4
27.5°	1027.3	1010.3	996.6	981.2	972.6	962.4	947.1	933.4	919.7	909.4	895.7
30°	969.2	950.4	936.8	921.4	912.8	904.3	888.8	875.3	863.3	851.3	844.4
32.5°	899.1	885.4	871.8	856.4	849.6	844.4	829.0	815.3	801.8	791.5	786.3
35°	832.5	817.1	805.2	791.5	782.9	777.8	764.1	752.1	745.3	733.4	726.5
37.5°	762.4	750.4	736.8	723.1	718.0	712.8	702.6	690.6	680.3	671.7	668.3
40°	688.9	678.6	666.7	658.2	653.0	647.9	639.3	630.8	623.9	615.4	611.9
42.5°	618.8	611.9	601.7	591.5	586.4	584.6	574.4	567.5	564.1	560.7	557.3
45°	555.5	545.3	538.4	531.6	526.4	523.1	518.0	512.9	509.4	506.0	502.6
47.5°	494.0	485.5	478.6	473.5	468.3	466.6	463.2	458.1	454.8	454.8	454.8
50°	437.6	430.8	423.9	420.5	418.8	415.4	412.0	410.2	408.5	408.5	408.5
52.5°	388.0	381.2	376.1	372.7	372.7	369.3	365.8	364.1	364.1	364.1	364.1
55°	341.9	336.7	333.3	329.9	326.5	324.7	324.7	324.7	323.0	323.0	324.7
57.5°	300.9	297.5	292.3	288.9	287.2	287.2	285.5	283.8	285.5	287.2	288.9
60°	263.2	259.8	258.1	252.9	252.9	252.9	251.2	251.2	251.2	252.9	254.7
62.5°	229.1	227.4	224.0	222.2	220.5	220.5	218.8	218.8	218.8	218.8	220.5
65°	198.3	194.8	191.4	191.4	191.4	189.7	189.7	186.3	188.0	188.0	186.3
67.5°	169.3	165.9	164.1	162.4	160.7	160.7	159.0	157.3	155.6	155.6	155.6
70°	141.9	138.5	138.5	135.0	135.0	133.3	131.6	131.6	129.9	128.2	126.5
72.5°	114.5	112.8	111.1	109.4	109.4	109.4	107.6	105.9	104.3	102.6	99.2
75°	90.6	90.6	87.2	85.5	85.5	83.8	82.1	80.4	78.6	76.9	75.2
77.5°	70.1	68.4	64.9	63.2	63.2	63.2	61.5	59.8	58.1	56.4	54.7
80°	51.3	49.5	47.8	46.1	46.1	46.1	44.4	44.4	42.7	42.7	42.7
82.5°	34.2	34.2	32.5	32.5	32.5	32.5	30.8	30.8	30.8	30.8	30.8
85°	20.5	20.5	18.8	18.8	18.8	18.8	18.8	18.8	18.8	18.8	18.8
87.5°	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584149

CATALOG NUMBER: HCC8S25D010BZ-HM82555835-81WWWB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1203.4	1203.4	1203.4	1203.4	1203.4	1203.4	1203.4	1203.4	1203.4	1203.4	1203.4
2.5°	1198.3	1198.3	1194.9	1193.2	1191.4	1193.2	1189.7	1188.0	1186.3	1186.3	1184.6
5°	1188.0	1186.3	1179.5	1177.7	1176.0	1174.3	1170.9	1167.5	1164.1	1162.3	1160.6
7.5°	1174.3	1169.2	1162.3	1160.6	1158.9	1153.9	1148.8	1145.3	1140.2	1138.5	1135.1
10°	1155.6	1148.8	1143.6	1138.5	1135.1	1129.9	1124.8	1119.6	1112.8	1111.1	1106.0
12.5°	1133.3	1124.8	1114.5	1112.8	1107.7	1100.8	1094.0	1088.8	1083.8	1080.4	1075.2
15°	1106.0	1097.4	1087.2	1082.1	1077.0	1071.8	1063.3	1056.4	1051.3	1046.1	1041.0
17.5°	1073.5	1063.3	1054.7	1049.6	1046.1	1037.6	1030.7	1022.2	1017.1	1012.0	1006.9
20°	1034.2	1025.6	1013.7	1008.6	1006.9	1000.0	991.5	988.0	981.2	976.1	972.6
22.5°	989.8	981.2	970.9	967.5	960.6	957.2	948.7	945.3	941.9	936.8	935.1
25°	940.2	931.6	923.1	921.4	916.2	912.8	907.7	902.5	902.5	897.4	897.4
27.5°	888.8	880.3	873.5	870.1	868.4	865.0	859.9	858.1	856.4	854.7	854.7
30°	834.2	823.9	820.5	818.8	817.1	813.6	811.9	808.5	810.2	811.9	810.2
32.5°	776.1	772.6	765.8	762.4	764.1	762.4	759.0	762.4	760.7	764.1	765.8
35°	719.7	716.3	712.8	712.8	709.4	709.4	709.4	711.1	714.5	716.3	719.7
37.5°	665.0	659.9	658.2	656.4	658.2	658.2	658.2	661.6	665.0	668.3	673.5
40°	606.8	603.4	603.4	603.4	603.4	608.5	606.8	610.2	613.6	618.8	623.9
42.5°	552.1	552.1	553.8	553.8	553.8	553.8	557.3	562.4	567.5	572.7	577.8
45°	500.9	500.9	500.9	504.3	504.3	506.0	512.9	516.3	519.7	524.8	529.9
47.5°	453.0	453.0	454.8	456.4	458.1	461.5	464.9	470.1	475.2	478.6	483.7
50°	408.5	410.2	413.7	417.1	417.1	418.8	423.9	427.4	430.8	435.9	437.6
52.5°	365.8	369.3	372.7	374.4	376.1	379.5	381.2	386.3	388.0	393.1	394.8
55°	326.5	328.2	333.3	335.0	335.0	338.4	341.9	345.3	350.4	350.4	353.8
57.5°	290.6	292.3	295.7	297.5	295.7	300.9	302.6	306.0	307.7	311.2	312.9
60°	254.7	258.1	259.8	259.8	261.5	263.2	266.6	266.6	270.1	273.5	273.5
62.5°	220.5	222.2	224.0	225.7	227.4	225.7	230.8	230.8	234.2	235.9	239.4
65°	188.0	189.7	189.7	191.4	191.4	193.1	193.1	194.8	196.6	200.0	201.7
67.5°	155.6	155.6	155.6	157.3	155.6	157.3	157.3	159.0	159.0	162.4	164.1
70°	126.5	124.8	123.0	123.0	123.0	123.0	121.3	123.0	123.0	124.8	124.8
72.5°	97.5	95.8	94.1	92.3	92.3	90.6	88.9	90.6	90.6	92.3	92.3
75°	73.5	70.1	70.1	70.1	68.4	68.4	68.4	70.1	70.1	70.1	71.8
77.5°	54.7	54.7	53.0	53.0	53.0	54.7	54.7	56.4	56.4	56.4	56.4
80°	41.0	42.7	42.7	42.7	42.7	44.4	44.4	44.4	44.4	46.1	46.1
82.5°	30.8	30.8	30.8	30.8	32.5	32.5	32.5	32.5	32.5	32.5	32.5
85°	18.8	20.5	20.5	18.8	20.5	20.5	20.5	20.5	20.5	20.5	20.5
87.5°	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584149

CATALOG NUMBER: HCC8S25D010BZ-HM82555835-81WWWB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1203.4	1203.4	1203.4	1203.4	1203.4	1203.4	1203.4	1203.4
2.5°	1182.9	1182.9	1182.9	1182.9	1181.2	1181.2	1181.2	1179.5
5°	1157.3	1157.3	1157.3	1153.9	1155.6	1155.6	1152.2	1153.9
7.5°	1131.6	1129.9	1128.2	1128.2	1126.5	1124.8	1123.1	1124.8
10°	1102.5	1097.4	1097.4	1095.7	1095.7	1092.3	1092.3	1094.0
12.5°	1070.1	1066.7	1066.7	1065.0	1063.3	1061.5	1059.8	1059.8
15°	1037.6	1034.2	1032.4	1030.7	1029.0	1025.6	1027.3	1025.6
17.5°	1005.2	1000.0	1000.0	998.3	996.6	993.2	993.2	991.5
20°	967.5	965.8	962.4	964.1	962.4	958.9	957.2	957.2
22.5°	929.9	929.9	928.2	928.2	926.5	924.8	923.1	923.1
25°	894.0	892.3	894.0	894.0	888.8	888.8	888.8	890.6
27.5°	853.0	854.7	853.0	853.0	853.0	853.0	854.7	853.0
30°	811.9	811.9	811.9	813.6	817.1	815.3	815.3	813.6
32.5°	767.5	769.2	769.2	770.9	772.6	776.1	776.1	777.8
35°	723.1	726.5	728.2	726.5	731.7	731.7	735.1	735.1
37.5°	676.9	678.6	682.0	683.7	687.2	688.9	690.6	690.6
40°	627.3	634.2	635.9	637.6	642.7	642.7	644.5	647.9
42.5°	581.2	588.1	589.8	591.5	594.9	599.9	598.2	601.7
45°	536.7	541.8	543.6	545.3	550.4	552.1	552.1	557.3
47.5°	488.9	492.3	494.0	497.4	500.9	504.3	507.7	506.0
50°	441.1	446.2	449.6	451.3	456.4	458.1	459.8	461.5
52.5°	398.3	401.7	403.4	405.1	410.2	412.0	413.7	417.1
55°	357.3	359.0	362.4	360.7	365.8	367.5	369.3	372.7
57.5°	316.2	317.9	319.6	319.6	323.0	326.5	328.2	329.9
60°	276.9	280.3	282.1	282.1	282.1	285.5	285.5	285.5
62.5°	241.1	241.1	242.8	242.8	246.1	246.1	246.1	246.1
65°	203.4	205.1	206.8	206.8	210.3	208.5	212.0	210.3
67.5°	164.1	164.1	167.6	167.6	165.9	167.6	167.6	167.6
70°	124.8	124.8	126.5	126.5	126.5	126.5	126.5	126.5
72.5°	92.3	92.3	92.3	94.1	92.3	92.3	94.1	92.3
75°	71.8	71.8	71.8	71.8	71.8	71.8	71.8	71.8
77.5°	56.4	56.4	58.1	58.1	58.1	58.1	58.1	58.1
80°	46.1	46.1	46.1	46.1	47.8	46.1	46.1	46.1
82.5°	34.2	32.5	34.2	32.5	34.2	34.2	34.2	34.2
85°	20.5	20.5	20.5	20.5	20.5	20.5	20.5	20.5
87.5°	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)