

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584146

Luminaire Tested: **HCC8S25D010MB-HM82555835-81WDWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584146
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S25D010MB-HM82555835-81WDWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2815.2 lumens
Efficiency: N/A
Efficacy: 105.0 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.14
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584146
CATALOG NUMBER: HCC8S25D010MB-HM82555835-81WDWB

Luminous Intensity Polar Plot





TEST NUMBER: P584146
 CATALOG NUMBER: HCC8S25D010MB-HM82555835-81WDWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90																											
2	105	99	94	89	102	97	92	88	93	90	86	90	87	84	88	85	83	81																											
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73																											
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65																											
5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61	59																											
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	56	54																											
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	59	55	51	49																											
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45																											
9	67	55	48	43	65	55	48	43	54	47	43	53	47	43	52	47	43	41																											
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	49443
5°	49102
10°	48972
15°	50258
20°	54411
25°	58334
30°	57031
35°	47488
40°	29172
45°	20200
50°	15414
55°	10107
60°	6328
65°	4735
70°	4778
75°	5492
80°	6073
85°	5449



TEST NUMBER: P584146
 CATALOG NUMBER: HCC8S25D010MB-HM82555835-81WDWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.7	5.4
10°-20°	451.9	16.1
20°-30°	778.0	27.6
30°-40°	753.8	26.8
40°-50°	371.2	13.2
50°-60°	175.2	6.2
60°-70°	69.0	2.5
70°-80°	47.6	1.7
80°-90°	17.7	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1380.7	49.0
0°-40°	2134.4	75.8
0°-60°	2680.8	95.2
0°-90°	2815.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2815.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1603	
5°	1586	151
15°	1574	452
25°	1714	778
35°	1262	754
45°	463	371
55°	188	175
65°	65	69
75°	46	48
85°	15	18
90°	0	



TEST NUMBER: P584146
CATALOG NUMBER: HCC8S25D010MB-HM82555835-81WDWB

CANDELA DISTRIBUTION (FULL):

0°	
0°	1603.4
2.5°	1598.3
5°	1586.3
7.5°	1574.3
10°	1564.0
12.5°	1562.3
15°	1574.3
17.5°	1610.2
20°	1658.1
22.5°	1700.8
25°	1714.5
27.5°	1683.8
30°	1601.7
32.5°	1466.6
35°	1261.5
37.5°	979.5
40°	724.7
42.5°	562.4
45°	463.2
47.5°	389.7
50°	321.3
52.5°	252.9
55°	188.0
57.5°	136.7
60°	102.6
62.5°	80.4
65°	64.9
67.5°	56.4
70°	53.0
72.5°	49.5
75°	46.1
77.5°	41.0
80°	34.2
82.5°	25.7
85°	15.4
87.5°	6.8
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)