

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584154

Luminaire Tested: **HCC8S25D010MB-HM82555840-81NDH**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584154  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-2)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S25D010MB-HM82555840-81NDH  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2506.5 lumens  
Efficiency: N/A  
Efficacy: 93.5 lumens/watt  
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.57  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584154  
CATALOG NUMBER: HCC8S25D010MB-HM82555840-81NDH

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584154

CATALOG NUMBER: HCC8S25D010MB-HM82555840-81NDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95					95			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89					89			
3	104	99	94	91	102	97	93	90	95	91	88	92	90	87	90	88	86	84					84			
4	100	93	88	84	98	92	87	84	90	86	83	88	85	82	86	83	81	80					80			
5	96	88	83	79	94	87	82	79	86	81	78	84	80	77	82	79	77	75					75			
6	92	84	78	75	90	83	78	74	81	77	74	80	76	73	79	76	73	72					72			
7	88	80	74	70	87	79	74	70	78	73	70	77	73	70	76	72	69	68					68			
8	84	76	71	67	83	75	70	67	74	70	66	73	69	66	72	69	66	65					65			
9	81	72	67	64	80	72	67	63	71	66	63	70	66	63	69	66	63	62					62			
10	78	69	64	61	77	69	64	61	68	63	60	67	63	60	67	63	60	59					59			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	199449
5°	168975
10°	122602
15°	92069
20°	72643
25°	58596
30°	43422
35°	17595
40°	7423
45°	3982
50°	1785
55°	903
60°	574
65°	409
70°	334
75°	214
80°	320
85°	637



TEST NUMBER: P584154  
 CATALOG NUMBER: HCC8S25D010MB-HM82555840-81NDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	468.7	18.7
10°-20°	810.0	32.3
20°-30°	783.2	31.2
30°-40°	344.0	13.7
40°-50°	74.4	3.0
50°-60°	16.7	0.7
60°-70°	5.7	0.2
70°-80°	2.2	0.1
80°-90°	1.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2061.9	82.3
0°-40°	2405.8	96.0
0°-60°	2496.9	99.6
0°-90°	2506.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2506.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6468	
5°	5459	469
15°	2884	810
25°	1722	783
35°	467	344
45°	91	74
55°	17	17
65°	6	6
75°	2	2
85°	2	2
90°	0	



TEST NUMBER: P584154  
CATALOG NUMBER: HCC8S25D010MB-HM82555840-81NDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	6468.0
1°	6419.7
2°	6287.4
3°	6049.1
4°	5764.3
5°	5458.9
6°	5125.6
7°	4790.5
8°	4475.9
9°	4183.6
10°	3915.5
11°	3662.3
12°	3435.1
13°	3228.4
14°	3046.0
15°	2884.0
17.5°	2520.9
20°	2213.7
22.5°	1943.8
25°	1722.2
27.5°	1496.9
30°	1219.5
32.5°	828.5
35°	467.4
37.5°	275.5
40°	184.4
42.5°	130.3
45°	91.3
47.5°	59.6
50°	37.2
52.5°	22.4
55°	16.8
57.5°	13.1
60°	9.3
62.5°	7.5
65°	5.6
67.5°	3.7
70°	3.7
72.5°	1.8
75°	1.8
77.5°	1.8
80°	1.8
82.5°	1.8

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



TEST NUMBER: P584154  
CATALOG NUMBER: HCC8S25D010MB-HM82555840-81NDH

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



85°		1.8
87.5°		1.8

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)