

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584311

Luminaire Tested: **HCC8W30D010MB-HM82555927-81RWWH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584311
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W30D010MB-HM82555927-81RWWH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2479.4 lumens
Efficiency: N/A
Efficacy: 88.5 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584311
CATALOG NUMBER: HCC8W30D010MB-HM82555927-81RWWH

Luminous Intensity Polar Plot





TEST NUMBER: P584311

CATALOG NUMBER: HCC8W30D010MB-HM82555927-81RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88					88			
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77					77			
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67					67			
4	88	77	70	64	86	76	69	63	74	67	63	71	66	62	69	65	61	59					59			
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52					52			
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47					47			
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42					42			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38					38			
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	36	35					35			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32					32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	40781	40781	40781
5°	41550	40606	39665
10°	42196	39895	38213
15°	42622	38903	36556
20°	42460	37403	34873
25°	41339	35246	32925
30°	39370	32673	31010
35°	35551	29818	28805
40°	31233	26765	26692
45°	26964	23523	24543
50°	23473	20633	22005
55°	20811	17919	19171
60°	18570	15141	15912
65°	16738	12295	12550
70°	14867	9205	7429
75°	12808	5338	3205
80°	9856	1900	959
85°	6369	637	637



TEST NUMBER: P584311
 CATALOG NUMBER: HCC8W30D010MB-HM82555927-81RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.2	5.0
10°-20°	345.6	13.9
20°-30°	488.8	19.7
30°-40°	515.1	20.8
40°-50°	437.8	17.7
50°-60°	315.2	12.7
60°-70°	181.8	7.3
70°-80°	62.2	2.5
80°-90°	8.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	958.6	38.7
0°-40°	1473.7	59.4
0°-60°	2226.7	89.8
0°-90°	2479.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2479.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1322	1322	1322	1322	1322	
5°	1342	1333	1312	1288	1281	128
15°	1335	1294	1219	1165	1145	376
25°	1215	1152	1036	982	968	557
35°	944	889	792	764	765	588
45°	618	590	539	543	563	480
55°	387	357	333	346	357	348
65°	229	197	168	165	172	228
75°	108	81	45	29	27	113
85°	18	11	2	2	2	24
90°	0	0	0	0	0	



TEST NUMBER: P584311

CATALOG NUMBER: HCC8W30D010MB-HM82555927-81RWWH

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5
2.5°	1335.1	1336.9	1335.1	1335.1	1333.3	1331.6	1329.7	1327.9	1324.3	1320.7	1320.7
5°	1342.3	1345.8	1342.3	1342.3	1336.9	1333.3	1329.7	1324.3	1317.2	1311.8	1311.8
7.5°	1347.6	1347.6	1347.6	1342.3	1338.7	1333.3	1324.3	1315.4	1306.5	1297.4	1293.9
10°	1347.6	1347.6	1345.8	1338.7	1335.1	1324.3	1315.4	1302.8	1290.3	1277.7	1274.1
12.5°	1342.3	1344.0	1340.5	1333.3	1324.3	1311.8	1299.2	1283.2	1268.8	1254.4	1247.3
15°	1335.1	1333.3	1329.7	1320.7	1310.0	1293.9	1281.4	1263.4	1243.7	1225.7	1218.6
17.5°	1317.2	1317.2	1311.8	1302.8	1288.5	1270.6	1250.8	1231.2	1209.7	1190.0	1181.0
20°	1293.9	1293.9	1286.7	1275.9	1261.6	1238.3	1216.8	1193.5	1168.4	1148.7	1139.8
22.5°	1259.9	1261.6	1252.6	1240.1	1224.0	1197.1	1175.6	1146.9	1121.8	1098.5	1091.4
25°	1215.0	1218.6	1209.7	1197.1	1175.6	1152.3	1125.4	1098.5	1069.9	1046.6	1035.9
27.5°	1163.1	1164.9	1155.8	1143.3	1121.8	1096.7	1069.9	1041.2	1014.3	989.2	978.4
30°	1105.7	1098.5	1095.0	1078.8	1055.5	1034.1	1003.5	980.2	951.6	930.0	917.6
32.5°	1025.0	1028.6	1017.9	1005.3	987.5	962.4	937.3	910.4	883.5	867.4	858.5
35°	944.4	948.0	942.6	930.0	910.4	888.9	863.8	844.1	820.8	801.0	792.1
37.5°	860.2	860.2	856.6	849.4	835.2	815.4	790.3	770.6	750.9	734.8	729.3
40°	775.9	772.4	770.6	765.2	752.6	734.8	718.6	702.5	682.7	672.0	664.9
42.5°	693.5	693.5	690.0	684.6	672.0	663.1	646.9	629.0	614.7	603.9	603.9
45°	618.3	620.1	614.7	611.1	603.9	589.6	575.2	562.8	550.2	543.0	539.4
47.5°	551.9	551.9	546.6	543.0	535.9	523.3	510.8	500.0	491.1	485.7	483.8
50°	489.3	489.3	489.3	480.2	471.3	462.4	453.4	440.9	435.5	431.8	430.1
52.5°	435.5	433.6	433.6	426.5	417.6	406.8	397.8	387.1	381.7	378.1	379.9
55°	387.1	387.1	385.2	376.3	367.4	356.6	347.7	338.7	335.1	331.5	333.3
56°	367.4	367.4	365.6	358.4	347.7	338.7	327.9	319.0	313.7	315.4	315.4
57°	353.0	349.4	349.4	340.5	331.5	319.0	310.0	301.1	297.5	295.7	295.7
58°	335.1	333.3	331.5	322.6	313.7	302.8	293.9	284.9	279.5	279.5	277.8
59°	317.2	317.2	313.7	306.4	297.5	286.8	277.8	268.8	263.5	261.7	261.7
60°	301.1	302.8	297.5	290.4	283.1	270.6	259.8	252.7	247.3	245.5	245.5
61°	286.8	286.8	283.1	274.2	265.3	256.2	245.5	236.6	232.9	229.4	229.4
62°	274.2	270.6	268.8	259.8	250.9	240.2	231.1	222.2	216.9	213.3	215.1
63°	258.0	256.2	252.7	245.5	236.6	225.8	215.1	207.8	202.5	197.1	198.9
64°	245.5	243.7	238.4	231.1	222.2	211.5	200.7	193.6	190.0	184.5	182.7
65°	229.4	227.6	225.8	216.9	207.8	197.1	188.2	181.0	175.6	172.0	168.5
66°	215.1	216.9	213.3	206.1	195.4	186.3	173.8	166.7	163.1	157.7	154.1
67°	202.5	202.5	198.9	191.8	181.0	172.0	163.1	154.1	148.7	143.4	141.6
67.5°	195.4	195.4	191.8	182.7	175.6	164.9	155.9	148.7	141.6	138.0	134.4
68°	188.2	188.2	186.3	179.2	170.3	159.4	150.5	141.6	134.4	129.0	127.2
69°	175.6	177.4	173.8	166.7	157.7	147.0	138.0	130.8	123.7	118.3	114.7
70°	164.9	163.1	159.4	152.3	143.4	136.1	127.2	118.3	111.1	103.9	102.1
71°	150.5	150.5	147.0	141.6	132.6	123.7	114.7	107.5	100.4	91.4	89.7
72°	139.8	139.8	136.1	129.0	121.9	113.0	103.9	95.0	89.7	80.6	77.0
72.5°	132.6	134.4	130.8	123.7	116.5	105.7	98.6	91.4	82.4	75.3	71.7
73°	129.0	127.2	125.4	118.3	109.3	102.1	93.2	86.0	77.0	69.9	66.3



TEST NUMBER: P584311
 CATALOG NUMBER: HCC8W30D010MB-HM82555927-81RWWH

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
77.5°	80.6	80.6	78.8	71.7	64.6	57.3	50.2	43.0	35.8	28.7	25.1
80°	55.5	57.3	53.7	50.2	44.8	37.7	30.4	25.1	18.0	14.4	10.7
82.5°	35.8	35.8	34.0	30.4	26.9	21.5	18.0	12.6	8.9	7.1	5.4
85°	18.0	19.7	18.0	16.2	12.6	10.7	8.9	5.4	3.6	1.8	1.8
87.5°	7.1	7.1	7.1	5.4	5.4	3.6	1.8	1.8	1.8	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584311

CATALOG NUMBER: HCC8W30D010MB-HM82555927-81RWWH

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5
2.5°	1317.2	1317.2	1313.6	1311.8	1310.0	1308.3	1306.5	1304.6	1304.6	1306.5
5°	1306.5	1302.8	1295.7	1293.9	1288.5	1286.7	1283.2	1281.4	1283.2	1281.4
7.5°	1290.3	1283.2	1274.1	1270.6	1263.4	1259.9	1254.4	1254.4	1250.8	1252.6
10°	1268.8	1258.1	1247.3	1240.1	1234.8	1229.3	1225.7	1222.2	1220.4	1220.4
12.5°	1241.9	1229.3	1218.6	1207.9	1198.9	1195.3	1188.2	1188.2	1184.6	1182.8
15°	1211.5	1195.3	1182.8	1172.0	1164.9	1157.7	1152.3	1148.7	1145.1	1145.1
17.5°	1172.0	1157.7	1145.1	1132.6	1121.8	1116.5	1111.1	1105.7	1105.7	1102.1
20°	1129.0	1112.9	1102.1	1089.6	1080.6	1071.6	1064.5	1064.5	1060.9	1062.7
22.5°	1080.6	1060.9	1050.1	1041.2	1032.3	1025.0	1017.9	1017.9	1016.1	1014.3
25°	1026.8	1010.8	998.2	987.5	982.1	974.9	973.1	969.5	967.7	967.7
27.5°	969.5	956.9	940.9	935.5	928.3	924.7	924.7	922.9	919.3	921.1
30°	908.6	894.2	885.3	881.6	874.5	874.5	872.7	869.2	869.2	870.9
32.5°	849.4	835.2	827.9	826.1	819.0	819.0	817.2	819.0	819.0	820.8
35°	785.0	772.4	770.6	765.2	763.5	763.5	763.5	767.0	770.6	765.2
37.5°	724.0	715.1	709.7	707.8	709.7	709.7	711.5	716.8	715.1	713.3
40°	661.3	654.1	650.5	650.5	654.1	657.6	657.6	663.1	664.9	663.1
42.5°	598.5	593.2	593.2	595.0	598.5	600.3	605.7	611.1	612.9	614.7
45°	539.4	539.4	539.4	541.2	543.0	546.6	553.7	559.1	561.0	562.8
47.5°	482.0	480.2	485.7	487.5	492.8	494.6	500.0	507.1	508.9	510.8
50°	428.3	431.8	433.6	439.1	442.7	442.7	449.8	453.4	458.7	458.7
52.5°	378.1	383.5	385.2	390.7	392.5	394.3	397.8	403.2	406.8	406.8
55°	333.3	335.1	338.7	340.5	345.9	347.7	351.2	353.0	358.4	356.6
56°	313.7	317.2	319.0	322.6	326.1	327.9	331.5	333.3	337.0	338.7
57°	295.7	297.5	302.8	304.6	308.2	308.2	310.0	315.4	315.4	317.2
58°	277.8	281.3	283.1	284.9	288.6	290.4	293.9	295.7	297.5	295.7
59°	261.7	263.5	265.3	265.3	268.8	268.8	274.2	277.8	279.5	279.5
60°	245.5	245.5	247.3	249.1	252.7	254.4	254.4	258.0	258.0	258.0
61°	229.4	229.4	231.1	232.9	234.7	234.7	238.4	238.4	240.2	242.0
62°	215.1	213.3	213.3	215.1	215.1	218.7	220.4	222.2	224.0	222.2
63°	198.9	197.1	197.1	197.1	197.1	200.7	200.7	202.5	206.1	204.3
64°	181.0	181.0	181.0	181.0	182.7	182.7	186.3	188.2	190.0	191.8
65°	168.5	164.9	163.1	163.1	164.9	166.7	168.5	170.3	172.0	172.0
66°	154.1	150.5	148.7	148.7	148.7	148.7	152.3	152.3	155.9	155.9
67°	138.0	134.4	132.6	130.8	130.8	130.8	136.1	134.4	134.4	134.4
67.5°	132.6	127.2	125.4	123.7	121.9	125.4	123.7	125.4	125.4	123.7
68°	125.4	121.9	118.3	114.7	114.7	114.7	116.5	118.3	116.5	114.7
69°	111.1	109.3	103.9	100.4	98.6	100.4	98.6	100.4	98.6	100.4
70°	98.6	93.2	87.9	86.0	84.2	84.2	84.2	82.4	84.2	82.4
71°	86.0	80.6	75.3	71.7	69.9	69.9	68.1	69.9	68.1	69.9
72°	73.5	68.1	60.9	57.3	57.3	57.3	57.3	55.5	57.3	55.5
72.5°	68.1	60.9	55.5	52.0	50.2	50.2	50.2	50.2	48.4	50.2
73°	62.8	55.5	48.4	46.6	46.6	46.6	44.8	43.0	44.8	44.8



TEST NUMBER: P584311
 CATALOG NUMBER: HCC8W30D010MB-HM82555927-81RWWH

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
77.5°	21.5	16.2	14.4	14.4	14.4	14.4	14.4	14.4	12.6	12.6
80°	8.9	7.1	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4
82.5°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
85°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



74°	116.5	116.5	113.0	107.5	98.6	89.7	82.4	75.3	66.3	57.3	53.7
75°	107.5	105.7	102.1	96.8	89.7	80.6	73.5	64.6	57.3	48.4	44.8

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



74°	52.0	43.0	39.5	35.8	35.8	35.8	34.0	34.0	34.0	35.8
75°	41.3	34.0	30.4	26.9	28.7	26.9	28.7	26.9	26.9	26.9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)