

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584319

Luminaire Tested: **HCC8W30D010MW-HM82555927-81WWWB**

Issue Date: 10/21/2021

### Test Information

Test Method: LM-41-14  
 Report Number: P584319  
 TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Issue Date: 10/21/2021  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: HALO COMMERCIAL  
 Catalog Number: HCC8W30D010MW-HM82555927-81WWWB  
 Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM  
 Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER  
 Ballast/Driver: ELECTRONIC DRIVER

### Summary


Lumens per Lamp: N/A  
 Luminaire Lumens: 2536.7 lumens  
 Efficiency: N/A  
 Efficacy: 90.6 lumens/watt  
 Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18  
 Luminous Opening: Circular (Dia: 0.67' x H: 0')  
 CIE Type: Direct

Input Watts (W): 28  
 Input Voltage (V): NR  
 Input Current (A<sub>in</sub>): NR  
 Voltage Rise (V): NR  
 Power Factor: NR  
 Total Harmonic Distortion (THDi): NR  
 Frequency (hertz): 60  
 Stabilization Time: NR  
 Operation Time: NR  
 Ambient Temperature (°C): NR  
 Test Distance: 25 FT



TEST NUMBER: P584319  
CATALOG NUMBER: HCC8W30D010MW-HM82555927-81WWWB

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584319

CATALOG NUMBER: HCC8W30D010MW-HM82555927-81WWWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75								
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65								
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57								
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50								
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45								
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40								
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37								
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33								
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	38894	38894	38894
5°	40315	38764	37433
10°	41457	38426	35902
15°	42379	37750	34318
20°	42447	36274	32924
25°	41632	34255	31758
30°	39488	31768	30365
35°	35879	28933	29001
40°	31370	25960	27332
45°	27190	23126	25468
50°	23809	20542	23204
55°	21193	18204	20999
60°	19119	16349	18452
65°	17256	14374	16074
70°	15498	12117	11955
75°	13654	9603	8971
80°	11436	7956	8595
85°	8881	6970	7607



TEST NUMBER: P584319

CATALOG NUMBER: HCC8W30D010MW-HM82555927-81WWWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	119.0	4.7
10°-20°	335.1	13.2
20°-30°	478.9	18.9
30°-40°	508.9	20.1
40°-50°	438.2	17.3
50°-60°	327.6	12.9
60°-70°	208.9	8.2
70°-80°	95.1	3.7
80°-90°	24.9	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	933.1	36.8
0°-40°	1442.0	56.8
0°-60°	2207.7	87.0
0°-90°	2536.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2536.7	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1261	1261	1261	1261	1261	
5°	1302	1284	1252	1220	1209	125
15°	1328	1283	1182	1102	1075	374
25°	1224	1147	1007	946	933	560
35°	953	887	769	749	770	594
45°	624	589	530	545	584	485
55°	394	362	339	367	391	354
65°	236	210	197	206	220	236
75°	115	99	81	74	75	122
85°	25	22	20	22	22	30
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584319

CATALOG NUMBER: HCC8W30D010MW-HM82555927-81WWWB

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1261.3	1261.3	1261.3	1261.3	1261.3	1261.3	1261.3	1261.3	1261.3	1261.3	1261.3
2.5°	1284.5	1280.9	1282.7	1280.9	1282.7	1282.7	1279.1	1279.1	1279.1	1279.1	1273.8
5°	1302.4	1300.6	1300.6	1298.9	1297.1	1298.9	1297.1	1295.3	1291.7	1289.9	1284.5
7.5°	1313.3	1313.3	1313.3	1313.3	1311.5	1309.6	1307.8	1304.2	1300.6	1297.1	1293.5
10°	1324.0	1325.7	1324.0	1322.2	1320.4	1316.8	1315.0	1311.5	1306.0	1300.6	1297.1
12.5°	1329.3	1329.3	1327.5	1327.5	1324.0	1322.2	1316.8	1311.5	1306.0	1300.6	1291.7
15°	1327.5	1327.5	1325.7	1324.0	1318.6	1316.8	1313.3	1307.8	1298.9	1291.7	1282.7
17.5°	1316.8	1315.0	1311.5	1311.5	1304.2	1302.4	1298.9	1291.7	1282.7	1272.0	1261.3
20°	1293.5	1293.5	1291.7	1289.9	1282.7	1277.3	1273.8	1264.9	1257.6	1245.1	1234.4
22.5°	1261.3	1264.9	1261.3	1257.6	1248.7	1246.9	1241.6	1230.7	1220.0	1205.8	1193.2
25°	1223.6	1221.8	1220.0	1216.5	1209.3	1205.8	1198.5	1187.8	1177.0	1160.9	1146.6
27.5°	1175.2	1168.1	1168.1	1160.9	1155.6	1150.1	1146.6	1135.9	1121.5	1109.0	1091.0
30°	1109.0	1110.8	1101.8	1100.1	1091.0	1087.5	1080.3	1069.5	1057.0	1042.6	1028.4
32.5°	1037.3	1031.9	1031.9	1024.8	1017.5	1012.2	1010.4	997.9	987.1	972.8	958.5
35°	953.1	953.1	947.8	946.0	938.7	935.1	929.8	922.7	910.1	897.6	886.8
37.5°	870.7	867.1	865.4	861.8	856.3	851.0	851.0	838.5	836.7	822.3	808.0
40°	779.3	783.0	779.3	773.9	772.1	768.6	766.8	759.7	754.2	741.7	732.8
42.5°	702.3	698.7	698.7	696.9	689.7	689.7	686.2	682.6	673.6	670.0	659.3
45°	623.5	627.1	621.6	623.5	616.3	616.3	616.3	609.1	602.0	596.6	589.4
47.5°	555.4	557.2	557.2	551.8	550.0	550.0	546.5	542.8	537.4	530.3	524.9
50°	496.3	498.1	494.5	492.7	489.0	487.3	487.3	480.1	476.6	469.4	465.9
52.5°	442.5	442.5	440.8	440.8	435.3	435.3	431.7	426.4	422.8	419.2	410.2
55°	394.2	394.2	392.4	390.6	390.6	385.2	383.3	378.0	374.4	367.3	361.9
57.5°	347.5	349.3	347.5	345.8	344.0	342.2	338.6	333.3	329.6	324.2	320.7
60°	310.0	310.0	308.2	306.4	302.7	300.9	299.2	295.6	290.2	286.7	281.3
62.5°	274.1	272.3	270.5	268.7	265.1	265.1	261.6	258.0	252.7	249.0	245.4
65°	236.5	236.5	234.7	234.7	232.9	229.4	227.6	225.8	218.5	216.8	209.6
67.5°	202.5	204.3	200.7	200.7	197.0	197.0	195.2	189.9	188.1	184.5	181.0
70°	171.9	171.9	171.9	170.1	166.6	164.8	163.0	159.4	157.7	154.1	150.5
72.5°	141.5	141.5	139.7	139.7	137.9	136.1	134.4	130.8	130.8	127.2	123.7
75°	114.6	114.6	112.8	111.1	109.3	109.3	107.5	105.7	102.1	100.4	98.6
77.5°	87.7	87.7	87.7	86.0	84.2	84.2	84.2	80.6	77.0	77.0	75.3
80°	64.4	64.4	62.7	62.7	60.9	60.9	60.9	59.1	57.3	55.5	53.7
82.5°	43.0	43.0	43.0	43.0	41.3	41.3	41.3	39.4	37.6	37.6	37.6
85°	25.1	25.1	25.1	25.1	23.3	23.3	23.3	23.3	23.3	21.5	21.5
87.5°	10.7	8.9	10.7	8.9	10.7	8.9	10.7	8.9	8.9	8.9	8.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584319

CATALOG NUMBER: HCC8W30D010MW-HM82555927-81WWWB

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1261.3	1261.3	1261.3	1261.3	1261.3	1261.3	1261.3	1261.3	1261.3	1261.3	1261.3
2.5°	1275.6	1273.8	1272.0	1270.2	1270.2	1268.4	1264.9	1263.1	1261.3	1259.5	1259.5
5°	1282.7	1280.9	1277.3	1273.8	1272.0	1268.4	1264.9	1261.3	1257.6	1252.3	1250.5
7.5°	1288.2	1282.7	1279.1	1272.0	1270.2	1266.6	1261.3	1255.8	1248.7	1241.6	1236.2
10°	1288.2	1280.9	1275.6	1266.6	1263.1	1259.5	1252.3	1243.3	1234.4	1227.2	1218.2
12.5°	1284.5	1275.6	1266.6	1257.6	1252.3	1246.9	1236.2	1227.2	1216.5	1205.8	1198.5
15°	1272.0	1261.3	1250.5	1239.8	1234.4	1227.2	1216.5	1203.9	1193.2	1182.5	1169.9
17.5°	1248.7	1238.0	1225.4	1212.9	1205.8	1200.3	1184.2	1175.2	1159.2	1148.3	1137.6
20°	1218.2	1205.8	1189.6	1177.0	1168.1	1162.7	1150.1	1134.1	1121.5	1105.4	1094.6
22.5°	1178.8	1162.7	1146.6	1134.1	1125.0	1117.9	1101.8	1085.7	1075.0	1060.6	1048.1
25°	1132.3	1116.1	1100.1	1082.1	1073.2	1065.9	1051.7	1037.3	1023.0	1006.8	996.1
27.5°	1076.8	1058.8	1044.4	1028.4	1019.3	1008.6	992.5	978.2	963.8	953.1	938.7
30°	1015.8	996.1	981.8	965.6	956.7	947.8	931.6	917.3	904.7	892.2	885.0
32.5°	942.4	928.0	913.6	897.6	890.4	885.0	868.9	854.5	840.3	829.4	824.1
35°	872.5	856.3	843.8	829.4	820.5	815.2	800.8	788.3	781.1	768.6	761.4
37.5°	799.0	786.5	772.1	757.9	752.4	747.0	736.3	723.7	713.0	704.1	700.4
40°	722.0	711.3	698.7	689.7	684.4	679.0	670.0	661.1	654.0	644.9	641.3
42.5°	648.5	641.3	630.6	619.8	614.5	612.7	602.0	594.7	591.2	587.6	584.0
45°	582.3	571.6	564.3	557.2	551.8	548.2	542.8	537.4	533.9	530.3	526.7
47.5°	517.8	508.8	501.6	496.3	490.9	489.0	485.5	480.1	476.6	476.6	476.6
50°	458.6	451.5	444.3	440.8	439.0	435.3	431.7	429.9	428.2	428.2	428.2
52.5°	406.6	399.5	394.2	390.6	390.6	387.0	383.3	381.6	381.6	381.6	381.6
55°	358.4	352.9	349.3	345.8	342.2	340.4	340.4	340.4	338.6	338.6	340.4
57.5°	315.3	311.8	306.4	302.7	300.9	300.9	299.2	297.4	299.2	300.9	302.7
60°	275.8	272.3	270.5	265.1	265.1	265.1	263.4	263.4	263.4	265.1	266.9
62.5°	240.1	238.3	234.7	232.9	231.1	231.1	229.4	229.4	229.4	229.4	231.1
65°	207.8	204.3	200.7	200.7	200.7	198.9	198.9	195.2	197.0	197.0	195.2
67.5°	177.4	173.8	171.9	170.1	168.4	168.4	166.6	164.8	163.0	163.0	163.0
70°	148.7	145.1	145.1	141.5	141.5	139.7	137.9	137.9	136.1	134.4	132.6
72.5°	120.1	118.2	116.4	114.6	114.6	114.6	112.8	111.1	109.3	107.5	103.9
75°	95.0	95.0	91.3	89.5	89.5	87.7	86.0	84.2	82.4	80.6	78.8
77.5°	73.5	71.7	68.1	66.3	66.3	66.3	64.4	62.7	60.9	59.1	57.3
80°	53.7	52.0	50.2	48.4	48.4	48.4	46.6	46.6	44.8	44.8	44.8
82.5°	35.8	35.8	34.0	34.0	34.0	34.0	32.2	32.2	32.2	32.2	32.2
85°	21.5	21.5	19.7	19.7	19.7	19.7	19.7	19.7	19.7	19.7	19.7
87.5°	8.9	8.9	8.9	8.9	8.9	8.9	8.9	8.9	8.9	8.9	8.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584319

CATALOG NUMBER: HCC8W30D010MW-HM82555927-81WWWB

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1261.3	1261.3	1261.3	1261.3	1261.3	1261.3	1261.3	1261.3	1261.3	1261.3	1261.3
2.5°	1255.8	1255.8	1252.3	1250.5	1248.7	1250.5	1246.9	1245.1	1243.3	1243.3	1241.6
5°	1245.1	1243.3	1236.2	1234.4	1232.6	1230.7	1227.2	1223.6	1220.0	1218.2	1216.5
7.5°	1230.7	1225.4	1218.2	1216.5	1214.7	1209.3	1203.9	1200.3	1194.9	1193.2	1189.6
10°	1211.1	1203.9	1198.5	1193.2	1189.6	1184.2	1178.8	1173.4	1166.3	1164.5	1159.2
12.5°	1187.8	1178.8	1168.1	1166.3	1160.9	1153.8	1146.6	1141.2	1135.9	1132.3	1126.9
15°	1159.2	1150.1	1139.4	1134.1	1128.7	1123.2	1114.3	1107.2	1101.8	1096.4	1091.0
17.5°	1125.0	1114.3	1105.4	1100.1	1096.4	1087.5	1080.3	1071.3	1065.9	1060.6	1055.2
20°	1083.9	1075.0	1062.4	1057.0	1055.2	1048.1	1039.1	1035.5	1028.4	1023.0	1019.3
22.5°	1037.3	1028.4	1017.5	1014.0	1006.8	1003.3	994.4	990.7	987.1	981.8	980.0
25°	985.3	976.4	967.5	965.6	960.2	956.7	951.3	946.0	946.0	940.6	940.6
27.5°	931.6	922.7	915.5	911.8	910.1	906.5	901.1	899.4	897.6	895.8	895.8
30°	874.3	863.6	859.9	858.1	856.3	852.8	851.0	847.4	849.2	851.0	849.2
32.5°	813.4	809.8	802.6	799.0	800.8	799.0	795.4	799.0	797.2	800.8	802.6
35°	754.2	750.6	747.0	747.0	743.5	743.5	743.5	745.3	748.8	750.6	754.2
37.5°	696.9	691.5	689.7	688.0	689.7	689.7	689.7	693.3	696.9	700.4	705.9
40°	636.0	632.4	632.4	632.4	632.4	637.8	636.0	639.6	643.1	648.5	654.0
42.5°	578.7	578.7	580.5	580.5	580.5	580.5	584.0	589.4	594.7	600.2	605.6
45°	524.9	524.9	524.9	528.5	528.5	530.3	537.4	541.0	544.7	550.0	555.4
47.5°	474.8	474.8	476.6	478.3	480.1	483.7	487.3	492.7	498.1	501.6	507.0
50°	428.2	429.9	433.5	437.2	437.2	439.0	444.3	447.9	451.5	456.8	458.6
52.5°	383.3	387.0	390.6	392.4	394.2	397.7	399.5	404.9	406.6	412.1	413.9
55°	342.2	344.0	349.3	351.1	351.1	354.7	358.4	361.9	367.3	367.3	370.8
57.5°	304.5	306.4	310.0	311.8	310.0	315.3	317.1	320.7	322.5	326.0	327.8
60°	266.9	270.5	272.3	272.3	274.1	275.8	279.5	279.5	283.1	286.7	286.7
62.5°	231.1	232.9	234.7	236.5	238.3	236.5	241.8	241.8	245.4	247.2	250.8
65°	197.0	198.9	198.9	200.7	200.7	202.5	202.5	204.3	206.1	209.6	211.4
67.5°	163.0	163.0	163.0	164.8	163.0	164.8	164.8	166.6	166.6	170.1	171.9
70°	132.6	130.8	129.0	129.0	129.0	129.0	127.2	129.0	129.0	130.8	130.8
72.5°	102.1	100.4	98.6	96.8	96.8	95.0	93.2	95.0	95.0	96.8	96.8
75°	77.0	73.5	73.5	73.5	71.7	71.7	71.7	73.5	73.5	73.5	75.3
77.5°	57.3	57.3	55.5	55.5	55.5	57.3	57.3	59.1	59.1	59.1	59.1
80°	43.0	44.8	44.8	44.8	44.8	46.6	46.6	46.6	46.6	48.4	48.4
82.5°	32.2	32.2	32.2	32.2	34.0	34.0	34.0	34.0	34.0	34.0	34.0
85°	19.7	21.5	21.5	19.7	21.5	21.5	21.5	21.5	21.5	21.5	21.5
87.5°	8.9	8.9	8.9	8.9	8.9	8.9	8.9	8.9	8.9	8.9	8.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584319

CATALOG NUMBER: HCC8W30D010MW-HM82555927-81WWWB

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1261.3	1261.3	1261.3	1261.3	1261.3	1261.3	1261.3	1261.3
2.5°	1239.8	1239.8	1239.8	1239.8	1238.0	1238.0	1238.0	1236.2
5°	1212.9	1212.9	1212.9	1209.3	1211.1	1211.1	1207.5	1209.3
7.5°	1186.0	1184.2	1182.5	1182.5	1180.7	1178.8	1177.0	1178.8
10°	1155.6	1150.1	1150.1	1148.3	1148.3	1144.8	1144.8	1146.6
12.5°	1121.5	1117.9	1117.9	1116.1	1114.3	1112.5	1110.8	1110.8
15°	1087.5	1083.9	1082.1	1080.3	1078.5	1075.0	1076.8	1075.0
17.5°	1053.5	1048.1	1048.1	1046.2	1044.4	1040.9	1040.9	1039.1
20°	1014.0	1012.2	1008.6	1010.4	1008.6	1005.1	1003.3	1003.3
22.5°	974.6	974.6	972.8	972.8	971.1	969.3	967.5	967.5
25°	936.9	935.1	936.9	936.9	931.6	931.6	931.6	933.4
27.5°	894.0	895.8	894.0	894.0	894.0	894.0	895.8	894.0
30°	851.0	851.0	851.0	852.8	856.3	854.5	854.5	852.8
32.5°	804.4	806.1	806.1	808.0	809.8	813.4	813.4	815.2
35°	757.9	761.4	763.2	761.4	766.8	766.8	770.4	770.4
37.5°	709.5	711.3	714.8	716.6	720.2	722.0	723.7	723.7
40°	657.5	664.7	666.4	668.2	673.6	673.6	675.4	679.0
42.5°	609.1	616.3	618.0	619.8	623.5	628.9	627.1	630.6
45°	562.5	567.9	569.8	571.6	576.9	578.7	578.7	584.0
47.5°	512.3	515.9	517.8	521.4	524.9	528.5	532.1	530.3
50°	462.2	467.6	471.2	473.0	478.3	480.1	481.9	483.7
52.5°	417.5	421.0	422.8	424.6	429.9	431.7	433.5	437.2
55°	374.4	376.2	379.8	378.0	383.3	385.2	387.0	390.6
57.5°	331.5	333.3	335.1	335.1	338.6	342.2	344.0	345.8
60°	290.2	293.8	295.6	295.6	295.6	299.2	299.2	299.2
62.5°	252.7	252.7	254.4	254.4	258.0	258.0	258.0	258.0
65°	213.2	215.0	216.8	216.8	220.3	218.5	222.1	220.3
67.5°	171.9	171.9	175.6	175.6	173.8	175.6	175.6	175.6
70°	130.8	130.8	132.6	132.6	132.6	132.6	132.6	132.6
72.5°	96.8	96.8	96.8	98.6	96.8	96.8	98.6	96.8
75°	75.3	75.3	75.3	75.3	75.3	75.3	75.3	75.3
77.5°	59.1	59.1	60.9	60.9	60.9	60.9	60.9	60.9
80°	48.4	48.4	48.4	48.4	50.2	48.4	48.4	48.4
82.5°	35.8	34.0	35.8	34.0	35.8	35.8	35.8	35.8
85°	21.5	21.5	21.5	21.5	21.5	21.5	21.5	21.5
87.5°	8.9	8.9	8.9	8.9	8.9	8.9	8.9	8.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)