

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593625

Luminaire Tested: **HCC8W25D010BZ-HM82555850-81WDC**

Issue Date: 10/21/2021

### Test Information

Test Method: LM-41-14  
 Report Number: P593625  
 TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-7)  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Issue Date: 10/21/2021  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: HALO COMMERCIAL  
 Catalog Number: HCC8W25D010BZ-HM82555850-81WDC  
 Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, SPECULAR TRIM  
 Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT  
 CYLINDER  
 Ballast/Driver: ELECTRONIC DRIVER

### Summary


Lumens per Lamp: N/A  
 Luminaire Lumens: 3110.1 lumens  
 Efficiency: N/A  
 Efficacy: 116.0 lumens/watt  
 Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.05  
 Luminous Opening: Circular (Dia: 0.67' x H: 0')  
 CIE Type: Direct

Input Watts (W): 26.8  
 Input Voltage (V): NR  
 Input Current (A<sub>in</sub>): NR  
 Voltage Rise (V): NR  
 Power Factor: NR  
 Total Harmonic Distortion (THDi): NR  
 Frequency (hertz): 60  
 Stabilization Time: NR  
 Operation Time: NR  
 Ambient Temperature (°C): NR  
 Test Distance: 25 FT



TEST NUMBER: P593625  
CATALOG NUMBER: HCC8W25D010BZ-HM82555850-81WDC

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P593625

CATALOG NUMBER: HCC8W25D010BZ-HM82555850-81WDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100													100															
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92													92															
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84													84															
3	100	93	87	83	98	91	86	82	89	84	81	86	83	79	84	81	78	77													77															
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	71	70													70															
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64													64															
6	83	73	66	62	82	72	66	61	71	65	61	69	64	61	68	64	60	59													59															
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	63	59	55	54													54															
8	74	63	57	52	73	63	56	52	62	56	52	60	55	51	59	55	51	50													50															
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46													46															
10	66	55	49	45	65	55	49	45	54	48	44	53	48	44	52	48	44	43													43															

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	74618
5°	72612
10°	72061
15°	70986
20°	68833
25°	66269
30°	61902
35°	51226
40°	30931
45°	20828
50°	15011
55°	8559
60°	3768
65°	1350
70°	505
75°	214
80°	0
85°	0



TEST NUMBER: P593625  
 CATALOG NUMBER: HCC8W25D010BZ-HM82555850-81WDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	222.9	7.2
10°-20°	624.9	20.1
20°-30°	891.4	28.7
30°-40°	811.7	26.1
40°-50°	382.9	12.3
50°-60°	150.6	4.8
60°-70°	24.0	0.8
70°-80°	1.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1739.2	55.9
0°-40°	2550.9	82.0
0°-60°	3084.4	99.2
0°-90°	3110.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3110.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2420	
5°	2346	223
15°	2224	625
25°	1948	891
35°	1361	812
45°	478	383
55°	159	151
65°	18	24
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P593625  
CATALOG NUMBER: HCC8W25D010BZ-HM82555850-81WDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2419.8
2.5°	2388.3
5°	2345.8
7.5°	2321.7
10°	2301.4
12.5°	2268.0
15°	2223.6
17.5°	2168.0
20°	2097.6
22.5°	2023.6
25°	1947.7
27.5°	1855.2
30°	1738.5
32.5°	1581.1
35°	1360.8
37.5°	1051.6
40°	768.4
42.5°	590.6
45°	477.6
47.5°	392.5
50°	312.9
52.5°	235.1
55°	159.2
57.5°	99.9
60°	61.1
62.5°	37.0
65°	18.5
67.5°	9.3
70°	5.6
72.5°	1.8
75°	1.8
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)