

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593632

Luminaire Tested: **HCC8S25D010BZ-HM82555850-81WWBB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P593632  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S25D010BZ-HM82555850-81WWBB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2306.7 lumens  
Efficiency: N/A  
Efficacy: 86.1 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P593632  
CATALOG NUMBER: HCC8S25D010BZ-HM82555850-81WWBB

### Luminous Intensity Polar Plot





TEST NUMBER: P593632

CATALOG NUMBER: HCC8S25D010BZ-HM82555850-81WWBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77			
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67			
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59			
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53			
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47			
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43			
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39			
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35			
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	38185	38185	38185
5°	39764	38101	36498
10°	41094	37615	34716
15°	42133	36754	32917
20°	42217	35231	31283
25°	41503	33003	29662
30°	39285	30447	28279
35°	35815	27386	26547
40°	31144	24140	24515
45°	26719	20911	22441
50°	22821	18028	20158
55°	19999	15526	17515
60°	17811	13241	14727
65°	15804	10806	11747
70°	14020	8006	6672
75°	11688	4194	1990
80°	9199	1314	320
85°	6545	637	0



TEST NUMBER: P593632  
 CATALOG NUMBER: HCC8S25D010BZ-HM82555850-81WWBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	116.7	5.1
10°-20°	327.1	14.2
20°-30°	462.9	20.1
30°-40°	484.3	21.0
40°-50°	403.9	17.5
50°-60°	286.4	12.4
60°-70°	165.0	7.2
70°-80°	53.1	2.3
80°-90°	7.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	906.6	39.3
0°-40°	1390.9	60.3
0°-60°	2081.3	90.2
0°-90°	2306.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2306.7	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1238	1238	1238	1238	1238	
5°	1285	1268	1231	1194	1179	123
15°	1320	1266	1151	1061	1031	371
25°	1220	1129	970	892	872	557
35°	951	868	728	688	705	590
45°	613	563	480	485	515	475
55°	372	333	289	304	326	336
65°	217	181	148	148	161	216
75°	98	72	35	17	17	106
85°	18	9	2	0	0	23
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P593632

CATALOG NUMBER: HCC8S25D010BZ-HM82555850-81WWBB

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3
2.5°	1264.3	1262.4	1260.6	1262.4	1260.6	1262.4	1260.6	1260.6	1258.7	1256.8	1256.8
5°	1284.6	1282.8	1282.8	1282.8	1280.9	1279.1	1279.1	1277.3	1273.5	1271.7	1268.0
7.5°	1297.6	1299.4	1299.4	1299.4	1295.8	1295.8	1292.0	1288.4	1284.6	1280.9	1275.3
10°	1312.4	1312.4	1310.5	1308.7	1305.0	1303.2	1301.3	1297.6	1292.0	1284.6	1279.1
12.5°	1317.9	1317.9	1316.1	1312.4	1310.5	1308.7	1306.8	1301.3	1293.8	1284.6	1277.3
15°	1319.8	1316.1	1314.3	1312.4	1308.7	1303.2	1303.2	1295.8	1286.5	1275.3	1266.1
17.5°	1305.0	1306.8	1303.2	1299.4	1293.8	1290.2	1284.6	1279.1	1268.0	1255.0	1245.8
20°	1286.5	1284.6	1282.8	1277.3	1269.9	1268.0	1262.4	1253.2	1243.9	1229.1	1216.2
22.5°	1256.8	1255.0	1251.4	1247.6	1240.2	1236.5	1230.9	1219.8	1206.9	1192.1	1177.3
25°	1219.8	1216.2	1210.6	1203.2	1197.7	1193.9	1186.5	1175.4	1160.6	1143.9	1129.2
27.5°	1160.6	1166.2	1162.4	1151.3	1145.8	1138.4	1136.6	1121.8	1108.7	1092.1	1075.5
30°	1103.3	1103.3	1097.7	1092.1	1082.8	1077.3	1069.9	1058.8	1045.8	1025.5	1012.5
32.5°	1031.1	1029.2	1021.7	1019.9	1012.5	1001.4	999.6	984.7	971.8	957.0	940.3
35°	951.4	947.7	940.3	934.8	931.1	925.6	920.0	907.0	894.1	879.2	868.1
37.5°	860.7	860.7	858.9	849.7	845.9	842.2	836.6	823.7	816.3	801.5	790.4
40°	773.7	771.9	766.3	764.5	760.8	755.2	751.6	744.1	733.1	721.9	710.8
42.5°	688.5	690.5	683.1	684.9	677.5	673.8	672.0	660.8	655.3	644.1	634.9
45°	612.7	610.9	607.1	605.3	601.6	597.9	594.2	588.6	579.4	568.3	562.7
47.5°	542.4	536.8	536.8	535.0	533.1	525.7	523.9	518.3	512.7	501.6	494.2
50°	475.7	475.7	475.7	473.9	468.3	466.4	462.8	457.2	451.6	444.3	433.1
52.5°	422.0	422.0	422.0	420.2	412.8	411.0	409.1	401.7	394.3	388.7	381.3
55°	372.0	374.0	372.0	368.4	362.8	362.8	357.3	353.5	346.1	340.6	333.2
57.5°	329.5	329.5	325.8	323.9	320.3	318.4	314.7	310.9	301.7	296.2	286.9
60°	288.8	286.9	286.9	283.2	279.5	275.8	273.9	268.4	264.7	255.4	248.0
62.5°	251.8	251.8	248.0	248.0	240.6	240.6	238.8	233.3	227.7	218.4	214.7
65°	216.6	216.6	214.7	212.8	207.4	205.4	203.6	198.1	192.5	186.9	181.4
67.5°	185.1	185.1	181.4	179.5	175.8	174.0	170.3	166.6	161.0	155.5	149.9
70°	155.5	153.7	151.8	149.9	146.3	144.3	140.7	137.0	131.4	127.8	122.2
72.5°	125.8	125.8	124.0	120.3	118.4	116.6	114.8	111.1	105.5	99.9	96.3
75°	98.1	98.1	98.1	94.4	90.7	88.8	88.8	85.2	81.4	75.9	72.2
77.5°	75.9	74.0	72.2	72.2	68.5	66.7	64.7	62.9	57.4	55.5	51.8
80°	51.8	53.7	51.8	50.0	48.2	46.2	46.2	42.6	40.8	37.0	33.3
82.5°	35.2	33.3	33.3	31.5	31.5	29.6	29.6	25.9	24.1	22.3	20.3
85°	18.5	18.5	16.7	16.7	16.7	14.8	14.8	12.9	12.9	11.1	9.2
87.5°	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6	3.7	3.7	3.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P593632

CATALOG NUMBER: HCC8S25D010BZ-HM82555850-81WWBB

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3
2.5°	1255.0	1251.4	1249.4	1249.4	1247.6	1245.8	1243.9	1242.1	1238.3	1238.3	1234.7
5°	1264.3	1260.6	1258.7	1253.2	1249.4	1249.4	1242.1	1240.2	1234.7	1230.9	1227.3
7.5°	1271.7	1264.3	1258.7	1253.2	1249.4	1245.8	1238.3	1230.9	1223.5	1216.2	1212.4
10°	1271.7	1264.3	1255.0	1245.8	1242.1	1238.3	1229.1	1218.0	1208.8	1201.3	1192.1
12.5°	1268.0	1256.8	1245.8	1238.3	1230.9	1225.4	1214.3	1203.2	1192.1	1177.3	1169.8
15°	1256.8	1242.1	1230.9	1218.0	1212.4	1203.2	1193.9	1177.3	1164.3	1151.3	1142.1
17.5°	1234.7	1216.2	1203.2	1190.3	1181.0	1175.4	1160.6	1145.8	1131.0	1116.2	1105.1
20°	1201.3	1184.7	1169.8	1153.2	1145.8	1138.4	1119.9	1105.1	1090.2	1073.6	1062.5
22.5°	1160.6	1143.9	1123.6	1110.7	1099.5	1090.2	1073.6	1056.9	1042.2	1027.3	1012.5
25°	1110.7	1094.0	1075.5	1055.1	1047.7	1038.4	1019.9	1003.2	986.6	970.0	957.0
27.5°	1056.9	1034.7	1019.9	997.7	990.3	981.1	960.6	942.1	927.4	914.4	899.7
30°	992.2	975.5	955.2	934.8	927.4	918.2	901.5	884.8	870.0	855.1	840.4
32.5°	921.8	905.1	884.8	870.0	858.9	851.5	834.8	820.0	805.2	790.4	777.5
35°	847.8	829.2	814.5	799.6	790.4	781.1	764.5	751.6	740.4	727.5	714.5
37.5°	771.9	759.0	744.1	727.5	718.2	710.8	697.9	683.1	673.8	662.7	653.4
40°	697.9	683.1	670.0	655.3	647.9	642.3	629.4	618.2	609.0	599.7	594.2
42.5°	622.0	609.0	596.0	586.8	581.2	575.7	566.5	553.5	547.9	538.6	533.1
45°	551.6	540.5	531.3	518.3	514.6	510.9	499.8	490.5	484.9	479.5	475.7
47.5°	484.9	477.5	466.4	459.0	453.5	449.8	442.4	435.0	429.5	425.8	422.0
50°	427.6	418.4	411.0	403.5	399.9	394.3	386.9	383.2	379.4	375.8	375.8
52.5°	374.0	364.7	357.3	351.7	348.0	344.3	338.8	336.9	333.2	333.2	331.4
55°	323.9	318.4	310.9	303.6	301.7	299.9	296.2	292.4	290.6	288.8	290.6
57.5°	281.4	275.8	268.4	262.9	261.0	259.2	257.3	253.6	251.8	251.8	251.8
60°	242.5	236.9	231.3	225.9	225.9	222.1	220.3	218.4	216.6	214.7	214.7
62.5°	207.4	201.8	196.2	192.5	190.7	188.9	185.1	183.3	181.4	181.4	179.5
65°	175.8	168.4	166.6	161.0	159.2	157.3	155.5	151.8	149.9	148.1	146.3
67.5°	144.3	140.7	135.1	131.4	129.6	127.8	125.8	122.2	120.3	118.4	114.8
70°	116.6	112.9	109.2	105.5	103.7	101.8	98.1	94.4	92.6	88.8	83.2
72.5°	90.7	87.0	83.2	79.6	77.8	75.9	72.2	68.5	64.7	61.1	57.4
75°	68.5	64.7	59.3	55.5	53.7	53.7	48.2	44.4	40.8	35.2	31.5
77.5°	48.2	42.6	40.8	37.0	35.2	31.5	27.7	24.1	20.3	18.5	14.8
80°	31.5	27.7	24.1	22.3	20.3	18.5	16.7	12.9	9.2	7.4	5.6
82.5°	18.5	16.7	14.8	12.9	11.1	9.2	7.4	7.4	5.6	3.7	1.8
85°	9.2	7.4	5.6	5.6	3.7	3.7	3.7	1.8	1.8	1.8	1.8
87.5°	3.7	1.8	1.8	1.8	1.8	1.8	1.8	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P593632

CATALOG NUMBER: HCC8S25D010BZ-HM82555850-81WWBB

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3
2.5°	1232.9	1230.9	1229.1	1227.3	1227.3	1223.5	1223.5	1221.7	1218.0	1216.2	1216.2
5°	1221.7	1216.2	1212.4	1210.6	1208.8	1203.2	1201.3	1197.7	1193.9	1190.3	1188.3
7.5°	1205.0	1195.8	1192.1	1190.3	1184.7	1179.1	1175.4	1169.8	1164.3	1158.8	1156.9
10°	1184.7	1175.4	1166.2	1162.4	1156.9	1153.2	1145.8	1138.4	1132.8	1127.2	1121.8
12.5°	1158.8	1147.7	1138.4	1134.7	1129.2	1121.8	1110.7	1106.9	1097.7	1094.0	1086.6
15°	1129.2	1116.2	1106.9	1101.4	1095.8	1084.8	1077.3	1069.9	1060.7	1056.9	1049.6
17.5°	1092.1	1077.3	1068.1	1062.5	1058.8	1049.6	1038.4	1029.2	1019.9	1016.2	1010.7
20°	1047.7	1038.4	1025.5	1019.9	1016.2	1005.2	994.0	990.3	982.9	975.5	970.0
22.5°	997.7	988.5	975.5	970.0	968.1	958.8	949.6	944.1	938.5	932.9	927.4
25°	945.9	934.8	923.6	920.0	916.2	908.9	901.5	897.7	892.2	888.5	884.8
27.5°	890.3	879.2	870.0	864.5	860.7	855.1	851.5	847.8	844.1	840.4	838.6
30°	831.2	820.0	812.7	808.9	805.2	803.4	797.8	796.0	794.2	790.4	792.2
32.5°	771.9	762.6	755.2	749.6	749.6	746.0	744.1	744.1	742.3	742.3	742.3
35°	707.1	701.6	696.0	694.1	692.3	690.5	688.5	690.5	688.5	690.5	692.3
37.5°	647.9	642.3	638.6	636.8	634.9	636.8	634.9	634.9	636.8	640.5	642.3
40°	586.8	583.0	579.4	581.2	579.4	579.4	579.4	585.0	586.8	588.6	590.5
42.5°	529.4	525.7	523.9	523.9	525.7	523.9	527.5	529.4	533.1	538.6	542.4
45°	473.9	472.0	472.0	473.9	472.0	475.7	475.7	479.5	484.9	488.7	492.4
47.5°	422.0	422.0	422.0	423.9	423.9	425.8	429.5	431.3	435.0	438.7	442.4
50°	374.0	375.8	377.6	377.6	377.6	381.3	385.0	386.9	388.7	390.6	396.1
52.5°	331.4	333.2	333.2	335.0	336.9	338.8	340.6	344.3	346.1	349.9	351.7
55°	290.6	290.6	294.4	296.2	296.2	296.2	299.9	299.9	303.6	305.4	309.1
57.5°	251.8	253.6	253.6	255.4	255.4	257.3	259.2	261.0	262.9	264.7	266.5
60°	214.7	214.7	214.7	216.6	218.4	220.3	218.4	222.1	222.1	225.9	227.7
62.5°	179.5	181.4	181.4	181.4	181.4	181.4	181.4	183.3	185.1	186.9	188.9
65°	146.3	146.3	146.3	144.3	146.3	144.3	146.3	148.1	148.1	149.9	151.8
67.5°	112.9	112.9	109.2	109.2	111.1	111.1	111.1	111.1	109.2	112.9	112.9
70°	81.4	79.6	77.8	75.9	75.9	74.0	74.0	72.2	72.2	72.2	72.2
72.5°	53.7	50.0	46.2	44.4	42.6	42.6	38.8	37.0	38.8	38.8	38.8
75°	27.7	24.1	22.3	20.3	18.5	18.5	16.7	16.7	16.7	16.7	16.7
77.5°	11.1	9.2	7.4	7.4	5.6	5.6	5.6	5.6	5.6	5.6	5.6
80°	3.7	3.7	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8
82.5°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8
85°	1.8	0.0	0.0	1.8	0.0	1.8	1.8	1.8	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P593632

CATALOG NUMBER: HCC8S25D010BZ-HM82555850-81WWBB

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3
2.5°	1214.3	1214.3	1212.4	1214.3	1210.6	1212.4	1210.6	1210.6
5°	1186.5	1182.8	1182.8	1182.8	1181.0	1181.0	1179.1	1179.1
7.5°	1153.2	1151.3	1149.5	1147.7	1145.8	1143.9	1143.9	1143.9
10°	1119.9	1116.2	1116.2	1114.3	1110.7	1108.7	1108.7	1108.7
12.5°	1081.0	1079.2	1077.3	1077.3	1069.9	1071.7	1069.9	1069.9
15°	1044.0	1042.2	1042.2	1036.6	1032.9	1032.9	1032.9	1031.1
17.5°	1005.2	1003.2	1001.4	997.7	994.0	994.0	992.2	994.0
20°	964.4	962.6	958.8	958.8	957.0	955.2	951.4	953.3
22.5°	923.6	920.0	918.2	918.2	916.2	916.2	912.6	912.6
25°	881.1	879.2	877.4	879.2	875.6	875.6	871.8	871.8
27.5°	836.6	834.8	834.8	834.8	833.0	834.8	833.0	833.0
30°	792.2	792.2	790.4	790.4	792.2	790.4	792.2	794.2
32.5°	744.1	744.1	746.0	746.0	747.8	747.8	747.8	747.8
35°	694.1	697.9	697.9	699.7	701.6	703.4	703.4	705.2
37.5°	647.9	649.7	651.5	653.4	657.1	657.1	657.1	657.1
40°	597.9	599.7	603.5	601.6	609.0	610.9	609.0	609.0
42.5°	546.0	549.8	551.6	555.3	557.1	560.9	562.7	562.7
45°	498.0	499.8	503.4	507.2	509.0	514.6	514.6	514.6
47.5°	447.9	451.6	453.5	457.2	459.0	464.6	466.4	464.6
50°	399.9	403.5	407.2	407.2	412.8	414.6	418.4	420.2
52.5°	353.5	355.5	359.1	360.9	364.7	368.4	370.2	372.0
55°	309.1	310.9	314.7	314.7	320.3	322.1	325.8	325.8
57.5°	268.4	270.3	273.9	272.1	275.8	279.5	279.5	277.7
60°	229.5	229.5	229.5	233.3	235.1	236.9	238.8	238.8
62.5°	188.9	192.5	194.3	194.3	196.2	198.1	198.1	196.2
65°	151.8	155.5	157.3	157.3	159.2	159.2	159.2	161.0
67.5°	114.8	114.8	114.8	116.6	114.8	114.8	114.8	114.8
70°	72.2	72.2	72.2	72.2	70.3	72.2	72.2	74.0
72.5°	38.8	38.8	38.8	38.8	38.8	38.8	38.8	38.8
75°	16.7	16.7	16.7	18.5	16.7	16.7	16.7	16.7
77.5°	7.4	5.6	7.4	7.4	5.6	5.6	5.6	5.6
80°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8
82.5°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8
85°	0.0	1.8	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)