

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584334

Luminaire Tested: **HCC8W30D010MB-HM82555930-81WWBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584334
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W30D010MB-HM82555930-81WWBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2658.0 lumens
Efficiency: N/A
Efficacy: 94.9 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584334
CATALOG NUMBER: HCC8W30D010MB-HM82555930-81WWBB

Luminous Intensity Polar Plot





TEST NUMBER: P584334
 CATALOG NUMBER: HCC8W30D010MB-HM82555930-81WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77								
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67								
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59								
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47								
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43								
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39								
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	44003	44003	44003
5°	45821	43908	42060
10°	47353	43348	40007
15°	48550	42354	37926
20°	48645	40599	36048
25°	47824	38029	34184
30°	45267	35087	32584
35°	41273	31553	30593
40°	35890	27815	28246
45°	30788	24090	25860
50°	26294	20772	23228
55°	23053	17892	20182
60°	20525	15258	16966
65°	18212	12448	13542
70°	16157	9232	7700
75°	13475	4825	2276
80°	10601	1527	373
85°	7536	743	0



TEST NUMBER: P584334
 CATALOG NUMBER: HCC8W30D010MB-HM82555930-81WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.5	5.1
10°-20°	376.9	14.2
20°-30°	533.4	20.1
30°-40°	558.1	21.0
40°-50°	465.5	17.5
50°-60°	330.1	12.4
60°-70°	190.1	7.2
70°-80°	61.2	2.3
80°-90°	8.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1044.7	39.3
0°-40°	1602.8	60.3
0°-60°	2398.3	90.2
0°-90°	2658.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2658.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1427	1427	1427	1427	1427	
5°	1480	1461	1418	1376	1359	142
15°	1521	1459	1327	1222	1188	428
25°	1406	1301	1118	1028	1005	641
35°	1096	1000	838	794	813	680
45°	706	648	552	559	593	547
55°	429	384	333	350	375	387
65°	250	209	171	171	186	249
75°	113	83	40	19	19	123
85°	21	11	2	0	0	27
90°	0	0	0	0	0	



TEST NUMBER: P584334

CATALOG NUMBER: HCC8W30D010MB-HM82555930-81WWBB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1427.0	1427.0	1427.0	1427.0	1427.0	1427.0	1427.0	1427.0	1427.0	1427.0	1427.0
2.5°	1456.9	1454.7	1452.6	1454.7	1452.6	1454.7	1452.6	1452.6	1450.5	1448.3	1448.3
5°	1480.3	1478.2	1478.2	1478.2	1476.0	1473.9	1473.9	1471.7	1467.5	1465.3	1461.2
7.5°	1495.3	1497.4	1497.4	1497.4	1493.1	1493.1	1488.9	1484.6	1480.3	1476.0	1469.6
10°	1512.3	1512.3	1510.1	1508.0	1503.7	1501.6	1499.6	1495.3	1488.9	1480.3	1473.9
12.5°	1518.7	1518.7	1516.6	1512.3	1510.1	1508.0	1505.9	1499.6	1491.0	1480.3	1471.7
15°	1520.8	1516.6	1514.4	1512.3	1508.0	1501.6	1501.6	1493.1	1482.4	1469.6	1459.0
17.5°	1503.7	1505.9	1501.6	1497.4	1491.0	1486.7	1480.3	1473.9	1461.2	1446.2	1435.5
20°	1482.4	1480.3	1478.2	1471.7	1463.3	1461.2	1454.7	1444.0	1433.3	1416.3	1401.4
22.5°	1448.3	1446.2	1441.9	1437.6	1429.2	1424.9	1418.5	1405.6	1390.8	1373.7	1356.6
25°	1405.6	1401.4	1394.9	1386.5	1380.1	1375.8	1367.2	1354.5	1337.4	1318.2	1301.1
27.5°	1337.4	1343.8	1339.5	1326.7	1320.4	1311.8	1309.7	1292.6	1277.7	1258.4	1239.3
30°	1271.3	1271.3	1264.9	1258.4	1247.9	1241.4	1232.9	1220.0	1205.2	1181.7	1166.8
32.5°	1188.0	1185.9	1177.5	1175.3	1166.8	1153.9	1151.8	1134.8	1119.8	1102.8	1083.5
35°	1096.4	1092.1	1083.5	1077.1	1073.0	1066.5	1060.1	1045.1	1030.3	1013.1	1000.4
37.5°	991.9	991.9	989.7	979.0	974.7	970.6	964.2	949.2	940.6	923.6	910.8
40°	891.6	889.5	883.1	880.9	876.6	870.2	865.9	857.5	844.7	831.8	819.1
42.5°	793.5	795.6	787.1	789.3	780.7	776.4	774.3	761.4	755.1	742.3	731.6
45°	706.0	703.9	699.6	697.5	693.2	688.9	684.7	678.3	667.6	654.8	648.5
47.5°	624.9	618.5	618.5	616.5	614.4	605.8	603.7	597.2	590.8	578.1	569.5
50°	548.1	548.1	548.1	546.1	539.7	537.5	533.3	526.8	520.4	512.0	499.1
52.5°	486.3	486.3	486.3	484.2	475.7	473.6	471.4	462.9	454.3	447.9	439.5
55°	428.8	430.9	428.8	424.5	418.1	418.1	411.6	407.4	398.9	392.5	383.9
57.5°	379.6	379.6	375.4	373.2	369.1	366.9	362.6	358.4	347.7	341.2	330.7
60°	332.8	330.7	330.7	326.4	322.1	317.8	315.7	309.3	305.0	294.4	285.8
62.5°	290.1	290.1	285.8	285.8	277.3	277.3	275.1	268.7	262.4	251.7	247.4
65°	249.6	249.6	247.4	245.3	238.9	236.7	234.6	228.3	221.9	215.4	209.0
67.5°	213.3	213.3	209.0	206.9	202.6	200.5	196.2	192.0	185.6	179.2	172.8
70°	179.2	177.0	174.9	172.8	168.5	166.3	162.1	157.9	151.5	147.2	140.8
72.5°	145.1	145.1	142.9	138.6	136.5	134.4	132.2	127.9	121.6	115.2	110.9
75°	113.1	113.1	113.1	108.8	104.5	102.4	102.4	98.1	93.8	87.5	83.2
77.5°	87.5	85.4	83.2	83.2	78.9	76.8	74.7	72.5	66.1	64.0	59.7
80°	59.7	61.8	59.7	57.5	55.4	53.3	53.3	49.1	47.0	42.7	38.4
82.5°	40.5	38.4	38.4	36.3	36.3	34.1	34.1	29.8	27.7	25.6	23.4
85°	21.3	21.3	19.1	19.1	19.1	17.1	17.1	15.0	15.0	12.8	10.7
87.5°	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4	4.3	4.3	4.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584334

CATALOG NUMBER: HCC8W30D010MB-HM82555930-81WWBB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1427.0	1427.0	1427.0	1427.0	1427.0	1427.0	1427.0	1427.0	1427.0	1427.0	1427.0
2.5°	1446.2	1441.9	1439.8	1439.8	1437.6	1435.5	1433.3	1431.2	1427.0	1427.0	1422.8
5°	1456.9	1452.6	1450.5	1444.0	1439.8	1439.8	1431.2	1429.2	1422.8	1418.5	1414.2
7.5°	1465.3	1456.9	1450.5	1444.0	1439.8	1435.5	1427.0	1418.5	1409.9	1401.4	1397.1
10°	1465.3	1456.9	1446.2	1435.5	1431.2	1427.0	1416.3	1403.5	1392.9	1384.4	1373.7
12.5°	1461.2	1448.3	1435.5	1427.0	1418.5	1412.1	1399.2	1386.5	1373.7	1356.6	1348.1
15°	1448.3	1431.2	1418.5	1403.5	1397.1	1386.5	1375.8	1356.6	1341.7	1326.7	1316.1
17.5°	1422.8	1401.4	1386.5	1371.5	1360.8	1354.5	1337.4	1320.4	1303.3	1286.3	1273.4
20°	1384.4	1365.1	1348.1	1328.8	1320.4	1311.8	1290.4	1273.4	1256.3	1237.2	1224.3
22.5°	1337.4	1318.2	1294.7	1279.8	1267.0	1256.3	1237.2	1218.0	1200.9	1183.8	1166.8
25°	1279.8	1260.6	1239.3	1215.9	1207.3	1196.6	1175.3	1156.1	1136.9	1117.7	1102.8
27.5°	1218.0	1192.3	1175.3	1149.6	1141.2	1130.5	1107.1	1085.7	1068.7	1053.7	1036.7
30°	1143.3	1124.1	1100.7	1077.1	1068.7	1058.0	1038.8	1019.6	1002.6	985.4	968.4
32.5°	1062.3	1043.0	1019.6	1002.6	989.7	981.2	962.0	944.9	927.9	910.8	895.9
35°	976.9	955.6	938.5	921.5	910.8	900.2	880.9	865.9	853.2	838.2	823.4
37.5°	889.5	874.5	857.5	838.2	827.7	819.1	804.1	787.1	776.4	763.6	753.0
40°	804.1	787.1	772.1	755.1	746.6	740.2	725.2	712.4	701.7	691.0	684.7
42.5°	716.7	701.7	686.9	676.2	669.8	663.3	652.8	637.8	631.4	620.7	614.4
45°	635.6	622.8	612.2	597.2	593.0	588.7	576.0	565.3	558.8	552.4	548.1
47.5°	558.8	550.3	537.5	529.0	522.6	518.3	509.8	501.3	494.9	490.6	486.3
50°	492.7	482.0	473.6	465.0	460.7	454.3	445.8	441.5	437.3	433.0	433.0
52.5°	430.9	420.2	411.6	405.3	401.0	396.8	390.3	388.2	383.9	383.9	381.8
55°	373.2	366.9	358.4	349.8	347.7	345.5	341.2	337.0	334.9	332.8	334.9
57.5°	324.2	317.8	309.3	302.8	300.7	298.7	296.5	292.3	290.1	290.1	290.1
60°	279.4	273.0	266.6	260.3	260.3	256.0	253.9	251.7	249.6	247.4	247.4
62.5°	238.9	232.4	226.1	221.9	219.7	217.6	213.3	211.2	209.0	209.0	206.9
65°	202.6	194.2	192.0	185.6	183.5	181.3	179.2	174.9	172.8	170.6	168.5
67.5°	166.3	162.1	155.8	151.5	149.3	147.2	145.1	140.8	138.6	136.5	132.2
70°	134.4	130.1	125.8	121.6	119.5	117.4	113.1	108.8	106.7	102.4	96.0
72.5°	104.5	100.2	96.0	91.7	89.5	87.5	83.2	78.9	74.7	70.4	66.1
75°	78.9	74.7	68.2	64.0	61.8	61.8	55.4	51.2	47.0	40.5	36.3
77.5°	55.4	49.1	47.0	42.7	40.5	36.3	32.0	27.7	23.4	21.3	17.1
80°	36.3	32.0	27.7	25.6	23.4	21.3	19.1	15.0	10.7	8.6	6.4
82.5°	21.3	19.1	17.1	15.0	12.8	10.7	8.6	8.6	6.4	4.3	2.1
85°	10.7	8.6	6.4	6.4	4.3	4.3	4.3	2.1	2.1	2.1	2.1
87.5°	4.3	2.1	2.1	2.1	2.1	2.1	2.1	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584334

CATALOG NUMBER: HCC8W30D010MB-HM82555930-81WWBB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1427.0	1427.0	1427.0	1427.0	1427.0	1427.0	1427.0	1427.0	1427.0	1427.0	1427.0
2.5°	1420.6	1418.5	1416.3	1414.2	1414.2	1409.9	1409.9	1407.8	1403.5	1401.4	1401.4
5°	1407.8	1401.4	1397.1	1394.9	1392.9	1386.5	1384.4	1380.1	1375.8	1371.5	1369.4
7.5°	1388.6	1377.9	1373.7	1371.5	1365.1	1358.8	1354.5	1348.1	1341.7	1335.2	1333.1
10°	1365.1	1354.5	1343.8	1339.5	1333.1	1328.8	1320.4	1311.8	1305.4	1299.0	1292.6
12.5°	1335.2	1322.5	1311.8	1307.5	1301.1	1292.6	1279.8	1275.6	1264.9	1260.6	1252.1
15°	1301.1	1286.3	1275.6	1269.1	1262.7	1250.0	1241.4	1232.9	1222.2	1218.0	1209.5
17.5°	1258.4	1241.4	1230.7	1224.3	1220.0	1209.5	1196.6	1185.9	1175.3	1171.0	1164.6
20°	1207.3	1196.6	1181.7	1175.3	1171.0	1158.2	1145.5	1141.2	1132.6	1124.1	1117.7
22.5°	1149.6	1139.1	1124.1	1117.7	1115.5	1104.9	1094.2	1087.8	1081.4	1075.1	1068.7
25°	1090.0	1077.1	1064.4	1060.1	1055.8	1047.3	1038.8	1034.5	1028.1	1023.8	1019.6
27.5°	1026.0	1013.1	1002.6	996.1	991.9	985.4	981.2	976.9	972.6	968.4	966.3
30°	957.7	944.9	936.3	932.2	927.9	925.8	919.3	917.2	915.1	910.8	912.9
32.5°	889.5	878.8	870.2	863.9	863.9	859.6	857.5	857.5	855.4	855.4	855.4
35°	814.8	808.4	802.0	799.8	797.7	795.6	793.5	795.6	793.5	795.6	797.7
37.5°	746.6	740.2	735.9	733.7	731.6	733.7	731.6	731.6	733.7	738.0	740.2
40°	676.2	671.9	667.6	669.8	667.6	667.6	667.6	674.0	676.2	678.3	680.5
42.5°	610.1	605.8	603.7	603.7	605.8	603.7	607.9	610.1	614.4	620.7	624.9
45°	546.1	544.0	544.0	546.1	544.0	548.1	548.1	552.4	558.8	563.1	567.4
47.5°	486.3	486.3	486.3	488.4	488.4	490.6	494.9	497.0	501.3	505.6	509.8
50°	430.9	433.0	435.2	435.2	435.2	439.5	443.6	445.8	447.9	450.0	456.5
52.5°	381.8	383.9	383.9	386.1	388.2	390.3	392.5	396.8	398.9	403.2	405.3
55°	334.9	334.9	339.1	341.2	341.2	341.2	345.5	345.5	349.8	351.9	356.2
57.5°	290.1	292.3	292.3	294.4	294.4	296.5	298.7	300.7	302.8	305.0	307.1
60°	247.4	247.4	247.4	249.6	251.7	253.9	251.7	256.0	256.0	260.3	262.4
62.5°	206.9	209.0	209.0	209.0	209.0	209.0	209.0	211.2	213.3	215.4	217.6
65°	168.5	168.5	168.5	166.3	168.5	166.3	168.5	170.6	170.6	172.8	174.9
67.5°	130.1	130.1	125.8	125.8	127.9	127.9	127.9	127.9	125.8	130.1	130.1
70°	93.8	91.7	89.5	87.5	87.5	85.4	85.4	83.2	83.2	83.2	83.2
72.5°	61.8	57.5	53.3	51.2	49.1	49.1	44.8	42.7	44.8	44.8	44.8
75°	32.0	27.7	25.6	23.4	21.3	21.3	19.1	19.1	19.1	19.1	19.1
77.5°	12.8	10.7	8.6	8.6	6.4	6.4	6.4	6.4	6.4	6.4	6.4
80°	4.3	4.3	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1
82.5°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1
85°	2.1	0.0	0.0	2.1	0.0	2.1	2.1	2.1	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584334

CATALOG NUMBER: HCC8W30D010MB-HM82555930-81WWBB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1427.0	1427.0	1427.0	1427.0	1427.0	1427.0	1427.0	1427.0
2.5°	1399.2	1399.2	1397.1	1399.2	1394.9	1397.1	1394.9	1394.9
5°	1367.2	1363.0	1363.0	1363.0	1360.8	1360.8	1358.8	1358.8
7.5°	1328.8	1326.7	1324.5	1322.5	1320.4	1318.2	1318.2	1318.2
10°	1290.4	1286.3	1286.3	1284.1	1279.8	1277.7	1277.7	1277.7
12.5°	1245.7	1243.6	1241.4	1241.4	1232.9	1235.0	1232.9	1232.9
15°	1203.0	1200.9	1200.9	1194.5	1190.2	1190.2	1190.2	1188.0
17.5°	1158.2	1156.1	1153.9	1149.6	1145.5	1145.5	1143.3	1145.5
20°	1111.4	1109.2	1104.9	1104.9	1102.8	1100.7	1096.4	1098.5
22.5°	1064.4	1060.1	1058.0	1058.0	1055.8	1055.8	1051.6	1051.6
25°	1015.3	1013.1	1011.0	1013.1	1008.9	1008.9	1004.7	1004.7
27.5°	964.2	962.0	962.0	962.0	959.9	962.0	959.9	959.9
30°	912.9	912.9	910.8	910.8	912.9	910.8	912.9	915.1
32.5°	857.5	857.5	859.6	859.6	861.8	861.8	861.8	861.8
35°	799.8	804.1	804.1	806.3	808.4	810.5	810.5	812.7
37.5°	746.6	748.7	750.9	753.0	757.3	757.3	757.3	757.3
40°	688.9	691.0	695.3	693.2	701.7	703.9	701.7	701.7
42.5°	629.2	633.5	635.6	639.9	642.1	646.3	648.5	648.5
45°	573.8	576.0	580.2	584.4	586.5	593.0	593.0	593.0
47.5°	516.1	520.4	522.6	526.8	529.0	535.4	537.5	535.4
50°	460.7	465.0	469.3	469.3	475.7	477.7	482.0	484.2
52.5°	407.4	409.5	413.8	415.9	420.2	424.5	426.6	428.8
55°	356.2	358.4	362.6	362.6	369.1	371.1	375.4	375.4
57.5°	309.3	311.4	315.7	313.5	317.8	322.1	322.1	320.0
60°	264.6	264.6	264.6	268.7	270.9	273.0	275.1	275.1
62.5°	217.6	221.9	224.0	224.0	226.1	228.3	228.3	226.1
65°	174.9	179.2	181.3	181.3	183.5	183.5	183.5	185.6
67.5°	132.2	132.2	132.2	134.4	132.2	132.2	132.2	132.2
70°	83.2	83.2	83.2	83.2	81.1	83.2	83.2	85.4
72.5°	44.8	44.8	44.8	44.8	44.8	44.8	44.8	44.8
75°	19.1	19.1	19.1	21.3	19.1	19.1	19.1	19.1
77.5°	8.6	6.4	8.6	8.6	6.4	6.4	6.4	6.4
80°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1
82.5°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1
85°	0.0	2.1	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)