

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584326

Luminaire Tested: **HCC8S30D010MB-HM82555930-81PSMDW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584326  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-12)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S30D010MB-HM82555930-81PSMDW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" PLASTIC TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3172.2 lumens  
Efficiency: N/A  
Efficacy: 113.3 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.97  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584326  
CATALOG NUMBER: HCC8S30D010MB-HM82555930-81PSMDW

### Luminous Intensity Polar Plot





TEST NUMBER: P584326

CATALOG NUMBER: HCC8S30D010MB-HM82555930-81PSMDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89			89
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79			79
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71			71
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64			64
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58			58
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			53
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49			49
8	71	60	53	48	70	59	52	48	58	52	47	57	51	47	56	51	47	45			45
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42			42
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39			39

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	74460
5°	73491
10°	70800
15°	68030
20°	66149
25°	64156
30°	57572
35°	37742
40°	20868
45°	17396
50°	15865
55°	15139
60°	14080
65°	12762
70°	11531
75°	10425
80°	9483
85°	9057



TEST NUMBER: P584326  
 CATALOG NUMBER: HCC8S30D010MB-HM82555930-81PSMDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	223.1	7.0
10°-20°	601.2	19.0
20°-30°	855.6	27.0
30°-40°	633.3	20.0
40°-50°	313.7	9.9
50°-60°	250.4	7.9
60°-70°	173.8	5.5
70°-80°	93.7	3.0
80°-90°	27.6	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1679.9	53.0
0°-40°	2313.2	72.9
0°-60°	2877.2	90.7
0°-90°	3172.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3172.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2415	
5°	2374	223
15°	2131	601
25°	1886	856
35°	1003	633
45°	399	314
55°	282	250
65°	175	174
75°	88	94
85°	26	28
90°	0	



TEST NUMBER: P584326  
CATALOG NUMBER: HCC8S30D010MB-HM82555930-81PSMDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2414.7
2.5°	2404.0
5°	2374.2
7.5°	2327.2
10°	2261.1
12.5°	2192.9
15°	2131.0
17.5°	2071.2
20°	2015.8
22.5°	1960.3
25°	1885.6
27.5°	1776.8
30°	1616.9
32.5°	1371.6
35°	1002.6
37.5°	684.7
40°	518.4
42.5°	443.7
45°	398.9
47.5°	362.6
50°	330.7
52.5°	303.0
55°	281.6
57.5°	256.0
60°	228.3
62.5°	200.5
65°	174.9
67.5°	149.3
70°	127.9
72.5°	106.7
75°	87.5
77.5°	70.4
80°	53.4
82.5°	38.4
85°	25.6
87.5°	10.7
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)