

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584180

Luminaire Tested: **HCC8W25D010MW-HM82555927-81WDWB**

Issue Date: 10/21/2021

### Test Information

Test Method: LM-41-14  
 Report Number: P584180  
 TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-10)  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Issue Date: 10/21/2021  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: HALO COMMERCIAL  
 Catalog Number: HCC8W25D010MW-HM82555927-81WDWB  
 Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE BAFFLE TRIM  
 Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER  
 Ballast/Driver: ELECTRONIC DRIVER

### Summary


Lumens per Lamp: N/A  
 Luminaire Lumens: 2193.0 lumens  
 Efficiency: N/A  
 Efficacy: 81.8 lumens/watt  
 Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.14  
 Luminous Opening: Circular (Dia: 0.67' x H: 0')  
 CIE Type: Direct

Input Watts (W): 26.8  
 Input Voltage (V): NR  
 Input Current (A<sub>in</sub>): NR  
 Voltage Rise (V): NR  
 Power Factor: NR  
 Total Harmonic Distortion (THDi): NR  
 Frequency (hertz): 60  
 Stabilization Time: NR  
 Operation Time: NR  
 Ambient Temperature (°C): NR  
 Test Distance: 25 FT



TEST NUMBER: P584180  
CATALOG NUMBER: HCC8W25D010MW-HM82555927-81WDWB

### Luminous Intensity Polar Plot





TEST NUMBER: P584180  
 CATALOG NUMBER: HCC8W25D010MW-HM82555927-81WDWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									20
RC	80									50									30									10									0									
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																									
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90																												
2	105	99	94	89	102	97	92	88	93	90	86	90	87	84	88	85	83	81																												
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73																												
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65																												
5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61	59																												
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	56	54																												
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	59	55	51	49																												
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45																												
9	67	55	48	43	65	55	48	43	54	47	43	53	47	43	52	47	43	41																												
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38																												

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	38511
5°	38247
10°	38147
15°	39149
20°	42381
25°	45439
30°	44423
35°	36989
40°	22723
45°	15734
50°	12008
55°	7876
60°	4928
65°	3692
70°	3724
75°	4289
80°	4724
85°	4246



TEST NUMBER: P584180  
 CATALOG NUMBER: HCC8W25D010MW-HM82555927-81WDWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	117.4	5.4
10°-20°	352.0	16.1
20°-30°	606.0	27.6
30°-40°	587.1	26.8
40°-50°	289.2	13.2
50°-60°	136.5	6.2
60°-70°	53.8	2.5
70°-80°	37.1	1.7
80°-90°	13.8	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1075.4	49.0
0°-40°	1662.6	75.8
0°-60°	2088.2	95.2
0°-90°	2193.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2193.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1249	
5°	1236	117
15°	1226	352
25°	1336	606
35°	983	587
45°	361	289
55°	146	136
65°	51	54
75°	36	37
85°	12	14
90°	0	



TEST NUMBER: P584180  
CATALOG NUMBER: HCC8W25D010MW-HM82555927-81WDWB

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1248.9
2.5°	1244.9
5°	1235.6
7.5°	1226.3
10°	1218.3
12.5°	1216.9
15°	1226.3
17.5°	1254.3
20°	1291.5
22.5°	1324.8
25°	1335.5
27.5°	1311.5
30°	1247.6
32.5°	1142.4
35°	982.6
37.5°	762.9
40°	564.5
42.5°	438.1
45°	360.8
47.5°	303.6
50°	250.3
52.5°	197.1
55°	146.5
57.5°	106.5
60°	79.9
62.5°	62.6
65°	50.6
67.5°	44.0
70°	41.3
72.5°	38.6
75°	36.0
77.5°	32.0
80°	26.6
82.5°	20.0
85°	12.0
87.5°	5.4
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)