

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584187

Luminaire Tested: **HCC8W25D010BZ-HM82555930-81NDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584187
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W25D010BZ-HM82555930-81NDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2354.4 lumens
Efficiency: N/A
Efficacy: 87.9 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.27
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584187
CATALOG NUMBER: HCC8W25D010BZ-HM82555930-81NDC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584187

CATALOG NUMBER: HCC8W25D010BZ-HM82555930-81NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	99	98	97	96	96	94	93	91																
	1	115	112	110	108	112	110	108	106	106	105	103	102	101	100	99	98	97	96	96	94	93	92	90	89	87	87	85	83																
	2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91	91	89	88	86	85	83	82	81	80	76																
	3	106	101	97	93	104	99	96	93	97	94	91	95	92	90	92	90	89	87	87	85	84	82	81	80	77	75	73	68																
	4	102	96	91	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83	83	81	80	78	77	75	74	72	71	66																
	5	98	92	87	83	97	91	86	83	89	85	82	87	84	82	86	83	81	80	77	75	74	72	71	69	67	66	66	66																
	6	95	88	83	79	93	87	82	79	86	82	79	84	81	78	83	80	78	76	76	74	72	71	69	67	66	66	66	66	66															
	7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73	73	71	69	67	66	66	66	66	66	66	66															
	8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71	71	69	67	66	66	66	66	66	66	66	66															
	9	85	78	73	70	84	77	73	70	76	72	70	76	72	69	75	72	69	68	68	66	66	66	66	66	66	66	66	66	66															
	10	83	75	70	67	82	75	70	67	74	70	67	73	69	67	73	69	67	66	66	66	66	66	66	66	66	66	66	66	66															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	443152
5°	284245
10°	128404
15°	77477
20°	59041
25°	47678
30°	34937
35°	12652
40°	4722
45°	2141
50°	681
55°	172
60°	99
65°	117
70°	0
75°	0
80°	284
85°	566



TEST NUMBER: P584187
 CATALOG NUMBER: HCC8W25D010BZ-HM82555930-81NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	700.4	29.7
10°-20°	711.4	30.2
20°-30°	636.8	27.0
30°-40°	256.5	10.9
40°-50°	42.0	1.8
50°-60°	3.8	0.2
60°-70°	1.4	0.1
70°-80°	1.1	0.0
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2048.5	87.0
0°-40°	2305.0	97.9
0°-60°	2350.9	99.8
0°-90°	2354.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2354.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	14371	
5°	9183	700
15°	2427	711
25°	1401	637
35°	336	257
45°	49	42
55°	3	4
65°	2	1
75°	0	1
85°	2	2
90°	0	



TEST NUMBER: P584187
CATALOG NUMBER: HCC8W25D010BZ-HM82555930-81NDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	14371.1
0.5°	14326.7
1°	14141.2
1.5°	13843.2
2°	13391.5
2.5°	12857.2
3°	12188.3
3.5°	11454.4
4°	10728.4
4.5°	9915.2
5°	9182.8
5.5°	8385.5
6°	7738.8
6.5°	7065.1
7°	6535.7
7.5°	5976.1
8°	5525.9
8.5°	5074.0
9°	4734.9
9.5°	4360.8
10°	4100.8
12.5°	3024.5
15°	2426.9
17.5°	2073.3
20°	1799.2
22.5°	1580.4
25°	1401.3
27.5°	1222.2
30°	981.2
32.5°	630.9
35°	336.1
37.5°	185.4
40°	117.3
42.5°	77.7
45°	49.1
47.5°	30.1
50°	14.2
52.5°	4.7
55°	3.2
57.5°	1.6
60°	1.6
62.5°	1.6
65°	1.6



TEST NUMBER: P584187
CATALOG NUMBER: HCC8W25D010BZ-HM82555930-81NDC

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	1.6
80°	1.6
82.5°	1.6
85°	1.6
87.5°	1.6
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



67.5°		1.6
70°		0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)