

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584322

Luminaire Tested: **HCC8W30D010MW-HM82555930-81MDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584322
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W30D010MW-HM82555930-81MDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3159.3 lumens
Efficiency: N/A
Efficacy: 112.8 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.95
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584322
CATALOG NUMBER: HCC8W30D010MW-HM82555930-81MDW

Luminous Intensity Polar Plot





TEST NUMBER: P584322
 CATALOG NUMBER: HCC8W30D010MW-HM82555930-81MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									50									30									10									0									
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90																												
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80																												
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72																												
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65																												
5	86	76	68	63	84	75	68	63	73	67	62	71	66	62	69	65	61	59																												
6	81	70	63	58	79	69	62	57	67	61	57	66	61	56	64	60	56	54																												
7	76	65	58	53	74	64	57	53	63	57	52	62	56	52	60	55	52	50																												
8	72	61	54	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46																												
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43																												
10	64	53	46	42	63	53	46	42	52	46	42	51	46	42	50	45	42	40																												

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	80785
5°	78586
10°	73950
15°	70013
20°	67347
25°	64748
30°	57505
35°	36620
40°	20437
45°	17117
50°	15452
55°	14569
60°	13284
65°	11988
70°	10585
75°	9400
80°	8346
85°	7536



TEST NUMBER: P584322
 CATALOG NUMBER: HCC8W30D010MW-HM82555930-81MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	236.7	7.5
10°-20°	618.5	19.6
20°-30°	862.9	27.3
30°-40°	620.9	19.7
40°-50°	307.7	9.7
50°-60°	240.7	7.6
60°-70°	163.0	5.2
70°-80°	84.6	2.7
80°-90°	24.4	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1718.0	54.4
0°-40°	2338.9	74.0
0°-60°	2887.3	91.4
0°-90°	3159.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3159.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2620	
5°	2539	237
15°	2193	619
25°	1903	863
35°	973	621
45°	392	308
55°	271	241
65°	164	163
75°	79	85
85°	21	24
90°	0	



TEST NUMBER: P584322
CATALOG NUMBER: HCC8W30D010MW-HM82555930-81MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2619.8
2.5°	2596.3
5°	2538.8
7.5°	2457.7
10°	2361.7
12.5°	2272.1
15°	2193.1
17.5°	2118.4
20°	2052.3
22.5°	1986.2
25°	1903.0
27.5°	1783.5
30°	1615.0
32.5°	1350.5
35°	972.8
37.5°	663.5
40°	507.7
42.5°	437.3
45°	392.5
47.5°	354.1
50°	322.1
52.5°	294.4
55°	271.0
57.5°	243.2
60°	215.4
62.5°	187.7
65°	164.3
67.5°	140.8
70°	117.4
72.5°	98.1
75°	78.9
77.5°	61.8
80°	47.0
82.5°	34.1
85°	21.3
87.5°	10.7
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)