

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584332

Luminaire Tested: **HCC8W30D010MW-HM82555930-81WDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584332
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W30D010MW-HM82555930-81WDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3276.7 lumens
Efficiency: N/A
Efficacy: 117.0 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584332
CATALOG NUMBER: HCC8W30D010MW-HM82555930-81WDW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584332

CATALOG NUMBER: HCC8W30D010MW-HM82555930-81WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52			52
7	74	63	56	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48			48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44			44
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37			37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	65509
5°	65428
10°	64785
15°	64005
20°	63412
25°	62700
30°	59161
35°	48173
40°	26616
45°	17766
50°	15759
55°	14790
60°	14598
65°	14469
70°	13082
75°	11688
80°	10211
85°	9057



TEST NUMBER: P584332
 CATALOG NUMBER: HCC8W30D010MW-HM82555930-81WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	200.3	6.1
10°-20°	566.1	17.3
20°-30°	841.2	25.7
30°-40°	757.5	23.1
40°-50°	335.8	10.2
50°-60°	248.7	7.6
60°-70°	193.4	5.9
70°-80°	104.9	3.2
80°-90°	28.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1607.6	49.1
0°-40°	2365.1	72.2
0°-60°	2949.7	90.0
0°-90°	3276.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3276.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2124	
5°	2114	200
15°	2005	566
25°	1843	841
35°	1280	758
45°	407	336
55°	275	249
65°	198	193
75°	98	105
85°	26	29
90°	0	



TEST NUMBER: P584332
CATALOG NUMBER: HCC8W30D010MW-HM82555930-81WDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2124.4
2.5°	2120.1
5°	2113.7
7.5°	2096.7
10°	2069.0
12.5°	2036.9
15°	2004.9
17.5°	1972.9
20°	1932.4
22.5°	1891.9
25°	1842.8
27.5°	1768.2
30°	1661.5
32.5°	1508.0
35°	1279.7
37.5°	955.6
40°	661.2
42.5°	488.4
45°	407.4
47.5°	360.5
50°	328.5
52.5°	298.6
55°	275.1
57.5°	256.0
60°	236.7
62.5°	219.7
65°	198.3
67.5°	172.8
70°	145.1
72.5°	121.6
75°	98.1
77.5°	76.8
80°	57.5
82.5°	40.5
85°	25.6
87.5°	10.7
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)