

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584208

Luminaire Tested: **HCC8S25D010BZ-HM82555935-81RWWC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584208
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S25D010BZ-HM82555935-81RWWC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2269.9 lumens
Efficiency: N/A
Efficacy: 84.7 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.08 / 1.17
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584208
CATALOG NUMBER: HCC8S25D010BZ-HM82555935-81RWWC

Luminous Intensity Polar Plot





TEST NUMBER: P584208

CATALOG NUMBER: HCC8S25D010BZ-HM82555935-81RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	85	82	79	77								
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67								
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	69	65	61	59								
5	81	70	62	56	80	69	62	56	67	61	56	65	59	55	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	36828	36828	36828
5°	37315	36671	36328
10°	37697	36297	35749
15°	38076	35532	34820
20°	37882	34220	33439
25°	36998	32173	31738
30°	35147	29867	29753
35°	31994	27254	27492
40°	28049	24390	25292
45°	24199	21700	23222
50°	21190	19050	21036
55°	18774	16370	18515
60°	16911	13765	15344
65°	15242	11054	11747
70°	13371	8051	6473
75°	11402	4182	1704
80°	8772	1137	284
85°	5626	0	0



TEST NUMBER: P584208

CATALOG NUMBER: HCC8S25D010BZ-HM82555935-81RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.7	5.0
10°-20°	316.8	14.0
20°-30°	449.6	19.8
30°-40°	473.3	20.9
40°-50°	402.6	17.7
50°-60°	290.9	12.8
60°-70°	165.5	7.3
70°-80°	52.1	2.3
80°-90°	6.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	879.1	38.7
0°-40°	1352.4	59.6
0°-60°	2045.9	90.1
0°-90°	2269.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2269.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1194	1194	1194	1194	1194	
5°	1206	1199	1185	1177	1174	115
15°	1193	1162	1113	1092	1091	336
25°	1087	1033	946	930	933	498
35°	850	800	724	719	730	529
45°	555	534	498	510	532	431
55°	349	324	304	322	344	315
65°	209	180	152	150	161	207
75°	96	73	35	16	14	103
85°	16	10	0	0	0	21
90°	0	0	0	0	0	



TEST NUMBER: P584208

CATALOG NUMBER: HCC8S25D010BZ-HM82555935-81RWWC

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3
2.5°	1200.6	1202.3	1199.1	1199.1	1202.3	1199.1	1200.6	1200.6	1199.1	1199.1	1197.5
5°	1205.5	1203.9	1203.9	1203.9	1205.5	1202.3	1200.6	1202.3	1199.1	1199.1	1199.1
7.5°	1207.1	1207.1	1205.5	1203.9	1203.9	1203.9	1202.3	1200.6	1199.1	1195.9	1194.3
10°	1203.9	1203.9	1205.5	1202.3	1202.3	1199.1	1199.1	1195.9	1195.9	1192.7	1187.9
12.5°	1200.6	1199.1	1199.1	1195.9	1195.9	1192.7	1192.7	1187.9	1186.3	1181.6	1176.8
15°	1192.7	1191.1	1187.9	1186.3	1184.7	1183.2	1180.0	1178.4	1173.6	1167.3	1162.4
17.5°	1176.8	1175.2	1173.6	1170.4	1167.3	1165.7	1164.1	1159.2	1152.8	1148.1	1140.1
20°	1154.4	1152.8	1152.8	1148.1	1146.5	1141.7	1140.1	1133.8	1129.0	1119.3	1113.0
22.5°	1124.1	1125.7	1122.5	1119.3	1116.2	1111.4	1108.2	1101.9	1093.9	1084.3	1076.3
25°	1087.4	1089.0	1085.8	1082.7	1077.9	1074.7	1071.5	1062.0	1054.0	1042.8	1033.3
27.5°	1041.2	1041.2	1041.2	1038.0	1030.1	1028.5	1025.3	1015.8	1004.5	995.0	985.5
30°	987.1	985.5	985.5	980.7	977.4	971.1	966.3	958.3	950.4	939.1	928.0
32.5°	921.7	923.2	918.5	915.3	910.5	910.5	904.2	897.7	888.2	877.0	865.8
35°	849.9	851.5	848.3	846.7	838.8	837.2	835.6	827.5	821.2	813.2	800.5
37.5°	776.5	775.0	773.4	773.4	768.6	765.4	762.2	757.5	747.8	741.5	735.1
40°	696.8	696.8	696.8	695.2	693.7	690.5	688.9	685.7	679.2	672.9	668.1
42.5°	625.1	625.1	623.5	621.9	618.7	620.3	617.1	613.9	607.5	602.7	599.5
45°	554.9	554.9	554.9	556.5	553.3	548.5	548.5	545.4	542.2	539.0	534.1
47.5°	492.7	497.6	494.3	492.7	494.3	487.9	487.9	484.7	481.6	478.4	472.0
50°	441.7	441.7	441.7	438.5	436.9	436.9	432.2	429.0	427.4	424.1	417.7
52.5°	395.5	392.3	392.3	390.7	389.1	385.8	385.8	382.7	376.3	373.1	368.3
55°	349.2	349.2	347.6	346.0	344.4	342.8	341.2	336.4	333.3	328.5	323.7
57.5°	307.7	310.9	309.3	306.1	302.9	302.9	299.8	296.6	291.8	287.0	282.3
60°	274.2	272.6	272.6	271.0	267.9	266.3	264.7	259.9	255.1	250.4	245.6
62.5°	239.1	239.1	239.1	236.0	232.8	231.2	229.6	226.4	220.1	215.3	212.1
65°	208.9	207.3	205.7	204.0	202.6	199.3	197.7	194.5	189.7	185.0	180.2
67.5°	178.6	177.0	177.0	175.4	170.7	169.1	169.1	164.2	159.4	154.7	149.9
70°	148.3	148.3	148.3	145.1	143.5	141.9	140.3	137.2	132.4	127.5	122.7
72.5°	122.7	121.2	121.2	119.6	114.8	113.2	111.6	108.4	103.7	100.5	97.3
75°	95.7	95.7	94.1	92.4	90.8	89.3	87.7	84.5	79.7	74.9	73.4
77.5°	73.4	71.8	71.8	70.2	67.0	65.4	65.4	62.2	57.4	54.2	51.0
80°	49.4	51.0	49.4	47.8	46.2	44.6	43.0	41.4	38.3	35.1	31.9
82.5°	30.3	31.9	30.3	30.3	28.7	27.1	27.1	24.0	22.4	20.8	19.2
85°	15.9	15.9	15.9	15.9	14.3	14.3	14.3	12.7	11.1	9.5	9.5
87.5°	4.8	6.4	4.8	4.8	4.8	4.8	4.8	4.8	3.2	3.2	3.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584208

CATALOG NUMBER: HCC8S25D010BZ-HM82555935-81RWWC

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3
2.5°	1199.1	1197.5	1195.9	1195.9	1195.9	1195.9	1195.9	1194.3	1192.7	1192.7	1192.7
5°	1195.9	1195.9	1195.9	1194.3	1192.7	1192.7	1189.5	1187.9	1186.3	1184.7	1183.2
7.5°	1192.7	1189.5	1187.9	1186.3	1184.7	1184.7	1181.6	1178.4	1178.4	1175.2	1172.0
10°	1183.2	1181.6	1178.4	1175.2	1173.6	1172.0	1168.8	1164.1	1162.4	1159.2	1156.0
12.5°	1172.0	1168.8	1165.7	1159.2	1157.6	1156.0	1149.7	1144.9	1141.7	1140.1	1132.2
15°	1157.6	1151.2	1146.5	1138.5	1136.9	1133.8	1129.0	1124.1	1117.8	1113.0	1109.8
17.5°	1132.2	1125.7	1117.8	1109.8	1106.6	1106.6	1098.7	1092.3	1084.3	1081.1	1074.7
20°	1101.9	1093.9	1087.4	1077.9	1073.1	1068.4	1063.6	1054.0	1047.6	1042.8	1034.9
22.5°	1066.8	1055.6	1047.6	1038.0	1030.1	1025.3	1017.4	1009.3	1001.4	996.6	990.2
25°	1022.1	1012.5	999.8	990.2	985.5	979.0	969.5	961.5	953.6	945.6	942.3
27.5°	972.6	959.9	948.8	937.6	932.8	928.0	916.9	907.3	900.9	892.9	889.7
30°	918.5	905.8	892.9	883.4	878.6	870.7	864.2	853.1	845.1	838.8	830.7
32.5°	856.3	846.7	835.6	821.2	818.0	811.6	802.1	797.3	787.7	782.9	776.5
35°	789.3	782.9	771.8	760.6	755.8	752.6	744.6	735.1	728.7	724.0	720.8
37.5°	725.6	717.5	706.4	698.4	695.2	690.5	680.8	676.1	669.7	666.5	660.2
40°	657.0	649.0	641.0	636.2	631.4	628.3	621.9	617.1	610.8	605.9	604.3
42.5°	590.0	585.2	578.9	572.4	570.8	566.0	562.9	558.1	553.3	551.7	546.9
45°	529.4	524.6	518.2	511.9	510.3	507.1	505.5	500.7	497.6	497.6	497.6
47.5°	468.8	464.1	457.6	454.4	456.0	449.6	449.6	448.1	444.9	444.9	446.5
50°	414.6	408.2	406.6	403.4	400.2	397.1	398.7	393.9	393.9	397.1	395.5
52.5°	363.6	357.2	355.6	352.4	350.9	350.9	349.2	349.2	347.6	349.2	349.2
55°	317.4	312.5	309.3	306.1	304.5	304.5	304.5	302.9	301.4	304.5	306.1
57.5°	275.8	274.2	271.0	266.3	264.7	263.1	261.5	261.5	261.5	261.5	263.1
60°	239.1	236.0	232.8	228.0	228.0	226.4	224.8	223.2	223.2	223.2	223.2
62.5°	207.3	202.6	197.7	194.5	192.9	191.3	189.7	186.6	186.6	186.6	186.6
65°	175.4	170.7	167.5	164.2	161.0	161.0	157.8	156.2	153.1	151.5	148.3
67.5°	145.1	141.9	138.8	134.0	132.4	130.8	127.5	125.9	121.2	119.6	118.0
70°	118.0	113.2	110.0	106.8	105.3	102.1	98.9	95.7	92.4	89.3	86.1
72.5°	92.4	87.7	84.5	81.3	78.1	78.1	73.4	70.2	65.4	62.2	57.4
75°	68.6	63.8	60.6	55.9	54.2	52.6	47.8	44.6	39.9	35.1	31.9
77.5°	46.2	43.0	39.9	35.1	31.9	31.9	27.1	24.0	20.8	15.9	14.3
80°	28.7	25.5	22.4	19.2	19.2	15.9	14.3	11.1	8.0	6.4	4.8
82.5°	15.9	14.3	12.7	9.5	9.5	8.0	6.4	4.8	3.2	1.6	1.6
85°	8.0	6.4	4.8	4.8	3.2	3.2	3.2	1.6	1.6	0.0	0.0
87.5°	3.2	1.6	1.6	1.6	1.6	1.6	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584208

CATALOG NUMBER: HCC8S25D010BZ-HM82555935-81RWWC

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3
2.5°	1191.1	1191.1	1189.5	1189.5	1189.5	1187.9	1189.5	1187.9	1187.9	1187.9	1189.5
5°	1184.7	1181.6	1181.6	1180.0	1180.0	1178.4	1180.0	1178.4	1176.8	1175.2	1176.8
7.5°	1172.0	1168.8	1167.3	1165.7	1165.7	1165.7	1164.1	1162.4	1164.1	1159.2	1162.4
10°	1154.4	1152.8	1149.7	1148.1	1146.5	1148.1	1146.5	1143.3	1143.3	1143.3	1141.7
12.5°	1132.2	1129.0	1127.4	1125.7	1122.5	1122.5	1124.1	1120.9	1120.9	1117.8	1117.8
15°	1105.0	1101.9	1098.7	1098.7	1095.5	1095.5	1093.9	1093.9	1092.3	1090.7	1090.7
17.5°	1071.5	1066.8	1063.6	1065.2	1063.6	1062.0	1062.0	1058.8	1057.2	1058.8	1058.8
20°	1031.7	1028.5	1025.3	1026.9	1023.7	1022.1	1023.7	1019.0	1020.5	1020.5	1020.5
22.5°	987.1	985.5	980.7	980.7	977.4	975.8	977.4	977.4	979.0	977.4	977.4
25°	937.6	934.4	931.2	931.2	929.6	928.0	929.6	931.2	929.6	931.2	931.2
27.5°	885.0	880.2	880.2	877.0	877.0	878.6	877.0	878.6	880.2	880.2	883.4
30°	827.5	825.9	824.4	822.8	822.8	824.4	824.4	824.4	825.9	829.1	829.1
32.5°	773.4	770.2	767.0	767.0	770.2	768.6	770.2	770.2	773.4	773.4	776.5
35°	714.3	714.3	711.1	712.7	712.7	712.7	712.7	715.9	719.1	720.8	724.0
37.5°	660.2	655.4	657.0	657.0	658.6	657.0	661.7	661.7	664.9	664.9	668.1
40°	601.1	601.1	602.7	601.1	602.7	602.7	605.9	609.2	610.8	613.9	615.5
42.5°	545.4	548.5	545.4	546.9	548.5	550.1	551.7	553.3	559.7	562.9	567.6
45°	494.3	495.9	497.6	499.0	497.6	500.7	502.3	505.5	510.3	511.9	513.5
47.5°	444.9	446.5	448.1	449.6	449.6	452.8	454.4	457.6	460.8	462.5	464.1
50°	397.1	400.2	401.8	401.8	403.4	406.6	409.8	409.8	413.0	417.7	419.3
52.5°	354.0	354.0	357.2	358.8	360.4	360.4	365.2	366.8	368.3	371.5	374.7
55°	306.1	310.9	312.5	312.5	315.8	318.9	320.5	322.1	322.1	328.5	328.5
57.5°	264.7	266.3	269.4	269.4	269.4	274.2	274.2	277.5	279.1	280.7	283.9
60°	223.2	226.4	226.4	228.0	226.4	229.6	231.2	234.4	236.0	237.5	239.1
62.5°	185.0	185.0	186.6	186.6	186.6	186.6	189.7	189.7	192.9	194.5	196.1
65°	148.3	148.3	148.3	148.3	148.3	148.3	148.3	148.3	149.9	149.9	153.1
67.5°	114.8	113.2	110.0	111.6	110.0	110.0	108.4	108.4	110.0	110.0	113.2
70°	82.9	81.3	78.1	78.1	76.5	74.9	73.4	71.8	70.2	70.2	70.2
72.5°	54.2	51.0	46.2	44.6	44.6	41.4	38.3	36.7	36.7	36.7	36.7
75°	27.1	24.0	20.8	19.2	19.2	15.9	17.5	15.9	15.9	15.9	15.9
77.5°	11.1	8.0	6.4	6.4	6.4	4.8	4.8	4.8	4.8	4.8	4.8
80°	3.2	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
82.5°	1.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584208

CATALOG NUMBER: HCC8S25D010BZ-HM82555935-81RWWC

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3
2.5°	1187.9	1187.9	1184.7	1186.3	1186.3	1186.3	1186.3	1186.3
5°	1173.6	1175.2	1173.6	1175.2	1175.2	1173.6	1173.6	1173.6
7.5°	1159.2	1160.8	1159.2	1160.8	1160.8	1160.8	1159.2	1159.2
10°	1141.7	1141.7	1141.7	1141.7	1141.7	1140.1	1141.7	1141.7
12.5°	1117.8	1117.8	1117.8	1119.3	1119.3	1117.8	1117.8	1116.2
15°	1092.3	1089.0	1090.7	1092.3	1090.7	1090.7	1090.7	1090.7
17.5°	1057.2	1058.8	1057.2	1057.2	1057.2	1057.2	1058.8	1057.2
20°	1020.5	1020.5	1022.1	1020.5	1020.5	1020.5	1020.5	1019.0
22.5°	979.0	977.4	977.4	979.0	979.0	977.4	979.0	979.0
25°	932.8	934.4	932.8	932.8	934.4	934.4	934.4	932.8
27.5°	883.4	885.0	886.6	885.0	885.0	885.0	886.6	888.2
30°	832.4	835.6	832.4	832.4	835.6	834.0	835.6	835.6
32.5°	778.1	782.9	779.7	782.9	782.9	784.5	782.9	784.5
35°	724.0	728.7	728.7	728.7	730.3	731.9	731.9	730.3
37.5°	672.9	674.5	674.5	677.6	679.2	680.8	680.8	679.2
40°	620.3	623.5	625.1	625.1	625.1	628.3	631.4	628.3
42.5°	569.2	570.8	572.4	572.4	575.7	577.3	578.9	578.9
45°	519.8	523.0	524.6	526.2	527.8	530.9	529.4	532.5
47.5°	468.8	473.6	475.2	476.8	480.0	481.6	483.1	484.7
50°	422.5	425.8	425.8	429.0	433.7	433.7	436.9	438.5
52.5°	376.3	377.9	379.5	381.1	384.2	387.4	387.4	390.7
55°	331.7	333.3	333.3	334.8	336.4	342.8	344.4	344.4
57.5°	285.5	285.5	288.6	290.2	291.8	295.0	295.0	295.0
60°	240.8	242.4	242.4	244.0	245.6	248.8	250.4	248.8
62.5°	196.1	197.7	197.7	199.3	202.6	204.0	202.6	202.6
65°	154.7	156.2	156.2	157.8	161.0	161.0	159.4	161.0
67.5°	113.2	113.2	113.2	113.2	113.2	113.2	113.2	113.2
70°	71.8	70.2	68.6	70.2	70.2	70.2	68.6	71.8
72.5°	35.1	36.7	36.7	36.7	36.7	36.7	36.7	35.1
75°	15.9	15.9	14.3	14.3	14.3	15.9	15.9	14.3
77.5°	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8
80°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)