

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584209

Luminaire Tested: **HCC8S25D010SL-HM82555935-81RWWH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584209
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S25D010SL-HM82555935-81RWWH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2206.1 lumens
Efficiency: N/A
Efficacy: 82.3 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584209
CATALOG NUMBER: HCC8S25D010SL-HM82555935-81RWWH

Luminous Intensity Polar Plot





TEST NUMBER: P584209

CATALOG NUMBER: HCC8S25D010SL-HM82555935-81RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77								
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67								
4	88	77	70	64	86	76	69	63	74	67	63	71	66	62	69	65	61	59								
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47								
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	36	35								
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	36288	36288	36288
5°	36968	36133	35291
10°	37546	35502	34002
15°	37923	34615	32531
20°	37780	33278	31030
25°	36783	31360	29295
30°	35033	29069	27595
35°	31636	26532	25628
40°	27795	23814	23750
45°	23989	20932	21835
50°	20883	18359	19582
55°	18515	15946	17064
60°	16522	13475	14160
65°	14899	10937	11171
70°	13226	8186	6618
75°	11402	4754	2859
80°	8772	1687	852
85°	5626	566	566



TEST NUMBER: P584209
 CATALOG NUMBER: HCC8S25D010SL-HM82555935-81RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.5	5.0
10°-20°	307.5	13.9
20°-30°	435.0	19.7
30°-40°	458.3	20.8
40°-50°	389.5	17.7
50°-60°	280.5	12.7
60°-70°	161.8	7.3
70°-80°	55.4	2.5
80°-90°	7.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	853.0	38.7
0°-40°	1311.3	59.4
0°-60°	1981.3	89.8
0°-90°	2206.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2206.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1177	1177	1177	1177	1177	
5°	1194	1186	1167	1146	1140	114
15°	1188	1151	1084	1036	1019	334
25°	1081	1025	922	874	861	496
35°	840	791	705	679	681	523
45°	550	525	480	483	501	427
55°	344	317	297	308	317	310
65°	204	175	150	147	153	203
75°	96	72	40	26	24	101
85°	16	10	2	2	2	21
90°	0	0	0	0	0	



TEST NUMBER: P584209

CATALOG NUMBER: HCC8S25D010SL-HM82555935-81RWWH

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	1176.8	1176.8	1176.8	1176.8	1176.8	1176.8	1176.8	1176.8	1176.8	1176.8	1176.8
2.5°	1187.9	1189.5	1187.9	1187.9	1186.4	1184.8	1183.2	1181.6	1178.4	1175.2	1175.2
5°	1194.3	1197.5	1194.3	1194.3	1189.5	1186.4	1183.2	1178.4	1172.0	1167.3	1167.3
7.5°	1199.1	1199.1	1199.1	1194.3	1191.1	1186.4	1178.4	1170.5	1162.4	1154.4	1151.3
10°	1199.1	1199.1	1197.5	1191.1	1187.9	1178.4	1170.5	1159.2	1148.1	1137.0	1133.8
12.5°	1194.3	1195.9	1192.7	1186.4	1178.4	1167.3	1156.0	1141.7	1129.0	1116.2	1109.8
15°	1187.9	1186.4	1183.2	1175.2	1165.7	1151.3	1140.1	1124.1	1106.6	1090.7	1084.3
17.5°	1172.0	1172.0	1167.3	1159.2	1146.5	1130.6	1113.0	1095.5	1076.3	1058.8	1050.8
20°	1151.3	1151.3	1144.9	1135.4	1122.5	1101.9	1082.7	1062.0	1039.6	1022.2	1014.1
22.5°	1121.0	1122.5	1114.6	1103.5	1089.0	1065.2	1046.0	1020.6	998.2	977.4	971.1
25°	1081.1	1084.3	1076.3	1065.2	1046.0	1025.3	1001.4	977.4	952.0	931.2	921.7
27.5°	1034.9	1036.5	1028.5	1017.4	998.2	975.8	952.0	926.4	902.5	880.2	870.7
30°	983.9	977.4	974.2	959.9	939.2	920.1	892.9	872.3	846.7	827.5	816.4
32.5°	912.1	915.3	905.8	894.5	878.6	856.3	834.0	810.1	786.1	771.8	763.8
35°	840.4	843.5	838.8	827.5	810.1	790.9	768.6	751.0	730.3	712.7	704.8
37.5°	765.4	765.4	762.2	755.8	743.1	725.6	703.2	685.7	668.1	653.8	649.0
40°	690.5	687.3	685.7	680.8	669.7	653.8	639.4	625.1	607.5	597.9	591.6
42.5°	617.1	617.1	613.9	609.2	597.9	590.0	575.7	559.7	547.0	537.4	537.4
45°	550.1	551.7	547.0	543.8	537.4	524.6	511.9	500.7	489.5	483.1	480.0
47.5°	491.1	491.1	486.3	483.1	476.8	465.7	454.4	444.9	436.9	432.2	430.6
50°	435.3	435.3	435.3	427.4	419.3	411.4	403.4	392.3	387.4	384.3	382.7
52.5°	387.4	385.8	385.8	379.5	371.5	362.0	354.0	344.4	339.6	336.4	338.0
55°	344.4	344.4	342.8	334.9	326.9	317.4	309.3	301.4	298.2	295.0	296.6
56°	326.9	326.9	325.3	319.0	309.3	301.4	291.8	283.9	279.1	280.7	280.7
57°	314.2	310.9	310.9	302.9	295.0	283.9	275.8	267.9	264.7	263.1	263.1
58°	298.2	296.6	295.0	287.0	279.1	269.5	261.5	253.6	248.8	248.8	247.2
59°	282.3	282.3	279.1	272.6	264.7	255.1	247.2	239.1	234.4	232.8	232.8
60°	267.9	269.5	264.7	258.3	252.0	240.8	231.2	224.8	220.1	218.5	218.5
61°	255.1	255.1	252.0	244.0	236.0	228.0	218.5	210.5	207.3	204.2	204.2
62°	244.0	240.8	239.1	231.2	223.2	213.7	205.7	197.7	192.9	189.7	191.3
63°	229.6	228.0	224.8	218.5	210.5	200.9	191.3	185.0	180.2	175.4	177.0
64°	218.5	216.9	212.1	205.7	197.7	188.2	178.6	172.2	169.1	164.2	162.6
65°	204.2	202.6	200.9	192.9	185.0	175.4	167.5	161.0	156.2	153.1	149.9
66°	191.3	192.9	189.7	183.4	173.8	165.9	154.7	148.3	145.1	140.3	137.2
67°	180.2	180.2	177.0	170.7	161.0	153.1	145.1	137.2	132.4	127.5	125.9
67.5°	173.8	173.8	170.7	162.6	156.2	146.7	138.8	132.4	125.9	122.7	119.6
68°	167.5	167.5	165.9	159.4	151.5	141.9	134.0	125.9	119.6	114.8	113.2
69°	156.2	157.8	154.7	148.3	140.3	130.8	122.7	116.4	110.0	105.3	102.1
70°	146.7	145.1	141.9	135.6	127.5	121.2	113.2	105.3	98.9	92.4	90.8
71°	134.0	134.0	130.8	125.9	118.0	110.0	102.1	95.7	89.3	81.3	79.7
72°	124.3	124.3	121.2	114.8	108.4	100.5	92.4	84.5	79.7	71.8	68.6
72.5°	118.0	119.6	116.4	110.0	103.7	94.1	87.7	81.3	73.4	67.0	63.8
73°	114.8	113.2	111.6	105.3	97.3	90.8	82.9	76.5	68.6	62.2	59.0



TEST NUMBER: P584209
 CATALOG NUMBER: HCC8S25D010SL-HM82555935-81RWWH

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
77.5°	71.8	71.8	70.2	63.8	57.4	51.0	44.6	38.3	31.9	25.5	22.4
80°	49.4	51.0	47.8	44.6	39.9	33.5	27.1	22.4	15.9	12.7	9.5
82.5°	31.9	31.9	30.3	27.1	24.0	19.2	15.9	11.1	8.0	6.4	4.8
85°	15.9	17.5	15.9	14.3	11.1	9.5	8.0	4.8	3.2	1.6	1.6
87.5°	6.4	6.4	6.4	4.8	4.8	3.2	1.6	1.6	1.6	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584209

CATALOG NUMBER: HCC8S25D010SL-HM82555935-81RWWH

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	1176.8	1176.8	1176.8	1176.8	1176.8	1176.8	1176.8	1176.8	1176.8	1176.8
2.5°	1172.0	1172.0	1168.9	1167.3	1165.7	1164.1	1162.4	1160.8	1160.8	1162.4
5°	1162.4	1159.2	1152.9	1151.3	1146.5	1144.9	1141.7	1140.1	1141.7	1140.1
7.5°	1148.1	1141.7	1133.8	1130.6	1124.1	1121.0	1116.2	1116.2	1113.0	1114.6
10°	1129.0	1119.4	1109.8	1103.5	1098.7	1093.9	1090.7	1087.5	1085.9	1085.9
12.5°	1105.0	1093.9	1084.3	1074.7	1066.8	1063.6	1057.2	1057.2	1054.1	1052.5
15°	1077.9	1063.6	1052.5	1042.8	1036.5	1030.1	1025.3	1022.2	1019.0	1019.0
17.5°	1042.8	1030.1	1019.0	1007.7	998.2	993.4	988.7	983.9	983.9	980.7
20°	1004.6	990.3	980.7	969.5	961.5	953.6	947.2	947.2	944.0	945.6
22.5°	961.5	944.0	934.4	926.4	918.5	912.1	905.8	905.8	904.2	902.5
25°	913.7	899.3	888.2	878.6	873.9	867.4	865.8	862.6	861.0	861.0
27.5°	862.6	851.5	837.2	832.4	826.0	822.8	822.8	821.2	818.0	819.6
30°	808.5	795.7	787.7	784.5	778.1	778.1	776.6	773.4	773.4	775.0
32.5°	755.8	743.1	736.7	735.1	728.7	728.7	727.2	728.7	728.7	730.3
35°	698.4	687.3	685.7	680.8	679.3	679.3	679.3	682.4	685.7	680.8
37.5°	644.2	636.2	631.4	629.9	631.4	631.4	633.0	637.8	636.2	634.6
40°	588.4	582.0	578.9	578.9	582.0	585.2	585.2	590.0	591.6	590.0
42.5°	532.5	527.8	527.8	529.4	532.5	534.1	539.0	543.8	545.4	547.0
45°	480.0	480.0	480.0	481.6	483.1	486.3	492.7	497.6	499.2	500.7
47.5°	429.0	427.4	432.2	433.8	438.5	440.1	444.9	451.2	452.8	454.4
50°	381.1	384.3	385.8	390.7	393.9	393.9	400.3	403.4	408.2	408.2
52.5°	336.4	341.2	342.8	347.6	349.2	350.9	354.0	358.8	362.0	362.0
55°	296.6	298.2	301.4	302.9	307.7	309.3	312.5	314.2	319.0	317.4
56°	279.1	282.3	283.9	287.0	290.2	291.8	295.0	296.6	299.8	301.4
57°	263.1	264.7	269.5	271.0	274.2	274.2	275.8	280.7	280.7	282.3
58°	247.2	250.4	252.0	253.6	256.7	258.3	261.5	263.1	264.7	263.1
59°	232.8	234.4	236.0	236.0	239.1	239.1	244.0	247.2	248.8	248.8
60°	218.5	218.5	220.1	221.6	224.8	226.4	226.4	229.6	229.6	229.6
61°	204.2	204.2	205.7	207.3	208.9	208.9	212.1	212.1	213.7	215.3
62°	191.3	189.7	189.7	191.3	191.3	194.5	196.1	197.7	199.3	197.7
63°	177.0	175.4	175.4	175.4	175.4	178.6	178.6	180.2	183.4	181.8
64°	161.0	161.0	161.0	161.0	162.6	162.6	165.9	167.5	169.1	170.7
65°	149.9	146.7	145.1	145.1	146.7	148.3	149.9	151.5	153.1	153.1
66°	137.2	134.0	132.4	132.4	132.4	132.4	135.6	135.6	138.8	138.8
67°	122.7	119.6	118.0	116.4	116.4	116.4	121.2	119.6	119.6	119.6
67.5°	118.0	113.2	111.6	110.0	108.4	111.6	110.0	111.6	111.6	110.0
68°	111.6	108.4	105.3	102.1	102.1	102.1	103.7	105.3	103.7	102.1
69°	98.9	97.3	92.4	89.3	87.7	89.3	87.7	89.3	87.7	89.3
70°	87.7	82.9	78.1	76.5	74.9	74.9	74.9	73.4	74.9	73.4
71°	76.5	71.8	67.0	63.8	62.2	62.2	60.6	62.2	60.6	62.2
72°	65.4	60.6	54.2	51.0	51.0	51.0	51.0	49.4	51.0	49.4
72.5°	60.6	54.2	49.4	46.2	44.6	44.6	44.6	44.6	43.0	44.6
73°	55.9	49.4	43.0	41.4	41.4	41.4	39.9	38.3	39.9	39.9



TEST NUMBER: P584209

CATALOG NUMBER: HCC8S25D010SL-HM82555935-81RWWH

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
77.5°	19.2	14.3	12.7	12.7	12.7	12.7	12.7	12.7	11.1	11.1
80°	8.0	6.4	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8
82.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
85°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



74°	103.7	103.7	100.5	95.7	87.7	79.7	73.4	67.0	59.0	51.0	47.8
75°	95.7	94.1	90.8	86.1	79.7	71.8	65.4	57.4	51.0	43.0	39.9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



74°	46.2	38.3	35.1	31.9	31.9	31.9	30.3	30.3	30.3	31.9
75°	36.7	30.3	27.1	24.0	25.5	24.0	25.5	24.0	24.0	24.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)