

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584217

Luminaire Tested: **HCC8W25D010MB-HM82555935-81WWWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584217
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W25D010MB-HM82555935-81WWWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2257.1 lumens
Efficiency: N/A
Efficacy: 84.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584217
CATALOG NUMBER: HCC8W25D010MB-HM82555935-81WWWB

Luminous Intensity Polar Plot





TEST NUMBER: P584217

CATALOG NUMBER: HCC8W25D010MB-HM82555935-81WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75								
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65								
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57								
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50								
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45								
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40								
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37								
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33								
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	34605	34605	34605
5°	35873	34492	33307
10°	36889	34190	31945
15°	37712	33587	30535
20°	37767	32274	29294
25°	37042	30482	28257
30°	35137	28265	27018
35°	31926	25741	25801
40°	27916	23098	24317
45°	24194	20579	22664
50°	21185	18278	20652
55°	18854	16198	18682
60°	17003	14549	16417
65°	15359	12798	14301
70°	13794	10774	10630
75°	12153	8543	7983
80°	10193	7068	7636
85°	7925	6192	6793



TEST NUMBER: P584217
 CATALOG NUMBER: HCC8W25D010MB-HM82555935-81WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.9	4.7
10°-20°	298.2	13.2
20°-30°	426.2	18.9
30°-40°	452.8	20.1
40°-50°	389.9	17.3
50°-60°	291.5	12.9
60°-70°	185.9	8.2
70°-80°	84.6	3.7
80°-90°	22.2	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	830.2	36.8
0°-40°	1283.0	56.8
0°-60°	1964.4	87.0
0°-90°	2257.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2257.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1122	1122	1122	1122	1122	
5°	1159	1143	1114	1086	1076	111
15°	1181	1141	1052	980	956	333
25°	1089	1020	896	842	830	498
35°	848	789	684	666	685	528
45°	555	524	472	485	520	431
55°	351	322	301	327	348	315
65°	210	186	175	183	196	210
75°	102	88	72	65	67	108
85°	22	19	18	19	19	27
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584217

CATALOG NUMBER: HCC8W25D010MB-HM82555935-81WWWB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1122.2	1122.2	1122.2	1122.2	1122.2	1122.2	1122.2	1122.2	1122.2	1122.2	1122.2
2.5°	1143.0	1139.8	1141.4	1139.8	1141.4	1141.4	1138.2	1138.2	1138.2	1138.2	1133.5
5°	1158.9	1157.3	1157.3	1155.7	1154.1	1155.7	1154.1	1152.5	1149.4	1147.8	1143.0
7.5°	1168.4	1168.4	1168.4	1168.4	1166.8	1165.3	1163.7	1160.5	1157.3	1154.1	1150.9
10°	1178.1	1179.7	1178.1	1176.5	1174.9	1171.6	1170.0	1166.8	1162.1	1157.3	1154.1
12.5°	1182.8	1182.8	1181.3	1181.3	1178.1	1176.5	1171.6	1166.8	1162.1	1157.3	1149.4
15°	1181.3	1181.3	1179.7	1178.1	1173.3	1171.6	1168.4	1163.7	1155.7	1149.4	1141.4
17.5°	1171.6	1170.0	1166.8	1166.8	1160.5	1158.9	1155.7	1149.4	1141.4	1131.8	1122.2
20°	1150.9	1150.9	1149.4	1147.8	1141.4	1136.6	1133.5	1125.4	1119.1	1107.9	1098.4
22.5°	1122.2	1125.4	1122.2	1119.1	1111.1	1109.5	1104.7	1095.1	1085.6	1072.8	1061.7
25°	1088.7	1087.2	1085.6	1082.4	1076.0	1072.8	1066.5	1056.8	1047.3	1033.0	1020.2
27.5°	1045.7	1039.4	1039.4	1033.0	1028.2	1023.5	1020.2	1010.6	997.9	986.8	970.8
30°	986.8	988.4	980.3	978.7	970.8	967.6	961.3	951.7	940.5	927.8	915.1
32.5°	923.0	918.2	918.2	911.9	905.4	900.6	899.1	887.9	878.4	865.6	852.9
35°	848.1	848.1	843.3	841.7	835.3	832.1	827.3	821.0	809.8	798.6	789.1
37.5°	774.8	771.6	770.0	766.8	761.9	757.2	757.2	746.0	744.4	731.7	718.9
40°	693.5	696.7	693.5	688.7	687.0	683.8	682.2	675.9	671.1	660.0	652.0
42.5°	624.9	621.7	621.7	620.1	613.8	613.8	610.5	607.3	599.4	596.2	586.7
45°	554.8	557.9	553.2	554.8	548.4	548.4	548.4	542.0	535.6	530.8	524.5
47.5°	494.1	495.7	495.7	491.0	489.4	489.4	486.2	483.0	478.2	471.9	467.1
50°	441.6	443.2	440.0	438.4	435.2	433.6	433.6	427.3	424.0	417.6	414.5
52.5°	393.8	393.8	392.2	392.2	387.3	387.3	384.1	379.4	376.2	373.0	365.1
55°	350.7	350.7	349.1	347.5	347.5	342.7	341.1	336.4	333.2	326.8	322.0
57.5°	309.2	310.8	309.2	307.6	306.0	304.5	301.3	296.5	293.3	288.6	285.4
60°	275.7	275.7	274.1	272.6	269.4	267.8	266.2	263.0	258.3	255.1	250.3
62.5°	243.9	242.4	240.8	239.1	235.9	235.9	232.7	229.5	224.8	221.6	218.4
65°	210.5	210.5	208.9	208.9	207.3	204.0	202.4	200.8	194.5	192.9	186.5
67.5°	180.1	181.7	178.6	178.6	175.4	175.4	173.8	169.0	167.3	164.2	161.0
70°	153.0	153.0	153.0	151.4	148.3	146.7	145.1	141.9	140.3	137.1	133.9
72.5°	125.9	125.9	124.3	124.3	122.7	121.1	119.5	116.4	116.4	113.2	110.0
75°	102.0	102.0	100.5	98.9	97.3	97.3	95.7	94.1	90.8	89.2	87.6
77.5°	78.1	78.1	78.1	76.5	74.9	74.9	74.9	71.7	68.6	68.6	67.0
80°	57.4	57.4	55.7	55.7	54.2	54.2	54.2	52.6	51.0	49.4	47.8
82.5°	38.3	38.3	38.3	38.3	36.7	36.7	36.7	35.1	33.5	33.5	33.5
85°	22.4	22.4	22.4	22.4	20.8	20.8	20.8	20.8	20.8	19.2	19.2
87.5°	9.5	7.9	9.5	7.9	9.5	7.9	9.5	7.9	7.9	7.9	7.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584217

CATALOG NUMBER: HCC8W25D010MB-HM82555935-81WWWB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1122.2	1122.2	1122.2	1122.2	1122.2	1122.2	1122.2	1122.2	1122.2	1122.2	1122.2
2.5°	1135.1	1133.5	1131.8	1130.2	1130.2	1128.6	1125.4	1123.8	1122.2	1120.6	1120.6
5°	1141.4	1139.8	1136.6	1133.5	1131.8	1128.6	1125.4	1122.2	1119.1	1114.3	1112.7
7.5°	1146.2	1141.4	1138.2	1131.8	1130.2	1127.0	1122.2	1117.5	1111.1	1104.7	1100.0
10°	1146.2	1139.8	1135.1	1127.0	1123.8	1120.6	1114.3	1106.3	1098.4	1091.9	1084.0
12.5°	1143.0	1135.1	1127.0	1119.1	1114.3	1109.5	1100.0	1091.9	1082.4	1072.8	1066.5
15°	1131.8	1122.2	1112.7	1103.2	1098.4	1091.9	1082.4	1071.3	1061.7	1052.1	1041.0
17.5°	1111.1	1101.6	1090.3	1079.2	1072.8	1068.1	1053.7	1045.7	1031.4	1021.8	1012.2
20°	1084.0	1072.8	1058.4	1047.3	1039.4	1034.6	1023.5	1009.1	997.9	983.5	974.0
22.5°	1048.9	1034.6	1020.2	1009.1	1001.1	994.7	980.3	966.0	956.5	943.7	932.5
25°	1007.5	993.2	978.7	962.9	954.9	948.4	935.7	923.0	910.2	895.9	886.3
27.5°	958.1	942.1	929.4	915.1	907.0	897.5	883.2	870.3	857.6	848.1	835.3
30°	903.8	886.3	873.5	859.2	851.3	843.3	828.9	816.2	805.1	793.8	787.5
32.5°	838.5	825.7	813.0	798.6	792.2	787.5	773.2	760.3	747.6	738.1	733.3
35°	776.3	761.9	750.8	738.1	730.1	725.4	712.5	701.4	695.1	683.8	677.5
37.5°	711.0	699.8	687.0	674.3	669.5	664.8	655.2	644.0	634.4	626.5	623.3
40°	642.4	632.9	621.7	613.8	608.9	604.1	596.2	588.2	581.9	573.8	570.7
42.5°	577.1	570.7	561.1	551.6	546.8	545.2	535.6	529.2	526.0	522.9	519.7
45°	518.1	508.6	502.2	495.7	491.0	487.8	483.0	478.2	475.1	471.9	468.7
47.5°	460.7	452.7	446.3	441.6	436.8	435.2	432.0	427.3	424.0	424.0	424.0
50°	408.1	401.7	395.4	392.2	390.6	387.3	384.1	382.6	381.0	381.0	381.0
52.5°	361.9	355.5	350.7	347.5	347.5	344.3	341.1	339.5	339.5	339.5	339.5
55°	318.9	314.0	310.8	307.6	304.5	302.9	302.9	302.9	301.3	301.3	302.9
57.5°	280.6	277.3	272.6	269.4	267.8	267.8	266.2	264.6	266.2	267.8	269.4
60°	245.5	242.4	240.8	235.9	235.9	235.9	234.3	234.3	234.3	235.9	237.5
62.5°	213.6	212.0	208.9	207.3	205.7	205.7	204.0	204.0	204.0	204.0	205.7
65°	184.9	181.7	178.6	178.6	178.6	177.0	177.0	173.8	175.4	175.4	173.8
67.5°	157.8	154.6	153.0	151.4	149.8	149.8	148.3	146.7	145.1	145.1	145.1
70°	132.4	129.1	129.1	125.9	125.9	124.3	122.7	122.7	121.1	119.5	117.9
72.5°	106.8	105.2	103.6	102.0	102.0	102.0	100.5	98.9	97.3	95.7	92.4
75°	84.5	84.5	81.3	79.7	79.7	78.1	76.5	74.9	73.3	71.7	70.2
77.5°	65.4	63.8	60.6	59.0	59.0	59.0	57.4	55.7	54.2	52.6	51.0
80°	47.8	46.2	44.6	43.0	43.0	43.0	41.4	41.4	39.8	39.8	39.8
82.5°	31.9	31.9	30.3	30.3	30.3	30.3	28.7	28.7	28.7	28.7	28.7
85°	19.2	19.2	17.5	17.5	17.5	17.5	17.5	17.5	17.5	17.5	17.5
87.5°	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584217

CATALOG NUMBER: HCC8W25D010MB-HM82555935-81WWWB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1122.2	1122.2	1122.2	1122.2	1122.2	1122.2	1122.2	1122.2	1122.2	1122.2	1122.2
2.5°	1117.5	1117.5	1114.3	1112.7	1111.1	1112.7	1109.5	1107.9	1106.3	1106.3	1104.7
5°	1107.9	1106.3	1100.0	1098.4	1096.8	1095.1	1091.9	1088.7	1085.6	1084.0	1082.4
7.5°	1095.1	1090.3	1084.0	1082.4	1080.8	1076.0	1071.3	1068.1	1063.3	1061.7	1058.4
10°	1077.6	1071.3	1066.5	1061.7	1058.4	1053.7	1048.9	1044.1	1037.8	1036.2	1031.4
12.5°	1056.8	1048.9	1039.4	1037.8	1033.0	1026.6	1020.2	1015.4	1010.6	1007.5	1002.7
15°	1031.4	1023.5	1013.8	1009.1	1004.3	999.5	991.6	985.1	980.3	975.6	970.8
17.5°	1001.1	991.6	983.5	978.7	975.6	967.6	961.3	953.3	948.4	943.7	938.9
20°	964.4	956.5	945.3	940.5	938.9	932.5	924.6	921.4	915.1	910.2	907.0
22.5°	923.0	915.1	905.4	902.2	895.9	892.7	884.7	881.6	878.4	873.5	871.9
25°	876.8	868.8	860.8	859.2	854.4	851.3	846.5	841.7	841.7	837.0	837.0
27.5°	828.9	821.0	814.6	811.4	809.8	806.6	801.9	800.3	798.6	797.0	797.0
30°	777.9	768.4	765.2	763.6	761.9	758.8	757.2	754.0	755.6	757.2	755.6
32.5°	723.7	720.5	714.1	711.0	712.5	711.0	707.8	711.0	709.4	712.5	714.1
35°	671.1	667.9	664.8	664.8	661.6	661.6	661.6	663.2	666.3	667.9	671.1
37.5°	620.1	615.4	613.8	612.1	613.8	613.8	613.8	617.0	620.1	623.3	628.1
40°	565.9	562.7	562.7	562.7	562.7	567.5	565.9	569.1	572.2	577.1	581.9
42.5°	514.9	514.9	516.5	516.5	516.5	516.5	519.7	524.5	529.2	534.0	538.9
45°	467.1	467.1	467.1	470.3	470.3	471.9	478.2	481.4	484.6	489.4	494.1
47.5°	422.4	422.4	424.0	425.6	427.3	430.5	433.6	438.4	443.2	446.3	451.1
50°	381.0	382.6	385.7	388.9	388.9	390.6	395.4	398.6	401.7	406.5	408.1
52.5°	341.1	344.3	347.5	349.1	350.7	353.8	355.5	360.3	361.9	366.7	368.2
55°	304.5	306.0	310.8	312.4	312.4	315.7	318.9	322.0	326.8	326.8	330.0
57.5°	271.0	272.6	275.7	277.3	275.7	280.6	282.2	285.4	287.0	290.1	291.7
60°	237.5	240.8	242.4	242.4	243.9	245.5	248.7	248.7	251.9	255.1	255.1
62.5°	205.7	207.3	208.9	210.5	212.0	210.5	215.2	215.2	218.4	220.0	223.2
65°	175.4	177.0	177.0	178.6	178.6	180.1	180.1	181.7	183.3	186.5	188.1
67.5°	145.1	145.1	145.1	146.7	145.1	146.7	146.7	148.3	148.3	151.4	153.0
70°	117.9	116.4	114.8	114.8	114.8	114.8	113.2	114.8	114.8	116.4	116.4
72.5°	90.8	89.2	87.6	86.1	86.1	84.5	82.9	84.5	84.5	86.1	86.1
75°	68.6	65.4	65.4	65.4	63.8	63.8	63.8	65.4	65.4	65.4	67.0
77.5°	51.0	51.0	49.4	49.4	49.4	51.0	51.0	52.6	52.6	52.6	52.6
80°	38.3	39.8	39.8	39.8	39.8	41.4	41.4	41.4	41.4	43.0	43.0
82.5°	28.7	28.7	28.7	28.7	30.3	30.3	30.3	30.3	30.3	30.3	30.3
85°	17.5	19.2	19.2	17.5	19.2	19.2	19.2	19.2	19.2	19.2	19.2
87.5°	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584217

CATALOG NUMBER: HCC8W25D010MB-HM82555935-81WWWB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1122.2	1122.2	1122.2	1122.2	1122.2	1122.2	1122.2	1122.2
2.5°	1103.2	1103.2	1103.2	1103.2	1101.6	1101.6	1101.6	1100.0
5°	1079.2	1079.2	1079.2	1076.0	1077.6	1077.6	1074.4	1076.0
7.5°	1055.3	1053.7	1052.1	1052.1	1050.5	1048.9	1047.3	1048.9
10°	1028.2	1023.5	1023.5	1021.8	1021.8	1018.6	1018.6	1020.2
12.5°	997.9	994.7	994.7	993.2	991.6	990.0	988.4	988.4
15°	967.6	964.4	962.9	961.3	959.7	956.5	958.1	956.5
17.5°	937.3	932.5	932.5	931.0	929.4	926.2	926.2	924.6
20°	902.2	900.6	897.5	899.1	897.5	894.3	892.7	892.7
22.5°	867.2	867.2	865.6	865.6	864.0	862.4	860.8	860.8
25°	833.7	832.1	833.7	833.7	828.9	828.9	828.9	830.5
27.5°	795.4	797.0	795.4	795.4	795.4	795.4	797.0	795.4
30°	757.2	757.2	757.2	758.8	761.9	760.3	760.3	758.8
32.5°	715.7	717.3	717.3	718.9	720.5	723.7	723.7	725.4
35°	674.3	677.5	679.1	677.5	682.2	682.2	685.4	685.4
37.5°	631.3	632.9	636.0	637.6	640.8	642.4	644.0	644.0
40°	585.1	591.4	593.0	594.6	599.4	599.4	601.0	604.1
42.5°	542.0	548.4	550.0	551.6	554.8	559.5	557.9	561.1
45°	500.5	505.4	507.0	508.6	513.3	514.9	514.9	519.7
47.5°	455.9	459.1	460.7	463.8	467.1	470.3	473.5	471.9
50°	411.3	416.0	419.2	420.8	425.6	427.3	428.9	430.5
52.5°	371.4	374.6	376.2	377.8	382.6	384.1	385.7	388.9
55°	333.2	334.8	337.9	336.4	341.1	342.7	344.3	347.5
57.5°	294.9	296.5	298.1	298.1	301.3	304.5	306.0	307.6
60°	258.3	261.4	263.0	263.0	263.0	266.2	266.2	266.2
62.5°	224.8	224.8	226.4	226.4	229.5	229.5	229.5	229.5
65°	189.7	191.3	192.9	192.9	196.0	194.5	197.6	196.0
67.5°	153.0	153.0	156.2	156.2	154.6	156.2	156.2	156.2
70°	116.4	116.4	117.9	117.9	117.9	117.9	117.9	117.9
72.5°	86.1	86.1	86.1	87.6	86.1	86.1	87.6	86.1
75°	67.0	67.0	67.0	67.0	67.0	67.0	67.0	67.0
77.5°	52.6	52.6	54.2	54.2	54.2	54.2	54.2	54.2
80°	43.0	43.0	43.0	43.0	44.6	43.0	43.0	43.0
82.5°	31.9	30.3	31.9	30.3	31.9	31.9	31.9	31.9
85°	19.2	19.2	19.2	19.2	19.2	19.2	19.2	19.2
87.5°	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)